

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434546

Luminaire Tested: **LAMR4B408R709027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R709027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3006.6 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434546

CATALOG NUMBER: LAMR4B408R709027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434546

CATALOG NUMBER: LAMR4B408R709027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1090369
5°	1070068
10°	1082441
15°	1113050
20°	1114982
25°	1011520
30°	903838
35°	793838
40°	584486
45°	327382
50°	161111
55°	90233
60°	54864
65°	36074
70°	26687
75°	23447
80°	17616
85°	17549



TEST NUMBER: P434546

CATALOG NUMBER: LAMR4B408R709027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.5	6.9
10°-20°	614.0	20.4
20°-30°	852.1	28.3
30°-40°	801.7	26.7
40°-50°	382.7	12.7
50°-60°	101.2	3.4
60°-70°	31.9	1.1
70°-80°	13.0	0.4
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1672.7	55.6
0°-40°	2474.4	82.3
0°-60°	2958.3	98.4
0°-90°	3006.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3006.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2210	
5°	2161	207
15°	2179	614
25°	1858	852
35°	1318	802
45°	469	383
55°	105	101
65°	31	32
75°	12	13
85°	3	3
90°	0	



TEST NUMBER: P434546

CATALOG NUMBER: LAMR4B408R709027DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2210.0
2.5°	2182.2
5°	2160.6
7.5°	2157.5
10°	2160.6
12.5°	2166.8
15°	2179.1
17.5°	2179.1
20°	2123.6
22.5°	2006.3
25°	1858.1
27.5°	1710.0
30°	1586.5
32.5°	1466.1
35°	1318.0
37.5°	1126.6
40°	907.5
42.5°	676.0
45°	469.2
47.5°	311.7
50°	209.9
52.5°	145.1
55°	104.9
57.5°	74.1
60°	55.6
62.5°	40.1
65°	30.9
67.5°	21.6
70°	18.5
72.5°	15.4
75°	12.3
77.5°	9.3
80°	6.2
82.5°	6.2
85°	3.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)