

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434429

Luminaire Tested: **LAMR4B408R459030DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R459030DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3186.5 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434429

CATALOG NUMBER: LAMR4B408R459030DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434429

CATALOG NUMBER: LAMR4B408R459030DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	94	91	103	98	93	90	95	92	89		93	90	87		90
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	79	76	91	84	79	75	82	78	75		81	77	74		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2944538
5°	2943553
10°	2797883
15°	2457689
20°	1880128
25°	1097587
30°	449213
35°	189967
40°	103565
45°	66914
50°	52194
55°	45246
60°	36609
65°	28836
70°	26831
75°	23638
80°	26424
85°	17549



TEST NUMBER: P434429

CATALOG NUMBER: LAMR4B408R459030DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	556.2	17.5
10°-20°	1309.9	41.1
20°-30°	923.0	29.0
30°-40°	227.2	7.1
40°-50°	79.3	2.5
50°-60°	46.9	1.5
60°-70°	26.0	0.8
70°-80°	14.3	0.4
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2789.1	87.5
0°-40°	3016.2	94.7
0°-60°	3142.4	98.6
0°-90°	3186.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3186.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5968	
5°	5943	556
15°	4812	1310
25°	2016	923
35°	315	227
45°	96	79
55°	53	47
65°	25	26
75°	12	14
85°	3	4
90°	0	



TEST NUMBER: P434429

CATALOG NUMBER: LAMR4B408R459030DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5968.1
2.5°	5952.6
5°	5943.4
7.5°	5835.1
10°	5584.7
12.5°	5244.5
15°	4811.6
17.5°	4251.9
20°	3580.9
22.5°	2810.9
25°	2016.2
27.5°	1301.9
30°	788.5
32.5°	479.3
35°	315.4
37.5°	222.6
40°	160.8
42.5°	123.7
45°	95.9
47.5°	80.4
50°	68.0
52.5°	58.8
55°	52.6
57.5°	46.4
60°	37.1
62.5°	30.9
65°	24.7
67.5°	21.6
70°	18.6
72.5°	15.5
75°	12.4
77.5°	12.4
80°	9.3
82.5°	6.2
85°	3.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)