

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434407

Luminaire Tested: **LAMR4B408R409035DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R409035DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3582.7 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434407

CATALOG NUMBER: LAMR4B408R409035DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434407

CATALOG NUMBER: LAMR4B408R409035DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	75	73	79	75	73	78	75	72	71		
10	85	78	73	71	84	77	73	70	77	73	70	76	73	70	75	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1350646
5°	1357519
10°	1347892
15°	1216010
20°	767191
25°	276308
30°	57891
35°	17622
40°	3512
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434407

CATALOG NUMBER: LAMR4B408R409035DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	796.0	22.2
10°-20°	1903.4	53.1
20°-30°	811.6	22.7
30°-40°	69.6	1.9
40°-50°	2.1	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3511.0	98.0
0°-40°	3580.6	99.9
0°-60°	3582.7	100.0
0°-90°	3582.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3582.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8384	
5°	8394	796
15°	7291	1903
25°	1554	812
35°	90	70
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434407

CATALOG NUMBER: LAMR4B408R409035DE01021MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8383.7
2.5°	8376.1
5°	8394.3
7.5°	8344.2
10°	8239.5
12.5°	7926.8
15°	7290.8
17.5°	6049.1
20°	4474.9
22.5°	2946.4
25°	1554.4
27.5°	630.0
30°	311.2
32.5°	165.5
35°	89.6
37.5°	45.5
40°	16.7
42.5°	3.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)