

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434504

Luminaire Tested: **LAMR4B408R609035DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R609035DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3148.3 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434504

CATALOG NUMBER: LAMR4B408R609035DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434504

CATALOG NUMBER: LAMR4B408R609035DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	96	91	88		93	89	86			91	87	85			88
4	98	91	85	81	96	90	85	81		88	83	80			86	82	79			84
5	93	85	80	75	92	84	79	75		83	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	70	66	83	75	69	65		74	69	65			72	68	65			71
8	80	71	65	61	79	71	65	61		70	65	61			69	64	61			68
9	77	67	62	58	76	67	61	58		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	58	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1785195
5°	1725352
10°	1709280
15°	1666893
20°	1538273
25°	1377564
30°	1065976
35°	638564
40°	245387
45°	89660
50°	3531
55°	2667
60°	3059
65°	1751
70°	2164
75°	2859
80°	4262
85°	0



TEST NUMBER: P434504

CATALOG NUMBER: LAMR4B408R609035DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.8	10.5
10°-20°	907.8	28.8
20°-30°	1132.5	36.0
30°-40°	659.8	21.0
40°-50°	110.1	3.5
50°-60°	2.9	0.1
60°-70°	2.1	0.1
70°-80°	1.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2371.2	75.3
0°-40°	3031.0	96.3
0°-60°	3144.1	99.9
0°-90°	3148.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3148.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3618	
5°	3484	331
15°	3263	908
25°	2530	1133
35°	1060	660
45°	128	110
55°	3	3
65°	2	2
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P434504

CATALOG NUMBER: LAMR4B408R609035DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3618.3
2.5°	3558.6
5°	3483.7
7.5°	3440.8
10°	3411.8
12.5°	3364.3
15°	3263.4
17.5°	3111.9
20°	2929.8
22.5°	2744.7
25°	2530.5
27.5°	2233.7
30°	1871.1
32.5°	1465.7
35°	1060.2
37.5°	668.6
40°	381.0
42.5°	223.4
45°	128.5
47.5°	44.4
50°	4.6
52.5°	3.1
55°	3.1
57.5°	3.1
60°	3.1
62.5°	3.1
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)