

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434360

Luminaire Tested: **LAMR4B408R309035DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R309035DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3372.9 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434360

CATALOG NUMBER: LAMR4B408R309035DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434360

CATALOG NUMBER: LAMR4B408R309035DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	111	109	107		107	105	104		103	102	101		100	99	98
2	111	107	104	102		109	106	103	100		102	100	98		100	98	96		97	95	94
3	107	103	99	96		105	101	98	95		99	96	94		96	94	92		94	92	91
4	104	98	94	91		102	97	94	91		95	92	90		93	91	89		92	90	88
5	101	95	91	87		99	94	90	87		92	89	86		91	88	86		89	87	85
6	98	91	87	84		97	91	87	84		89	86	83		88	85	83		87	84	82
7	95	88	84	81		94	88	84	81		87	83	81		86	83	80		85	82	80
8	92	86	81	79		91	85	81	78		84	81	78		83	80	78		83	80	78
9	90	83	79	76		89	83	79	76		82	78	76		81	78	76		80	78	75
10	88	81	77	74		87	80	77	74		80	76	74		79	76	74		78	76	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6111098
5°	5977591
10°	5182899
15°	3212372
20°	1177358
25°	393590
30°	193187
35°	96309
40°	59769
45°	37957
50°	27018
55°	22021
60°	18946
65°	14943
70°	18465
75°	18300
80°	18184
85°	18115



TEST NUMBER: P434360

CATALOG NUMBER: LAMR4B408R309035DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1100.0	32.6
10°-20°	1660.7	49.2
20°-30°	404.9	12.0
30°-40°	110.9	3.3
40°-50°	44.6	1.3
50°-60°	23.9	0.7
60°-70°	14.3	0.4
70°-80°	11.0	0.3
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3165.6	93.9
0°-40°	3276.5	97.1
0°-60°	3345.0	99.2
0°-90°	3372.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3372.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12386	
5°	12070	###
15°	6289	1661
25°	723	405
35°	160	111
45°	54	45
55°	26	24
65°	13	14
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P434360

CATALOG NUMBER: LAMR4B408R309035DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	12386.2
2.5°	12303.0
5°	12069.5
7.5°	11512.9
10°	10345.3
12.5°	8515.5
15°	6289.1
17.5°	4053.0
20°	2242.4
22.5°	1196.4
25°	723.0
27.5°	489.4
30°	339.1
32.5°	230.3
35°	159.9
37.5°	118.4
40°	92.8
42.5°	70.4
45°	54.4
47.5°	44.8
50°	35.2
52.5°	32.0
55°	25.6
57.5°	22.4
60°	19.2
62.5°	16.0
65°	12.8
67.5°	12.8
70°	12.8
72.5°	12.8
75°	9.6
77.5°	9.6
80°	6.4
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)