

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433259

Luminaire Tested: **LAM4B408R609040DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B408R609040DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3347.9 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433259

CATALOG NUMBER: LAM4B408R609040DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433259

CATALOG NUMBER: LAM4B408R609040DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	96	91	88		93	89	86			91	87	85			88
4	98	91	85	81	96	90	85	81		88	83	80			86	82	79			84
5	93	85	80	75	92	84	79	75		83	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	70	66	83	75	69	65		74	69	65			72	68	65			71
8	80	71	65	61	79	71	65	61		70	65	61			69	64	61			68
9	77	67	62	58	76	67	61	58		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	58	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1898376
5°	1834706
10°	1817594
15°	1772523
20°	1635773
25°	1464883
30°	1133543
35°	679099
40°	260909
45°	95382
50°	3761
55°	2839
60°	3256
65°	1868
70°	2308
75°	3050
80°	4546
85°	0



TEST NUMBER: P433259

CATALOG NUMBER: LAM4B408R609040DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.8	10.5
10°-20°	965.4	28.8
20°-30°	1204.3	36.0
30°-40°	701.6	21.0
40°-50°	117.1	3.5
50°-60°	3.1	0.1
60°-70°	2.2	0.1
70°-80°	1.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2521.5	75.3
0°-40°	3223.1	96.3
0°-60°	3343.4	99.9
0°-90°	3347.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3347.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3848	
5°	3704	352
15°	3470	965
25°	2691	1204
35°	1128	702
45°	137	117
55°	3	3
65°	2	2
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P433259

CATALOG NUMBER: LAM4B408R609040DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3847.7
2.5°	3784.2
5°	3704.5
7.5°	3658.9
10°	3628.0
12.5°	3577.6
15°	3470.2
17.5°	3309.1
20°	3115.5
22.5°	2918.7
25°	2690.9
27.5°	2375.3
30°	1989.7
32.5°	1558.6
35°	1127.5
37.5°	711.0
40°	405.1
42.5°	237.5
45°	136.7
47.5°	47.2
50°	4.9
52.5°	3.3
55°	3.3
57.5°	3.3
60°	3.3
62.5°	3.3
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)