

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434291

Luminaire Tested: **LAMR4B408R159040DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-6)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R159040DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 15 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3527.8 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434291

CATALOG NUMBER: LAMR4B408R159040DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434291

CATALOG NUMBER: LAMR4B408R159040DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	102		102	101	100		100
3	110	106	103	101	108	105	102	100	103	100	98		100	99	97		98
4	108	103	100	97	106	102	99	97	100	98	96		98	96	95		97
5	105	101	97	95	104	100	97	94	98	96	94		97	95	93		95
6	103	98	95	92	102	98	94	92	96	94	92		95	93	91		94
7	101	96	93	90	100	96	92	90	95	92	90		94	91	89		93
8	99	94	91	89	99	94	91	89	93	90	88		92	90	88		91
9	98	92	89	87	97	92	89	87	91	89	87		91	88	87		90
10	96	91	88	86	95	91	88	86	90	87	85		89	87	85		89

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5046303
5°	4258891
10°	1956607
15°	610107
20°	248610
25°	81556
30°	25281
35°	5349
40°	1346
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434291

CATALOG NUMBER: LAMR4B408R159040DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2032.2	57.6
10°-20°	1211.1	34.3
20°-30°	256.6	7.3
30°-40°	27.0	0.8
40°-50°	0.9	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3499.9	99.2
0°-40°	3526.9	100.0
0°-60°	3527.8	100.0
0°-90°	3527.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3527.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31323	
5°	26335	###
15°	3658	1211
25°	459	257
35°	27	27
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434291

CATALOG NUMBER: LAMR4B408R159040DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	31323.3
2.5°	30333.7
5°	26335.1
7.5°	19495.5
10°	11960.5
12.5°	6382.3
15°	3658.0
17.5°	2297.4
20°	1450.1
22.5°	855.3
25°	458.8
27.5°	259.0
30°	135.9
32.5°	68.7
35°	27.2
37.5°	14.4
40°	6.4
42.5°	1.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)