

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433310

Luminaire Tested: **LAM4B408R709050DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B408R709050DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3612.5 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433310

CATALOG NUMBER: LAM4B408R709050DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433310

CATALOG NUMBER: LAM4B408R709050DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	92		104	99	95	91		96	92	89		93	90	87		90	88	86
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	85	79	74		92	84	78	74		82	77	73		80	76	72		78	74	71
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	64	60
7	78	68	61	56		77	67	61	56		66	60	56		65	59	56		63	59	55
8	74	63	57	52		73	63	56	52		62	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	51	48		56	51	47
10	66	55	49	45		65	55	49	44		54	48	44		53	48	44		52	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1310120
5°	1285706
10°	1300572
15°	1337386
20°	1339649
25°	1215392
30°	1085973
35°	953811
40°	702220
45°	393318
50°	193579
55°	108469
60°	65916
65°	43312
70°	32169
75°	28213
80°	21025
85°	20945



TEST NUMBER: P433310

CATALOG NUMBER: LAM4B408R709050DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.2	6.9
10°-20°	737.8	20.4
20°-30°	1023.9	28.3
30°-40°	963.3	26.7
40°-50°	459.8	12.7
50°-60°	121.6	3.4
60°-70°	38.4	1.1
70°-80°	15.6	0.4
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2009.8	55.6
0°-40°	2973.1	82.3
0°-60°	3554.5	98.4
0°-90°	3612.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3612.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2655	
5°	2596	248
15°	2618	738
25°	2233	1024
35°	1584	963
45°	564	460
55°	126	122
65°	37	38
75°	15	16
85°	4	4
90°	0	



TEST NUMBER: P433310

CATALOG NUMBER: LAM4B408R709050DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2655.4
2.5°	2622.0
5°	2596.0
7.5°	2592.3
10°	2596.0
12.5°	2603.4
15°	2618.3
17.5°	2618.3
20°	2551.5
22.5°	2410.6
25°	2232.6
27.5°	2054.6
30°	1906.2
32.5°	1761.6
35°	1583.6
37.5°	1353.6
40°	1090.3
42.5°	812.2
45°	563.7
47.5°	374.6
50°	252.2
52.5°	174.3
55°	126.1
57.5°	89.0
60°	66.8
62.5°	48.2
65°	37.1
67.5°	26.0
70°	22.3
72.5°	18.5
75°	14.8
77.5°	11.1
80°	7.4
82.5°	7.4
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)