

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434410

Luminaire Tested: **LAMR4B408R409040DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R409040DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3809.8 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434410

CATALOG NUMBER: LAMR4B408R409040DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434410

CATALOG NUMBER: LAMR4B408R409040DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91	89	87	86
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88	86	84	82
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85	83	80	79
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83	80	78	77
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	79	75	73		79	75	73		78	75	72	71
10	85	78	73	71	84	77	73	70	77	73	70		76	73	70		75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1436257
5°	1443570
10°	1433335
15°	1293082
20°	815829
25°	293817
30°	61556
35°	18723
40°	3743
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434410

CATALOG NUMBER: LAMR4B408R409040DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	846.5	22.2
10°-20°	2024.0	53.1
20°-30°	863.0	22.7
30°-40°	74.0	1.9
40°-50°	2.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3733.6	98.0
0°-40°	3807.6	99.9
0°-60°	3809.8	100.0
0°-90°	3809.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3809.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8915	
5°	8926	846
15°	7753	2024
25°	1653	863
35°	95	74
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434410

CATALOG NUMBER: LAMR4B408R409040DE01021MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8915.1
2.5°	8907.0
5°	8926.4
7.5°	8873.1
10°	8761.8
12.5°	8429.2
15°	7752.9
17.5°	6432.5
20°	4758.6
22.5°	3133.1
25°	1652.9
27.5°	669.9
30°	330.9
32.5°	175.9
35°	95.2
37.5°	48.4
40°	17.8
42.5°	3.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)