

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434484

Luminaire Tested: **LAMR4B408R559040DE01021MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P434484  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B408R559040DE01021MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3555.2 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 41.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P434484

CATALOG NUMBER: LAMR4B408R559040DE01021MW

### Luminous Intensity Polar Plot





TEST NUMBER: P434484

CATALOG NUMBER: LAMR4B408R559040DE01021MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 |  | 105 | 104 | 102 |  |  | 102 | 101 | 99  |  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  |  | 97  | 95  | 93  |  |  | 94  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  |  | 93  | 90  | 88  |  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 92  | 88  | 85  |  | 90  | 87  | 84  |  |  | 88  | 85  | 83  |  |  | 87  |
| 5   | 96  | 89  | 83  | 80  | 94  | 88  | 83  | 79  |  | 86  | 82  | 79  |  |  | 84  | 81  | 78  |  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 78  | 75  |  | 82  | 78  | 74  |  |  | 81  | 77  | 74  |  |  | 79  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  |  | 78  | 74  | 70  |  |  | 77  | 73  | 70  |  |  | 76  |
| 8   | 84  | 76  | 71  | 67  | 83  | 75  | 70  | 67  |  | 74  | 70  | 67  |  |  | 73  | 69  | 66  |  |  | 72  |
| 9   | 81  | 72  | 67  | 64  | 80  | 72  | 67  | 63  |  | 71  | 66  | 63  |  |  | 70  | 66  | 63  |  |  | 69  |
| 10  | 78  | 69  | 64  | 60  | 77  | 69  | 64  | 60  |  | 68  | 63  | 60  |  |  | 67  | 63  | 60  |  |  | 66  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2392743 |
| 5°  | 2426250 |
| 10° | 2483010 |
| 15° | 2379232 |
| 20° | 2161657 |
| 25° | 1737184 |
| 30° | 1000004 |
| 35° | 290251  |
| 40° | 44311   |
| 45° | 0       |
| 50° | 0       |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P434484

CATALOG NUMBER: LAMR4B408R559040DE01021MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 469.8  | 13.2      |
| 10°-20°   | 1296.0 | 36.5      |
| 20°-30°   | 1398.8 | 39.3      |
| 30°-40°   | 382.6  | 10.8      |
| 40°-50°   | 8.0    | 0.2       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3164.5 | 89.0      |
| 0°-40°    | 3547.1 | 99.8      |
| 0°-60°    | 3555.2 | 100.0     |
| 0°-90°    | 3555.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3555.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4850 |      |
| 5°  | 4899 | 470  |
| 15° | 4658 | 1296 |
| 25° | 3191 | 1399 |
| 35° | 482  | 383  |
| 45° | 0    | 8    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P434484

CATALOG NUMBER: LAMR4B408R559040DE01021MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4849.7 |
| 2.5°  | 4830.0 |
| 5°    | 4898.9 |
| 7.5°  | 4953.0 |
| 10°   | 4956.2 |
| 12.5° | 4830.0 |
| 15°   | 4658.0 |
| 17.5° | 4430.1 |
| 20°   | 4117.1 |
| 22.5° | 3713.9 |
| 25°   | 3191.1 |
| 27.5° | 2524.0 |
| 30°   | 1755.3 |
| 32.5° | 962.1  |
| 35°   | 481.9  |
| 37.5° | 206.5  |
| 40°   | 68.8   |
| 42.5° | 9.8    |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)