

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434414

Luminaire Tested: **LAMR4B408R409050DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R409050DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3995.4 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434414

CATALOG NUMBER: LAMR4B408R409050DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434414

CATALOG NUMBER: LAMR4B408R409050DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	75	73		79	75	73		78
10	85	78	73	71	84	77	73	70	77	73	70		76	73	70		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1506256
5°	1513918
10°	1503187
15°	1356094
20°	855587
25°	308144
30°	64551
35°	19647
40°	3912
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434414

CATALOG NUMBER: LAMR4B408R409050DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	887.7	22.2
10°-20°	2122.7	53.1
20°-30°	905.1	22.7
30°-40°	77.6	1.9
40°-50°	2.3	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3915.5	98.0
0°-40°	3993.1	99.9
0°-60°	3995.4	100.0
0°-90°	3995.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3995.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9350	
5°	9361	888
15°	8131	2123
25°	1734	905
35°	100	78
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434414

CATALOG NUMBER: LAMR4B408R409050DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9349.6
2.5°	9341.1
5°	9361.4
7.5°	9305.6
10°	9188.8
12.5°	8840.1
15°	8130.7
17.5°	6746.0
20°	4990.5
22.5°	3285.8
25°	1733.5
27.5°	702.5
30°	347.0
32.5°	184.5
35°	99.9
37.5°	50.8
40°	18.6
42.5°	3.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)