

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434371

Luminaire Tested: **LAMR4B408R309730DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R309730DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2975.8 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434371

CATALOG NUMBER: LAMR4B408R309730DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434371

CATALOG NUMBER: LAMR4B408R309730DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	111	109	107		107	105	104		103	102	101		100	99	98
2	111	107	104	102		109	106	103	100		102	100	98		100	98	96		97	95	94
3	107	103	99	96		105	101	98	95		99	96	94		96	94	92		94	92	91
4	104	98	94	91		102	97	94	91		95	92	90		93	91	89		92	90	88
5	101	95	91	87		99	94	90	87		92	89	86		91	88	86		89	87	85
6	98	91	87	84		97	91	87	84		89	86	83		88	85	83		87	84	82
7	95	88	84	81		94	88	84	81		87	83	81		86	83	80		85	82	80
8	92	86	81	79		91	85	81	78		84	81	78		83	80	78		83	80	78
9	90	83	79	76		89	83	79	76		82	78	76		81	78	76		80	78	75
10	88	81	77	74		87	80	77	74		80	76	74		79	76	74		78	76	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5391849
5°	5274019
10°	4572893
15°	2834290
20°	1038799
25°	347263
30°	170456
35°	84985
40°	52684
45°	33492
50°	23794
55°	19440
60°	16676
65°	13192
70°	16301
75°	16203
80°	15911
85°	15851



TEST NUMBER: P434371

CATALOG NUMBER: LAMR4B408R309730DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	970.5	32.6
10°-20°	1465.3	49.2
20°-30°	357.3	12.0
30°-40°	97.8	3.3
40°-50°	39.4	1.3
50°-60°	21.1	0.7
60°-70°	12.6	0.4
70°-80°	9.7	0.3
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2793.0	93.9
0°-40°	2890.8	97.1
0°-60°	2951.3	99.2
0°-90°	2975.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2975.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10928	
5°	10649	971
15°	5549	1465
25°	638	357
35°	141	98
45°	48	39
55°	23	21
65°	11	13
75°	8	10
85°	3	2
90°	0	



TEST NUMBER: P434371

CATALOG NUMBER: LAMR4B408R309730DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	10928.4
2.5°	10855.0
5°	10648.9
7.5°	10157.8
10°	9127.7
12.5°	7513.3
15°	5548.9
17.5°	3576.0
20°	1978.5
22.5°	1055.6
25°	637.9
27.5°	431.8
30°	299.2
32.5°	203.2
35°	141.1
37.5°	104.4
40°	81.8
42.5°	62.1
45°	48.0
47.5°	39.5
50°	31.0
52.5°	28.2
55°	22.6
57.5°	19.8
60°	16.9
62.5°	14.1
65°	11.3
67.5°	11.3
70°	11.3
72.5°	11.3
75°	8.5
77.5°	8.5
80°	5.6
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)