

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212062

Luminaire Tested: **LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 760.4 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	83	79		85	81	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	86	76	69	64	85	75	69	64	73	68	63		72	67	63		70
6	81	70	63	58	79	69	62	57	67	61	57		66	61	57		64
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	7953	7953	7953
5°	15229	7575	6146
10°	49805	6719	5233
15°	121966	5546	4623
20°	229794	4227	4144
25°	384676	3004	3624
30°	487305	2058	3087
35°	444030	1336	2625
40°	292430	948	2226
45°	126673	630	1836
50°	22471	437	1522
55°	3614	355	1267
60°	891	329	969
65°	298	390	779
70°	227	482	595
75°	299	487	487
80°	0	725	446
85°	0	1445	445



TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.5	1.4
10°-20°	84.6	11.1
20°-30°	254.8	33.5
30°-40°	290.0	38.1
40°-50°	107.2	14.1
50°-60°	8.5	1.1
60°-70°	2.3	0.3
70°-80°	1.6	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.9	46.0
0°-40°	639.8	84.1
0°-60°	755.6	99.4
0°-90°	760.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	82	82	82	82	82	
5°	157	115	78	65	63	25
15°	1216	411	55	44	46	381
25°	3599	600	28	27	34	1643
35°	3755	210	11	16	22	2232
45°	925	25	5	8	13	783
55°	21	5	2	5	8	35
65°	1	1	2	3	3	2
75°	1	1	1	2	1	1
85°	0	1	1	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1
2.5°	105.5	106.4	105.5	103.9	103.9	101.8	100.9	100.1	98.0	96.7	95.1
5°	156.6	154.1	152.0	147.0	145.3	140.7	137.4	132.7	126.5	121.0	115.2
7.5°	268.0	264.2	256.3	241.2	232.0	220.7	211.9	197.2	178.4	162.9	147.4
10°	506.3	489.9	471.1	437.2	412.5	386.1	365.2	325.8	278.5	239.5	201.8
12.5°	815.7	817.0	781.8	724.4	678.8	632.3	596.3	523.4	439.7	366.4	294.0
15°	1216.1	1193.0	1156.6	1068.7	977.4	910.0	852.6	742.0	623.5	516.3	410.8
17.5°	1637.8	1647.4	1562.4	1418.7	1274.3	1173.4	1086.7	919.2	778.5	645.7	516.7
20°	2229.0	2162.9	2041.4	1808.6	1584.2	1438.0	1309.5	1092.1	895.7	727.0	582.1
22.5°	2910.8	2804.0	2556.9	2229.0	1889.4	1687.2	1507.9	1208.9	970.3	768.4	604.3
25°	3598.8	3517.1	3123.5	2633.6	2147.0	1884.8	1652.8	1288.1	1005.9	778.0	600.5
27.5°	4129.8	3996.6	3548.1	2909.5	2300.6	1991.2	1720.3	1312.4	998.3	754.6	564.9
30°	4356.3	4188.0	3690.9	2972.3	2301.9	1973.6	1686.8	1264.2	944.7	695.1	497.9
32.5°	4216.5	4022.2	3520.9	2798.5	2144.5	1836.2	1557.4	1160.0	855.9	601.8	373.9
35°	3754.6	3561.1	3096.7	2455.6	1893.2	1623.9	1381.5	1023.9	729.1	446.0	210.2
37.5°	3074.5	2909.5	2577.4	2058.2	1595.5	1376.9	1175.0	862.6	543.1	255.9	105.5
40°	2312.4	2196.4	1997.0	1632.3	1291.4	1125.2	962.7	660.8	330.0	128.6	59.9
42.5°	1603.0	1527.6	1427.5	1207.7	996.2	881.9	751.7	441.4	169.6	70.8	37.3
45°	924.6	877.3	849.7	755.9	673.4	617.7	502.5	237.9	85.8	42.3	24.7
47.5°	408.3	376.9	363.5	324.1	301.5	286.4	227.4	101.3	46.1	27.2	20.5
50°	149.1	149.1	149.5	131.5	107.6	96.7	75.8	44.8	26.0	21.4	15.1
52.5°	52.8	51.9	54.0	51.1	44.8	40.2	33.5	22.6	15.9	13.4	8.4
55°	21.4	20.5	21.4	20.1	18.8	17.6	15.5	12.1	10.1	8.4	4.6
57.5°	9.6	9.6	10.1	9.6	9.6	8.8	8.0	9.2	7.1	4.6	2.9
60°	4.6	4.6	5.0	5.0	5.0	4.6	4.6	5.0	4.2	2.9	2.1
62.5°	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.9	2.1	1.7	1.3
65°	1.3	0.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3	1.3
70°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	1.3
80°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
82.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1
2.5°	93.4	92.1	89.6	88.4	86.7	85.4	84.6	82.9	81.2	80.0	79.1
5°	109.7	105.1	99.7	95.5	92.1	90.0	86.7	83.8	80.4	77.9	75.8
7.5°	133.6	122.3	110.1	101.8	97.2	93.0	87.1	82.1	77.5	74.1	71.2
10°	170.9	146.6	125.2	108.9	100.9	95.1	85.8	78.7	72.9	68.3	65.3
12.5°	232.8	183.0	145.3	117.7	105.5	96.7	83.8	74.1	67.0	62.4	58.6
15°	317.8	236.6	172.9	128.1	111.0	98.4	80.4	68.7	60.7	55.3	51.9
17.5°	397.8	292.7	204.4	140.7	116.4	99.2	75.8	61.6	53.2	48.2	44.8
20°	448.1	329.1	225.3	147.8	118.1	96.7	69.5	54.0	45.6	41.0	37.7
22.5°	459.8	333.3	223.6	141.1	111.0	89.2	60.7	46.5	38.5	34.3	31.4
25°	442.6	309.9	200.2	121.9	94.6	75.0	50.7	37.7	31.8	28.1	26.0
27.5°	399.5	263.8	158.3	91.7	70.8	55.3	38.5	29.3	25.5	22.6	21.4
30°	322.0	185.5	99.2	57.0	45.2	36.4	27.6	22.6	19.7	18.4	17.2
32.5°	195.1	95.5	52.3	33.9	28.5	24.7	20.1	16.8	15.1	14.2	13.8
35°	93.0	50.3	32.2	23.0	20.1	17.6	14.7	12.6	11.7	11.3	11.3
37.5°	52.8	32.7	21.8	15.5	13.8	12.1	10.9	9.6	9.2	9.2	9.2
40°	33.5	20.9	14.2	11.3	10.1	9.2	8.4	7.5	7.5	7.5	7.5
42.5°	21.8	15.1	10.9	8.4	7.5	7.1	6.3	5.9	5.9	5.9	6.3
45°	17.2	12.6	8.8	6.7	5.9	5.4	5.0	4.6	4.6	4.6	5.0
47.5°	14.7	8.8	5.9	4.6	3.8	3.8	3.4	3.4	3.4	3.8	4.2
50°	8.8	5.4	3.8	2.9	2.5	2.5	2.5	2.5	2.5	2.9	3.4
52.5°	5.0	3.4	2.5	2.1	1.7	1.7	1.7	1.7	2.1	2.5	2.5
55°	3.4	2.5	1.7	1.7	1.3	1.3	1.3	1.7	1.7	2.1	2.5
57.5°	2.1	1.7	1.3	1.3	1.3	1.3	1.3	1.3	1.7	2.1	2.1
60°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1
62.5°	1.3	1.3	1.7	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1
65°	1.3	1.3	1.7	1.7	1.3	1.3	1.3	1.3	1.3	1.7	2.1
67.5°	1.3	1.3	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.7	1.7
70°	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.7	1.7
72.5°	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.7	1.7
75°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.7
77.5°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.7
80°	1.3	1.3	1.3	1.7	1.3	1.7	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1
2.5°	77.9	77.1	75.8	75.4	75.8	75.4	73.3	72.9	72.0	72.0	72.0
5°	73.7	72.4	70.8	69.9	69.9	69.1	67.0	66.6	65.3	65.3	64.9
7.5°	68.7	67.0	64.9	64.1	64.1	63.2	61.1	60.3	59.5	59.5	59.0
10°	62.8	60.7	58.6	58.2	57.8	56.5	55.3	54.9	53.6	54.0	53.6
12.5°	56.1	54.4	52.8	51.9	51.9	50.7	49.8	49.4	49.0	49.0	49.0
15°	49.8	47.7	46.1	45.6	45.6	45.2	44.4	44.4	43.6	44.4	44.4
17.5°	42.7	41.0	40.6	39.8	40.2	39.8	38.9	39.4	39.4	39.8	40.2
20°	36.0	34.8	34.3	33.9	34.3	34.3	33.9	34.3	34.8	36.0	36.9
22.5°	30.2	29.3	29.3	28.9	29.3	29.7	29.3	30.2	31.0	31.8	33.1
25°	25.1	24.7	24.7	24.7	25.1	25.5	26.0	26.8	27.2	28.5	29.3
27.5°	20.5	20.5	20.5	20.9	21.4	21.8	22.2	23.5	23.9	25.1	26.0
30°	17.2	16.8	17.2	17.6	18.0	18.8	19.3	20.1	20.5	21.8	22.6
32.5°	13.8	14.2	14.7	15.1	15.5	15.9	16.3	17.2	18.0	18.8	19.7
35°	11.7	11.7	12.1	12.6	13.0	13.8	14.2	14.7	15.5	16.3	16.8
37.5°	9.6	10.1	10.5	10.9	11.3	11.7	12.1	12.6	13.0	13.8	14.7
40°	8.0	8.4	8.8	9.2	9.2	10.1	10.1	10.9	11.3	12.1	13.0
42.5°	6.7	7.1	7.5	8.0	8.0	8.4	8.8	9.2	9.6	10.5	11.3
45°	5.4	5.9	6.3	6.7	6.7	7.1	7.5	8.0	8.4	9.2	9.6
47.5°	4.6	5.0	5.4	5.9	5.9	6.3	6.7	7.1	7.1	8.0	8.4
50°	3.8	4.2	4.6	5.0	5.0	5.4	5.9	6.3	6.3	6.7	7.1
52.5°	2.9	3.4	4.2	4.2	4.6	5.0	5.0	5.4	5.4	5.9	6.3
55°	2.9	3.4	3.8	3.8	4.2	4.6	4.6	5.0	5.0	5.0	5.4
57.5°	2.5	2.9	3.4	3.8	3.8	4.2	4.2	4.2	4.2	4.6	4.6
60°	2.5	2.9	2.9	3.4	3.4	3.8	3.8	3.8	3.8	4.2	4.2
62.5°	2.5	2.5	2.9	2.9	3.4	3.4	3.4	3.8	3.8	3.8	3.8
65°	2.1	2.5	2.9	2.9	2.9	3.4	3.4	3.4	3.4	3.4	3.4
67.5°	2.1	2.5	2.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
70°	2.1	2.1	2.5	2.5	2.5	2.9	2.9	2.9	2.5	2.9	2.5
72.5°	1.7	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	1.7	2.1	2.1	2.1	2.1	2.5	2.5	2.1	2.1	2.1	2.1
77.5°	1.7	1.7	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	1.7
80°	1.7	1.7	1.7	1.7	2.1	2.1	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3
85°	1.3	1.3	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.3	0.8
87.5°	1.3	1.3	1.3	1.7	1.3	1.3	1.3	1.3	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212062

CATALOG NUMBER: LDSQA4A10927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1
2.5°	70.8	70.4	70.8	70.4	70.4	70.8	69.5	70.4
5°	64.1	63.2	63.7	63.2	62.8	63.2	62.4	63.2
7.5°	58.2	57.8	57.8	57.8	57.4	57.8	57.0	57.8
10°	53.2	52.8	52.8	52.8	52.8	53.2	52.3	53.2
12.5°	48.2	48.2	48.6	48.2	48.6	49.0	48.2	49.0
15°	44.0	44.4	44.8	44.8	45.2	45.6	45.2	46.1
17.5°	40.6	41.0	41.9	41.9	42.3	43.1	42.7	43.6
20°	37.3	37.7	38.5	38.5	38.9	39.8	39.4	40.2
22.5°	33.5	34.3	34.8	35.2	35.6	36.4	36.0	36.9
25°	29.7	31.0	31.4	31.8	32.2	33.1	33.1	33.9
27.5°	26.8	27.6	28.1	28.5	29.3	30.2	30.2	30.6
30°	23.5	24.3	25.1	25.5	26.0	26.8	26.8	27.6
32.5°	20.5	21.4	21.8	22.2	23.0	23.9	24.3	24.7
35°	17.6	18.8	19.3	20.1	20.5	21.8	21.8	22.2
37.5°	15.5	16.3	17.2	17.6	18.4	19.3	19.3	20.1
40°	13.8	14.7	15.1	15.5	16.3	17.2	17.2	17.6
42.5°	11.7	13.0	13.4	13.8	14.2	15.1	15.5	15.9
45°	10.5	10.9	11.3	11.7	12.1	13.0	13.0	13.4
47.5°	8.8	9.2	9.6	10.1	10.5	10.9	11.3	11.7
50°	7.5	8.0	8.4	8.4	8.8	9.6	9.6	10.1
52.5°	6.3	6.7	7.1	7.1	7.5	8.4	8.4	8.8
55°	5.4	5.9	6.3	6.3	6.7	7.1	7.1	7.5
57.5°	5.0	5.0	5.4	5.4	5.9	5.9	6.3	6.3
60°	4.2	4.6	4.6	4.6	5.0	5.0	5.0	5.0
62.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.2
65°	3.4	3.4	3.4	3.4	3.4	3.4	2.9	3.4
67.5°	2.9	2.9	2.9	2.9	2.5	2.5	2.5	2.5
70°	2.5	2.5	2.5	2.5	2.5	2.1	2.1	2.1
72.5°	2.1	2.1	2.1	2.1	2.1	1.7	1.7	1.7
75°	2.1	2.1	1.7	1.7	1.7	1.7	1.7	1.3
77.5°	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	1.3	0.8	0.8
82.5°	1.3	0.8	0.8	0.8	0.8	0.8	0.8	0.8
85°	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4
87.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)