

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434320

Luminaire Tested: **LAMR4B408R209727DE01021MB**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P434320  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B408R209727DE01021MB  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2754.7 lumens  
Efficiency: N/A  
Efficacy: 66.9 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 41.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P434320

CATALOG NUMBER: LAMR4B408R209727DE01021MB

### Luminous Intensity Polar Plot





TEST NUMBER: P434320

CATALOG NUMBER: LAMR4B408R209727DE01021MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 |  | 103 | 102 | 102 |  | 100 |
| 2   | 112 | 108 | 105 | 103 | 110 | 106 | 104 | 102 | 103 | 101 | 100 |  | 101 | 99  | 97  |  | 98  |
| 3   | 108 | 104 | 100 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  |  | 98  | 96  | 94  |  | 96  |
| 4   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 93  | 97  | 94  | 92  |  | 96  | 93  | 91  |  | 94  |
| 5   | 103 | 97  | 93  | 90  | 101 | 96  | 93  | 90  | 95  | 92  | 89  |  | 93  | 91  | 89  |  | 92  |
| 6   | 100 | 94  | 90  | 88  | 99  | 94  | 90  | 87  | 92  | 89  | 87  |  | 91  | 88  | 86  |  | 90  |
| 7   | 98  | 92  | 88  | 85  | 97  | 91  | 88  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 8   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 83  |  | 87  | 85  | 82  |  | 87  |
| 9   | 94  | 88  | 84  | 81  | 93  | 87  | 84  | 81  | 86  | 83  | 81  |  | 86  | 83  | 81  |  | 85  |
| 10  | 92  | 86  | 82  | 80  | 91  | 85  | 82  | 80  | 85  | 82  | 79  |  | 84  | 81  | 79  |  | 83  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 9515811 |
| 5°  | 8043338 |
| 10° | 4724343 |
| 15° | 1691615 |
| 20° | 559696  |
| 25° | 222762  |
| 30° | 106478  |
| 35° | 60833   |
| 40° | 43925   |
| 45° | 36980   |
| 50° | 42676   |
| 55° | 34751   |
| 60° | 17466   |
| 65° | 14710   |
| 70° | 18176   |
| 75° | 19253   |
| 80° | 14490   |
| 85° | 14152   |



TEST NUMBER: P434320

CATALOG NUMBER: LAMR4B408R209727DE01021MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1329.8 | 48.3      |
| 10°-20°   | 1037.0 | 37.6      |
| 20°-30°   | 215.2  | 7.8       |
| 30°-40°   | 67.8   | 2.5       |
| 40°-50°   | 43.6   | 1.6       |
| 50°-60°   | 35.0   | 1.3       |
| 60°-70°   | 13.8   | 0.5       |
| 70°-80°   | 10.3   | 0.4       |
| 80°-90°   | 2.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2582.1 | 93.7      |
| 0°-40°    | 2649.9 | 96.2      |
| 0°-60°    | 2728.6 | 99.1      |
| 0°-90°    | 2754.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2754.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 19287 |      |
| 5°  | 16240 | ###  |
| 15° | 3312  | 1037 |
| 25° | 409   | 215  |
| 35° | 101   | 68   |
| 45° | 53    | 44   |
| 55° | 40    | 35   |
| 65° | 13    | 14   |
| 75° | 10    | 10   |
| 85° | 2     | 2    |
| 90° | 0     |      |



TEST NUMBER: P434320

CATALOG NUMBER: LAMR4B408R209727DE01021MB

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 19287.0 |
| 2.5°  | 18579.7 |
| 5°    | 16240.5 |
| 7.5°  | 13012.1 |
| 10°   | 9430.0  |
| 12.5° | 5949.0  |
| 15°   | 3311.8  |
| 17.5° | 1821.3  |
| 20°   | 1066.0  |
| 22.5° | 651.7   |
| 25°   | 409.2   |
| 27.5° | 270.3   |
| 30°   | 186.9   |
| 32.5° | 131.4   |
| 35°   | 101.0   |
| 37.5° | 80.8    |
| 40°   | 68.2    |
| 42.5° | 58.1    |
| 45°   | 53.0    |
| 47.5° | 53.0    |
| 50°   | 55.6    |
| 52.5° | 53.0    |
| 55°   | 40.4    |
| 57.5° | 27.8    |
| 60°   | 17.7    |
| 62.5° | 15.2    |
| 65°   | 12.6    |
| 67.5° | 12.6    |
| 70°   | 12.6    |
| 72.5° | 12.6    |
| 75°   | 10.1    |
| 77.5° | 7.6     |
| 80°   | 5.1     |
| 82.5° | 2.5     |
| 85°   | 2.5     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)