

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212068

Luminaire Tested: **LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 898.2 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9087	9087	9087
5°	20110	8597	6039
10°	80496	7466	5046
15°	185552	5937	4433
20°	276989	4216	3959
25°	363309	2811	3517
30°	417044	1767	3076
35°	382392	1135	2661
40°	313575	733	2264
45°	181802	521	1822
50°	51513	377	1507
55°	4712	355	1267
60°	736	407	1046
65°	183	390	756
70°	227	482	595
75°	299	636	636
80°	0	948	446
85°	0	1890	445



TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.3	1.5
10°-20°	119.4	13.3
20°-30°	291.0	32.4
30°-40°	315.4	35.1
40°-50°	142.9	15.9
50°-60°	11.1	1.2
60°-70°	2.3	0.3
70°-80°	1.7	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	47.2
0°-40°	739.1	82.3
0°-60°	893.1	99.4
0°-90°	898.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	94	94	94	94	94	
5°	207	153	88	67	62	37
15°	1850	605	59	43	44	538
25°	3399	869	26	26	33	1549
35°	3233	221	10	15	22	1989
45°	1327	28	4	8	13	1048
55°	28	4	2	5	8	64
65°	1	1	2	3	3	1
75°	1	1	2	2	2	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8
2.5°	140.5	138.0	139.2	135.9	133.8	132.2	133.0	132.2	126.7	125.5	121.3
5°	206.8	203.0	203.0	195.9	188.4	183.8	183.8	178.4	166.8	161.3	152.6
7.5°	370.6	363.1	356.9	334.8	306.0	289.7	285.6	262.6	233.0	214.3	192.2
10°	818.3	787.1	765.0	707.5	630.3	582.4	562.0	482.8	388.5	317.7	253.5
12.5°	1376.1	1333.6	1294.9	1200.6	1089.7	1014.3	973.8	857.1	674.1	543.2	406.5
15°	1850.1	1804.3	1758.4	1643.8	1526.6	1461.2	1387.0	1232.3	990.5	804.6	605.3
17.5°	2239.1	2213.3	2166.1	1998.1	1850.6	1748.4	1671.3	1469.1	1220.2	1008.0	782.5
20°	2686.8	2623.1	2538.8	2335.0	2133.2	2005.2	1896.8	1650.5	1362.8	1118.9	876.3
22.5°	3063.7	3018.3	2897.4	2628.5	2331.6	2222.4	2089.9	1793.4	1454.5	1166.0	887.1
25°	3398.9	3327.6	3175.8	2856.1	2552.2	2366.2	2203.7	1871.0	1488.3	1169.4	869.2
27.5°	3595.2	3502.3	3323.8	2975.3	2628.5	2422.9	2242.9	1884.3	1467.0	1125.2	803.8
30°	3728.2	3543.1	3345.9	2976.6	2604.3	2394.2	2207.4	1817.2	1378.6	1024.3	693.7
32.5°	3508.9	3401.8	3213.4	2858.2	2472.6	2267.4	2081.9	1671.7	1240.7	874.6	482.8
35°	3233.4	3146.7	2982.8	2630.1	2275.0	2081.5	1884.7	1485.0	1061.0	601.2	220.9
37.5°	2913.2	2845.3	2668.9	2346.7	2034.0	1844.7	1647.5	1265.7	747.1	298.1	134.2
40°	2479.6	2422.1	2277.5	2018.6	1730.5	1550.4	1368.6	946.7	405.6	166.3	87.5
42.5°	2038.2	1989.8	1858.1	1634.2	1381.1	1232.7	1072.6	577.0	201.8	104.6	48.8
45°	1327.0	1266.5	1195.6	1093.1	968.0	876.7	687.9	278.5	119.6	58.4	27.9
47.5°	760.8	720.8	604.5	476.9	387.3	353.5	257.2	129.7	65.9	33.8	17.1
50°	341.8	316.0	265.1	215.9	156.3	122.1	103.8	65.0	32.5	18.3	11.7
52.5°	84.2	85.9	81.3	71.3	63.4	53.8	46.7	30.4	17.1	11.3	7.5
55°	27.9	28.3	25.8	24.6	22.5	20.8	19.2	13.8	10.4	10.0	3.8
57.5°	10.0	10.0	10.4	9.6	9.2	8.8	8.3	7.1	6.3	3.8	2.1
60°	3.8	3.8	3.8	4.2	4.2	4.2	4.6	4.2	2.9	2.1	1.7
62.5°	1.7	1.7	1.7	1.7	2.1	2.1	2.5	2.1	1.7	1.7	1.3
65°	0.8	0.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3	1.3
70°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3	1.3
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3	1.3
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8	1.3
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8	1.3
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8	1.3
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	1.3
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8
2.5°	117.1	114.6	109.6	105.9	103.0	102.6	100.1	95.9	94.2	91.3	88.8
5°	144.2	138.0	130.1	122.6	117.1	114.2	105.5	97.6	93.0	88.4	84.2
7.5°	173.4	159.3	145.5	133.4	125.9	121.3	110.9	98.0	89.6	83.0	77.5
10°	210.1	180.9	157.2	138.4	128.4	122.1	109.6	94.2	83.8	75.9	70.5
12.5°	293.9	214.3	168.0	140.9	128.4	119.6	104.6	89.2	77.5	68.0	62.1
15°	437.3	299.3	199.3	142.2	124.2	114.2	97.1	80.9	69.2	59.2	53.8
17.5°	572.4	394.0	248.9	150.9	121.7	106.3	87.1	71.3	59.2	49.6	45.0
20°	642.4	441.1	276.4	157.6	117.6	96.3	75.5	60.9	49.2	40.9	37.1
22.5°	644.1	436.9	263.1	142.2	102.1	82.5	64.6	50.0	40.0	32.9	30.0
25°	604.5	386.5	216.4	110.9	82.5	69.2	53.8	40.9	31.3	26.3	24.2
27.5°	529.9	312.7	159.7	80.0	64.6	55.0	42.1	31.3	23.8	20.4	19.2
30°	409.8	193.4	88.4	59.2	48.8	41.3	30.4	20.8	17.9	15.8	15.0
32.5°	203.4	94.6	62.5	42.1	33.4	26.3	19.2	15.4	13.8	12.5	12.1
35°	110.5	68.0	39.2	25.4	20.0	16.7	12.9	10.8	10.0	9.6	9.6
37.5°	77.1	40.4	23.8	15.4	12.5	11.3	9.2	7.9	7.5	7.5	7.5
40°	42.5	24.2	14.6	10.0	8.3	7.5	6.3	5.8	5.8	5.8	6.3
42.5°	24.6	15.0	10.0	7.1	5.8	5.4	4.6	4.2	4.6	4.6	5.0
45°	15.8	11.3	6.7	5.0	4.2	3.8	3.3	3.3	3.8	3.8	4.2
47.5°	11.3	7.9	4.6	3.3	2.5	2.5	2.5	2.5	2.9	3.3	3.8
50°	6.7	4.2	2.5	2.1	1.7	1.7	1.7	2.1	2.5	2.5	2.9
52.5°	3.8	2.5	1.7	1.7	1.3	1.3	1.7	1.7	2.1	2.5	2.9
55°	2.1	1.7	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.5
57.5°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.1
60°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.1
62.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	2.1
65°	1.3	1.3	1.3	1.7	1.3	1.7	1.7	1.7	1.7	1.7	2.1
67.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.1
70°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.1
72.5°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.1
75°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
77.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
87.5°	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8
2.5°	88.0	85.0	83.0	82.1	80.5	80.9	79.6	78.8	76.3	76.3	74.6
5°	81.3	77.5	75.0	73.8	72.1	71.7	70.5	69.2	66.7	66.3	65.0
7.5°	74.2	70.5	67.5	66.3	64.6	64.2	62.5	61.7	59.6	59.2	57.9
10°	66.7	62.5	60.0	58.8	57.1	57.1	55.9	55.0	53.4	53.4	52.5
12.5°	58.8	55.0	53.4	51.7	50.9	50.9	50.0	49.2	47.9	48.4	47.9
15°	50.4	47.5	45.9	45.0	44.6	44.6	44.2	43.8	42.9	43.8	42.9
17.5°	42.5	40.4	39.2	38.8	38.4	38.4	38.4	38.8	38.4	39.2	39.2
20°	35.0	33.4	32.5	32.5	32.1	32.9	32.9	33.8	33.8	35.0	35.4
22.5°	28.8	27.5	27.1	27.1	27.1	27.9	28.3	29.2	29.6	30.8	31.7
25°	22.9	22.5	22.5	22.5	22.9	23.8	24.6	25.4	25.8	27.5	27.9
27.5°	18.8	18.3	18.8	18.8	19.2	20.4	21.3	22.1	22.9	24.2	25.0
30°	15.0	15.0	15.4	15.8	16.3	17.1	18.3	19.2	20.0	21.3	22.1
32.5°	12.1	12.5	12.9	13.3	13.3	14.6	15.4	16.7	17.1	18.3	19.2
35°	10.0	10.4	10.8	11.3	11.3	12.5	13.3	14.2	15.0	15.8	16.7
37.5°	7.9	8.3	9.2	9.6	9.6	10.8	11.3	12.1	12.9	13.8	14.6
40°	6.7	7.1	7.9	7.9	8.3	9.2	9.6	10.4	11.3	12.1	12.9
42.5°	5.4	5.8	6.7	7.1	7.1	7.9	8.3	9.2	9.6	10.4	10.8
45°	5.0	5.0	5.8	5.8	6.3	6.7	7.5	7.9	8.3	9.2	9.6
47.5°	4.2	4.6	5.0	5.4	5.4	5.8	6.3	6.7	7.1	7.9	8.3
50°	3.3	3.8	4.6	4.6	4.6	5.4	5.8	6.3	6.3	6.7	7.1
52.5°	3.3	3.3	3.8	4.2	4.2	4.6	5.0	5.4	5.4	5.8	6.3
55°	2.9	2.9	3.3	3.8	3.8	4.2	4.6	4.6	5.0	5.0	5.4
57.5°	2.5	2.9	3.3	3.3	3.3	3.8	4.2	4.2	4.6	4.6	5.0
60°	2.5	2.9	2.9	3.3	3.3	3.8	3.8	3.8	4.2	4.2	4.2
62.5°	2.5	2.5	2.9	2.9	2.9	3.3	3.3	3.8	3.8	3.8	3.8
65°	2.5	2.5	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.3
67.5°	2.1	2.5	2.5	2.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9
70°	2.1	2.1	2.5	2.5	2.5	2.9	2.9	2.9	2.9	2.9	2.9
72.5°	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.1	2.1	2.1	2.1	2.1	2.5	2.5	2.5	2.5	2.1	2.1
77.5°	1.7	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	1.7
80°	1.7	1.7	2.1	1.7	2.1	2.1	2.1	2.1	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3
85°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	0.8
87.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212068

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8
2.5°	73.8	74.6	73.8	74.6	72.5	73.4	74.2	72.1
5°	64.2	63.4	63.8	64.6	62.9	63.4	63.8	62.1
7.5°	57.5	57.9	57.1	57.9	56.7	57.1	57.5	56.3
10°	52.1	52.5	52.1	52.5	51.3	52.1	52.5	51.3
12.5°	47.1	47.9	47.5	48.4	47.1	47.9	48.8	47.1
15°	43.4	44.2	43.8	44.6	43.8	44.6	45.4	44.2
17.5°	39.6	40.4	40.4	41.3	40.9	41.7	42.5	41.3
20°	35.9	37.1	37.1	37.9	37.9	38.4	39.6	38.4
22.5°	32.5	33.8	33.8	34.6	34.6	35.4	36.3	35.4
25°	28.8	30.4	30.8	31.7	31.7	32.5	33.8	32.9
27.5°	26.3	27.5	27.9	28.8	29.2	30.0	30.8	30.0
30°	22.9	24.6	25.0	25.8	26.3	27.5	27.9	27.5
32.5°	20.4	21.7	22.1	22.9	23.8	24.6	25.4	25.0
35°	17.9	19.2	19.6	20.4	20.8	22.1	22.9	22.5
37.5°	15.8	17.1	17.5	17.9	18.3	19.6	20.4	20.0
40°	13.8	14.6	15.0	15.8	16.3	17.1	17.9	17.9
42.5°	12.1	12.9	13.3	13.8	14.2	15.0	15.8	15.4
45°	10.4	11.3	11.7	12.1	12.5	12.9	13.8	13.3
47.5°	8.8	9.6	10.0	10.4	10.8	11.3	12.1	11.7
50°	7.5	8.3	8.3	8.8	9.2	9.6	10.4	10.0
52.5°	6.7	7.1	7.5	7.5	7.9	8.3	9.2	8.8
55°	5.8	6.3	6.3	6.7	6.7	7.1	7.5	7.5
57.5°	5.0	5.4	5.4	5.8	5.8	6.3	6.7	6.7
60°	4.6	4.6	5.0	5.0	5.0	5.4	5.4	5.4
62.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
65°	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
67.5°	2.9	2.9	2.9	2.9	2.9	2.5	2.5	2.5
70°	2.5	2.5	2.5	2.5	2.5	2.1	2.1	2.1
72.5°	2.5	2.5	2.1	2.1	2.1	2.1	2.1	1.7
75°	2.1	2.1	2.1	2.1	1.7	1.7	1.7	1.7
77.5°	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.3
80°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	0.8
82.5°	1.3	1.3	1.3	0.8	0.8	0.8	0.8	0.8
85°	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4
87.5°	0.8	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)