

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212070

Luminaire Tested: **LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 834.1 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9009	9009	9009
5°	20159	8470	6068
10°	79050	7417	4781
15°	171611	6008	4162
20°	256010	4443	3753
25°	332984	3132	3271
30°	372512	2103	2852
35°	335240	1242	2424
40°	273588	847	2125
45°	157087	575	1726
50°	45952	437	1447
55°	5303	355	1199
60°	1143	407	969
65°	390	390	665
70°	368	482	482
75°	299	636	487
80°	0	948	446
85°	0	1890	445



TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.3	1.6
10°-20°	114.2	13.7
20°-30°	272.4	32.7
30°-40°	287.5	34.5
40°-50°	130.4	15.6
50°-60°	11.4	1.4
60°-70°	2.4	0.3
70°-80°	1.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	399.9	47.9
0°-40°	687.3	82.4
0°-60°	829.1	99.4
0°-90°	834.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	93	93	93	93	93	
5°	207	152	87	67	62	37
15°	1711	602	60	41	42	498
25°	3115	828	29	25	31	1415
35°	2835	229	10	14	20	1751
45°	1147	32	4	8	13	909
55°	31	5	2	5	7	63
65°	2	2	2	3	3	2
75°	1	1	2	2	1	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0
2.5°	138.2	139.0	135.3	135.7	131.9	133.6	132.3	129.0	126.5	122.3	120.6
5°	207.3	208.5	200.2	197.7	188.9	188.9	185.1	176.3	168.3	158.7	152.0
7.5°	379.0	384.0	358.9	340.0	312.4	305.7	292.7	262.6	237.9	212.7	193.9
10°	803.6	794.4	742.5	699.8	628.6	602.2	567.0	480.3	400.8	321.6	259.6
12.5°	1267.2	1296.9	1196.8	1162.1	1049.4	1025.6	950.6	809.1	674.6	534.8	410.8
15°	1711.1	1719.9	1632.4	1575.8	1438.5	1407.5	1315.4	1149.1	968.2	773.1	601.8
17.5°	2067.5	2102.6	1974.1	1913.4	1735.0	1685.1	1576.7	1374.4	1173.0	959.8	756.7
20°	2483.3	2492.5	2340.1	2223.3	1990.0	1914.2	1784.4	1533.5	1293.6	1050.3	840.5
22.5°	2861.5	2859.4	2663.4	2498.4	2203.2	2112.7	1952.3	1655.0	1376.1	1090.5	848.4
25°	3115.2	3121.9	2912.1	2717.0	2354.7	2232.5	2051.6	1718.2	1404.1	1089.2	828.3
27.5°	3250.5	3243.8	3018.9	2810.4	2410.4	2273.5	2077.1	1720.3	1378.6	1046.5	768.0
30°	3330.1	3240.4	3000.5	2784.0	2372.8	2232.0	2032.3	1654.1	1293.6	951.0	660.4
32.5°	3117.3	3082.6	2873.6	2643.7	2242.9	2103.5	1906.2	1513.4	1158.7	804.9	473.2
35°	2834.7	2835.9	2632.0	2417.1	2039.4	1918.0	1714.4	1342.2	994.2	559.5	228.6
37.5°	2538.2	2542.4	2348.5	2148.7	1812.4	1684.7	1494.2	1147.0	715.3	284.8	137.8
40°	2163.4	2172.2	2005.1	1844.7	1534.4	1411.3	1241.2	868.1	399.9	159.1	93.4
42.5°	1767.6	1778.5	1630.3	1487.9	1224.1	1122.7	972.0	537.7	198.5	103.0	54.9
45°	1146.6	1178.0	1067.9	1008.0	855.1	794.8	634.4	274.3	119.8	60.3	32.2
47.5°	656.2	656.6	563.7	451.4	370.2	322.0	251.7	124.8	69.9	33.9	19.7
50°	304.9	312.4	247.5	206.0	147.4	124.8	102.6	67.4	36.9	19.7	12.1
52.5°	88.8	93.8	85.0	77.1	65.3	58.2	49.8	33.1	19.3	11.7	7.5
55°	31.4	33.5	31.4	29.3	26.4	23.9	21.4	15.9	10.9	7.1	5.0
57.5°	13.0	13.4	13.0	12.6	11.7	11.7	10.5	8.8	6.7	4.6	3.4
60°	5.9	6.3	5.9	6.3	5.9	5.9	5.9	6.3	4.2	2.9	2.5
62.5°	2.5	2.9	2.9	2.9	2.9	3.4	3.4	2.9	2.5	2.1	1.7
65°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
70°	1.3	1.3	1.3	1.3	1.3	1.3	0.8	0.8	1.3	1.3	1.3
72.5°	1.3	1.3	1.3	1.3	0.8	0.8	0.8	0.8	0.8	1.3	1.3
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	0.8
80°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	0.8
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0
2.5°	118.5	114.7	108.9	105.1	103.4	100.9	99.2	95.1	93.4	90.0	88.8
5°	145.7	138.2	129.4	122.3	117.7	112.6	105.1	96.7	92.5	87.1	84.2
7.5°	176.7	160.4	144.9	132.3	126.5	119.8	110.1	97.2	89.2	82.1	77.9
10°	216.1	182.6	158.3	138.2	129.4	120.6	108.9	93.8	83.8	75.4	70.8
12.5°	308.2	220.3	170.4	141.5	130.2	119.3	104.7	89.2	77.5	67.8	62.8
15°	443.5	307.8	203.1	144.5	127.3	113.9	97.2	81.7	69.5	59.9	54.9
17.5°	563.2	392.4	248.3	155.4	126.5	107.6	87.9	72.0	60.3	51.1	46.9
20°	628.6	436.8	278.5	162.1	122.7	98.0	77.5	62.4	51.1	43.1	39.4
22.5°	629.8	434.3	267.6	147.4	108.0	85.0	67.0	52.8	42.7	35.6	32.7
25°	592.1	387.4	223.2	116.0	88.4	72.0	56.1	44.0	34.8	29.3	26.8
27.5°	521.8	314.9	164.2	83.8	69.1	58.2	45.2	35.2	27.2	23.9	21.8
30°	410.4	205.2	95.9	62.4	53.6	44.8	34.3	24.7	21.4	18.8	17.2
32.5°	220.3	99.7	67.0	46.1	38.1	31.4	22.6	18.0	15.5	13.8	13.4
35°	115.2	72.9	44.8	29.3	24.3	20.5	15.5	12.6	11.3	10.5	10.5
37.5°	82.5	45.6	28.5	18.8	15.9	13.0	10.9	9.2	8.4	8.4	8.4
40°	49.0	28.1	17.2	12.1	10.5	9.2	8.0	6.7	6.7	6.7	6.7
42.5°	29.7	17.6	12.1	8.4	7.5	6.7	5.9	5.4	5.0	5.0	5.4
45°	18.4	12.1	8.0	6.3	5.9	5.0	4.6	4.2	4.2	4.2	4.6
47.5°	11.7	8.8	5.9	4.2	3.8	3.4	2.9	2.9	3.4	3.4	3.8
50°	8.8	5.4	3.8	2.9	2.5	2.5	2.1	2.5	2.5	2.9	3.4
52.5°	5.0	3.4	2.5	2.1	2.1	1.7	1.7	2.1	2.1	2.5	2.9
55°	3.4	2.5	2.1	1.7	1.7	1.7	1.7	1.7	2.1	2.1	2.5
57.5°	2.5	2.1	1.7	1.7	1.7	1.3	1.7	1.7	1.7	2.1	2.5
60°	2.1	1.7	1.7	1.7	1.7	1.3	1.3	1.7	1.7	2.1	2.1
62.5°	1.7	1.7	1.7	1.7	1.7	1.3	1.7	1.7	1.7	1.7	2.1
65°	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.1
67.5°	1.3	1.3	1.7	1.7	1.7	1.3	1.7	1.7	1.7	1.7	2.1
70°	1.3	1.3	1.3	1.7	1.7	1.3	1.7	1.7	1.7	1.7	1.7
72.5°	1.3	1.3	1.3	1.7	1.7	1.3	1.7	1.7	1.7	1.7	1.7
75°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7
77.5°	1.3	1.3	1.3	1.3	1.7	1.3	1.7	1.7	1.7	1.7	1.7
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0
2.5°	85.4	84.2	81.7	81.2	80.8	79.1	77.9	76.6	76.6	75.4	74.5
5°	79.1	77.1	74.1	72.9	72.4	70.4	68.7	67.4	67.0	65.7	64.5
7.5°	72.4	69.9	66.6	65.3	64.9	62.8	61.1	59.9	59.0	57.8	57.0
10°	65.3	62.4	59.5	58.2	57.8	55.7	54.4	53.2	52.3	51.5	50.7
12.5°	57.8	55.3	52.3	51.1	50.7	49.0	47.7	46.9	46.5	45.6	45.2
15°	50.3	47.7	45.2	44.4	44.0	42.7	41.9	41.5	41.0	41.0	40.6
17.5°	42.7	40.6	38.5	38.1	37.7	36.9	36.4	36.0	36.4	36.4	36.9
20°	35.6	33.9	32.2	32.2	31.8	31.4	31.4	31.4	32.2	32.7	33.5
22.5°	29.3	28.1	26.8	26.8	26.8	26.8	26.8	27.6	28.5	29.3	29.7
25°	24.3	23.0	22.6	22.6	22.6	23.0	23.5	24.3	25.1	26.0	26.8
27.5°	19.7	18.8	18.8	18.8	19.3	19.7	20.1	20.9	22.2	23.0	23.9
30°	15.9	15.5	15.5	15.9	16.3	16.8	17.6	18.4	19.3	20.1	20.9
32.5°	12.6	13.0	13.0	13.4	13.8	14.2	15.1	15.9	16.8	17.6	18.0
35°	10.5	10.5	10.9	11.3	11.7	12.1	13.0	13.8	14.2	15.1	15.9
37.5°	8.4	8.8	9.2	9.6	10.1	10.5	10.9	11.7	12.1	13.0	13.8
40°	7.1	7.5	8.0	8.4	8.4	9.2	9.2	10.1	10.5	11.3	12.1
42.5°	5.9	6.3	6.7	7.1	7.1	7.5	8.0	8.4	9.2	9.6	10.5
45°	4.6	5.0	5.4	5.9	6.3	6.7	6.7	7.5	8.0	8.4	9.2
47.5°	4.2	4.6	5.0	5.0	5.4	5.9	5.9	6.7	7.1	7.5	8.0
50°	3.4	3.8	4.2	4.6	4.6	5.0	5.4	5.9	6.3	6.7	6.7
52.5°	2.9	3.4	3.8	3.8	4.2	4.6	4.6	5.0	5.4	5.4	5.9
55°	2.9	3.4	3.4	3.8	3.8	4.2	4.2	4.6	4.6	5.0	5.0
57.5°	2.5	2.9	2.9	3.4	3.4	3.8	3.8	4.2	4.2	4.2	4.6
60°	2.5	2.5	2.9	2.9	3.4	3.4	3.4	3.8	3.8	3.8	4.2
62.5°	2.1	2.5	2.5	2.9	2.9	2.9	3.4	3.4	3.4	3.8	3.8
65°	2.1	2.5	2.5	2.9	2.9	2.9	2.9	2.9	3.4	3.4	3.4
67.5°	2.1	2.1	2.5	2.5	2.5	2.5	2.9	2.9	2.9	2.9	2.9
70°	2.1	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
72.5°	1.7	2.1	2.1	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.1
75°	1.7	1.7	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	1.7	1.7	1.7	2.1	2.1	2.1	2.1	2.1	2.1	1.7	1.7
80°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3
85°	1.7	1.3	1.7	1.7	1.7	1.3	1.3	1.3	1.3	1.3	0.8
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212070

CATALOG NUMBER: LDSQA4A10927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	93.0	93.0	93.0	93.0	93.0	93.0	93.0	93.0
2.5°	73.7	72.9	73.3	73.3	72.4	72.0	72.0	72.4
5°	63.7	62.8	63.2	63.2	62.4	62.0	62.0	62.4
7.5°	56.1	55.3	55.7	55.7	54.9	54.9	54.9	54.9
10°	50.3	49.8	49.8	49.8	49.0	49.4	49.0	48.6
12.5°	44.8	44.8	44.8	44.8	44.4	44.8	44.4	44.4
15°	40.6	40.6	41.0	41.0	41.0	41.5	41.5	41.5
17.5°	37.3	37.7	38.1	38.5	38.5	38.9	38.9	38.9
20°	33.9	34.8	35.2	35.6	35.6	36.4	36.0	36.4
22.5°	30.6	31.4	31.8	32.2	32.7	33.1	33.1	33.5
25°	27.6	28.5	28.9	29.3	29.7	30.6	30.6	30.6
27.5°	24.7	25.5	26.0	26.8	27.2	28.1	28.1	28.1
30°	21.8	22.6	23.0	23.5	24.3	25.1	25.1	25.5
32.5°	18.8	20.1	20.5	20.9	21.8	22.6	23.0	23.0
35°	16.8	17.6	18.0	18.8	19.3	20.5	20.5	20.5
37.5°	14.7	15.5	16.3	16.8	17.2	18.0	18.4	18.8
40°	13.0	13.8	14.2	14.7	15.5	16.3	16.8	16.8
42.5°	11.3	12.1	12.6	13.0	13.4	14.2	14.2	14.2
45°	10.1	10.5	10.9	11.3	11.7	12.1	12.6	12.6
47.5°	8.4	9.2	9.2	9.6	10.1	10.9	10.9	11.3
50°	7.1	8.0	8.0	8.4	8.8	9.2	9.6	9.6
52.5°	6.3	6.7	7.1	7.1	7.5	8.0	8.4	8.4
55°	5.4	5.9	5.9	6.3	6.3	6.7	7.1	7.1
57.5°	4.6	5.0	5.4	5.4	5.4	5.9	5.9	6.3
60°	4.2	4.6	4.6	4.6	4.6	5.0	5.0	5.0
62.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
65°	3.4	3.4	3.4	3.4	2.9	2.9	2.9	2.9
67.5°	2.9	2.9	2.9	2.9	2.5	2.5	2.5	2.5
70°	2.5	2.5	2.5	2.5	2.1	2.1	2.1	1.7
72.5°	2.1	2.1	2.1	2.1	2.1	1.7	1.7	1.7
75°	2.1	1.7	1.7	1.7	1.7	1.7	1.3	1.3
77.5°	1.7	1.7	1.7	1.3	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	0.8	0.8	0.8
82.5°	1.3	0.8	0.8	0.8	0.8	0.8	0.8	0.8
85°	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4
87.5°	0.8	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)