

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434562

Luminaire Tested: **LAMR4B408R709727DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R709727DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2667.2 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434562

CATALOG NUMBER: LAMR4B408R709727DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P434562

CATALOG NUMBER: LAMR4B408R709727DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	92		104	99	95	91		96	92	89		93	90	87		90	88	86
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	85	79	74		92	84	78	74		82	77	73		80	76	72		78	74	71
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	64	60
7	78	68	61	56		77	67	61	56		66	60	56		65	59	56		63	59	55
8	74	63	57	52		73	63	56	52		62	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	51	48		56	51	47
10	66	55	49	45		65	55	49	44		54	48	44		53	48	44		52	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	967271
5°	949273
10°	960249
15°	987397
20°	989130
25°	897363
30°	801804
35°	704215
40°	518469
45°	290401
50°	142920
55°	80083
60°	48647
65°	31988
70°	23658
75°	20969
80°	15627
85°	15284



TEST NUMBER: P434562

CATALOG NUMBER: LAMR4B408R709727DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	6.9
10°-20°	544.7	20.4
20°-30°	755.9	28.3
30°-40°	711.2	26.7
40°-50°	339.5	12.7
50°-60°	89.8	3.4
60°-70°	28.3	1.1
70°-80°	11.6	0.4
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1483.9	55.6
0°-40°	2195.1	82.3
0°-60°	2624.4	98.4
0°-90°	2667.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2667.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1960	
5°	1917	183
15°	1933	545
25°	1648	756
35°	1169	711
45°	416	340
55°	93	90
65°	27	28
75°	11	12
85°	3	3
90°	0	



TEST NUMBER: P434562

CATALOG NUMBER: LAMR4B408R709727DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1960.5
2.5°	1935.9
5°	1916.7
7.5°	1914.0
10°	1916.7
12.5°	1922.2
15°	1933.1
17.5°	1933.1
20°	1883.9
22.5°	1779.8
25°	1648.4
27.5°	1516.9
30°	1407.4
32.5°	1300.6
35°	1169.2
37.5°	999.4
40°	805.0
42.5°	599.7
45°	416.2
47.5°	276.6
50°	186.2
52.5°	128.7
55°	93.1
57.5°	65.7
60°	49.3
62.5°	35.6
65°	27.4
67.5°	19.2
70°	16.4
72.5°	13.7
75°	11.0
77.5°	8.2
80°	5.5
82.5°	5.5
85°	2.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)