

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434275

Luminaire Tested: **LAMR4B408R109730DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R109730DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2881.9 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434275

CATALOG NUMBER: LAMR4B408R109730DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434275

CATALOG NUMBER: LAMR4B408R109730DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	102	102	101	99	99	98	97	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93		
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91		
6	103	98	95	93	102	98	95	92	97	94	92	95	93	91	94	92	91	90		
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	89		
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88		
9	98	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87		
10	97	92	89	87	96	92	89	87	91	88	87	90	88	86	90	88	86	86		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20842128
5°	13999930
10°	3573016
15°	924928
20°	414417
25°	197176
30°	105794
35°	61495
40°	47854
45°	25886
50°	21415
55°	15999
60°	18354
65°	10857
70°	13416
75°	17728
80°	0
85°	0



TEST NUMBER: P434275

CATALOG NUMBER: LAMR4B408R109730DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1942.7	67.4
10°-20°	618.5	21.5
20°-30°	180.6	6.3
30°-40°	68.7	2.4
40°-50°	32.7	1.1
50°-60°	19.7	0.7
60°-70°	10.3	0.4
70°-80°	8.6	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2741.9	95.1
0°-40°	2810.6	97.5
0°-60°	2863.0	99.3
0°-90°	2881.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2881.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	42244	
5°	28268	###
15°	1811	619
25°	362	181
35°	102	69
45°	37	33
55°	19	20
65°	9	10
75°	9	9
85°	0	0
90°	0	



TEST NUMBER: P434275

CATALOG NUMBER: LAMR4B408R109730DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	42243.6
1°	41835.0
2°	40144.8
3°	36922.5
4°	32938.6
5°	28267.6
6°	23104.4
7°	18340.5
8°	13697.4
9°	9982.8
10°	7131.9
11°	5051.8
12°	3742.4
13°	2841.6
14°	2256.6
15°	1810.8
17.5°	1179.4
20°	789.3
22.5°	529.3
25°	362.2
27.5°	250.7
30°	185.7
32.5°	130.0
35°	102.1
37.5°	83.6
40°	74.3
42.5°	55.7
45°	37.1
47.5°	27.9
50°	27.9
52.5°	27.9
55°	18.6
57.5°	18.6
60°	18.6
62.5°	9.3
65°	9.3
67.5°	9.3
70°	9.3
72.5°	9.3
75°	9.3
77.5°	9.3
80°	0.0
82.5°	0.0



TEST NUMBER: P434275

CATALOG NUMBER: LAMR4B408R109730DE01021MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)