

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434564

Luminaire Tested: **LAMR4B408R709730DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R709730DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2858.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434564

CATALOG NUMBER: LAMR4B408R709730DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434564

CATALOG NUMBER: LAMR4B408R709730DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63
8	74	63	57	52	73	63	56	52	62	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1036492
5°	1017174
10°	1028935
15°	1058038
20°	1059853
25°	961546
30°	859173
35°	754568
40°	555567
45°	311194
50°	153129
55°	85846
60°	52101
65°	34206
70°	25389
75°	22303
80°	16763
85°	16417



TEST NUMBER: P434564

CATALOG NUMBER: LAMR4B408R709730DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.3	6.9
10°-20°	583.7	20.4
20°-30°	810.0	28.3
30°-40°	762.1	26.7
40°-50°	363.8	12.7
50°-60°	96.2	3.4
60°-70°	30.3	1.1
70°-80°	12.4	0.4
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1590.0	55.6
0°-40°	2352.1	82.3
0°-60°	2812.1	98.4
0°-90°	2858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2101	
5°	2054	196
15°	2071	584
25°	1766	810
35°	1253	762
45°	446	364
55°	100	96
65°	29	30
75°	12	12
85°	3	3
90°	0	



TEST NUMBER: P434564

CATALOG NUMBER: LAMR4B408R709730DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2100.8
2.5°	2074.4
5°	2053.8
7.5°	2050.9
10°	2053.8
12.5°	2059.7
15°	2071.4
17.5°	2071.4
20°	2018.6
22.5°	1907.1
25°	1766.3
27.5°	1625.5
30°	1508.1
32.5°	1393.7
35°	1252.8
37.5°	1070.9
40°	862.6
42.5°	642.6
45°	446.0
47.5°	296.3
50°	199.5
52.5°	137.9
55°	99.8
57.5°	70.4
60°	52.8
62.5°	38.1
65°	29.3
67.5°	20.5
70°	17.6
72.5°	14.7
75°	11.7
77.5°	8.8
80°	5.9
82.5°	5.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)