

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212082

Luminaire Tested: **LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 939.7 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9503	9503	9503
5°	21034	8995	6321
10°	84224	7811	5282
15°	194147	6208	4634
20°	289814	4402	4134
25°	380123	2939	3688
30°	436352	1857	3222
35°	400096	1183	2791
40°	328093	771	2377
45°	190214	534	1918
50°	53909	392	1582
55°	4932	372	1334
60°	756	426	1104
65°	206	390	802
70°	255	482	623
75°	337	636	636
80°	0	948	502
85°	0	1890	445



TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.9	1.5
10°-20°	125.0	13.3
20°-30°	304.5	32.4
30°-40°	330.0	35.1
40°-50°	149.5	15.9
50°-60°	11.6	1.2
60°-70°	2.4	0.3
70°-80°	1.7	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.4	47.2
0°-40°	773.4	82.3
0°-60°	934.4	99.4
0°-90°	939.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	98	98	98	98	98	
5°	216	160	92	70	65	39
15°	1936	633	62	45	46	563
25°	3556	909	28	27	34	1621
35°	3383	231	10	16	24	2081
45°	1388	29	4	9	14	1096
55°	29	4	2	5	8	67
65°	1	1	2	4	4	1
75°	1	1	2	3	2	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1
2.5°	147.0	144.4	145.7	142.2	140.0	138.3	139.1	138.3	132.6	131.3	126.9
5°	216.3	212.4	212.4	205.0	197.2	192.4	192.4	186.7	174.5	168.8	159.6
7.5°	387.8	379.9	373.4	350.3	320.2	303.1	298.8	274.8	243.8	224.2	201.1
10°	856.2	823.5	800.4	740.2	659.5	609.4	588.0	505.1	406.5	332.4	265.2
12.5°	1439.8	1395.4	1354.8	1256.2	1140.2	1061.2	1018.9	896.8	705.3	568.3	425.3
15°	1935.8	1887.8	1839.8	1719.9	1597.3	1528.8	1451.2	1289.4	1036.4	841.8	633.3
17.5°	2342.7	2315.7	2266.4	2090.6	1936.2	1829.4	1748.7	1537.1	1276.7	1054.7	818.7
20°	2811.2	2744.5	2656.4	2443.1	2232.0	2098.0	1984.6	1726.9	1425.9	1170.7	916.9
22.5°	3205.5	3158.0	3031.5	2750.1	2439.6	2325.3	2186.6	1876.5	1521.8	1220.0	928.2
25°	3556.2	3481.6	3322.9	2988.3	2670.3	2475.8	2305.7	1957.6	1557.2	1223.5	909.4
27.5°	3761.7	3664.4	3477.7	3113.1	2750.1	2535.1	2346.7	1971.6	1534.9	1177.3	841.0
30°	3900.8	3707.1	3500.8	3114.4	2724.8	2505.0	2309.6	1901.3	1442.5	1071.7	725.8
32.5°	3671.4	3559.3	3362.1	2990.5	2587.0	2372.4	2178.3	1749.1	1298.1	915.1	505.1
35°	3383.1	3292.3	3120.9	2751.9	2380.3	2177.9	1972.0	1553.7	1110.1	629.0	231.2
37.5°	3048.1	2977.0	2792.5	2455.3	2128.1	1930.1	1723.8	1324.3	781.6	311.9	140.5
40°	2594.4	2534.2	2382.9	2112.0	1810.6	1622.2	1432.0	990.6	424.4	174.0	91.6
42.5°	2132.5	2081.9	1944.1	1709.8	1445.1	1289.8	1122.3	603.7	211.1	109.5	51.0
45°	1388.4	1325.1	1251.0	1143.7	1012.8	917.3	719.7	291.4	125.2	61.1	29.2
47.5°	796.0	754.2	632.5	499.0	405.2	369.9	269.1	135.7	68.9	35.3	17.9
50°	357.7	330.6	277.4	225.9	163.6	127.8	108.6	68.0	34.0	19.2	12.2
52.5°	88.1	89.9	85.1	74.6	66.3	56.3	48.9	31.8	17.9	11.8	7.9
55°	29.2	29.7	27.0	25.7	23.6	21.8	20.1	14.4	10.9	10.5	3.9
57.5°	10.5	10.5	10.9	10.0	9.6	9.2	8.7	7.4	6.5	3.9	2.2
60°	3.9	3.9	3.9	4.4	4.4	4.4	4.8	4.4	3.1	2.2	1.7
62.5°	1.7	1.7	1.7	1.7	2.2	2.2	2.6	2.2	1.7	1.7	1.3
65°	0.9	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	1.3
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1
2.5°	122.6	120.0	114.7	110.8	107.7	107.3	104.7	100.3	98.6	95.5	92.9
5°	150.9	144.4	136.1	128.2	122.6	119.5	110.4	102.1	97.3	92.5	88.1
7.5°	181.5	166.6	152.2	139.6	131.7	126.9	116.0	102.5	93.8	86.8	81.1
10°	219.8	189.3	164.4	144.8	134.3	127.8	114.7	98.6	87.7	79.4	73.7
12.5°	307.5	224.2	175.8	147.4	134.3	125.2	109.5	93.3	81.1	71.1	65.0
15°	457.6	313.2	208.5	148.7	130.0	119.5	101.6	84.6	72.4	61.9	56.3
17.5°	598.9	412.2	260.4	157.9	127.4	111.2	91.2	74.6	61.9	51.9	47.1
20°	672.2	461.5	289.2	164.9	123.0	100.8	78.9	63.7	51.5	42.7	38.8
22.5°	673.9	457.1	275.2	148.7	106.9	86.4	67.6	52.3	41.9	34.5	31.4
25°	632.5	404.3	226.4	116.0	86.4	72.4	56.3	42.7	32.7	27.5	25.3
27.5°	554.4	327.1	167.1	83.7	67.6	57.6	44.1	32.7	24.9	21.4	20.1
30°	428.8	202.4	92.5	61.9	51.0	43.2	31.8	21.8	18.8	16.6	15.7
32.5°	212.9	99.0	65.4	44.1	34.9	27.5	20.1	16.1	14.4	13.1	12.6
35°	115.6	71.1	41.0	26.6	20.9	17.4	13.5	11.3	10.5	10.0	10.0
37.5°	80.7	42.3	24.9	16.1	13.1	11.8	9.6	8.3	7.9	7.9	7.9
40°	44.5	25.3	15.3	10.5	8.7	7.9	6.5	6.1	6.1	6.1	6.5
42.5°	25.7	15.7	10.5	7.4	6.1	5.7	4.8	4.4	4.8	4.8	5.2
45°	16.6	11.8	7.0	5.2	4.4	3.9	3.5	3.5	3.9	3.9	4.4
47.5°	11.8	8.3	4.8	3.5	2.6	2.6	2.6	2.6	3.1	3.5	3.9
50°	7.0	4.4	2.6	2.2	1.7	1.7	1.7	2.2	2.6	2.6	3.1
52.5°	3.9	2.6	1.7	1.7	1.3	1.3	1.7	1.7	2.2	2.6	3.1
55°	2.2	1.7	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.2	2.6
57.5°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.2	2.2
60°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.2	2.2
62.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	2.2
65°	1.3	1.3	1.3	1.7	1.3	1.7	1.7	1.7	1.7	1.7	2.2
67.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.2
70°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.2
72.5°	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.2
75°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
77.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
80°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
87.5°	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1
2.5°	92.0	89.0	86.8	85.9	84.2	84.6	83.3	82.4	79.8	79.8	78.1
5°	85.1	81.1	78.5	77.2	75.5	75.0	73.7	72.4	69.8	69.4	68.0
7.5°	77.6	73.7	70.7	69.4	67.6	67.2	65.4	64.6	62.4	61.9	60.6
10°	69.8	65.4	62.8	61.5	59.8	59.8	58.4	57.6	55.8	55.8	55.0
12.5°	61.5	57.6	55.8	54.1	53.2	53.2	52.3	51.5	50.2	50.6	50.2
15°	52.8	49.7	48.0	47.1	46.7	46.7	46.2	45.8	44.9	45.8	44.9
17.5°	44.5	42.3	41.0	40.6	40.1	40.1	40.1	40.6	40.1	41.0	41.0
20°	36.6	34.9	34.0	34.0	33.6	34.5	34.5	35.3	35.3	36.6	37.1
22.5°	30.1	28.8	28.4	28.4	28.4	29.2	29.7	30.5	31.0	32.3	33.2
25°	24.0	23.6	23.6	23.6	24.0	24.9	25.7	26.6	27.0	28.8	29.2
27.5°	19.6	19.2	19.6	19.6	20.1	21.4	22.2	23.1	24.0	25.3	26.2
30°	15.7	15.7	16.1	16.6	17.0	17.9	19.2	20.1	20.9	22.2	23.1
32.5°	12.6	13.1	13.5	14.0	14.0	15.3	16.1	17.4	17.9	19.2	20.1
35°	10.5	10.9	11.3	11.8	11.8	13.1	14.0	14.8	15.7	16.6	17.4
37.5°	8.3	8.7	9.6	10.0	10.0	11.3	11.8	12.6	13.5	14.4	15.3
40°	7.0	7.4	8.3	8.3	8.7	9.6	10.0	10.9	11.8	12.6	13.5
42.5°	5.7	6.1	7.0	7.4	7.4	8.3	8.7	9.6	10.0	10.9	11.3
45°	5.2	5.2	6.1	6.1	6.5	7.0	7.9	8.3	8.7	9.6	10.0
47.5°	4.4	4.8	5.2	5.7	5.7	6.1	6.5	7.0	7.4	8.3	8.7
50°	3.5	3.9	4.8	4.8	4.8	5.7	6.1	6.5	6.5	7.0	7.4
52.5°	3.5	3.5	3.9	4.4	4.4	4.8	5.2	5.7	5.7	6.1	6.5
55°	3.1	3.1	3.5	3.9	3.9	4.4	4.8	4.8	5.2	5.2	5.7
57.5°	2.6	3.1	3.5	3.5	3.5	3.9	4.4	4.4	4.8	4.8	5.2
60°	2.6	3.1	3.1	3.5	3.5	3.9	3.9	3.9	4.4	4.4	4.4
62.5°	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.9	3.9	3.9	3.9
65°	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	2.2	2.6	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	2.2	2.2	2.6	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1
72.5°	2.2	2.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
75°	2.2	2.2	2.2	2.2	2.2	2.6	2.6	2.6	2.6	2.2	2.2
77.5°	1.7	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.7
80°	1.7	1.7	2.2	1.7	2.2	2.2	2.2	2.2	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3
85°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	0.9
87.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212082

CATALOG NUMBER: LDSQA4A10930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	98.1	98.1	98.1	98.1	98.1	98.1	98.1	98.1
2.5°	77.2	78.1	77.2	78.1	75.9	76.8	77.6	75.5
5°	67.2	66.3	66.7	67.6	65.9	66.3	66.7	65.0
7.5°	60.2	60.6	59.8	60.6	59.3	59.8	60.2	58.9
10°	54.5	55.0	54.5	55.0	53.7	54.5	55.0	53.7
12.5°	49.3	50.2	49.7	50.6	49.3	50.2	51.0	49.3
15°	45.4	46.2	45.8	46.7	45.8	46.7	47.5	46.2
17.5°	41.4	42.3	42.3	43.2	42.7	43.6	44.5	43.2
20°	37.5	38.8	38.8	39.7	39.7	40.1	41.4	40.1
22.5°	34.0	35.3	35.3	36.2	36.2	37.1	37.9	37.1
25°	30.1	31.8	32.3	33.2	33.2	34.0	35.3	34.5
27.5°	27.5	28.8	29.2	30.1	30.5	31.4	32.3	31.4
30°	24.0	25.7	26.2	27.0	27.5	28.8	29.2	28.8
32.5°	21.4	22.7	23.1	24.0	24.9	25.7	26.6	26.2
35°	18.8	20.1	20.5	21.4	21.8	23.1	24.0	23.6
37.5°	16.6	17.9	18.3	18.8	19.2	20.5	21.4	20.9
40°	14.4	15.3	15.7	16.6	17.0	17.9	18.8	18.8
42.5°	12.6	13.5	14.0	14.4	14.8	15.7	16.6	16.1
45°	10.9	11.8	12.2	12.6	13.1	13.5	14.4	14.0
47.5°	9.2	10.0	10.5	10.9	11.3	11.8	12.6	12.2
50°	7.9	8.7	8.7	9.2	9.6	10.0	10.9	10.5
52.5°	7.0	7.4	7.9	7.9	8.3	8.7	9.6	9.2
55°	6.1	6.5	6.5	7.0	7.0	7.4	7.9	7.9
57.5°	5.2	5.7	5.7	6.1	6.1	6.5	7.0	7.0
60°	4.8	4.8	5.2	5.2	5.2	5.7	5.7	5.7
62.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
65°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	3.1	3.1	3.1	3.1	3.1	2.6	2.6	2.6
70°	2.6	2.6	2.6	2.6	2.6	2.2	2.2	2.2
72.5°	2.6	2.6	2.2	2.2	2.2	2.2	2.2	1.7
75°	2.2	2.2	2.2	2.2	1.7	1.7	1.7	1.7
77.5°	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.3
80°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	0.9
82.5°	1.3	1.3	1.3	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.4	0.4	0.4	0.4
87.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)