

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212072

Luminaire Tested: **LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 914.9 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10346	10346	10346
5°	27200	9851	6428
10°	106623	8529	5351
15°	196293	6720	4744
20°	246660	4753	4320
25°	295028	3132	3848
30°	310250	1969	3367
35°	312758	1183	2921
40°	287802	797	2491
45°	204764	575	2069
50°	84609	437	1703
55°	4881	422	1486
60°	562	407	1221
65°	183	481	871
70°	227	482	595
75°	299	636	636
80°	0	948	725
85°	0	1890	889

TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.8	1.8
10°-20°	134.1	14.7
20°-30°	277.3	30.3
30°-40°	301.9	33.0
40°-50°	165.5	18.1
50°-60°	14.3	1.6
60°-70°	2.3	0.3
70°-80°	1.7	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.1	46.8
0°-40°	730.0	79.8
0°-60°	909.8	99.4
0°-90°	914.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	107	107	107	107	107	
5°	280	191	101	70	66	51
15°	1957	823	67	45	47	547
25°	2760	1094	29	28	36	1246
35°	2645	299	10	16	25	1623
45°	1495	31	4	9	15	1141
55°	29	3	2	5	9	99
65°	1	1	2	3	4	1
75°	1	1	2	2	2	1
85°	0	1	2	1	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
2.5°	167.9	162.0	161.2	162.0	157.8	157.4	158.2	154.9	152.0	149.0	146.5
5°	279.7	267.5	263.7	258.7	246.2	242.0	241.1	227.7	214.8	202.6	191.3
7.5°	543.4	519.1	506.1	481.0	442.5	425.3	416.1	372.2	331.1	293.9	260.0
10°	1083.9	1020.2	989.3	941.9	857.8	816.4	786.2	675.7	566.8	462.2	370.1
12.5°	1581.6	1546.5	1500.8	1475.7	1339.2	1286.9	1237.1	1083.9	918.1	749.0	581.1
15°	1957.2	1905.7	1857.1	1845.4	1738.2	1677.1	1621.8	1463.2	1266.0	1050.8	822.6
17.5°	2177.8	2140.9	2094.9	2072.7	1947.1	1897.7	1834.9	1681.3	1489.5	1275.2	1010.2
20°	2392.6	2338.1	2273.2	2239.7	2100.8	2043.8	1972.7	1811.1	1608.0	1380.3	1115.3
22.5°	2588.9	2518.6	2426.5	2374.6	2218.4	2155.6	2076.1	1901.1	1681.3	1420.9	1124.1
25°	2760.1	2696.5	2573.8	2483.0	2298.8	2224.7	2132.2	1949.2	1707.6	1417.5	1094.3
27.5°	2792.8	2750.1	2640.0	2534.9	2326.8	2244.4	2148.5	1959.3	1689.2	1371.1	1014.4
30°	2773.5	2727.5	2639.1	2532.0	2315.1	2231.8	2132.2	1916.6	1617.2	1262.6	867.8
32.5°	2727.0	2687.3	2581.8	2468.7	2257.3	2170.7	2065.6	1816.5	1493.7	1090.1	638.4
35°	2644.6	2584.7	2457.4	2364.5	2165.6	2076.5	1948.0	1682.9	1309.1	783.7	299.3
37.5°	2476.7	2418.5	2326.8	2241.0	2047.2	1942.1	1806.5	1497.1	970.4	427.4	185.0
40°	2275.8	2225.5	2145.6	2062.2	1862.5	1741.6	1592.1	1170.1	571.0	240.7	113.9
42.5°	2057.2	2005.3	1914.9	1817.8	1600.1	1472.4	1310.8	757.3	301.0	141.9	62.0
45°	1494.6	1448.1	1382.4	1312.4	1186.4	1094.3	881.7	397.7	166.6	75.4	30.6
47.5°	1022.7	967.5	846.1	699.1	566.8	484.8	364.6	172.5	85.4	37.7	18.0
50°	561.4	502.8	440.8	343.3	229.8	188.8	146.9	83.3	38.5	18.8	10.0
52.5°	137.7	121.8	111.4	102.6	81.2	73.3	62.0	34.7	17.6	10.5	7.1
55°	28.9	26.8	25.5	25.1	23.0	22.2	19.3	13.4	9.6	6.7	3.3
57.5°	8.4	8.0	8.4	8.4	8.4	8.0	8.0	5.9	5.4	3.3	2.1
60°	2.9	2.9	2.9	3.3	3.3	3.3	3.8	3.8	2.9	2.1	1.7
62.5°	1.3	1.3	1.3	1.7	1.7	2.1	2.1	2.1	1.7	1.7	1.3
65°	0.8	0.8	0.8	0.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
70°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8	1.3
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.8	0.8	0.8	0.8
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	0.8
85°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
2.5°	139.4	135.2	130.2	124.8	123.9	121.0	116.8	110.9	108.8	104.7	100.9
5°	175.0	163.7	152.0	141.5	138.2	133.5	126.0	115.5	108.8	101.3	95.0
7.5°	222.7	196.8	172.9	154.1	148.2	140.7	128.9	115.5	105.5	95.0	86.7
10°	286.4	233.6	192.6	162.0	152.4	142.3	126.8	110.5	98.8	86.7	77.9
12.5°	409.0	287.6	211.0	166.2	152.8	139.8	120.2	102.6	89.2	77.0	68.2
15°	581.5	390.2	248.3	169.1	148.6	132.7	109.7	91.7	78.3	67.0	58.6
17.5°	727.2	487.3	298.1	177.5	145.7	123.5	97.5	79.1	66.1	56.1	49.4
20°	798.4	530.8	320.7	178.8	137.3	109.7	83.3	65.7	54.4	46.1	40.2
22.5°	790.0	516.2	299.7	156.6	116.0	92.5	69.1	53.2	43.5	36.8	32.7
25°	733.9	452.6	244.5	119.7	90.4	74.9	54.0	41.4	33.9	29.3	26.0
27.5°	639.7	363.4	178.3	84.6	68.7	56.9	40.2	31.8	26.0	22.6	20.5
30°	492.7	232.3	102.6	60.7	49.8	40.6	30.1	23.0	19.7	17.6	15.9
32.5°	254.1	113.0	68.2	43.5	35.2	29.3	20.9	16.7	14.7	13.4	12.6
35°	139.4	80.4	47.3	28.0	22.6	18.8	14.2	11.7	10.9	10.0	10.0
37.5°	95.9	49.8	26.4	16.7	13.8	11.7	9.6	8.4	8.0	8.0	8.0
40°	55.3	26.4	15.1	10.5	8.8	8.0	6.7	6.3	6.3	6.3	6.7
42.5°	28.5	15.5	10.0	7.1	6.3	5.4	4.6	4.6	4.6	5.0	5.4
45°	16.7	10.5	6.7	4.6	4.2	3.8	3.3	3.3	3.8	4.2	4.6
47.5°	10.5	7.1	4.2	2.9	2.5	2.5	2.5	2.5	2.9	3.3	3.8
50°	7.1	3.8	2.5	1.7	1.7	1.7	1.7	2.1	2.5	2.9	3.3
52.5°	3.8	2.1	1.7	1.3	1.3	1.3	1.7	1.7	2.1	2.5	2.9
55°	2.1	1.7	1.3	1.3	1.3	1.3	1.3	1.7	2.1	2.5	2.9
57.5°	1.7	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.5
60°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.5
62.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.1
65°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	2.1	2.1
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	2.1
70°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	2.1
72.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7
75°	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	2.1
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7
85°	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7	1.7
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
2.5°	98.8	95.5	92.1	92.1	90.4	87.9	87.1	84.6	82.9	82.1	81.2
5°	90.4	85.4	80.8	80.4	78.3	75.4	74.1	71.6	69.9	69.1	68.7
7.5°	80.8	75.8	71.2	70.3	68.7	66.6	65.3	63.2	62.4	61.5	61.1
10°	71.6	66.6	63.2	62.4	61.1	59.4	58.2	56.9	56.1	55.7	55.7
12.5°	62.4	58.6	55.7	54.8	54.0	52.7	51.9	51.1	50.7	50.7	50.7
15°	54.0	50.7	48.1	48.1	47.3	46.5	46.5	45.6	45.2	45.6	46.1
17.5°	45.6	43.1	41.0	41.0	40.6	40.2	40.2	40.2	40.6	41.0	41.9
20°	37.7	35.6	34.7	34.7	34.3	34.7	34.7	35.2	35.6	36.8	38.1
22.5°	30.6	29.3	28.5	28.9	28.9	29.3	29.7	30.6	31.4	32.7	33.9
25°	24.7	23.9	23.4	23.9	24.3	24.7	25.5	26.4	27.6	28.9	30.6
27.5°	19.7	19.3	19.3	19.7	20.1	20.9	22.2	23.0	24.3	25.5	27.2
30°	15.9	15.5	15.9	16.7	17.2	18.0	18.8	20.1	21.4	22.6	24.3
32.5°	12.6	13.0	13.4	13.8	14.2	15.5	16.3	17.2	18.4	19.7	21.4
35°	10.5	10.9	11.3	11.7	12.1	13.0	13.8	14.7	15.9	17.2	18.8
37.5°	8.4	8.8	9.2	10.0	10.5	10.9	12.1	12.6	13.8	14.7	16.3
40°	7.1	7.5	8.0	8.4	8.8	9.6	10.5	10.9	11.7	13.0	14.2
42.5°	5.9	6.3	6.7	7.1	7.5	8.4	8.8	9.6	10.5	11.3	12.1
45°	5.0	5.4	5.9	6.3	6.7	7.1	7.5	8.4	8.8	9.6	10.5
47.5°	4.2	4.6	5.4	5.4	5.9	6.3	6.7	7.1	8.0	8.4	9.2
50°	3.8	4.2	4.6	5.0	5.0	5.4	5.9	6.3	6.7	7.1	8.0
52.5°	3.3	3.8	4.2	4.2	4.6	5.0	5.4	5.4	5.9	6.3	6.7
55°	2.9	3.3	3.8	3.8	4.2	4.6	4.6	5.0	5.4	5.4	5.9
57.5°	2.9	2.9	3.3	3.3	3.8	3.8	4.2	4.6	4.6	5.0	5.4
60°	2.5	2.9	2.9	3.3	3.3	3.8	3.8	4.2	4.2	4.6	4.6
62.5°	2.5	2.5	2.9	2.9	3.3	3.3	3.8	3.8	3.8	4.2	4.2
65°	2.5	2.5	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.8	3.8
67.5°	2.1	2.5	2.5	2.9	2.9	2.9	2.9	2.9	3.3	3.3	3.3
70°	2.1	2.5	2.5	2.5	2.5	2.9	2.9	2.9	2.9	2.9	2.9
72.5°	2.1	2.1	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.1	2.1	2.1	2.1	2.1	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
80°	1.7	1.7	1.7	1.7	1.7	2.1	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3
85°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.3	1.3	1.3	1.3
87.5°	1.7	1.7	1.7	1.3	1.3	1.3	1.3	1.3	1.3	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212072

CATALOG NUMBER: LDSQA4A10927D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
2.5°	80.0	79.1	80.0	79.1	79.1	77.4	78.7	77.9
5°	67.4	66.6	67.4	67.0	66.1	65.7	66.6	66.1
7.5°	60.3	59.4	60.3	60.3	59.4	59.0	59.9	59.4
10°	54.8	54.4	54.8	54.8	54.4	54.0	54.8	54.4
12.5°	50.2	49.8	50.7	50.7	50.2	50.2	51.1	50.2
15°	46.1	46.1	46.9	46.9	46.9	46.9	47.7	47.3
17.5°	41.9	42.7	43.5	44.0	44.0	44.0	44.8	44.8
20°	38.5	39.4	40.2	40.6	41.0	41.0	41.9	41.9
22.5°	34.7	35.6	36.8	37.3	37.7	38.1	38.9	38.9
25°	31.4	32.2	33.5	33.9	34.7	35.2	36.0	36.0
27.5°	28.0	29.3	30.1	31.0	31.4	32.2	33.1	33.1
30°	25.1	26.4	27.2	28.0	28.5	29.3	30.1	30.1
32.5°	22.2	23.4	24.3	25.1	26.0	26.4	27.6	27.6
35°	19.7	20.5	21.8	22.2	23.0	23.9	24.7	24.7
37.5°	17.2	18.0	18.8	19.7	20.5	20.9	21.8	22.2
40°	15.1	15.9	16.7	17.2	18.0	18.8	19.3	19.7
42.5°	13.0	13.8	14.7	15.1	15.9	16.3	17.2	17.2
45°	11.3	12.1	12.6	13.0	13.8	14.2	15.1	15.1
47.5°	9.6	10.5	10.9	11.3	11.7	12.1	13.0	13.0
50°	8.4	8.8	9.2	9.6	10.0	10.9	11.3	11.3
52.5°	7.1	8.0	8.0	8.4	8.8	9.2	9.6	10.0
55°	6.3	6.7	7.1	7.1	7.5	8.0	8.4	8.8
57.5°	5.4	5.9	6.3	6.3	6.7	6.7	7.1	7.5
60°	5.0	5.0	5.4	5.4	5.4	5.9	5.9	6.3
62.5°	4.2	4.2	4.6	4.6	4.6	4.6	4.6	4.6
65°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	3.3	3.3	3.3	3.3	2.9	2.9	2.9	2.9
70°	2.9	2.9	2.9	2.9	2.5	2.5	2.5	2.1
72.5°	2.5	2.5	2.5	2.5	2.1	2.1	1.7	1.7
75°	2.1	2.1	2.1	2.1	2.1	1.7	1.7	1.7
77.5°	2.1	1.7	1.7	1.7	1.7	1.7	1.7	1.3
80°	1.7	1.7	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	0.8	0.8	0.8	0.8
85°	1.3	0.8	0.8	0.8	0.8	0.8	0.8	0.8
87.5°	0.8	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)