

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212090

Luminaire Tested: **LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 803.2 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	84
3	99	91	85	81	97	90	84	80		87	83	79		85	81	77		82	79	76
4	92	83	77	72	90	82	76	71		80	75	70		78	73	70		76	72	69
5	86	76	69	64	85	75	69	64		73	68	63		72	67	63		70	66	62
6	81	70	63	58	79	69	62	57		67	61	57		66	61	57		64	60	56
7	75	64	57	52	74	63	57	52		62	56	51		61	55	51		59	55	51
8	70	59	52	47	69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	54	47	42	65	54	47	42		53	46	42		52	46	42		51	46	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8399	8399	8399
5°	16084	8003	6496
10°	52608	7092	5528
15°	128836	5857	4884
20°	242742	4464	4381
25°	406343	3164	3827
30°	514756	2181	3266
35°	469043	1407	2767
40°	308896	1012	2352
45°	133810	671	1945
50°	23737	467	1598
55°	3817	372	1351
60°	949	349	1027
65°	298	413	802
70°	255	510	623
75°	337	487	487
80°	0	725	502
85°	0	1445	445



TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	1.4
10°-20°	89.3	11.1
20°-30°	269.1	33.5
30°-40°	306.3	38.1
40°-50°	113.3	14.1
50°-60°	9.0	1.1
60°-70°	2.4	0.3
70°-80°	1.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.6	46.0
0°-40°	675.9	84.1
0°-60°	798.1	99.4
0°-90°	803.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	87	87	87	87	87	
5°	165	122	82	69	67	27
15°	1285	434	58	46	49	403
25°	3802	634	30	29	36	1735
35°	3966	222	12	16	23	2358
45°	977	26	5	9	14	827
55°	23	5	2	5	8	37
65°	1	1	2	4	4	2
75°	1	1	1	2	1	1
85°	0	1	1	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
2.5°	111.5	112.4	111.5	109.7	109.7	107.5	106.6	105.7	103.5	102.2	100.4
5°	165.4	162.8	160.6	155.3	153.5	148.6	145.1	140.2	133.6	127.8	121.6
7.5°	283.1	279.1	270.7	254.8	245.1	233.1	223.8	208.3	188.4	172.1	155.7
10°	534.8	517.5	497.6	461.8	435.7	407.8	385.7	344.1	294.2	253.0	213.2
12.5°	861.7	863.0	825.9	765.3	717.0	667.9	629.9	552.9	464.5	387.1	310.5
15°	1284.6	1260.2	1221.8	1128.9	1032.4	961.2	900.6	783.8	658.7	545.4	433.9
17.5°	1730.0	1740.2	1650.4	1498.7	1346.1	1239.5	1147.9	970.9	822.3	682.1	545.9
20°	2354.6	2284.7	2156.4	1910.5	1673.4	1519.0	1383.2	1153.6	946.2	767.9	614.9
22.5°	3074.7	2961.9	2701.0	2354.6	1995.9	1782.2	1592.9	1277.0	1024.9	811.7	638.3
25°	3801.5	3715.3	3299.5	2781.9	2267.9	1991.0	1745.9	1360.7	1062.5	821.9	634.3
27.5°	4362.4	4221.7	3748.0	3073.4	2430.2	2103.4	1817.2	1386.3	1054.6	797.1	596.7
30°	4601.7	4423.9	3898.8	3139.8	2431.6	2084.8	1781.8	1335.4	997.9	734.3	525.9
32.5°	4454.0	4248.7	3719.2	2956.2	2265.2	1939.7	1645.1	1225.3	904.2	635.6	395.0
35°	3966.1	3761.7	3271.1	2593.9	1999.8	1715.4	1459.3	1081.5	770.1	471.1	222.1
37.5°	3247.7	3073.4	2722.6	2174.1	1685.3	1454.4	1241.2	911.2	573.7	270.3	111.5
40°	2442.6	2320.1	2109.5	1724.3	1364.2	1188.6	1017.0	698.0	348.6	135.8	63.3
42.5°	1693.3	1613.7	1508.0	1275.7	1052.3	931.6	794.0	466.2	179.1	74.8	39.4
45°	976.7	926.7	897.5	798.4	711.3	652.5	530.8	251.3	90.7	44.7	26.1
47.5°	431.3	398.1	384.0	342.4	318.5	302.6	240.2	107.0	48.7	28.8	21.7
50°	157.5	157.5	157.9	138.9	113.7	102.2	80.1	47.3	27.4	22.6	15.9
52.5°	55.7	54.9	57.1	54.0	47.3	42.5	35.4	23.9	16.8	14.2	8.8
55°	22.6	21.7	22.6	21.2	19.9	18.6	16.4	12.8	10.6	8.8	4.9
57.5°	10.2	10.2	10.6	10.2	10.2	9.3	8.4	9.7	7.5	4.9	3.1
60°	4.9	4.9	5.3	5.3	5.3	4.9	4.9	5.3	4.4	3.1	2.2
62.5°	2.2	2.2	2.7	2.7	2.7	2.7	2.7	3.1	2.2	1.8	1.3
65°	1.3	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	1.3
80°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
2.5°	98.6	97.3	94.7	93.3	91.6	90.2	89.4	87.6	85.8	84.5	83.6
5°	115.9	111.0	105.3	100.9	97.3	95.1	91.6	88.5	84.9	82.3	80.1
7.5°	141.1	129.2	116.3	107.5	102.6	98.2	92.0	86.7	81.8	78.3	75.2
10°	180.5	154.8	132.3	115.0	106.6	100.4	90.7	83.2	77.0	72.1	69.0
12.5°	245.9	193.3	153.5	124.3	111.5	102.2	88.5	78.3	70.8	65.9	61.9
15°	335.7	249.9	182.7	135.4	117.2	104.0	84.9	72.5	64.1	58.4	54.9
17.5°	420.2	309.2	215.9	148.6	123.0	104.8	80.1	65.0	56.2	50.9	47.3
20°	473.3	347.7	238.0	156.1	124.7	102.2	73.4	57.1	48.2	43.3	39.8
22.5°	485.7	352.1	236.2	149.1	117.2	94.2	64.1	49.1	40.7	36.3	33.2
25°	467.6	327.3	211.4	128.7	100.0	79.2	53.5	39.8	33.6	29.6	27.4
27.5°	422.0	278.7	167.2	96.9	74.8	58.4	40.7	31.0	27.0	23.9	22.6
30°	340.2	196.0	104.8	60.2	47.8	38.5	29.2	23.9	20.8	19.5	18.1
32.5°	206.1	100.9	55.3	35.8	30.1	26.1	21.2	17.7	15.9	15.0	14.6
35°	98.2	53.1	34.1	24.3	21.2	18.6	15.5	13.3	12.4	11.9	11.9
37.5°	55.7	34.5	23.0	16.4	14.6	12.8	11.5	10.2	9.7	9.7	9.7
40°	35.4	22.1	15.0	11.9	10.6	9.7	8.8	8.0	8.0	8.0	8.0
42.5°	23.0	15.9	11.5	8.8	8.0	7.5	6.6	6.2	6.2	6.2	6.6
45°	18.1	13.3	9.3	7.1	6.2	5.8	5.3	4.9	4.9	4.9	5.3
47.5°	15.5	9.3	6.2	4.9	4.0	4.0	3.5	3.5	3.5	4.0	4.4
50°	9.3	5.8	4.0	3.1	2.7	2.7	2.7	2.7	2.7	3.1	3.5
52.5°	5.3	3.5	2.7	2.2	1.8	1.8	1.8	1.8	2.2	2.7	2.7
55°	3.5	2.7	1.8	1.8	1.3	1.3	1.3	1.8	1.8	2.2	2.7
57.5°	2.2	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.8	2.2	2.2
60°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
62.5°	1.3	1.3	1.8	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
65°	1.3	1.3	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.8	2.2
67.5°	1.3	1.3	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8	1.8
70°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.8	1.8
72.5°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.8	1.8
75°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8
77.5°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8
80°	1.3	1.3	1.3	1.8	1.3	1.8	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
2.5°	82.3	81.4	80.1	79.6	80.1	79.6	77.4	77.0	76.1	76.1	76.1
5°	77.9	76.5	74.8	73.9	73.9	73.0	70.8	70.3	69.0	69.0	68.6
7.5°	72.5	70.8	68.6	67.7	67.7	66.8	64.6	63.7	62.8	62.8	62.4
10°	66.4	64.1	61.9	61.5	61.0	59.7	58.4	57.9	56.6	57.1	56.6
12.5°	59.3	57.5	55.7	54.9	54.9	53.5	52.6	52.2	51.8	51.8	51.8
15°	52.6	50.4	48.7	48.2	48.2	47.8	46.9	46.9	46.0	46.9	46.9
17.5°	45.1	43.3	42.9	42.0	42.5	42.0	41.1	41.6	41.6	42.0	42.5
20°	38.0	36.7	36.3	35.8	36.3	36.3	35.8	36.3	36.7	38.0	38.9
22.5°	31.8	31.0	31.0	30.5	31.0	31.4	31.0	31.8	32.7	33.6	34.9
25°	26.5	26.1	26.1	26.1	26.5	27.0	27.4	28.3	28.8	30.1	31.0
27.5°	21.7	21.7	21.7	22.1	22.6	23.0	23.4	24.8	25.2	26.5	27.4
30°	18.1	17.7	18.1	18.6	19.0	19.9	20.3	21.2	21.7	23.0	23.9
32.5°	14.6	15.0	15.5	15.9	16.4	16.8	17.3	18.1	19.0	19.9	20.8
35°	12.4	12.4	12.8	13.3	13.7	14.6	15.0	15.5	16.4	17.3	17.7
37.5°	10.2	10.6	11.1	11.5	11.9	12.4	12.8	13.3	13.7	14.6	15.5
40°	8.4	8.8	9.3	9.7	9.7	10.6	10.6	11.5	11.9	12.8	13.7
42.5°	7.1	7.5	8.0	8.4	8.4	8.8	9.3	9.7	10.2	11.1	11.9
45°	5.8	6.2	6.6	7.1	7.1	7.5	8.0	8.4	8.8	9.7	10.2
47.5°	4.9	5.3	5.8	6.2	6.2	6.6	7.1	7.5	7.5	8.4	8.8
50°	4.0	4.4	4.9	5.3	5.3	5.8	6.2	6.6	6.6	7.1	7.5
52.5°	3.1	3.5	4.4	4.4	4.9	5.3	5.3	5.8	5.8	6.2	6.6
55°	3.1	3.5	4.0	4.0	4.4	4.9	4.9	5.3	5.3	5.3	5.8
57.5°	2.7	3.1	3.5	4.0	4.0	4.4	4.4	4.4	4.4	4.9	4.9
60°	2.7	3.1	3.1	3.5	3.5	4.0	4.0	4.0	4.0	4.4	4.4
62.5°	2.7	2.7	3.1	3.1	3.5	3.5	3.5	4.0	4.0	4.0	4.0
65°	2.2	2.7	3.1	3.1	3.1	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	2.2	2.7	2.7	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	2.2	2.2	2.7	2.7	2.7	3.1	3.1	3.1	2.7	3.1	2.7
72.5°	1.8	2.2	2.2	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	1.8	2.2	2.2	2.2	2.2	2.7	2.7	2.2	2.2	2.2	2.2
77.5°	1.8	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.8
80°	1.8	1.8	1.8	1.8	2.2	2.2	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3
85°	1.3	1.3	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3	0.9
87.5°	1.3	1.3	1.3	1.8	1.3	1.3	1.3	1.3	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212090

CATALOG NUMBER: LDSQA4A10935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	86.7	86.7	86.7	86.7	86.7	86.7	86.7	86.7
2.5°	74.8	74.3	74.8	74.3	74.3	74.8	73.4	74.3
5°	67.7	66.8	67.2	66.8	66.4	66.8	65.9	66.8
7.5°	61.5	61.0	61.0	61.0	60.6	61.0	60.2	61.0
10°	56.2	55.7	55.7	55.7	55.7	56.2	55.3	56.2
12.5°	50.9	50.9	51.3	50.9	51.3	51.8	50.9	51.8
15°	46.4	46.9	47.3	47.3	47.8	48.2	47.8	48.7
17.5°	42.9	43.3	44.2	44.2	44.7	45.6	45.1	46.0
20°	39.4	39.8	40.7	40.7	41.1	42.0	41.6	42.5
22.5°	35.4	36.3	36.7	37.2	37.6	38.5	38.0	38.9
25°	31.4	32.7	33.2	33.6	34.1	34.9	34.9	35.8
27.5°	28.3	29.2	29.6	30.1	31.0	31.8	31.8	32.3
30°	24.8	25.7	26.5	27.0	27.4	28.3	28.3	29.2
32.5°	21.7	22.6	23.0	23.4	24.3	25.2	25.7	26.1
35°	18.6	19.9	20.3	21.2	21.7	23.0	23.0	23.4
37.5°	16.4	17.3	18.1	18.6	19.5	20.3	20.3	21.2
40°	14.6	15.5	15.9	16.4	17.3	18.1	18.1	18.6
42.5°	12.4	13.7	14.2	14.6	15.0	15.9	16.4	16.8
45°	11.1	11.5	11.9	12.4	12.8	13.7	13.7	14.2
47.5°	9.3	9.7	10.2	10.6	11.1	11.5	11.9	12.4
50°	8.0	8.4	8.8	8.8	9.3	10.2	10.2	10.6
52.5°	6.6	7.1	7.5	7.5	8.0	8.8	8.8	9.3
55°	5.8	6.2	6.6	6.6	7.1	7.5	7.5	8.0
57.5°	5.3	5.3	5.8	5.8	6.2	6.2	6.6	6.6
60°	4.4	4.9	4.9	4.9	5.3	5.3	5.3	5.3
62.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4
65°	3.5	3.5	3.5	3.5	3.5	3.5	3.1	3.5
67.5°	3.1	3.1	3.1	3.1	2.7	2.7	2.7	2.7
70°	2.7	2.7	2.7	2.7	2.7	2.2	2.2	2.2
72.5°	2.2	2.2	2.2	2.2	2.2	1.8	1.8	1.8
75°	2.2	2.2	1.8	1.8	1.8	1.8	1.8	1.3
77.5°	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9
82.5°	1.3	0.9	0.9	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.4	0.4	0.4	0.4
87.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)