

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212076

Luminaire Tested: **LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 795.6 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	84
3	99	91	85	81	97	90	84	80		87	83	79		85	81	77		82	79	76
4	92	83	77	72	90	82	76	71		80	75	70		78	73	70		76	72	69
5	86	76	69	64	85	75	69	64		73	68	63		72	67	63		70	66	62
6	81	70	63	58	79	69	62	57		67	61	57		66	61	57		64	60	56
7	75	64	57	52	74	63	57	52		62	56	51		61	55	51		59	55	51
8	70	59	52	47	69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	54	47	42	65	54	47	42		53	46	42		52	46	42		51	46	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8322	8322	8322
5°	15939	7926	6438
10°	52107	7024	5469
15°	127613	5797	4834
20°	240433	4423	4340
25°	402484	3143	3795
30°	509867	2159	3233
35°	464585	1396	2744
40°	305962	999	2327
45°	132536	658	1918
50°	23511	467	1582
55°	3766	372	1334
60°	930	349	1027
65°	298	413	802
70°	255	510	623
75°	337	487	487
80°	0	725	502
85°	0	1445	445



TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.0	1.4
10°-20°	88.5	11.1
20°-30°	266.6	33.5
30°-40°	303.4	38.1
40°-50°	112.2	14.1
50°-60°	8.9	1.1
60°-70°	2.4	0.3
70°-80°	1.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.1	46.0
0°-40°	669.5	84.1
0°-60°	790.5	99.4
0°-90°	795.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	86	86	86	86	86	
5°	164	120	82	68	66	27
15°	1272	430	58	46	48	399
25°	3765	628	29	28	36	1719
35°	3928	220	12	16	23	2336
45°	967	26	5	9	14	819
55°	22	5	2	5	8	37
65°	1	1	2	4	4	2
75°	1	1	1	2	1	1
85°	0	1	1	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9
2.5°	110.4	111.3	110.4	108.7	108.7	106.5	105.6	104.7	102.5	101.2	99.5
5°	163.9	161.2	159.0	153.8	152.0	147.2	143.7	138.9	132.3	126.6	120.5
7.5°	280.4	276.5	268.1	252.4	242.7	230.9	221.7	206.4	186.6	170.4	154.2
10°	529.7	512.6	492.9	457.4	431.6	404.0	382.1	340.9	291.4	250.6	211.2
12.5°	853.5	854.8	818.0	758.0	710.2	661.6	623.9	547.7	460.0	383.4	307.6
15°	1272.4	1248.3	1210.1	1118.1	1022.6	952.1	892.1	776.4	652.4	540.2	429.8
17.5°	1713.6	1723.6	1634.7	1484.4	1333.3	1227.7	1137.0	961.7	814.5	675.6	540.7
20°	2332.2	2263.0	2135.9	1892.3	1657.5	1504.6	1370.1	1142.7	937.2	760.6	609.0
22.5°	3045.5	2933.8	2675.3	2332.2	1976.9	1765.3	1577.7	1264.9	1015.2	804.0	632.2
25°	3765.4	3679.9	3268.1	2755.5	2246.3	1972.1	1729.3	1347.7	1052.4	814.1	628.3
27.5°	4320.9	4181.6	3712.4	3044.2	2407.1	2083.4	1799.9	1373.1	1044.5	789.5	591.1
30°	4558.0	4381.8	3861.8	3109.9	2408.5	2065.0	1764.8	1322.7	988.4	727.3	520.9
32.5°	4411.6	4208.3	3683.9	2928.1	2243.7	1921.2	1629.4	1213.7	895.6	629.6	391.3
35°	3928.4	3726.0	3240.1	2569.3	1980.8	1699.1	1445.4	1071.3	762.8	466.6	219.9
37.5°	3216.8	3044.2	2696.8	2153.5	1669.3	1440.6	1229.4	902.6	568.3	267.7	110.4
40°	2419.4	2298.0	2089.5	1707.9	1351.2	1177.3	1007.3	691.4	345.3	134.5	62.7
42.5°	1677.2	1598.3	1493.6	1263.6	1042.3	922.7	786.5	461.8	177.4	74.0	39.0
45°	967.4	917.9	889.0	790.8	704.5	646.3	525.8	248.9	89.8	44.3	25.9
47.5°	427.2	394.3	380.3	339.1	315.5	299.7	237.9	106.0	48.2	28.5	21.5
50°	156.0	156.0	156.4	137.6	112.6	101.2	79.3	46.9	27.2	22.3	15.8
52.5°	55.2	54.3	56.5	53.5	46.9	42.1	35.1	23.7	16.6	14.0	8.8
55°	22.3	21.5	22.3	21.0	19.7	18.4	16.2	12.7	10.5	8.8	4.8
57.5°	10.1	10.1	10.5	10.1	10.1	9.2	8.3	9.6	7.4	4.8	3.1
60°	4.8	4.8	5.3	5.3	5.3	4.8	4.8	5.3	4.4	3.1	2.2
62.5°	2.2	2.2	2.6	2.6	2.6	2.6	2.6	3.1	2.2	1.8	1.3
65°	1.3	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	1.3
80°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9
2.5°	97.7	96.4	93.8	92.4	90.7	89.4	88.5	86.8	85.0	83.7	82.8
5°	114.8	110.0	104.3	99.9	96.4	94.2	90.7	87.6	84.1	81.5	79.3
7.5°	139.8	127.9	115.2	106.5	101.6	97.3	91.1	85.9	81.1	77.6	74.5
10°	178.8	153.3	131.0	113.9	105.6	99.5	89.8	82.4	76.2	71.4	68.4
12.5°	243.6	191.5	152.0	123.1	110.4	101.2	87.6	77.6	70.1	65.3	61.3
15°	332.5	247.5	181.0	134.1	116.1	103.0	84.1	71.9	63.5	57.8	54.3
17.5°	416.2	306.3	213.8	147.2	121.8	103.8	79.3	64.4	55.6	50.4	46.9
20°	468.8	344.4	235.7	154.7	123.6	101.2	72.7	56.5	47.8	42.9	39.4
22.5°	481.1	348.8	234.0	147.7	116.1	93.3	63.5	48.6	40.3	35.9	32.9
25°	463.1	324.2	209.4	127.5	99.0	78.4	53.0	39.4	33.3	29.4	27.2
27.5°	418.0	276.0	165.6	96.0	74.0	57.8	40.3	30.7	26.7	23.7	22.3
30°	336.9	194.1	103.8	59.6	47.3	38.1	28.9	23.7	20.6	19.3	18.0
32.5°	204.2	99.9	54.8	35.5	29.8	25.9	21.0	17.5	15.8	14.9	14.5
35°	97.3	52.6	33.7	24.1	21.0	18.4	15.3	13.1	12.3	11.8	11.8
37.5°	55.2	34.2	22.8	16.2	14.5	12.7	11.4	10.1	9.6	9.6	9.6
40°	35.1	21.9	14.9	11.8	10.5	9.6	8.8	7.9	7.9	7.9	7.9
42.5°	22.8	15.8	11.4	8.8	7.9	7.4	6.6	6.1	6.1	6.1	6.6
45°	18.0	13.1	9.2	7.0	6.1	5.7	5.3	4.8	4.8	4.8	5.3
47.5°	15.3	9.2	6.1	4.8	3.9	3.9	3.5	3.5	3.5	3.9	4.4
50°	9.2	5.7	3.9	3.1	2.6	2.6	2.6	2.6	2.6	3.1	3.5
52.5°	5.3	3.5	2.6	2.2	1.8	1.8	1.8	1.8	2.2	2.6	2.6
55°	3.5	2.6	1.8	1.8	1.3	1.3	1.3	1.8	1.8	2.2	2.6
57.5°	2.2	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.8	2.2	2.2
60°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
62.5°	1.3	1.3	1.8	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
65°	1.3	1.3	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.8	2.2
67.5°	1.3	1.3	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8	1.8
70°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.8	1.8
72.5°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.8	1.8
75°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8
77.5°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.8
80°	1.3	1.3	1.3	1.8	1.3	1.8	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9
2.5°	81.5	80.6	79.3	78.9	79.3	78.9	76.7	76.2	75.4	75.4	75.4
5°	77.1	75.8	74.0	73.2	73.2	72.3	70.1	69.7	68.4	68.4	67.9
7.5°	71.9	70.1	67.9	67.0	67.0	66.2	64.0	63.1	62.2	62.2	61.8
10°	65.7	63.5	61.3	60.9	60.5	59.1	57.8	57.4	56.1	56.5	56.1
12.5°	58.7	57.0	55.2	54.3	54.3	53.0	52.1	51.7	51.3	51.3	51.3
15°	52.1	49.9	48.2	47.8	47.8	47.3	46.4	46.4	45.6	46.4	46.4
17.5°	44.7	42.9	42.5	41.6	42.1	41.6	40.7	41.2	41.2	41.6	42.1
20°	37.7	36.4	35.9	35.5	35.9	35.9	35.5	35.9	36.4	37.7	38.6
22.5°	31.5	30.7	30.7	30.2	30.7	31.1	30.7	31.5	32.4	33.3	34.6
25°	26.3	25.9	25.9	25.9	26.3	26.7	27.2	28.0	28.5	29.8	30.7
27.5°	21.5	21.5	21.5	21.9	22.3	22.8	23.2	24.5	25.0	26.3	27.2
30°	18.0	17.5	18.0	18.4	18.8	19.7	20.2	21.0	21.5	22.8	23.7
32.5°	14.5	14.9	15.3	15.8	16.2	16.6	17.1	18.0	18.8	19.7	20.6
35°	12.3	12.3	12.7	13.1	13.6	14.5	14.9	15.3	16.2	17.1	17.5
37.5°	10.1	10.5	11.0	11.4	11.8	12.3	12.7	13.1	13.6	14.5	15.3
40°	8.3	8.8	9.2	9.6	9.6	10.5	10.5	11.4	11.8	12.7	13.6
42.5°	7.0	7.4	7.9	8.3	8.3	8.8	9.2	9.6	10.1	11.0	11.8
45°	5.7	6.1	6.6	7.0	7.0	7.4	7.9	8.3	8.8	9.6	10.1
47.5°	4.8	5.3	5.7	6.1	6.1	6.6	7.0	7.4	7.4	8.3	8.8
50°	3.9	4.4	4.8	5.3	5.3	5.7	6.1	6.6	6.6	7.0	7.4
52.5°	3.1	3.5	4.4	4.4	4.8	5.3	5.3	5.7	5.7	6.1	6.6
55°	3.1	3.5	3.9	3.9	4.4	4.8	4.8	5.3	5.3	5.3	5.7
57.5°	2.6	3.1	3.5	3.9	3.9	4.4	4.4	4.4	4.4	4.8	4.8
60°	2.6	3.1	3.1	3.5	3.5	3.9	3.9	3.9	3.9	4.4	4.4
62.5°	2.6	2.6	3.1	3.1	3.5	3.5	3.5	3.9	3.9	3.9	3.9
65°	2.2	2.6	3.1	3.1	3.1	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	2.2	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	2.2	2.2	2.6	2.6	2.6	3.1	3.1	3.1	2.6	3.1	2.6
72.5°	1.8	2.2	2.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
75°	1.8	2.2	2.2	2.2	2.2	2.6	2.6	2.2	2.2	2.2	2.2
77.5°	1.8	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.8
80°	1.8	1.8	1.8	1.8	2.2	2.2	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3
85°	1.3	1.3	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3	0.9
87.5°	1.3	1.3	1.3	1.8	1.3	1.3	1.3	1.3	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212076

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	85.9	85.9	85.9	85.9	85.9	85.9	85.9	85.9
2.5°	74.0	73.6	74.0	73.6	73.6	74.0	72.7	73.6
5°	67.0	66.2	66.6	66.2	65.7	66.2	65.3	66.2
7.5°	60.9	60.5	60.5	60.5	60.0	60.5	59.6	60.5
10°	55.6	55.2	55.2	55.2	55.2	55.6	54.8	55.6
12.5°	50.4	50.4	50.8	50.4	50.8	51.3	50.4	51.3
15°	46.0	46.4	46.9	46.9	47.3	47.8	47.3	48.2
17.5°	42.5	42.9	43.8	43.8	44.3	45.1	44.7	45.6
20°	39.0	39.4	40.3	40.3	40.7	41.6	41.2	42.1
22.5°	35.1	35.9	36.4	36.8	37.2	38.1	37.7	38.6
25°	31.1	32.4	32.9	33.3	33.7	34.6	34.6	35.5
27.5°	28.0	28.9	29.4	29.8	30.7	31.5	31.5	32.0
30°	24.5	25.4	26.3	26.7	27.2	28.0	28.0	28.9
32.5°	21.5	22.3	22.8	23.2	24.1	25.0	25.4	25.9
35°	18.4	19.7	20.2	21.0	21.5	22.8	22.8	23.2
37.5°	16.2	17.1	18.0	18.4	19.3	20.2	20.2	21.0
40°	14.5	15.3	15.8	16.2	17.1	18.0	18.0	18.4
42.5°	12.3	13.6	14.0	14.5	14.9	15.8	16.2	16.6
45°	11.0	11.4	11.8	12.3	12.7	13.6	13.6	14.0
47.5°	9.2	9.6	10.1	10.5	11.0	11.4	11.8	12.3
50°	7.9	8.3	8.8	8.8	9.2	10.1	10.1	10.5
52.5°	6.6	7.0	7.4	7.4	7.9	8.8	8.8	9.2
55°	5.7	6.1	6.6	6.6	7.0	7.4	7.4	7.9
57.5°	5.3	5.3	5.7	5.7	6.1	6.1	6.6	6.6
60°	4.4	4.8	4.8	4.8	5.3	5.3	5.3	5.3
62.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4
65°	3.5	3.5	3.5	3.5	3.5	3.5	3.1	3.5
67.5°	3.1	3.1	3.1	3.1	2.6	2.6	2.6	2.6
70°	2.6	2.6	2.6	2.6	2.6	2.2	2.2	2.2
72.5°	2.2	2.2	2.2	2.2	2.2	1.8	1.8	1.8
75°	2.2	2.2	1.8	1.8	1.8	1.8	1.8	1.3
77.5°	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9
82.5°	1.3	0.9	0.9	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.4	0.4	0.4	0.4
87.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)