

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212077

Luminaire Tested: **LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26829)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 862.6 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.39
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212077

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212077

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	115	113	111	109	113	111	109	108		107	106	104			103	102	101			100
2	111	108	105	102	109	106	104	101		103	101	99			100	99	97			98
3	108	103	100	97	106	102	99	96		100	97	95			97	95	93			95
4	105	99	96	93	103	98	95	92		96	93	91			95	92	90			93
5	102	96	92	89	100	95	91	89		93	90	88			92	89	87			91
6	99	93	89	86	98	92	88	85		91	87	85			89	87	84			88
7	96	90	86	83	95	89	85	83		88	85	82			87	84	82			86
8	94	87	83	80	93	87	83	80		86	82	80			85	82	80			84
9	91	85	81	78	90	84	80	78		83	80	78			83	80	77			82
10	89	82	78	76	88	82	78	76		81	78	76			81	78	75			80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	440648	440648	440648
5°	367909	367909	369659
10°	230490	229969	232300
15°	131534	132276	132497
20°	74464	74237	73928
25°	27952	36150	28561
30°	5739	12103	5783
35°	2282	3938	2223
40°	1163	1720	1113
45°	781	904	658
50°	467	467	332
55°	220	304	152
60°	174	174	78
65°	92	92	92
70°	113	113	113
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P1212077

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.3	36.4
10°-20°	373.8	43.3
20°-30°	149.0	17.3
30°-40°	18.8	2.2
40°-50°	4.6	0.5
50°-60°	1.4	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.2	97.1
0°-40°	856.0	99.2
0°-60°	862.0	99.9
0°-90°	862.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	862.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4549	4549	4549	4549	4549	
5°	3783	3818	3783	3787	3801	313
15°	1312	1319	1319	1319	1321	373
25°	262	321	338	308	267	135
35°	19	23	33	22	19	14
45°	6	6	7	5	5	4
55°	1	1	2	1	1	2
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212077

CATALOG NUMBER: LDSQA4A10930D010TE LAR15SP 4LSQA1H-LSF-20

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4548.6	4548.6	4548.6	4548.6	4548.6
2.5°	4325.2	4348.4	4303.7	4308.1	4313.8
5°	3783.3	3817.9	3783.3	3786.8	3801.3
7.5°	3044.4	3074.6	3054.9	3063.6	3047.9
10°	2343.1	2354.0	2337.8	2345.7	2361.5
12.5°	1761.8	1774.1	1762.2	1762.7	1769.7
15°	1311.5	1319.4	1318.9	1318.9	1321.1
17.5°	979.5	990.0	978.6	979.5	982.1
20°	722.3	729.3	720.1	718.8	717.1
22.5°	492.8	507.7	513.4	505.9	482.3
25°	261.5	321.1	338.2	307.9	267.2
27.5°	105.1	159.9	197.6	156.4	114.3
30°	51.3	69.6	108.2	71.4	51.7
32.5°	30.2	37.7	59.1	37.2	29.8
35°	19.3	23.2	33.3	22.3	18.8
37.5°	12.7	15.3	20.6	14.9	12.3
40°	9.2	10.5	13.6	10.1	8.8
42.5°	7.0	7.4	9.2	7.4	6.6
45°	5.7	5.7	6.6	5.3	4.8
47.5°	4.4	4.4	4.4	3.9	3.1
50°	3.1	3.1	3.1	2.6	2.2
52.5°	2.2	2.2	2.2	1.8	1.3
55°	1.3	1.3	1.8	1.3	0.9
57.5°	1.3	0.9	1.3	0.9	0.9
60°	0.9	0.9	0.9	0.4	0.4
62.5°	0.4	0.4	0.4	0.4	0.4
65°	0.4	0.4	0.4	0.4	0.4
67.5°	0.4	0.4	0.4	0.4	0.4
70°	0.4	0.4	0.4	0.4	0.4
72.5°	0.4	0.4	0.4	0.4	0.0
75°	0.0	0.4	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)