

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212100

Luminaire Tested: **LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 966.4 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10928	10928	10928
5°	28726	10405	6797
10°	112624	9001	5656
15°	207345	7101	5015
20°	260546	5010	4557
25°	311649	3314	4062
30°	327734	2081	3557
35°	330368	1254	3087
40°	304002	835	2630
45°	216286	603	2178
50°	89372	467	1793
55°	5151	456	1571
60°	601	426	1279
65°	206	504	917
70°	255	510	623
75°	337	674	674
80°	0	1004	725
85°	0	2001	1000

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.7	1.8
10°-20°	141.6	14.7
20°-30°	292.9	30.3
30°-40°	318.9	33.0
40°-50°	174.8	18.1
50°-60°	15.1	1.6
60°-70°	2.5	0.3
70°-80°	1.8	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.2	46.8
0°-40°	771.1	79.8
0°-60°	961.1	99.4
0°-90°	966.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	113	113	113	113	113	
5°	295	202	107	74	70	54
15°	2067	869	71	48	50	577
25°	2916	1156	31	29	38	1317
35°	2794	316	11	17	26	1714
45°	1579	32	4	9	16	1205
55°	30	4	3	6	9	104
65°	1	1	2	4	4	1
75°	1	1	2	3	2	1
85°	0	1	2	1	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
2.5°	177.3	171.1	170.3	171.1	166.7	166.3	167.2	163.6	160.5	157.4	154.8
5°	295.4	282.6	278.6	273.3	260.0	255.6	254.7	240.6	226.9	214.0	202.1
7.5°	574.0	548.4	534.7	508.1	467.4	449.3	439.6	393.1	349.8	310.4	274.6
10°	1144.9	1077.7	1045.0	995.0	906.1	862.3	830.5	713.8	598.8	488.2	390.9
12.5°	1670.7	1633.6	1585.4	1558.8	1414.7	1359.4	1306.8	1144.9	969.8	791.1	613.8
15°	2067.4	2013.0	1961.7	1949.3	1836.1	1771.6	1713.2	1545.6	1337.3	1110.0	869.0
17.5°	2300.5	2261.5	2212.9	2189.5	2056.8	2004.6	1938.3	1776.0	1573.4	1347.0	1067.1
20°	2527.3	2469.8	2401.3	2365.9	2219.1	2159.0	2083.8	1913.1	1698.6	1458.0	1178.1
22.5°	2734.7	2660.4	2563.1	2508.3	2343.4	2277.0	2193.0	2008.2	1776.0	1500.9	1187.4
25°	2915.6	2848.4	2718.8	2622.8	2428.3	2350.0	2252.3	2059.0	1803.8	1497.4	1156.0
27.5°	2950.1	2905.0	2788.7	2677.7	2457.9	2370.8	2269.5	2069.6	1784.4	1448.3	1071.5
30°	2929.8	2881.1	2787.8	2674.6	2445.5	2357.5	2252.3	2024.5	1708.3	1333.8	916.7
32.5°	2880.7	2838.7	2727.2	2607.8	2384.5	2292.9	2181.9	1918.8	1577.9	1151.6	674.4
35°	2793.5	2730.3	2595.9	2497.7	2287.6	2193.4	2057.7	1777.8	1382.8	827.8	316.2
37.5°	2616.2	2554.7	2457.9	2367.2	2162.5	2051.5	1908.2	1581.4	1025.1	451.5	195.5
40°	2403.9	2350.9	2266.4	2178.4	1967.5	1839.7	1681.8	1236.0	603.2	254.3	120.3
42.5°	2173.1	2118.3	2022.7	1920.1	1690.2	1555.3	1384.6	800.0	318.0	149.9	65.4
45°	1578.7	1529.7	1460.2	1386.4	1253.3	1156.0	931.3	420.1	176.0	79.6	32.3
47.5°	1080.4	1022.0	893.7	738.5	598.8	512.1	385.2	182.2	90.2	39.8	19.0
50°	593.0	531.1	465.7	362.6	242.8	199.4	155.2	88.0	40.7	19.9	10.6
52.5°	145.5	128.7	117.6	108.3	85.8	77.4	65.4	36.7	18.6	11.1	7.5
55°	30.5	28.3	27.0	26.5	24.3	23.4	20.3	14.2	10.2	7.1	3.5
57.5°	8.8	8.4	8.8	8.8	8.8	8.4	8.4	6.2	5.7	3.5	2.2
60°	3.1	3.1	3.1	3.5	3.5	3.5	4.0	4.0	3.1	2.2	1.8
62.5°	1.3	1.3	1.3	1.8	1.8	2.2	2.2	2.2	1.8	1.8	1.3
65°	0.9	0.9	0.9	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
2.5°	147.3	142.8	137.5	131.8	130.9	127.8	123.4	117.2	115.0	110.6	106.6
5°	184.9	172.9	160.5	149.5	145.9	141.1	133.1	122.1	115.0	107.0	100.4
7.5°	235.3	207.8	182.6	162.7	156.5	148.6	136.2	122.1	111.4	100.4	91.5
10°	302.5	246.8	203.4	171.1	161.0	150.4	134.0	116.7	104.4	91.5	82.3
12.5°	432.1	303.8	222.9	175.6	161.4	147.7	126.9	108.3	94.2	81.4	72.1
15°	614.3	412.2	262.2	178.7	157.0	140.2	115.9	96.8	82.7	70.8	61.9
17.5°	768.1	514.8	314.9	187.5	153.9	130.5	103.0	83.6	69.9	59.3	52.2
20°	843.3	560.7	338.7	188.8	145.1	115.9	88.0	69.4	57.5	48.6	42.5
22.5°	834.5	545.3	316.6	165.4	122.5	97.7	73.0	56.2	46.0	38.9	34.5
25°	775.2	478.0	258.3	126.5	95.5	79.2	57.0	43.8	35.8	31.0	27.4
27.5°	675.7	383.9	188.4	89.3	72.5	60.1	42.5	33.6	27.4	23.9	21.7
30°	520.5	245.4	108.3	64.1	52.6	42.9	31.8	24.3	20.8	18.6	16.8
32.5°	268.4	119.4	72.1	46.0	37.1	31.0	22.1	17.7	15.5	14.2	13.3
35°	147.3	84.9	50.0	29.6	23.9	19.9	15.0	12.4	11.5	10.6	10.6
37.5°	101.3	52.6	27.9	17.7	14.6	12.4	10.2	8.8	8.4	8.4	8.4
40°	58.4	27.9	15.9	11.1	9.3	8.4	7.1	6.6	6.6	6.6	7.1
42.5°	30.1	16.4	10.6	7.5	6.6	5.7	4.9	4.9	4.9	5.3	5.7
45°	17.7	11.1	7.1	4.9	4.4	4.0	3.5	3.5	4.0	4.4	4.9
47.5°	11.1	7.5	4.4	3.1	2.7	2.7	2.7	2.7	3.1	3.5	4.0
50°	7.5	4.0	2.7	1.8	1.8	1.8	1.8	2.2	2.7	3.1	3.5
52.5°	4.0	2.2	1.8	1.3	1.3	1.3	1.8	1.8	2.2	2.7	3.1
55°	2.2	1.8	1.3	1.3	1.3	1.3	1.3	1.8	2.2	2.7	3.1
57.5°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.7
60°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.7
62.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.2
65°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.2
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	2.2
70°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	2.2
72.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
75°	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	2.2
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8
85°	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
2.5°	104.4	100.8	97.3	97.3	95.5	92.9	92.0	89.3	87.6	86.7	85.8
5°	95.5	90.2	85.3	84.9	82.7	79.6	78.3	75.6	73.9	73.0	72.5
7.5°	85.3	80.0	75.2	74.3	72.5	70.3	69.0	66.8	65.9	65.0	64.6
10°	75.6	70.3	66.8	65.9	64.6	62.8	61.5	60.1	59.3	58.8	58.8
12.5°	65.9	61.9	58.8	57.9	57.0	55.7	54.8	54.0	53.5	53.5	53.5
15°	57.0	53.5	50.9	50.9	50.0	49.1	49.1	48.2	47.8	48.2	48.6
17.5°	48.2	45.5	43.3	43.3	42.9	42.5	42.5	42.5	42.9	43.3	44.2
20°	39.8	37.6	36.7	36.7	36.3	36.7	36.7	37.1	37.6	38.9	40.2
22.5°	32.3	31.0	30.1	30.5	30.5	31.0	31.4	32.3	33.2	34.5	35.8
25°	26.1	25.2	24.8	25.2	25.6	26.1	27.0	27.9	29.2	30.5	32.3
27.5°	20.8	20.3	20.3	20.8	21.2	22.1	23.4	24.3	25.6	27.0	28.7
30°	16.8	16.4	16.8	17.7	18.1	19.0	19.9	21.2	22.6	23.9	25.6
32.5°	13.3	13.7	14.2	14.6	15.0	16.4	17.2	18.1	19.5	20.8	22.6
35°	11.1	11.5	11.9	12.4	12.8	13.7	14.6	15.5	16.8	18.1	19.9
37.5°	8.8	9.3	9.7	10.6	11.1	11.5	12.8	13.3	14.6	15.5	17.2
40°	7.5	8.0	8.4	8.8	9.3	10.2	11.1	11.5	12.4	13.7	15.0
42.5°	6.2	6.6	7.1	7.5	8.0	8.8	9.3	10.2	11.1	11.9	12.8
45°	5.3	5.7	6.2	6.6	7.1	7.5	8.0	8.8	9.3	10.2	11.1
47.5°	4.4	4.9	5.7	5.7	6.2	6.6	7.1	7.5	8.4	8.8	9.7
50°	4.0	4.4	4.9	5.3	5.3	5.7	6.2	6.6	7.1	7.5	8.4
52.5°	3.5	4.0	4.4	4.4	4.9	5.3	5.7	5.7	6.2	6.6	7.1
55°	3.1	3.5	4.0	4.0	4.4	4.9	4.9	5.3	5.7	5.7	6.2
57.5°	3.1	3.1	3.5	3.5	4.0	4.0	4.4	4.9	4.9	5.3	5.7
60°	2.7	3.1	3.1	3.5	3.5	4.0	4.0	4.4	4.4	4.9	4.9
62.5°	2.7	2.7	3.1	3.1	3.5	3.5	4.0	4.0	4.0	4.4	4.4
65°	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5	3.5	4.0	4.0
67.5°	2.2	2.7	2.7	3.1	3.1	3.1	3.1	3.1	3.5	3.5	3.5
70°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.1	3.1	3.1
72.5°	2.2	2.2	2.2	2.2	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	2.2	2.2	2.2	2.2	2.2	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
80°	1.8	1.8	1.8	1.8	1.8	2.2	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3
85°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3
87.5°	1.8	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212100

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	112.8	112.8	112.8	112.8	112.8	112.8	112.8	112.8
2.5°	84.5	83.6	84.5	83.6	83.6	81.8	83.1	82.3
5°	71.2	70.3	71.2	70.8	69.9	69.4	70.3	69.9
7.5°	63.7	62.8	63.7	63.7	62.8	62.4	63.2	62.8
10°	57.9	57.5	57.9	57.9	57.5	57.0	57.9	57.5
12.5°	53.1	52.6	53.5	53.5	53.1	53.1	54.0	53.1
15°	48.6	48.6	49.5	49.5	49.5	49.5	50.4	50.0
17.5°	44.2	45.1	46.0	46.4	46.4	46.4	47.3	47.3
20°	40.7	41.6	42.5	42.9	43.3	43.3	44.2	44.2
22.5°	36.7	37.6	38.9	39.4	39.8	40.2	41.1	41.1
25°	33.2	34.1	35.4	35.8	36.7	37.1	38.0	38.0
27.5°	29.6	31.0	31.8	32.7	33.2	34.1	34.9	34.9
30°	26.5	27.9	28.7	29.6	30.1	31.0	31.8	31.8
32.5°	23.4	24.8	25.6	26.5	27.4	27.9	29.2	29.2
35°	20.8	21.7	23.0	23.4	24.3	25.2	26.1	26.1
37.5°	18.1	19.0	19.9	20.8	21.7	22.1	23.0	23.4
40°	15.9	16.8	17.7	18.1	19.0	19.9	20.3	20.8
42.5°	13.7	14.6	15.5	15.9	16.8	17.2	18.1	18.1
45°	11.9	12.8	13.3	13.7	14.6	15.0	15.9	15.9
47.5°	10.2	11.1	11.5	11.9	12.4	12.8	13.7	13.7
50°	8.8	9.3	9.7	10.2	10.6	11.5	11.9	11.9
52.5°	7.5	8.4	8.4	8.8	9.3	9.7	10.2	10.6
55°	6.6	7.1	7.5	7.5	8.0	8.4	8.8	9.3
57.5°	5.7	6.2	6.6	6.6	7.1	7.1	7.5	8.0
60°	5.3	5.3	5.7	5.7	5.7	6.2	6.2	6.6
62.5°	4.4	4.4	4.9	4.9	4.9	4.9	4.9	4.9
65°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
67.5°	3.5	3.5	3.5	3.5	3.1	3.1	3.1	3.1
70°	3.1	3.1	3.1	3.1	2.7	2.7	2.7	2.2
72.5°	2.7	2.7	2.7	2.7	2.2	2.2	1.8	1.8
75°	2.2	2.2	2.2	2.2	2.2	1.8	1.8	1.8
77.5°	2.2	1.8	1.8	1.8	1.8	1.8	1.8	1.3
80°	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	0.9	0.9	0.9	0.9
85°	1.3	0.9	0.9	0.9	0.9	0.9	0.9	0.9
87.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)