

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212088

Luminaire Tested: **LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 889.3 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10656	10656	10656
5°	24963	10055	7031
10°	98645	8834	5863
15°	182563	7071	5145
20°	234093	5144	4649
25°	280084	3656	4126
30°	297810	2405	3624
35°	305225	1455	3158
40°	279392	936	2719
45°	201613	658	2219
50°	88015	527	1854
55°	6063	439	1554
60°	1104	426	1279
65°	413	413	894
70°	368	510	623
75°	337	674	674
80°	0	1004	725
85°	0	2001	445



TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	1.8
10°-20°	125.9	14.2
20°-30°	263.5	29.6
30°-40°	293.3	33.0
40°-50°	168.4	18.9
50°-60°	16.8	1.9
60°-70°	2.6	0.3
70°-80°	1.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.4	45.6
0°-40°	698.8	78.6
0°-60°	884.0	99.4
0°-90°	889.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	889.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	110	110	110	110	110	
5°	257	177	103	75	72	47
15°	1820	727	70	50	51	515
25°	2620	1000	34	30	39	1187
35°	2581	305	12	18	27	1576
45°	1472	37	5	10	16	1124
55°	36	5	3	6	9	107
65°	2	1	2	4	4	2
75°	1	1	2	2	2	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0
2.5°	164.3	160.8	157.3	155.1	152.9	156.0	153.8	152.9	146.8	143.7	141.1
5°	256.7	250.2	240.5	232.6	224.7	226.5	220.4	212.9	197.6	186.6	177.0
7.5°	495.5	479.3	449.5	420.6	391.7	386.4	367.1	333.8	290.9	258.5	230.4
10°	1002.8	953.7	899.0	839.8	770.6	751.3	703.6	613.3	514.8	402.2	320.7
12.5°	1480.3	1458.0	1393.6	1316.9	1242.0	1196.0	1146.5	997.6	841.2	659.8	508.2
15°	1820.3	1806.7	1750.2	1680.6	1599.9	1570.2	1509.7	1361.2	1163.6	946.7	726.8
17.5°	2072.2	2049.0	1989.9	1914.1	1818.6	1793.2	1720.9	1573.2	1368.2	1150.5	906.4
20°	2270.7	2256.2	2179.6	2088.4	1974.1	1943.4	1858.9	1705.1	1482.1	1250.8	1002.4
22.5°	2449.0	2424.5	2330.3	2221.6	2091.1	2058.2	1964.0	1795.3	1555.7	1298.1	1019.5
25°	2620.3	2583.1	2468.7	2326.3	2173.0	2128.3	2024.9	1846.2	1582.9	1302.0	1000.2
27.5°	2670.2	2651.4	2545.8	2380.2	2202.8	2152.4	2044.6	1857.6	1572.8	1266.1	931.0
30°	2662.3	2646.6	2558.5	2385.5	2197.5	2144.5	2035.0	1822.5	1514.1	1172.4	808.7
32.5°	2637.4	2631.2	2524.8	2339.9	2148.5	2090.6	1972.3	1735.3	1404.1	1029.5	591.0
35°	2580.9	2556.8	2424.0	2250.1	2066.1	2002.6	1868.9	1610.5	1259.1	749.6	305.4
37.5°	2415.3	2396.4	2291.7	2139.3	1960.1	1878.6	1737.5	1449.2	974.8	426.3	182.7
40°	2209.3	2200.1	2117.8	1981.5	1790.1	1698.1	1544.7	1185.9	594.9	242.3	120.5
42.5°	1998.2	1995.6	1907.5	1765.1	1557.5	1451.9	1292.8	800.0	316.3	146.3	69.7
45°	1471.6	1487.4	1426.0	1340.6	1182.0	1105.3	899.0	412.3	182.3	81.0	36.8
47.5°	1032.2	1014.6	906.0	756.6	611.6	517.8	391.7	195.0	97.3	42.5	21.0
50°	584.0	587.1	488.9	395.6	259.4	205.5	156.0	98.1	46.9	22.3	12.7
52.5°	152.5	159.5	137.6	118.3	100.8	81.9	66.2	42.5	22.3	13.1	8.3
55°	35.9	37.2	34.6	32.4	30.7	27.2	24.1	18.4	12.3	8.3	5.3
57.5°	12.7	13.1	12.7	12.7	12.3	11.8	11.0	9.6	7.4	5.3	3.5
60°	5.7	6.1	5.7	6.1	6.1	6.1	6.1	6.1	4.4	3.1	2.2
62.5°	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.5	2.6	2.2	1.8
65°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
70°	1.3	1.3	1.3	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0
2.5°	136.2	135.8	131.0	127.5	125.7	123.1	120.0	115.7	110.8	106.5	104.7
5°	165.6	159.9	149.8	141.5	137.6	133.6	126.6	118.7	111.3	103.4	99.4
7.5°	203.7	187.1	167.4	152.0	145.4	138.9	128.8	117.8	107.8	97.3	91.6
10°	255.9	217.3	183.1	158.6	149.0	140.2	125.7	112.2	101.2	89.8	82.4
12.5°	365.8	270.3	199.8	161.7	149.0	137.6	120.0	104.3	92.0	80.2	73.2
15°	527.0	364.9	236.1	164.7	145.9	131.4	111.3	94.2	81.0	70.5	64.0
17.5°	657.2	452.1	281.3	172.6	141.9	123.1	99.9	81.9	69.7	60.0	54.8
20°	722.9	488.9	301.9	173.9	132.3	110.0	86.3	69.2	58.3	49.9	45.6
22.5°	721.6	477.1	283.5	152.5	116.1	95.1	72.7	57.0	48.2	41.6	38.1
25°	676.0	422.3	236.6	121.8	93.8	78.9	59.1	46.0	39.0	34.2	31.1
27.5°	590.6	343.0	176.6	90.2	73.2	62.2	46.0	36.8	31.1	27.6	25.4
30°	463.5	229.6	111.3	67.0	55.6	46.9	35.5	28.5	24.5	21.5	20.2
32.5°	255.4	119.6	74.9	49.1	40.7	34.2	26.3	20.6	18.0	15.8	15.3
35°	141.1	84.6	53.4	32.9	27.2	23.2	18.0	14.9	13.1	12.3	12.3
37.5°	99.9	54.3	32.0	20.6	17.5	15.3	12.3	10.5	10.1	9.6	9.6
40°	60.0	32.0	19.3	13.6	11.8	10.5	9.2	7.9	7.9	7.4	7.9
42.5°	32.9	19.3	13.1	9.6	8.3	7.9	6.6	6.1	6.1	6.1	6.6
45°	19.7	12.7	9.2	7.0	6.1	5.3	4.8	4.4	4.8	4.8	5.3
47.5°	12.7	9.2	6.1	4.4	3.9	3.5	3.1	3.5	3.5	3.9	4.4
50°	8.8	5.7	3.9	2.6	2.6	2.2	2.6	2.6	3.1	3.5	3.9
52.5°	5.7	3.9	2.6	2.2	1.8	1.8	1.8	2.2	2.6	3.1	3.5
55°	3.5	2.6	2.2	1.8	1.8	1.8	1.8	1.8	2.2	2.6	3.1
57.5°	2.6	2.2	1.8	1.3	1.3	1.3	1.8	1.8	2.2	2.2	2.6
60°	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.6
62.5°	1.8	1.8	1.3	1.3	1.3	1.3	1.8	1.8	1.8	2.2	2.2
65°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	2.2
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
70°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2
72.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8
75°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
77.5°	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
82.5°	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
85°	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
87.5°	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0
2.5°	102.5	99.4	96.8	97.7	95.9	92.9	92.0	89.8	87.2	86.7	86.7
5°	95.1	90.2	86.3	85.9	84.1	80.6	79.7	77.5	75.4	74.9	74.5
7.5°	85.9	80.6	77.1	76.2	74.9	71.8	71.4	69.2	67.9	67.0	67.0
10°	76.7	71.8	68.8	68.3	67.5	64.8	64.4	62.6	61.3	60.9	60.5
12.5°	67.9	64.0	61.3	60.9	60.0	57.8	57.4	56.1	55.2	54.8	54.8
15°	59.6	56.1	53.9	53.4	53.0	50.8	50.8	49.9	49.5	49.5	49.9
17.5°	51.3	48.2	46.4	46.0	46.0	44.2	44.7	44.2	44.2	44.2	45.1
20°	42.9	40.3	39.0	39.4	38.6	38.1	38.6	38.6	38.6	39.4	40.7
22.5°	35.9	33.7	32.4	32.9	32.9	32.4	32.9	33.3	34.2	35.5	36.8
25°	29.4	27.6	27.2	27.6	27.6	27.6	28.5	29.4	30.2	31.5	32.9
27.5°	23.7	22.3	22.3	22.8	23.2	23.2	24.5	25.4	26.7	28.0	29.4
30°	18.8	18.4	18.4	19.3	19.3	19.7	21.5	22.3	23.2	24.5	25.8
32.5°	14.9	14.9	15.3	16.2	16.2	17.1	18.4	19.3	20.2	21.5	22.8
35°	12.3	12.7	13.1	13.6	14.0	14.5	15.8	16.6	17.5	18.8	19.7
37.5°	10.1	10.5	11.0	11.8	11.8	12.3	13.6	14.5	14.9	16.2	17.5
40°	8.3	8.8	9.2	10.1	10.1	10.5	11.8	12.3	12.7	14.0	15.3
42.5°	7.0	7.4	7.9	8.3	8.8	9.2	10.1	10.5	11.4	12.3	13.1
45°	5.7	6.1	6.6	7.0	7.4	7.9	8.3	9.2	9.6	10.5	11.4
47.5°	4.8	5.3	5.7	6.1	6.6	6.6	7.4	7.9	8.3	9.2	10.1
50°	4.4	4.8	5.3	5.3	5.7	6.1	6.6	7.0	7.4	7.9	8.8
52.5°	3.5	3.9	4.4	4.8	4.8	5.3	5.7	6.1	6.6	7.0	7.4
55°	3.5	3.5	3.9	4.4	4.4	4.8	5.3	5.7	5.7	6.1	6.6
57.5°	3.1	3.5	3.5	3.9	3.9	4.4	4.8	4.8	5.3	5.3	5.7
60°	2.6	3.1	3.5	3.5	3.5	3.9	3.9	4.4	4.4	4.8	4.8
62.5°	2.6	3.1	3.1	3.5	3.5	3.5	3.9	3.9	3.9	4.4	4.4
65°	2.6	2.6	3.1	3.1	3.1	3.1	3.5	3.5	3.5	3.9	3.9
67.5°	2.2	2.6	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.5	3.5
70°	2.2	2.2	2.6	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.1
72.5°	2.2	2.2	2.2	2.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6
75°	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
77.5°	1.8	1.8	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3
85°	1.8	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212088

CATALOG NUMBER: LDSQA4A10930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	110.0	110.0	110.0	110.0	110.0	110.0	110.0	110.0
2.5°	85.0	84.1	83.7	85.0	83.2	84.1	83.7	84.1
5°	73.2	72.3	71.8	73.2	71.4	72.3	71.4	72.3
7.5°	65.7	65.3	64.8	65.7	64.4	65.3	64.8	65.3
10°	59.6	59.1	58.7	60.0	58.7	59.6	59.1	59.6
12.5°	54.3	54.3	53.9	54.8	53.9	54.8	54.3	54.8
15°	49.5	49.9	49.5	50.4	49.9	50.8	50.4	51.3
17.5°	45.6	46.0	46.0	47.3	46.9	48.2	47.8	48.2
20°	41.6	42.1	42.5	43.4	43.4	44.7	44.2	45.1
22.5°	37.7	38.6	38.6	39.9	39.9	41.2	41.2	41.6
25°	33.7	35.0	35.5	36.4	36.8	38.1	38.1	38.6
27.5°	30.7	31.5	32.0	33.3	33.7	35.0	35.0	35.9
30°	27.2	28.5	28.9	29.8	30.2	31.5	31.5	32.4
32.5°	24.1	25.0	25.8	26.7	27.2	28.5	28.5	29.4
35°	21.0	22.3	22.8	23.7	24.5	25.8	25.8	26.7
37.5°	18.4	19.7	20.2	21.0	21.9	23.2	23.2	24.1
40°	16.2	17.5	18.0	18.8	19.3	21.0	21.0	21.5
42.5°	14.5	15.3	15.8	16.6	17.1	18.0	18.0	18.8
45°	12.3	13.1	13.6	14.0	14.9	15.8	15.8	16.2
47.5°	10.5	11.4	11.8	12.3	12.7	13.6	13.6	14.5
50°	9.2	9.6	10.1	10.5	11.0	11.8	11.8	12.3
52.5°	7.9	8.3	8.8	9.2	9.6	10.1	10.5	11.0
55°	7.0	7.4	7.4	7.9	8.3	8.8	8.8	9.2
57.5°	6.1	6.6	6.6	6.6	7.0	7.4	7.4	7.9
60°	5.3	5.7	5.7	5.7	6.1	6.1	6.1	6.6
62.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
65°	3.9	3.9	3.9	3.9	3.9	3.9	3.5	3.9
67.5°	3.5	3.5	3.5	3.1	3.1	3.1	3.1	3.1
70°	3.1	3.1	3.1	2.6	2.6	2.6	2.2	2.2
72.5°	2.6	2.6	2.6	2.2	2.2	2.2	1.8	1.8
75°	2.2	2.2	2.2	2.2	1.8	1.8	1.8	1.8
77.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3
80°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	1.3	1.3	1.3	1.3	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.9	0.9	0.4	0.4
87.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)