

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212105

Luminaire Tested: **LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26829)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 940.3 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.39
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212105

CATALOG NUMBER: LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20

Luminous Intensity Polar Plot



TEST NUMBER: P1212105

CATALOG NUMBER: LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	113	111	109	113	111	109	108		107	106	104			103	102	101			97
2	111	108	105	102	109	106	104	101		103	101	99			100	99	97			94
3	108	103	100	97	106	102	99	96		100	97	95			97	95	93			91
4	105	99	96	93	103	98	95	92		96	93	91			95	92	90			88
5	102	96	92	89	100	95	91	89		93	90	88			92	89	87			85
6	99	93	89	86	98	92	88	85		91	87	85			89	87	84			83
7	96	90	86	83	95	89	85	83		88	85	82			87	84	82			80
8	94	87	83	80	93	87	83	80		86	82	80			85	82	80			78
9	91	85	81	78	90	84	80	78		83	80	78			83	80	77			76
10	89	82	78	76	88	82	78	76		81	78	75			81	78	75			74

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	480337	480337	480337
5°	401060	401060	402956
10°	251247	250686	253224
15°	143379	144191	144432
20°	81175	80928	80588
25°	30474	39400	31137
30°	6253	13189	6298
35°	2484	4293	2424
40°	1265	1872	1201
45°	849	986	726
50°	497	497	362
55°	236	321	169
60°	194	194	97
65°	115	115	115
70°	142	142	142
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P1212105

CATALOG NUMBER: LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.6	36.4
10°-20°	407.5	43.3
20°-30°	162.5	17.3
30°-40°	20.5	2.2
40°-50°	5.0	0.5
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	912.6	97.0
0°-40°	933.1	99.2
0°-60°	939.6	99.9
0°-90°	940.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	940.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4958	4958	4958	4958	4958	
5°	4124	4162	4124	4128	4144	342
15°	1430	1438	1438	1438	1440	406
25°	285	350	369	336	291	147
35°	21	25	36	24	20	15
45°	6	6	7	6	5	5
55°	1	1	2	1	1	2
65°	0	0	0	0	0	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212105

CATALOG NUMBER: LDSQA4A10940D010TE LAR15SP 4LSQA1H-LSF-20

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4958.3	4958.3	4958.3	4958.3	4958.3
2.5°	4714.8	4740.1	4691.4	4696.2	4702.4
5°	4124.2	4161.9	4124.2	4128.0	4143.7
7.5°	3318.6	3351.6	3330.1	3339.6	3322.4
10°	2554.1	2566.1	2548.4	2557.0	2574.2
12.5°	1920.5	1933.9	1921.0	1921.5	1929.1
15°	1429.6	1438.2	1437.7	1437.7	1440.1
17.5°	1067.7	1079.1	1066.7	1067.7	1070.6
20°	787.4	795.0	785.0	783.6	781.7
22.5°	537.2	553.4	559.6	551.5	525.7
25°	285.1	350.0	368.6	335.7	291.3
27.5°	114.6	174.3	215.4	170.5	124.6
30°	55.9	75.9	117.9	77.8	56.3
32.5°	32.9	41.1	64.5	40.6	32.5
35°	21.0	25.3	36.3	24.4	20.5
37.5°	13.8	16.7	22.4	16.2	13.4
40°	10.0	11.5	14.8	11.0	9.5
42.5°	7.6	8.1	10.0	8.1	7.2
45°	6.2	6.2	7.2	5.7	5.3
47.5°	4.8	4.8	4.8	4.3	3.3
50°	3.3	3.3	3.3	2.9	2.4
52.5°	2.4	2.4	2.4	1.9	1.4
55°	1.4	1.4	1.9	1.4	1.0
57.5°	1.4	1.0	1.4	1.0	1.0
60°	1.0	1.0	1.0	0.5	0.5
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.5	0.5	0.5	0.5	0.5
67.5°	0.5	0.5	0.5	0.5	0.5
70°	0.5	0.5	0.5	0.5	0.5
72.5°	0.5	0.5	0.5	0.5	0.0
75°	0.0	0.5	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)