

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212096

Luminaire Tested: **LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 948.7 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9600	9600	9600
5°	21238	9083	6379
10°	85031	7879	5332
15°	196012	6268	4684
20°	292598	4454	4175
25°	383768	2961	3720
30°	440535	1868	3255
35°	403927	1194	2815
40°	331242	784	2390
45°	192036	548	1932
50°	54422	392	1598
55°	4982	372	1334
60°	775	426	1104
65°	206	413	802
70°	255	510	623
75°	337	674	674
80°	0	1004	502
85°	0	2001	445

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.1	1.5
10°-20°	126.2	13.3
20°-30°	307.4	32.4
30°-40°	333.2	35.1
40°-50°	151.0	15.9
50°-60°	11.7	1.2
60°-70°	2.4	0.3
70°-80°	1.8	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	447.6	47.2
0°-40°	780.8	82.3
0°-60°	943.4	99.4
0°-90°	948.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	99	99	99	99	99	
5°	218	161	93	70	66	39
15°	1954	639	62	45	47	568
25°	3590	918	28	27	35	1637
35°	3416	233	10	16	24	2101
45°	1402	30	4	9	14	1107
55°	30	4	2	5	8	67
65°	1	1	2	4	4	1
75°	1	1	2	3	2	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1
2.5°	148.4	145.8	147.1	143.6	141.4	139.6	140.5	139.6	133.9	132.6	128.1
5°	218.4	214.5	214.5	207.0	199.0	194.2	194.2	188.5	176.1	170.4	161.2
7.5°	391.5	383.6	377.0	353.6	323.2	306.1	301.7	277.4	246.2	226.4	203.0
10°	864.4	831.4	808.1	747.3	665.8	615.2	593.6	509.9	410.4	335.6	267.7
12.5°	1453.7	1408.7	1367.8	1268.3	1151.1	1071.4	1028.7	905.4	712.1	573.8	429.4
15°	1954.4	1905.9	1857.5	1736.4	1612.6	1543.5	1465.1	1301.7	1046.3	849.9	639.4
17.5°	2365.2	2337.9	2288.2	2110.7	1954.8	1846.9	1765.4	1551.9	1289.0	1064.8	826.6
20°	2838.2	2770.8	2681.9	2466.5	2253.4	2118.2	2003.7	1743.4	1439.6	1182.0	925.7
22.5°	3236.3	3188.3	3060.6	2776.5	2463.0	2347.6	2207.6	1894.5	1536.5	1231.7	937.1
25°	3590.3	3515.0	3354.7	3017.0	2695.9	2499.5	2327.8	1976.4	1572.1	1235.2	918.2
27.5°	3797.8	3699.5	3511.1	3142.9	2776.5	2559.4	2369.2	1990.5	1549.7	1188.6	849.0
30°	3938.2	3742.7	3534.4	3144.2	2751.0	2529.0	2331.8	1919.6	1456.3	1082.0	732.8
32.5°	3706.6	3593.4	3394.4	3019.2	2611.8	2395.2	2199.2	1765.9	1310.5	923.9	509.9
35°	3415.5	3323.9	3150.8	2778.3	2403.1	2198.8	1990.9	1568.6	1120.7	635.0	233.4
37.5°	3077.3	3005.5	2819.2	2478.8	2148.6	1948.6	1740.3	1337.0	789.1	314.9	141.8
40°	2619.3	2558.6	2405.7	2132.3	1828.0	1637.7	1445.7	1000.1	428.5	175.7	92.5
42.5°	2153.0	2101.9	1962.7	1726.3	1458.9	1302.2	1133.1	609.5	213.1	110.5	51.5
45°	1401.7	1337.8	1263.0	1154.7	1022.5	926.1	726.6	294.2	126.4	61.7	29.5
47.5°	803.7	761.4	638.5	503.8	409.1	373.4	271.7	137.0	69.6	35.7	18.1
50°	361.1	333.8	280.1	228.1	165.1	129.0	109.7	68.7	34.3	19.4	12.3
52.5°	89.0	90.7	85.9	75.3	66.9	56.8	49.3	32.1	18.1	11.9	7.9
55°	29.5	29.9	27.3	26.0	23.8	22.0	20.3	14.5	11.0	10.6	4.0
57.5°	10.6	10.6	11.0	10.1	9.7	9.2	8.8	7.5	6.6	4.0	2.2
60°	4.0	4.0	4.0	4.4	4.4	4.4	4.8	4.4	3.1	2.2	1.8
62.5°	1.8	1.8	1.8	1.8	2.2	2.2	2.6	2.2	1.8	1.8	1.3
65°	0.9	0.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
67.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.3
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
80°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9	1.3
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	1.3
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1
2.5°	123.7	121.1	115.8	111.9	108.8	108.3	105.7	101.3	99.5	96.4	93.8
5°	152.4	145.8	137.4	129.5	123.7	120.7	111.4	103.0	98.2	93.4	89.0
7.5°	183.2	168.2	153.7	140.9	133.0	128.1	117.1	103.5	94.7	87.6	81.9
10°	221.9	191.1	166.0	146.2	135.6	129.0	115.8	99.5	88.5	80.1	74.4
12.5°	310.5	226.4	177.5	148.8	135.6	126.4	110.5	94.2	81.9	71.8	65.6
15°	461.9	316.2	210.5	150.2	131.2	120.7	102.6	85.4	73.1	62.5	56.8
17.5°	604.6	416.1	262.9	159.4	128.6	112.3	92.0	75.3	62.5	52.4	47.6
20°	678.6	465.9	292.0	166.5	124.2	101.7	79.7	64.3	52.0	43.2	39.2
22.5°	680.4	461.5	277.9	150.2	107.9	87.2	68.3	52.8	42.3	34.8	31.7
25°	638.5	408.2	228.6	117.1	87.2	73.1	56.8	43.2	33.0	27.7	25.5
27.5°	559.7	330.3	168.7	84.6	68.3	58.1	44.5	33.0	25.1	21.6	20.3
30°	432.9	204.3	93.4	62.5	51.5	43.6	32.1	22.0	18.9	16.7	15.9
32.5°	214.9	100.0	66.1	44.5	35.2	27.7	20.3	16.3	14.5	13.2	12.8
35°	116.7	71.8	41.4	26.9	21.1	17.6	13.7	11.4	10.6	10.1	10.1
37.5°	81.5	42.7	25.1	16.3	13.2	11.9	9.7	8.4	7.9	7.9	7.9
40°	44.9	25.5	15.4	10.6	8.8	7.9	6.6	6.2	6.2	6.2	6.6
42.5°	26.0	15.9	10.6	7.5	6.2	5.7	4.8	4.4	4.8	4.8	5.3
45°	16.7	11.9	7.0	5.3	4.4	4.0	3.5	3.5	4.0	4.0	4.4
47.5°	11.9	8.4	4.8	3.5	2.6	2.6	2.6	2.6	3.1	3.5	4.0
50°	7.0	4.4	2.6	2.2	1.8	1.8	1.8	2.2	2.6	2.6	3.1
52.5°	4.0	2.6	1.8	1.8	1.3	1.3	1.8	1.8	2.2	2.6	3.1
55°	2.2	1.8	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.6
57.5°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.2
60°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	2.2	2.2
62.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	2.2
65°	1.3	1.3	1.3	1.8	1.3	1.8	1.8	1.8	1.8	1.8	2.2
67.5°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.2
70°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.2
72.5°	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.2
75°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
77.5°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
80°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
85°	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
87.5°	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1
2.5°	92.9	89.8	87.6	86.8	85.0	85.4	84.1	83.2	80.6	80.6	78.8
5°	85.9	81.9	79.3	77.9	76.2	75.7	74.4	73.1	70.5	70.0	68.7
7.5°	78.4	74.4	71.3	70.0	68.3	67.8	66.1	65.2	63.0	62.5	61.2
10°	70.5	66.1	63.4	62.1	60.3	60.3	59.0	58.1	56.4	56.4	55.5
12.5°	62.1	58.1	56.4	54.6	53.7	53.7	52.8	52.0	50.6	51.1	50.6
15°	53.3	50.2	48.4	47.6	47.1	47.1	46.7	46.2	45.4	46.2	45.4
17.5°	44.9	42.7	41.4	41.0	40.5	40.5	40.5	41.0	40.5	41.4	41.4
20°	37.0	35.2	34.3	34.3	33.9	34.8	34.8	35.7	35.7	37.0	37.4
22.5°	30.4	29.1	28.6	28.6	28.6	29.5	29.9	30.8	31.3	32.6	33.5
25°	24.2	23.8	23.8	23.8	24.2	25.1	26.0	26.9	27.3	29.1	29.5
27.5°	19.8	19.4	19.8	19.8	20.3	21.6	22.5	23.3	24.2	25.5	26.4
30°	15.9	15.9	16.3	16.7	17.2	18.1	19.4	20.3	21.1	22.5	23.3
32.5°	12.8	13.2	13.7	14.1	14.1	15.4	16.3	17.6	18.1	19.4	20.3
35°	10.6	11.0	11.4	11.9	11.9	13.2	14.1	15.0	15.9	16.7	17.6
37.5°	8.4	8.8	9.7	10.1	10.1	11.4	11.9	12.8	13.7	14.5	15.4
40°	7.0	7.5	8.4	8.4	8.8	9.7	10.1	11.0	11.9	12.8	13.7
42.5°	5.7	6.2	7.0	7.5	7.5	8.4	8.8	9.7	10.1	11.0	11.4
45°	5.3	5.3	6.2	6.2	6.6	7.0	7.9	8.4	8.8	9.7	10.1
47.5°	4.4	4.8	5.3	5.7	5.7	6.2	6.6	7.0	7.5	8.4	8.8
50°	3.5	4.0	4.8	4.8	4.8	5.7	6.2	6.6	6.6	7.0	7.5
52.5°	3.5	3.5	4.0	4.4	4.4	4.8	5.3	5.7	5.7	6.2	6.6
55°	3.1	3.1	3.5	4.0	4.0	4.4	4.8	4.8	5.3	5.3	5.7
57.5°	2.6	3.1	3.5	3.5	3.5	4.0	4.4	4.4	4.8	4.8	5.3
60°	2.6	3.1	3.1	3.5	3.5	4.0	4.0	4.0	4.4	4.4	4.4
62.5°	2.6	2.6	3.1	3.1	3.1	3.5	3.5	4.0	4.0	4.0	4.0
65°	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	2.2	2.6	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	2.2	2.2	2.6	2.6	2.6	3.1	3.1	3.1	3.1	3.1	3.1
72.5°	2.2	2.2	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
75°	2.2	2.2	2.2	2.2	2.2	2.6	2.6	2.6	2.6	2.2	2.2
77.5°	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.8
80°	1.8	1.8	2.2	1.8	2.2	2.2	2.2	2.2	1.8	1.8	1.8
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3
85°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	0.9
87.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212096

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	99.1	99.1	99.1	99.1	99.1	99.1	99.1	99.1
2.5°	77.9	78.8	77.9	78.8	76.6	77.5	78.4	76.2
5°	67.8	66.9	67.4	68.3	66.5	66.9	67.4	65.6
7.5°	60.8	61.2	60.3	61.2	59.9	60.3	60.8	59.4
10°	55.0	55.5	55.0	55.5	54.2	55.0	55.5	54.2
12.5°	49.8	50.6	50.2	51.1	49.8	50.6	51.5	49.8
15°	45.8	46.7	46.2	47.1	46.2	47.1	48.0	46.7
17.5°	41.8	42.7	42.7	43.6	43.2	44.0	44.9	43.6
20°	37.9	39.2	39.2	40.1	40.1	40.5	41.8	40.5
22.5°	34.3	35.7	35.7	36.6	36.6	37.4	38.3	37.4
25°	30.4	32.1	32.6	33.5	33.5	34.3	35.7	34.8
27.5°	27.7	29.1	29.5	30.4	30.8	31.7	32.6	31.7
30°	24.2	26.0	26.4	27.3	27.7	29.1	29.5	29.1
32.5°	21.6	22.9	23.3	24.2	25.1	26.0	26.9	26.4
35°	18.9	20.3	20.7	21.6	22.0	23.3	24.2	23.8
37.5°	16.7	18.1	18.5	18.9	19.4	20.7	21.6	21.1
40°	14.5	15.4	15.9	16.7	17.2	18.1	18.9	18.9
42.5°	12.8	13.7	14.1	14.5	15.0	15.9	16.7	16.3
45°	11.0	11.9	12.3	12.8	13.2	13.7	14.5	14.1
47.5°	9.2	10.1	10.6	11.0	11.4	11.9	12.8	12.3
50°	7.9	8.8	8.8	9.2	9.7	10.1	11.0	10.6
52.5°	7.0	7.5	7.9	7.9	8.4	8.8	9.7	9.2
55°	6.2	6.6	6.6	7.0	7.0	7.5	7.9	7.9
57.5°	5.3	5.7	5.7	6.2	6.2	6.6	7.0	7.0
60°	4.8	4.8	5.3	5.3	5.3	5.7	5.7	5.7
62.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
65°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
67.5°	3.1	3.1	3.1	3.1	3.1	2.6	2.6	2.6
70°	2.6	2.6	2.6	2.6	2.6	2.2	2.2	2.2
72.5°	2.6	2.6	2.2	2.2	2.2	2.2	2.2	1.8
75°	2.2	2.2	2.2	2.2	1.8	1.8	1.8	1.8
77.5°	1.8	1.8	1.8	1.8	1.3	1.3	1.3	1.3
80°	1.8	1.3	1.3	1.3	1.3	1.3	1.3	0.9
82.5°	1.3	1.3	1.3	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.4	0.4	0.4	0.4
87.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)