

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212114

Luminaire Tested: **LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1043.5 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	83	79		85	81	77		82
4	92	83	77	72	91	82	76	71	80	75	71		78	73	70		76
5	86	76	69	64	85	75	69	64	74	68	63		72	67	63		70
6	81	70	63	58	79	69	62	58	68	62	57		66	61	57		65
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55
9	66	55	48	43	65	54	47	43	53	47	43		52	46	42		51
10	62	50	44	39	61	50	43	39	49	43	39		48	43	39		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	11799	11799	11799
5°	31021	11242	7332
10°	121605	9719	6109
15°	223874	7662	5416
20°	281319	5412	4918
25°	336490	3570	4393
30°	353853	2248	3848
35°	356717	1360	3335
40°	328244	911	2833
45°	233535	658	2356
50°	96501	497	1944
55°	5557	490	1689
60°	639	465	1395
65°	229	550	986
70°	283	538	680
75°	374	711	711
80°	0	1060	781
85°	0	2112	1112



TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.1	1.8
10°-20°	152.9	14.7
20°-30°	316.3	30.3
30°-40°	344.3	33.0
40°-50°	188.8	18.1
50°-60°	16.3	1.6
60°-70°	2.7	0.3
70°-80°	1.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.3	46.8
0°-40°	832.6	79.8
0°-60°	1037.7	99.4
0°-90°	1043.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1043.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	122	122	122	122	122	
5°	319	218	116	80	75	58
15°	2232	938	76	52	54	623
25°	3148	1248	33	32	41	1422
35°	3016	341	12	18	28	1851
45°	1705	35	5	10	17	1301
55°	33	4	3	6	10	113
65°	1	1	2	4	4	1
75°	1	1	2	3	2	1
85°	0	1	2	1	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8
2.5°	191.5	184.8	183.8	184.8	180.0	179.5	180.5	176.7	173.3	170.0	167.1
5°	319.0	305.1	300.8	295.1	280.8	276.0	275.0	259.8	244.9	231.1	218.2
7.5°	619.8	592.1	577.3	548.6	504.7	485.1	474.6	424.5	377.7	335.2	296.5
10°	1236.2	1163.6	1128.3	1074.3	978.4	931.1	896.7	770.7	646.5	527.1	422.1
12.5°	1803.9	1763.8	1711.8	1683.1	1527.5	1467.8	1411.0	1236.2	1047.1	854.2	662.7
15°	2232.2	2173.5	2118.1	2104.7	1982.5	1912.8	1849.8	1668.8	1443.9	1198.5	938.3
17.5°	2483.9	2441.8	2389.3	2364.0	2220.8	2164.4	2092.8	1917.6	1698.9	1454.4	1152.2
20°	2728.8	2666.7	2592.7	2554.5	2396.0	2331.1	2249.9	2065.6	1834.0	1574.3	1272.0
22.5°	2952.8	2872.5	2767.5	2708.3	2530.2	2458.6	2367.8	2168.3	1917.6	1620.6	1282.0
25°	3148.0	3075.5	2935.6	2832.0	2621.9	2537.3	2431.8	2223.2	1947.7	1616.8	1248.1
27.5°	3185.3	3136.6	3011.0	2891.2	2653.9	2559.8	2450.4	2234.6	1926.6	1563.8	1156.9
30°	3163.3	3110.8	3010.1	2887.8	2640.5	2545.5	2431.8	2185.9	1844.5	1440.1	989.8
32.5°	3110.3	3065.0	2944.6	2815.7	2574.6	2475.8	2355.9	2071.8	1703.7	1243.4	728.2
35°	3016.3	2948.0	2802.8	2696.8	2470.0	2368.3	2221.7	1919.5	1493.1	893.8	341.4
37.5°	2824.8	2758.4	2653.9	2556.0	2334.9	2215.0	2060.3	1707.5	1106.8	487.5	211.0
40°	2595.6	2538.3	2447.1	2352.1	2124.3	1986.3	1815.9	1334.6	651.3	274.6	129.9
42.5°	2346.4	2287.1	2184.0	2073.2	1824.9	1679.3	1495.0	863.8	343.3	161.9	70.7
45°	1704.6	1651.6	1576.6	1496.9	1353.2	1248.1	1005.6	453.6	190.0	85.9	34.9
47.5°	1166.5	1103.5	965.0	797.4	646.5	552.9	415.9	196.7	97.4	43.0	20.5
50°	640.3	573.5	502.8	391.5	262.1	215.3	167.6	95.0	43.9	21.5	11.5
52.5°	157.1	138.9	127.0	117.0	92.6	83.6	70.7	39.6	20.1	11.9	8.1
55°	32.9	30.6	29.1	28.6	26.3	25.3	22.0	15.3	11.0	7.6	3.8
57.5°	9.5	9.1	9.5	9.5	9.5	9.1	9.1	6.7	6.2	3.8	2.4
60°	3.3	3.3	3.3	3.8	3.8	3.8	4.3	4.3	3.3	2.4	1.9
62.5°	1.4	1.4	1.4	1.9	1.9	2.4	2.4	2.4	1.9	1.9	1.4
65°	1.0	1.0	1.0	1.0	1.4	1.4	1.4	1.4	1.4	1.4	1.4
67.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4
70°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4
72.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4
75°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4
77.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.4
80°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.0
82.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
85°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
87.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8
2.5°	159.0	154.2	148.5	142.3	141.3	138.0	133.2	126.5	124.1	119.4	115.1
5°	199.6	186.7	173.3	161.4	157.6	152.3	143.7	131.8	124.1	115.6	108.4
7.5°	254.0	224.4	197.2	175.7	169.0	160.4	147.1	131.8	120.3	108.4	98.8
10°	326.6	266.4	219.6	184.8	173.8	162.3	144.7	126.1	112.7	98.8	88.8
12.5°	466.5	328.0	240.7	189.6	174.3	159.5	137.0	117.0	101.7	87.9	77.8
15°	663.2	445.0	283.1	192.9	169.5	151.4	125.1	104.6	89.3	76.4	66.8
17.5°	829.4	555.8	340.0	202.5	166.2	140.9	111.3	90.2	75.4	64.0	56.3
20°	910.6	605.4	365.8	203.9	156.6	125.1	95.0	75.0	62.1	52.5	45.8
22.5°	901.0	588.7	341.9	178.6	132.3	105.5	78.8	60.6	49.7	42.0	37.2
25°	837.0	516.2	278.9	136.6	103.1	85.5	61.6	47.3	38.7	33.4	29.6
27.5°	729.6	414.5	203.4	96.5	78.3	64.9	45.8	36.3	29.6	25.8	23.4
30°	562.0	265.0	117.0	69.2	56.8	46.3	34.4	26.3	22.4	20.1	18.1
32.5°	289.8	128.9	77.8	49.7	40.1	33.4	23.9	19.1	16.7	15.3	14.3
35°	159.0	91.7	54.0	32.0	25.8	21.5	16.2	13.4	12.4	11.5	11.5
37.5°	109.3	56.8	30.1	19.1	15.8	13.4	11.0	9.5	9.1	9.1	9.1
40°	63.0	30.1	17.2	11.9	10.0	9.1	7.6	7.2	7.2	7.2	7.6
42.5°	32.5	17.7	11.5	8.1	7.2	6.2	5.3	5.3	5.3	5.7	6.2
45°	19.1	11.9	7.6	5.3	4.8	4.3	3.8	3.8	4.3	4.8	5.3
47.5°	11.9	8.1	4.8	3.3	2.9	2.9	2.9	2.9	3.3	3.8	4.3
50°	8.1	4.3	2.9	1.9	1.9	1.9	1.9	2.4	2.9	3.3	3.8
52.5°	4.3	2.4	1.9	1.4	1.4	1.4	1.9	1.9	2.4	2.9	3.3
55°	2.4	1.9	1.4	1.4	1.4	1.4	1.4	1.9	2.4	2.9	3.3
57.5°	1.9	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.9
60°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.9
62.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.4
65°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.4
67.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	2.4
70°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	2.4
72.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9
75°	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	2.4
77.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
85°	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8
2.5°	112.7	108.9	105.0	105.0	103.1	100.3	99.3	96.5	94.5	93.6	92.6
5°	103.1	97.4	92.2	91.7	89.3	85.9	84.5	81.6	79.7	78.8	78.3
7.5°	92.2	86.4	81.2	80.2	78.3	75.9	74.5	72.1	71.1	70.2	69.7
10°	81.6	75.9	72.1	71.1	69.7	67.8	66.4	64.9	64.0	63.5	63.5
12.5°	71.1	66.8	63.5	62.6	61.6	60.2	59.2	58.3	57.8	57.8	57.8
15°	61.6	57.8	54.9	54.9	54.0	53.0	53.0	52.0	51.6	52.0	52.5
17.5°	52.0	49.2	46.8	46.8	46.3	45.8	45.8	45.8	46.3	46.8	47.7
20°	43.0	40.6	39.6	39.6	39.2	39.6	39.6	40.1	40.6	42.0	43.5
22.5°	34.9	33.4	32.5	32.9	32.9	33.4	33.9	34.9	35.8	37.2	38.7
25°	28.2	27.2	26.7	27.2	27.7	28.2	29.1	30.1	31.5	32.9	34.9
27.5°	22.4	22.0	22.0	22.4	22.9	23.9	25.3	26.3	27.7	29.1	31.0
30°	18.1	17.7	18.1	19.1	19.6	20.5	21.5	22.9	24.4	25.8	27.7
32.5°	14.3	14.8	15.3	15.8	16.2	17.7	18.6	19.6	21.0	22.4	24.4
35°	11.9	12.4	12.9	13.4	13.8	14.8	15.8	16.7	18.1	19.6	21.5
37.5°	9.5	10.0	10.5	11.5	11.9	12.4	13.8	14.3	15.8	16.7	18.6
40°	8.1	8.6	9.1	9.5	10.0	11.0	11.9	12.4	13.4	14.8	16.2
42.5°	6.7	7.2	7.6	8.1	8.6	9.5	10.0	11.0	11.9	12.9	13.8
45°	5.7	6.2	6.7	7.2	7.6	8.1	8.6	9.5	10.0	11.0	11.9
47.5°	4.8	5.3	6.2	6.2	6.7	7.2	7.6	8.1	9.1	9.5	10.5
50°	4.3	4.8	5.3	5.7	5.7	6.2	6.7	7.2	7.6	8.1	9.1
52.5°	3.8	4.3	4.8	4.8	5.3	5.7	6.2	6.2	6.7	7.2	7.6
55°	3.3	3.8	4.3	4.3	4.8	5.3	5.3	5.7	6.2	6.2	6.7
57.5°	3.3	3.3	3.8	3.8	4.3	4.3	4.8	5.3	5.3	5.7	6.2
60°	2.9	3.3	3.3	3.8	3.8	4.3	4.3	4.8	4.8	5.3	5.3
62.5°	2.9	2.9	3.3	3.3	3.8	3.8	4.3	4.3	4.3	4.8	4.8
65°	2.9	2.9	3.3	3.3	3.3	3.8	3.8	3.8	3.8	4.3	4.3
67.5°	2.4	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.8	3.8	3.8
70°	2.4	2.9	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.4	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.9	2.9	2.9
75°	2.4	2.4	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.9	2.9
77.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
80°	1.9	1.9	1.9	1.9	1.9	2.4	1.9	1.9	1.9	1.9	1.9
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4
85°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.4
87.5°	1.9	1.9	1.9	1.4	1.4	1.4	1.4	1.4	1.4	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212114

CATALOG NUMBER: LDSQA4A10940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	121.8	121.8	121.8	121.8	121.8	121.8	121.8	121.8
2.5°	91.2	90.2	91.2	90.2	90.2	88.3	89.8	88.8
5°	76.9	75.9	76.9	76.4	75.4	75.0	75.9	75.4
7.5°	68.8	67.8	68.8	68.8	67.8	67.3	68.3	67.8
10°	62.6	62.1	62.6	62.6	62.1	61.6	62.6	62.1
12.5°	57.3	56.8	57.8	57.8	57.3	57.3	58.3	57.3
15°	52.5	52.5	53.5	53.5	53.5	53.5	54.4	54.0
17.5°	47.7	48.7	49.7	50.1	50.1	50.1	51.1	51.1
20°	43.9	44.9	45.8	46.3	46.8	46.8	47.7	47.7
22.5°	39.6	40.6	42.0	42.5	43.0	43.5	44.4	44.4
25°	35.8	36.8	38.2	38.7	39.6	40.1	41.1	41.1
27.5°	32.0	33.4	34.4	35.3	35.8	36.8	37.7	37.7
30°	28.6	30.1	31.0	32.0	32.5	33.4	34.4	34.4
32.5°	25.3	26.7	27.7	28.6	29.6	30.1	31.5	31.5
35°	22.4	23.4	24.8	25.3	26.3	27.2	28.2	28.2
37.5°	19.6	20.5	21.5	22.4	23.4	23.9	24.8	25.3
40°	17.2	18.1	19.1	19.6	20.5	21.5	22.0	22.4
42.5°	14.8	15.8	16.7	17.2	18.1	18.6	19.6	19.6
45°	12.9	13.8	14.3	14.8	15.8	16.2	17.2	17.2
47.5°	11.0	11.9	12.4	12.9	13.4	13.8	14.8	14.8
50°	9.5	10.0	10.5	11.0	11.5	12.4	12.9	12.9
52.5°	8.1	9.1	9.1	9.5	10.0	10.5	11.0	11.5
55°	7.2	7.6	8.1	8.1	8.6	9.1	9.5	10.0
57.5°	6.2	6.7	7.2	7.2	7.6	7.6	8.1	8.6
60°	5.7	5.7	6.2	6.2	6.2	6.7	6.7	7.2
62.5°	4.8	4.8	5.3	5.3	5.3	5.3	5.3	5.3
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	3.8	3.8	3.8	3.8	3.3	3.3	3.3	3.3
70°	3.3	3.3	3.3	3.3	2.9	2.9	2.9	2.4
72.5°	2.9	2.9	2.9	2.9	2.4	2.4	1.9	1.9
75°	2.4	2.4	2.4	2.4	2.4	1.9	1.9	1.9
77.5°	2.4	1.9	1.9	1.9	1.9	1.9	1.9	1.4
80°	1.9	1.9	1.4	1.4	1.4	1.4	1.4	1.4
82.5°	1.4	1.4	1.4	1.4	1.0	1.0	1.0	1.0
85°	1.4	1.0	1.0	1.0	1.0	1.0	1.0	1.0
87.5°	1.0	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)