

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212098

Luminaire Tested: **LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 881.1 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	9513	9513	9513
5°	21297	8947	6408
10°	83506	7830	5046
15°	181279	6349	4393
20°	270433	4701	3969
25°	351744	3314	3453
30°	393486	2226	3020
35°	354115	1313	2566
40°	288991	898	2238
45°	165937	603	1822
50°	48529	467	1537
55°	5607	372	1267
60°	1201	426	1027
65°	413	413	711
70°	368	510	510
75°	337	674	487
80°	0	1004	502
85°	0	2001	445

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.1	1.6
10°-20°	120.6	13.7
20°-30°	287.7	32.7
30°-40°	303.6	34.5
40°-50°	137.7	15.6
50°-60°	12.1	1.4
60°-70°	2.5	0.3
70°-80°	1.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.4	47.9
0°-40°	726.0	82.4
0°-60°	875.8	99.4
0°-90°	881.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	98	98	98	98	98	
5°	219	161	92	71	66	39
15°	1808	636	63	43	44	526
25°	3291	875	31	26	32	1495
35°	2994	242	11	15	22	1849
45°	1211	34	4	8	13	960
55°	33	5	2	5	8	66
65°	2	2	2	4	3	2
75°	1	1	2	2	1	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
2.5°	146.0	146.9	142.9	143.3	139.3	141.1	139.8	136.2	133.6	129.2	127.4
5°	219.0	220.3	211.4	208.8	199.5	199.5	195.5	186.2	177.8	167.7	160.6
7.5°	400.3	405.6	379.1	359.2	330.0	322.9	309.2	277.4	251.3	224.7	204.8
10°	848.9	839.2	784.3	739.2	664.0	636.1	599.0	507.4	423.3	339.7	274.3
12.5°	1338.6	1370.0	1264.3	1227.6	1108.6	1083.3	1004.2	854.6	712.6	564.9	434.0
15°	1807.5	1816.8	1724.3	1664.6	1519.5	1486.8	1389.5	1213.8	1022.7	816.6	635.7
17.5°	2183.9	2221.1	2085.3	2021.1	1832.7	1780.1	1665.5	1451.8	1239.1	1013.9	799.3
20°	2623.2	2632.9	2471.9	2348.5	2102.1	2022.0	1884.9	1619.9	1366.5	1109.4	887.8
22.5°	3022.6	3020.4	2813.4	2639.1	2327.3	2231.7	2062.3	1748.2	1453.6	1151.9	896.2
25°	3290.7	3297.8	3076.2	2870.0	2487.4	2358.2	2167.1	1815.0	1483.2	1150.6	875.0
27.5°	3433.6	3426.5	3189.0	2968.7	2546.2	2401.6	2194.1	1817.2	1456.3	1105.5	811.3
30°	3517.6	3423.0	3169.5	2940.8	2506.4	2357.8	2146.8	1747.3	1366.5	1004.6	697.6
32.5°	3292.9	3256.2	3035.5	2792.6	2369.3	2222.0	2013.6	1598.7	1224.0	850.2	499.9
35°	2994.3	2995.7	2780.2	2553.3	2154.3	2026.0	1811.0	1417.8	1050.2	591.0	241.5
37.5°	2681.1	2685.6	2480.8	2269.8	1914.5	1779.6	1578.3	1211.6	755.6	300.8	145.5
40°	2285.2	2294.5	2118.0	1948.6	1620.8	1490.8	1311.2	917.0	422.5	168.1	98.6
42.5°	1867.2	1878.7	1722.1	1571.7	1293.0	1186.0	1026.7	568.0	209.7	108.8	57.9
45°	1211.2	1244.4	1128.0	1064.8	903.3	839.6	670.2	289.7	126.5	63.7	34.1
47.5°	693.2	693.6	595.4	476.9	391.0	340.2	265.9	131.8	73.9	35.8	20.8
50°	322.0	330.0	261.4	217.6	155.7	131.8	108.4	71.2	38.9	20.8	12.8
52.5°	93.8	99.1	89.8	81.4	69.0	61.5	52.6	34.9	20.3	12.4	8.0
55°	33.2	35.4	33.2	31.0	27.9	25.2	22.6	16.8	11.5	7.5	5.3
57.5°	13.7	14.2	13.7	13.3	12.4	12.4	11.1	9.3	7.1	4.9	3.5
60°	6.2	6.6	6.2	6.6	6.2	6.2	6.2	6.6	4.4	3.1	2.7
62.5°	2.7	3.1	3.1	3.1	3.1	3.5	3.5	3.1	2.7	2.2	1.8
65°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
70°	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9	1.3	1.3	1.3
72.5°	1.3	1.3	1.3	1.3	0.9	0.9	0.9	0.9	0.9	1.3	1.3
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
82.5°	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.9	0.9	0.9
85°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.4	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
2.5°	125.2	121.2	115.0	111.0	109.3	106.6	104.8	100.4	98.6	95.1	93.8
5°	153.9	146.0	136.7	129.2	124.3	119.0	111.0	102.2	97.8	92.0	88.9
7.5°	186.7	169.4	153.1	139.8	133.6	126.5	116.3	102.6	94.2	86.7	82.3
10°	228.3	192.9	167.2	146.0	136.7	127.4	115.0	99.1	88.5	79.6	74.8
12.5°	325.6	232.7	180.0	149.5	137.6	126.1	110.6	94.2	81.8	71.7	66.4
15°	468.5	325.1	214.5	152.6	134.5	120.3	102.6	86.3	73.4	63.3	57.9
17.5°	595.0	414.5	262.3	164.1	133.6	113.7	92.9	76.1	63.7	54.0	49.5
20°	664.0	461.4	294.2	171.2	129.6	103.5	81.8	65.9	54.0	45.6	41.6
22.5°	665.3	458.7	282.7	155.7	114.1	89.8	70.8	55.7	45.1	37.6	34.5
25°	625.5	409.2	235.8	122.5	93.3	76.1	59.3	46.4	36.7	31.0	28.3
27.5°	551.2	332.7	173.4	88.5	73.0	61.5	47.8	37.2	28.8	25.2	23.0
30°	433.5	216.8	101.3	65.9	56.6	47.3	36.3	26.1	22.6	19.9	18.1
32.5°	232.7	105.3	70.8	48.7	40.3	33.2	23.9	19.0	16.4	14.6	14.2
35°	121.6	77.0	47.3	31.0	25.7	21.7	16.4	13.3	11.9	11.1	11.1
37.5°	87.1	48.2	30.1	19.9	16.8	13.7	11.5	9.7	8.8	8.8	8.8
40°	51.8	29.6	18.1	12.8	11.1	9.7	8.4	7.1	7.1	7.1	7.1
42.5°	31.4	18.6	12.8	8.8	8.0	7.1	6.2	5.8	5.3	5.3	5.8
45°	19.5	12.8	8.4	6.6	6.2	5.3	4.9	4.4	4.4	4.4	4.9
47.5°	12.4	9.3	6.2	4.4	4.0	3.5	3.1	3.1	3.5	3.5	4.0
50°	9.3	5.8	4.0	3.1	2.7	2.7	2.2	2.7	2.7	3.1	3.5
52.5°	5.3	3.5	2.7	2.2	2.2	1.8	1.8	2.2	2.2	2.7	3.1
55°	3.5	2.7	2.2	1.8	1.8	1.8	1.8	1.8	2.2	2.2	2.7
57.5°	2.7	2.2	1.8	1.8	1.8	1.3	1.8	1.8	1.8	2.2	2.7
60°	2.2	1.8	1.8	1.8	1.8	1.3	1.3	1.8	1.8	2.2	2.2
62.5°	1.8	1.8	1.8	1.8	1.8	1.3	1.8	1.8	1.8	1.8	2.2
65°	1.3	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.2
67.5°	1.3	1.3	1.8	1.8	1.8	1.3	1.8	1.8	1.8	1.8	2.2
70°	1.3	1.3	1.3	1.8	1.8	1.3	1.8	1.8	1.8	1.8	1.8
72.5°	1.3	1.3	1.3	1.8	1.8	1.3	1.8	1.8	1.8	1.8	1.8
75°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8
77.5°	1.3	1.3	1.3	1.3	1.8	1.3	1.8	1.8	1.8	1.8	1.8
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8	1.8
82.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
85°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8	1.8
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
2.5°	90.2	88.9	86.3	85.8	85.4	83.6	82.3	81.0	81.0	79.6	78.7
5°	83.6	81.4	78.3	77.0	76.5	74.3	72.5	71.2	70.8	69.5	68.1
7.5°	76.5	73.9	70.3	69.0	68.6	66.4	64.6	63.3	62.4	61.0	60.2
10°	69.0	65.9	62.8	61.5	61.0	58.8	57.5	56.2	55.3	54.4	53.5
12.5°	61.0	58.4	55.3	54.0	53.5	51.8	50.4	49.5	49.1	48.2	47.8
15°	53.1	50.4	47.8	46.9	46.4	45.1	44.2	43.8	43.4	43.4	42.9
17.5°	45.1	42.9	40.7	40.3	39.8	38.9	38.5	38.0	38.5	38.5	38.9
20°	37.6	35.8	34.1	34.1	33.6	33.2	33.2	33.2	34.1	34.5	35.4
22.5°	31.0	29.6	28.3	28.3	28.3	28.3	28.3	29.2	30.1	31.0	31.4
25°	25.7	24.3	23.9	23.9	23.9	24.3	24.8	25.7	26.5	27.4	28.3
27.5°	20.8	19.9	19.9	19.9	20.3	20.8	21.2	22.1	23.4	24.3	25.2
30°	16.8	16.4	16.4	16.8	17.3	17.7	18.6	19.5	20.3	21.2	22.1
32.5°	13.3	13.7	13.7	14.2	14.6	15.0	15.9	16.8	17.7	18.6	19.0
35°	11.1	11.1	11.5	11.9	12.4	12.8	13.7	14.6	15.0	15.9	16.8
37.5°	8.8	9.3	9.7	10.2	10.6	11.1	11.5	12.4	12.8	13.7	14.6
40°	7.5	8.0	8.4	8.8	8.8	9.7	9.7	10.6	11.1	11.9	12.8
42.5°	6.2	6.6	7.1	7.5	7.5	8.0	8.4	8.8	9.7	10.2	11.1
45°	4.9	5.3	5.8	6.2	6.6	7.1	7.1	8.0	8.4	8.8	9.7
47.5°	4.4	4.9	5.3	5.3	5.8	6.2	6.2	7.1	7.5	8.0	8.4
50°	3.5	4.0	4.4	4.9	4.9	5.3	5.8	6.2	6.6	7.1	7.1
52.5°	3.1	3.5	4.0	4.0	4.4	4.9	4.9	5.3	5.8	5.8	6.2
55°	3.1	3.5	3.5	4.0	4.0	4.4	4.4	4.9	4.9	5.3	5.3
57.5°	2.7	3.1	3.1	3.5	3.5	4.0	4.0	4.4	4.4	4.4	4.9
60°	2.7	2.7	3.1	3.1	3.5	3.5	3.5	4.0	4.0	4.0	4.4
62.5°	2.2	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5	4.0	4.0
65°	2.2	2.7	2.7	3.1	3.1	3.1	3.1	3.1	3.5	3.5	3.5
67.5°	2.2	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.1	3.1
70°	2.2	2.2	2.2	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
72.5°	1.8	2.2	2.2	2.2	2.2	2.7	2.7	2.7	2.7	2.7	2.2
75°	1.8	1.8	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
77.5°	1.8	1.8	1.8	2.2	2.2	2.2	2.2	2.2	2.2	1.8	1.8
80°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3
82.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.3	1.3	1.3
85°	1.8	1.3	1.8	1.8	1.8	1.3	1.3	1.3	1.3	1.3	0.9
87.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212098

CATALOG NUMBER: LDSQA4A10935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	98.2	98.2	98.2	98.2	98.2	98.2	98.2	98.2
2.5°	77.9	77.0	77.4	77.4	76.5	76.1	76.1	76.5
5°	67.2	66.4	66.8	66.8	65.9	65.5	65.5	65.9
7.5°	59.3	58.4	58.8	58.8	57.9	57.9	57.9	57.9
10°	53.1	52.6	52.6	52.6	51.8	52.2	51.8	51.3
12.5°	47.3	47.3	47.3	47.3	46.9	47.3	46.9	46.9
15°	42.9	42.9	43.4	43.4	43.4	43.8	43.8	43.8
17.5°	39.4	39.8	40.3	40.7	40.7	41.1	41.1	41.1
20°	35.8	36.7	37.2	37.6	37.6	38.5	38.0	38.5
22.5°	32.3	33.2	33.6	34.1	34.5	34.9	34.9	35.4
25°	29.2	30.1	30.5	31.0	31.4	32.3	32.3	32.3
27.5°	26.1	27.0	27.4	28.3	28.8	29.6	29.6	29.6
30°	23.0	23.9	24.3	24.8	25.7	26.5	26.5	27.0
32.5°	19.9	21.2	21.7	22.1	23.0	23.9	24.3	24.3
35°	17.7	18.6	19.0	19.9	20.3	21.7	21.7	21.7
37.5°	15.5	16.4	17.3	17.7	18.1	19.0	19.5	19.9
40°	13.7	14.6	15.0	15.5	16.4	17.3	17.7	17.7
42.5°	11.9	12.8	13.3	13.7	14.2	15.0	15.0	15.0
45°	10.6	11.1	11.5	11.9	12.4	12.8	13.3	13.3
47.5°	8.8	9.7	9.7	10.2	10.6	11.5	11.5	11.9
50°	7.5	8.4	8.4	8.8	9.3	9.7	10.2	10.2
52.5°	6.6	7.1	7.5	7.5	8.0	8.4	8.8	8.8
55°	5.8	6.2	6.2	6.6	6.6	7.1	7.5	7.5
57.5°	4.9	5.3	5.8	5.8	5.8	6.2	6.2	6.6
60°	4.4	4.9	4.9	4.9	4.9	5.3	5.3	5.3
62.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
65°	3.5	3.5	3.5	3.5	3.1	3.1	3.1	3.1
67.5°	3.1	3.1	3.1	3.1	2.7	2.7	2.7	2.7
70°	2.7	2.7	2.7	2.7	2.2	2.2	2.2	1.8
72.5°	2.2	2.2	2.2	2.2	2.2	1.8	1.8	1.8
75°	2.2	1.8	1.8	1.8	1.8	1.8	1.3	1.3
77.5°	1.8	1.8	1.8	1.3	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	0.9	0.9	0.9
82.5°	1.3	0.9	0.9	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.4	0.4	0.4	0.4
87.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)