

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212103

Luminaire Tested: **LDSQA4A10935D010TE LAR35FL 4LSQAL1H**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26798)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10935D010TE LAR35FL 4LSQAL1H
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 965.9 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.57
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212103

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQAL1H

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212103

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQAL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82		
6	97	90	86	82	95	89	85	82	88	84	82	87	83	81	86	83	81	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	259461	259461	259461
5°	253188	252070	251593
10°	219867	219827	220083
15°	183395	182423	182332
20°	120299	119340	120392
25°	36781	46529	36642
30°	9206	11130	9005
35°	2980	4600	2933
40°	1404	2188	1227
45°	726	904	548
50°	407	467	271
55°	220	304	152
60°	174	174	174
65°	92	92	92
70°	113	113	113
75°	0	150	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P1212103

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQAL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.3	24.4
10°-20°	487.5	50.5
20°-30°	212.9	22.0
30°-40°	23.2	2.4
40°-50°	4.8	0.5
50°-60°	1.3	0.1
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.7	96.9
0°-40°	959.0	99.3
0°-60°	965.1	99.9
0°-90°	965.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2678	2678	2678	2678	2678	
5°	2604	2596	2592	2599	2587	236
15°	1829	1821	1819	1822	1818	489
25°	344	424	435	428	343	199
35°	25	30	39	30	25	20
45°	5	6	7	5	4	4
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212103

CATALOG NUMBER: LDSQA4A10935D010TE LAR35FL 4LSQAL1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2678.3	2678.3	2678.3	2678.3	2678.3
2.5°	2666.4	2656.7	2651.4	2662.9	2651.4
5°	2603.6	2596.5	2592.1	2598.7	2587.2
7.5°	2431.5	2424.4	2430.6	2430.6	2424.9
10°	2235.1	2231.1	2234.7	2244.0	2237.3
12.5°	2044.5	2041.4	2042.7	2052.4	2044.9
15°	1828.6	1820.7	1818.9	1821.5	1818.0
17.5°	1541.1	1529.2	1521.6	1527.8	1529.6
20°	1166.9	1166.9	1157.6	1162.9	1167.8
22.5°	746.2	763.5	765.2	764.4	761.3
25°	344.1	424.2	435.3	428.2	342.8
27.5°	139.3	172.1	214.1	177.4	134.5
30°	82.3	86.7	99.5	85.4	80.5
32.5°	43.3	52.2	61.0	51.8	42.0
35°	25.2	30.1	38.9	29.6	24.8
37.5°	16.4	19.0	26.1	19.0	15.5
40°	11.1	12.4	17.3	11.9	9.7
42.5°	7.5	8.4	11.1	7.5	6.2
45°	5.3	5.8	6.6	4.9	4.0
47.5°	3.5	4.0	4.4	3.1	2.7
50°	2.7	2.7	3.1	2.2	1.8
52.5°	1.8	2.2	2.2	1.3	1.3
55°	1.3	1.3	1.8	0.9	0.9
57.5°	1.3	1.3	1.3	0.9	0.9
60°	0.9	0.9	0.9	0.9	0.9
62.5°	0.4	0.9	0.9	0.4	0.4
65°	0.4	0.4	0.4	0.4	0.4
67.5°	0.4	0.4	0.4	0.4	0.4
70°	0.4	0.4	0.4	0.4	0.4
72.5°	0.4	0.4	0.4	0.4	0.4
75°	0.0	0.4	0.4	0.0	0.0
77.5°	0.0	0.4	0.4	0.4	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)