

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212110

Luminaire Tested: **LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1024.4 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10366	10366	10366
5°	22930	9802	6885
10°	91818	8509	5755
15°	211638	6770	5055
20°	315928	4804	4505
25°	414371	3207	4019
30°	475660	2025	3512
35°	436131	1289	3039
40°	357647	847	2580
45°	207340	589	2082
50°	58762	437	1718
55°	5388	405	1453
60°	833	465	1201
65°	229	436	871
70°	283	538	680
75°	374	711	711
80°	0	1060	558
85°	0	2112	556



TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.2	1.5
10°-20°	136.2	13.3
20°-30°	331.9	32.4
30°-40°	359.7	35.1
40°-50°	163.0	15.9
50°-60°	12.6	1.2
60°-70°	2.6	0.3
70°-80°	1.9	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.3	47.2
0°-40°	843.0	82.3
0°-60°	1018.6	99.4
0°-90°	1024.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	107	107	107	107	107	
5°	236	174	101	76	71	42
15°	2110	690	68	49	50	613
25°	3877	991	30	30	38	1767
35°	3688	252	11	17	26	2268
45°	1513	32	4	10	15	1195
55°	32	4	2	6	9	73
65°	1	1	2	4	4	2
75°	1	1	2	3	2	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	160.2	157.4	158.8	155.0	152.6	150.7	151.7	150.7	144.5	143.1	138.4
5°	235.8	231.6	231.6	223.5	214.9	209.7	209.7	203.5	190.2	184.0	174.0
7.5°	422.7	414.1	407.0	381.8	349.0	330.5	325.7	299.6	265.8	244.4	219.2
10°	933.4	897.7	872.5	806.9	718.9	664.2	640.9	550.6	443.1	362.3	289.1
12.5°	1569.6	1521.1	1476.8	1369.4	1242.9	1156.8	1110.7	977.6	768.8	619.5	463.6
15°	2110.2	2057.9	2005.6	1874.8	1741.2	1666.6	1581.9	1405.5	1129.7	917.7	690.4
17.5°	2553.8	2524.3	2470.6	2279.0	2110.7	1994.2	1906.2	1675.6	1391.7	1149.7	892.5
20°	3064.5	2991.7	2895.7	2663.2	2433.0	2287.1	2163.4	1882.4	1554.3	1276.2	999.5
22.5°	3494.3	3442.5	3304.6	2997.9	2659.4	2534.8	2383.6	2045.5	1658.9	1329.9	1011.8
25°	3876.6	3795.3	3622.2	3257.5	2910.9	2698.8	2513.4	2133.9	1697.5	1333.7	991.4
27.5°	4100.5	3994.5	3791.0	3393.5	2997.9	2763.5	2558.1	2149.2	1673.2	1283.3	916.7
30°	4252.2	4041.1	3816.2	3394.9	2970.3	2730.7	2517.7	2072.6	1572.4	1168.3	791.2
32.5°	4002.1	3879.9	3665.0	3259.9	2820.1	2586.1	2374.5	1906.7	1415.0	997.6	550.6
35°	3687.8	3588.9	3402.1	2999.8	2594.7	2374.1	2149.6	1693.7	1210.1	685.6	252.0
37.5°	3322.6	3245.1	3044.0	2676.5	2319.9	2104.0	1879.1	1443.6	852.1	340.0	153.1
40°	2828.1	2762.5	2597.5	2302.3	1973.7	1768.3	1561.0	1079.8	462.6	189.7	99.9
42.5°	2324.6	2269.5	2119.2	1863.9	1575.3	1406.0	1223.4	658.1	230.1	119.3	55.6
45°	1513.4	1444.5	1363.7	1246.7	1104.1	999.9	784.5	317.6	136.5	66.6	31.9
47.5°	867.7	822.1	689.4	543.9	441.7	403.2	293.4	147.9	75.1	38.5	19.5
50°	389.9	360.4	302.4	246.3	178.3	139.3	118.4	74.2	37.1	20.9	13.3
52.5°	96.0	97.9	92.7	81.3	72.3	61.3	53.3	34.7	19.5	12.8	8.6
55°	31.9	32.3	29.5	28.1	25.7	23.8	21.9	15.7	11.9	11.4	4.3
57.5°	11.4	11.4	11.9	10.9	10.5	10.0	9.5	8.1	7.1	4.3	2.4
60°	4.3	4.3	4.3	4.8	4.8	4.8	5.2	4.8	3.3	2.4	1.9
62.5°	1.9	1.9	1.9	1.9	2.4	2.4	2.9	2.4	1.9	1.9	1.4
65°	1.0	1.0	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
67.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4	1.4
70°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4	1.4
72.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4	1.4
75°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.4
77.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.4
80°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.4
82.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.4
85°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.4
87.5°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	133.6	130.8	125.1	120.8	117.4	117.0	114.1	109.4	107.5	104.1	101.3
5°	164.5	157.4	148.3	139.8	133.6	130.3	120.3	111.3	106.0	100.8	96.0
7.5°	197.8	181.6	165.9	152.2	143.6	138.4	126.5	111.7	102.2	94.6	88.4
10°	239.6	206.4	179.3	157.9	146.4	139.3	125.1	107.5	95.6	86.5	80.4
12.5°	335.2	244.4	191.6	160.7	146.4	136.5	119.3	101.8	88.4	77.5	70.8
15°	498.8	341.4	227.3	162.1	141.7	130.3	110.8	92.2	78.9	67.5	61.3
17.5°	652.8	449.3	283.9	172.1	138.8	121.2	99.4	81.3	67.5	56.6	51.4
20°	732.7	503.1	315.2	179.7	134.1	109.8	86.1	69.4	56.1	46.6	42.3
22.5°	734.6	498.3	300.0	162.1	116.5	94.1	73.7	57.1	45.6	37.6	34.2
25°	689.4	440.8	246.8	126.5	94.1	78.9	61.3	46.6	35.7	30.0	27.6
27.5°	604.3	356.6	182.1	91.3	73.7	62.8	48.0	35.7	27.1	23.3	21.9
30°	467.4	220.6	100.8	67.5	55.6	47.1	34.7	23.8	20.4	18.1	17.1
32.5°	232.0	107.9	71.3	48.0	38.0	30.0	21.9	17.6	15.7	14.3	13.8
35°	126.0	77.5	44.7	29.0	22.8	19.0	14.7	12.4	11.4	10.9	10.9
37.5°	88.0	46.1	27.1	17.6	14.3	12.8	10.5	9.0	8.6	8.6	8.6
40°	48.5	27.6	16.6	11.4	9.5	8.6	7.1	6.7	6.7	6.7	7.1
42.5°	28.1	17.1	11.4	8.1	6.7	6.2	5.2	4.8	5.2	5.2	5.7
45°	18.1	12.8	7.6	5.7	4.8	4.3	3.8	3.8	4.3	4.3	4.8
47.5°	12.8	9.0	5.2	3.8	2.9	2.9	2.9	2.9	3.3	3.8	4.3
50°	7.6	4.8	2.9	2.4	1.9	1.9	1.9	2.4	2.9	2.9	3.3
52.5°	4.3	2.9	1.9	1.9	1.4	1.4	1.9	1.9	2.4	2.9	3.3
55°	2.4	1.9	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.9
57.5°	1.9	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.4
60°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	2.4	2.4
62.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	2.4
65°	1.4	1.4	1.4	1.9	1.4	1.9	1.9	1.9	1.9	1.9	2.4
67.5°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.4
70°	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.4
72.5°	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.4
75°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
77.5°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
80°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
82.5°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
85°	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	100.3	97.0	94.6	93.7	91.8	92.2	90.8	89.9	87.0	87.0	85.1
5°	92.7	88.4	85.6	84.2	82.3	81.8	80.4	78.9	76.1	75.6	74.2
7.5°	84.6	80.4	77.0	75.6	73.7	73.2	71.3	70.4	68.0	67.5	66.1
10°	76.1	71.3	68.5	67.0	65.1	65.1	63.7	62.8	60.9	60.9	59.9
12.5°	67.0	62.8	60.9	59.0	58.0	58.0	57.1	56.1	54.7	55.2	54.7
15°	57.5	54.2	52.3	51.4	50.9	50.9	50.4	49.9	49.0	49.9	49.0
17.5°	48.5	46.1	44.7	44.2	43.7	43.7	43.7	44.2	43.7	44.7	44.7
20°	39.9	38.0	37.1	37.1	36.6	37.6	37.6	38.5	38.5	39.9	40.4
22.5°	32.8	31.4	30.9	30.9	30.9	31.9	32.3	33.3	33.8	35.2	36.1
25°	26.2	25.7	25.7	25.7	26.2	27.1	28.1	29.0	29.5	31.4	31.9
27.5°	21.4	20.9	21.4	21.4	21.9	23.3	24.2	25.2	26.2	27.6	28.5
30°	17.1	17.1	17.6	18.1	18.5	19.5	20.9	21.9	22.8	24.2	25.2
32.5°	13.8	14.3	14.7	15.2	15.2	16.6	17.6	19.0	19.5	20.9	21.9
35°	11.4	11.9	12.4	12.8	12.8	14.3	15.2	16.2	17.1	18.1	19.0
37.5°	9.0	9.5	10.5	10.9	10.9	12.4	12.8	13.8	14.7	15.7	16.6
40°	7.6	8.1	9.0	9.0	9.5	10.5	10.9	11.9	12.8	13.8	14.7
42.5°	6.2	6.7	7.6	8.1	8.1	9.0	9.5	10.5	10.9	11.9	12.4
45°	5.7	5.7	6.7	6.7	7.1	7.6	8.6	9.0	9.5	10.5	10.9
47.5°	4.8	5.2	5.7	6.2	6.2	6.7	7.1	7.6	8.1	9.0	9.5
50°	3.8	4.3	5.2	5.2	5.2	6.2	6.7	7.1	7.1	7.6	8.1
52.5°	3.8	3.8	4.3	4.8	4.8	5.2	5.7	6.2	6.2	6.7	7.1
55°	3.3	3.3	3.8	4.3	4.3	4.8	5.2	5.2	5.7	5.7	6.2
57.5°	2.9	3.3	3.8	3.8	3.8	4.3	4.8	4.8	5.2	5.2	5.7
60°	2.9	3.3	3.3	3.8	3.8	4.3	4.3	4.3	4.8	4.8	4.8
62.5°	2.9	2.9	3.3	3.3	3.3	3.8	3.8	4.3	4.3	4.3	4.3
65°	2.9	2.9	3.3	3.3	3.3	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	2.4	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.3	3.3
70°	2.4	2.4	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.3
72.5°	2.4	2.4	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
75°	2.4	2.4	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.4	2.4
77.5°	1.9	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	1.9
80°	1.9	1.9	2.4	1.9	2.4	2.4	2.4	2.4	1.9	1.9	1.9
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4
85°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.0
87.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212110

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	107.0	107.0	107.0	107.0	107.0	107.0	107.0	107.0
2.5°	84.2	85.1	84.2	85.1	82.7	83.7	84.6	82.3
5°	73.2	72.3	72.7	73.7	71.8	72.3	72.7	70.8
7.5°	65.6	66.1	65.1	66.1	64.7	65.1	65.6	64.2
10°	59.4	59.9	59.4	59.9	58.5	59.4	59.9	58.5
12.5°	53.7	54.7	54.2	55.2	53.7	54.7	55.6	53.7
15°	49.4	50.4	49.9	50.9	49.9	50.9	51.8	50.4
17.5°	45.2	46.1	46.1	47.1	46.6	47.5	48.5	47.1
20°	40.9	42.3	42.3	43.3	43.3	43.7	45.2	43.7
22.5°	37.1	38.5	38.5	39.5	39.5	40.4	41.4	40.4
25°	32.8	34.7	35.2	36.1	36.1	37.1	38.5	37.6
27.5°	30.0	31.4	31.9	32.8	33.3	34.2	35.2	34.2
30°	26.2	28.1	28.5	29.5	30.0	31.4	31.9	31.4
32.5°	23.3	24.7	25.2	26.2	27.1	28.1	29.0	28.5
35°	20.4	21.9	22.3	23.3	23.8	25.2	26.2	25.7
37.5°	18.1	19.5	20.0	20.4	20.9	22.3	23.3	22.8
40°	15.7	16.6	17.1	18.1	18.5	19.5	20.4	20.4
42.5°	13.8	14.7	15.2	15.7	16.2	17.1	18.1	17.6
45°	11.9	12.8	13.3	13.8	14.3	14.7	15.7	15.2
47.5°	10.0	10.9	11.4	11.9	12.4	12.8	13.8	13.3
50°	8.6	9.5	9.5	10.0	10.5	10.9	11.9	11.4
52.5°	7.6	8.1	8.6	8.6	9.0	9.5	10.5	10.0
55°	6.7	7.1	7.1	7.6	7.6	8.1	8.6	8.6
57.5°	5.7	6.2	6.2	6.7	6.7	7.1	7.6	7.6
60°	5.2	5.2	5.7	5.7	5.7	6.2	6.2	6.2
62.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
65°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	3.3	3.3	3.3	3.3	3.3	2.9	2.9	2.9
70°	2.9	2.9	2.9	2.9	2.9	2.4	2.4	2.4
72.5°	2.9	2.9	2.4	2.4	2.4	2.4	2.4	1.9
75°	2.4	2.4	2.4	2.4	1.9	1.9	1.9	1.9
77.5°	1.9	1.9	1.9	1.9	1.4	1.4	1.4	1.4
80°	1.9	1.4	1.4	1.4	1.4	1.4	1.4	1.0
82.5°	1.4	1.4	1.4	1.0	1.0	1.0	1.0	1.0
85°	1.0	1.0	1.0	1.0	0.5	0.5	0.5	0.5
87.5°	1.0	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)