

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212112

Luminaire Tested: **LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 951.3 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	10269	10269	10269
5°	22989	9656	6924
10°	90166	8460	5450
15°	195731	6850	4744
20°	291989	5072	4289
25°	379792	3570	3730
30°	424863	2405	3255
35°	382356	1407	2767
40°	312032	961	2415
45°	179158	658	1959
50°	52402	497	1658
55°	6047	405	1368
60°	1298	465	1104
65°	436	436	756
70°	397	538	538
75°	374	711	524
80°	0	1060	558
85°	0	2112	556



TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.2	1.6
10°-20°	130.2	13.7
20°-30°	310.7	32.7
30°-40°	327.9	34.5
40°-50°	148.7	15.6
50°-60°	13.0	1.4
60°-70°	2.7	0.3
70°-80°	1.8	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.1	47.9
0°-40°	783.9	82.4
0°-60°	945.7	99.4
0°-90°	951.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	106	106	106	106	106	
5°	236	173	99	76	71	42
15°	1952	686	68	47	47	568
25°	3553	945	33	29	35	1614
35°	3233	261	12	16	23	1997
45°	1308	37	5	9	14	1037
55°	36	6	2	5	8	71
65°	2	2	2	4	3	3
75°	1	1	2	2	1	1
85°	0	1	2	1	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
2.5°	157.6	158.6	154.3	154.8	150.5	152.4	150.9	147.1	144.2	139.5	137.6
5°	236.4	237.9	228.3	225.4	215.4	215.4	211.1	201.1	192.0	181.0	173.4
7.5°	432.3	438.0	409.3	387.8	356.3	348.7	333.9	299.5	271.3	242.6	221.1
10°	916.6	906.1	846.8	798.1	716.9	686.8	646.7	547.8	457.1	366.8	296.1
12.5°	1445.3	1479.2	1365.1	1325.4	1196.9	1169.7	1084.2	922.8	769.5	609.9	468.6
15°	1951.6	1961.6	1861.8	1797.3	1640.7	1605.3	1500.2	1310.6	1104.3	881.7	686.4
17.5°	2358.0	2398.2	2251.5	2182.3	1978.8	1922.0	1798.3	1567.6	1337.8	1094.7	863.1
20°	2832.3	2842.8	2669.0	2535.7	2269.7	2183.2	2035.2	1749.1	1475.4	1197.9	958.6
22.5°	3263.6	3261.2	3037.7	2849.5	2512.8	2409.6	2226.7	1887.6	1569.5	1243.7	967.7
25°	3553.1	3560.7	3321.4	3098.8	2685.7	2546.2	2339.9	1959.7	1601.5	1242.3	944.7
27.5°	3707.3	3699.7	3443.2	3205.4	2749.2	2593.0	2369.0	1962.1	1572.4	1193.6	876.0
30°	3798.1	3695.9	3422.2	3175.3	2706.2	2545.8	2317.9	1886.6	1475.4	1084.7	753.2
32.5°	3555.5	3515.8	3277.5	3015.3	2558.2	2399.1	2174.2	1726.1	1321.6	918.0	539.7
35°	3233.1	3234.5	3001.9	2756.9	2326.0	2187.5	1955.4	1530.8	1133.9	638.1	260.8
37.5°	2894.9	2899.7	2678.5	2450.7	2067.2	1921.5	1704.2	1308.2	815.8	324.8	157.1
40°	2467.4	2477.5	2286.9	2104.0	1750.0	1609.6	1415.7	990.1	456.1	181.5	106.5
42.5°	2016.1	2028.5	1859.4	1697.0	1396.1	1280.5	1108.6	613.3	226.4	117.5	62.6
45°	1307.7	1343.6	1218.0	1149.7	975.3	906.5	723.6	312.8	136.6	68.8	36.8
47.5°	748.4	748.9	642.9	514.9	422.2	367.3	287.1	142.3	79.8	38.7	22.4
50°	347.7	356.3	282.3	235.0	168.1	142.3	117.0	76.9	42.0	22.4	13.9
52.5°	101.3	107.0	97.0	87.9	74.5	66.4	56.8	37.7	22.0	13.4	8.6
55°	35.8	38.2	35.8	33.4	30.1	27.2	24.4	18.1	12.4	8.1	5.7
57.5°	14.8	15.3	14.8	14.3	13.4	13.4	11.9	10.0	7.6	5.3	3.8
60°	6.7	7.2	6.7	7.2	6.7	6.7	6.7	7.2	4.8	3.3	2.9
62.5°	2.9	3.3	3.3	3.3	3.3	3.8	3.8	3.3	2.9	2.4	1.9
65°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
67.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
70°	1.4	1.4	1.4	1.4	1.4	1.4	1.0	1.0	1.4	1.4	1.4
72.5°	1.4	1.4	1.4	1.4	1.0	1.0	1.0	1.0	1.0	1.4	1.4
75°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
77.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
80°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0
82.5°	0.0	0.0	0.0	0.5	0.5	0.5	0.5	0.5	1.0	1.0	1.0
85°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0
87.5°	0.0	0.0	0.0	0.0	0.5	0.5	0.5	0.5	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
2.5°	135.2	130.9	124.2	119.9	118.0	115.1	113.2	108.4	106.5	102.7	101.3
5°	166.2	157.6	147.6	139.5	134.2	128.5	119.9	110.3	105.6	99.3	96.0
7.5°	201.6	182.9	165.3	150.9	144.2	136.6	125.6	110.8	101.7	93.6	88.8
10°	246.5	208.2	180.5	157.6	147.6	137.6	124.2	107.0	95.5	86.0	80.7
12.5°	351.5	251.2	194.4	161.4	148.5	136.1	119.4	101.7	88.4	77.4	71.6
15°	505.8	351.1	231.6	164.8	145.2	129.9	110.8	93.1	79.3	68.3	62.6
17.5°	642.4	447.5	283.2	177.2	144.2	122.8	100.3	82.2	68.8	58.3	53.5
20°	716.9	498.2	317.6	184.8	139.9	111.8	88.4	71.2	58.3	49.2	44.9
22.5°	718.4	495.3	305.2	168.1	123.2	97.0	76.4	60.2	48.7	40.6	37.3
25°	675.4	441.8	254.6	132.3	100.8	82.2	64.0	50.2	39.6	33.4	30.6
27.5°	595.1	359.2	187.2	95.5	78.8	66.4	51.6	40.1	31.0	27.2	24.8
30°	468.1	234.0	109.4	71.2	61.1	51.1	39.2	28.2	24.4	21.5	19.6
32.5°	251.2	113.7	76.4	52.5	43.5	35.8	25.8	20.5	17.7	15.8	15.3
35°	131.3	83.1	51.1	33.4	27.7	23.4	17.7	14.3	12.9	11.9	11.9
37.5°	94.1	52.1	32.5	21.5	18.1	14.8	12.4	10.5	9.6	9.6	9.6
40°	55.9	32.0	19.6	13.9	11.9	10.5	9.1	7.6	7.6	7.6	7.6
42.5°	33.9	20.1	13.9	9.6	8.6	7.6	6.7	6.2	5.7	5.7	6.2
45°	21.0	13.9	9.1	7.2	6.7	5.7	5.3	4.8	4.8	4.8	5.3
47.5°	13.4	10.0	6.7	4.8	4.3	3.8	3.3	3.3	3.8	3.8	4.3
50°	10.0	6.2	4.3	3.3	2.9	2.9	2.4	2.9	2.9	3.3	3.8
52.5°	5.7	3.8	2.9	2.4	2.4	1.9	1.9	2.4	2.4	2.9	3.3
55°	3.8	2.9	2.4	1.9	1.9	1.9	1.9	1.9	2.4	2.4	2.9
57.5°	2.9	2.4	1.9	1.9	1.9	1.4	1.9	1.9	1.9	2.4	2.9
60°	2.4	1.9	1.9	1.9	1.9	1.4	1.4	1.9	1.9	2.4	2.4
62.5°	1.9	1.9	1.9	1.9	1.9	1.4	1.9	1.9	1.9	1.9	2.4
65°	1.4	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.4
67.5°	1.4	1.4	1.9	1.9	1.9	1.4	1.9	1.9	1.9	1.9	2.4
70°	1.4	1.4	1.4	1.9	1.9	1.4	1.9	1.9	1.9	1.9	1.9
72.5°	1.4	1.4	1.4	1.9	1.9	1.4	1.9	1.9	1.9	1.9	1.9
75°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9
77.5°	1.4	1.4	1.4	1.4	1.9	1.4	1.9	1.9	1.9	1.9	1.9
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
82.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9
85°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9	1.9
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
2.5°	97.4	96.0	93.1	92.7	92.2	90.3	88.8	87.4	87.4	86.0	85.0
5°	90.3	87.9	84.5	83.1	82.6	80.2	78.3	76.9	76.4	75.0	73.6
7.5°	82.6	79.8	75.9	74.5	74.0	71.6	69.7	68.3	67.3	65.9	65.0
10°	74.5	71.2	67.8	66.4	65.9	63.5	62.1	60.7	59.7	58.7	57.8
12.5°	65.9	63.0	59.7	58.3	57.8	55.9	54.4	53.5	53.0	52.1	51.6
15°	57.3	54.4	51.6	50.6	50.2	48.7	47.8	47.3	46.8	46.8	46.3
17.5°	48.7	46.3	43.9	43.5	43.0	42.0	41.6	41.1	41.6	41.6	42.0
20°	40.6	38.7	36.8	36.8	36.3	35.8	35.8	35.8	36.8	37.3	38.2
22.5°	33.4	32.0	30.6	30.6	30.6	30.6	30.6	31.5	32.5	33.4	33.9
25°	27.7	26.3	25.8	25.8	25.8	26.3	26.7	27.7	28.7	29.6	30.6
27.5°	22.4	21.5	21.5	21.5	22.0	22.4	22.9	23.9	25.3	26.3	27.2
30°	18.1	17.7	17.7	18.1	18.6	19.1	20.1	21.0	22.0	22.9	23.9
32.5°	14.3	14.8	14.8	15.3	15.8	16.2	17.2	18.1	19.1	20.1	20.5
35°	11.9	11.9	12.4	12.9	13.4	13.9	14.8	15.8	16.2	17.2	18.1
37.5°	9.6	10.0	10.5	11.0	11.5	11.9	12.4	13.4	13.9	14.8	15.8
40°	8.1	8.6	9.1	9.6	9.6	10.5	10.5	11.5	11.9	12.9	13.9
42.5°	6.7	7.2	7.6	8.1	8.1	8.6	9.1	9.6	10.5	11.0	11.9
45°	5.3	5.7	6.2	6.7	7.2	7.6	7.6	8.6	9.1	9.6	10.5
47.5°	4.8	5.3	5.7	5.7	6.2	6.7	6.7	7.6	8.1	8.6	9.1
50°	3.8	4.3	4.8	5.3	5.3	5.7	6.2	6.7	7.2	7.6	7.6
52.5°	3.3	3.8	4.3	4.3	4.8	5.3	5.3	5.7	6.2	6.2	6.7
55°	3.3	3.8	3.8	4.3	4.3	4.8	4.8	5.3	5.3	5.7	5.7
57.5°	2.9	3.3	3.3	3.8	3.8	4.3	4.3	4.8	4.8	4.8	5.3
60°	2.9	2.9	3.3	3.3	3.8	3.8	3.8	4.3	4.3	4.3	4.8
62.5°	2.4	2.9	2.9	3.3	3.3	3.3	3.8	3.8	3.8	4.3	4.3
65°	2.4	2.9	2.9	3.3	3.3	3.3	3.3	3.3	3.8	3.8	3.8
67.5°	2.4	2.4	2.9	2.9	2.9	2.9	3.3	3.3	3.3	3.3	3.3
70°	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
72.5°	1.9	2.4	2.4	2.4	2.4	2.9	2.9	2.9	2.9	2.9	2.4
75°	1.9	1.9	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
77.5°	1.9	1.9	1.9	2.4	2.4	2.4	2.4	2.4	2.4	1.9	1.9
80°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.4	1.4	1.4
85°	1.9	1.4	1.9	1.9	1.9	1.4	1.4	1.4	1.4	1.4	1.0
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212112

CATALOG NUMBER: LDSQA4A10940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
2.5°	84.1	83.1	83.6	83.6	82.6	82.2	82.2	82.6
5°	72.6	71.6	72.1	72.1	71.2	70.7	70.7	71.2
7.5°	64.0	63.0	63.5	63.5	62.6	62.6	62.6	62.6
10°	57.3	56.8	56.8	56.8	55.9	56.4	55.9	55.4
12.5°	51.1	51.1	51.1	51.1	50.6	51.1	50.6	50.6
15°	46.3	46.3	46.8	46.8	46.8	47.3	47.3	47.3
17.5°	42.5	43.0	43.5	43.9	43.9	44.4	44.4	44.4
20°	38.7	39.6	40.1	40.6	40.6	41.6	41.1	41.6
22.5°	34.9	35.8	36.3	36.8	37.3	37.7	37.7	38.2
25°	31.5	32.5	33.0	33.4	33.9	34.9	34.9	34.9
27.5°	28.2	29.1	29.6	30.6	31.0	32.0	32.0	32.0
30°	24.8	25.8	26.3	26.7	27.7	28.7	28.7	29.1
32.5°	21.5	22.9	23.4	23.9	24.8	25.8	26.3	26.3
35°	19.1	20.1	20.5	21.5	22.0	23.4	23.4	23.4
37.5°	16.7	17.7	18.6	19.1	19.6	20.5	21.0	21.5
40°	14.8	15.8	16.2	16.7	17.7	18.6	19.1	19.1
42.5°	12.9	13.9	14.3	14.8	15.3	16.2	16.2	16.2
45°	11.5	11.9	12.4	12.9	13.4	13.9	14.3	14.3
47.5°	9.6	10.5	10.5	11.0	11.5	12.4	12.4	12.9
50°	8.1	9.1	9.1	9.6	10.0	10.5	11.0	11.0
52.5°	7.2	7.6	8.1	8.1	8.6	9.1	9.6	9.6
55°	6.2	6.7	6.7	7.2	7.2	7.6	8.1	8.1
57.5°	5.3	5.7	6.2	6.2	6.2	6.7	6.7	7.2
60°	4.8	5.3	5.3	5.3	5.3	5.7	5.7	5.7
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
65°	3.8	3.8	3.8	3.8	3.3	3.3	3.3	3.3
67.5°	3.3	3.3	3.3	3.3	2.9	2.9	2.9	2.9
70°	2.9	2.9	2.9	2.9	2.4	2.4	2.4	1.9
72.5°	2.4	2.4	2.4	2.4	2.4	1.9	1.9	1.9
75°	2.4	1.9	1.9	1.9	1.9	1.9	1.4	1.4
77.5°	1.9	1.9	1.9	1.4	1.4	1.4	1.4	1.4
80°	1.4	1.4	1.4	1.4	1.4	1.0	1.0	1.0
82.5°	1.4	1.0	1.0	1.0	1.0	1.0	1.0	1.0
85°	1.0	1.0	1.0	1.0	0.5	0.5	0.5	0.5
87.5°	1.0	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)