

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219463

Luminaire Tested: **LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1316.9 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	86	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	13320	13320	13320
5°	29475	12603	8859
10°	118024	10949	7388
15°	272044	8705	6489
20°	406103	6175	5794
25°	532655	4115	5163
30°	611438	2606	4508
35°	560626	1668	3903
40°	459752	1075	3313
45°	266525	754	2685
50°	75521	558	2215
55°	6925	524	1858
60°	1066	601	1531
65°	275	573	1123
70°	340	708	878
75°	449	936	936
80°	0	1395	669
85°	0	2779	667



TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.5	1.5
10°-20°	175.1	13.3
20°-30°	426.6	32.4
30°-40°	462.4	35.1
40°-50°	209.5	15.9
50°-60°	16.2	1.2
60°-70°	3.4	0.3
70°-80°	2.5	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.3	47.2
0°-40°	1083.7	82.3
0°-60°	1309.4	99.4
0°-90°	1316.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1316.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	138	138	138	138	138	
5°	303	224	130	98	91	55
15°	2712	887	87	63	65	788
25°	4983	1274	38	38	48	2271
35°	4740	324	14	22	33	2916
45°	1945	41	6	12	20	1536
55°	41	6	3	7	11	94
65°	1	2	2	5	5	2
75°	1	2	2	4	2	1
85°	0	2	2	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
2.5°	206.0	202.4	204.1	199.3	196.2	193.7	194.9	193.7	185.8	183.9	177.9
5°	303.1	297.7	297.7	287.3	276.3	269.6	269.6	261.6	244.5	236.5	223.7
7.5°	543.3	532.3	523.2	490.8	448.7	424.8	418.7	385.0	341.6	314.1	281.8
10°	1199.8	1153.9	1121.6	1037.2	924.2	853.9	823.9	707.8	569.6	465.7	371.6
12.5°	2017.6	1955.2	1898.4	1760.2	1597.7	1487.1	1427.8	1256.6	988.3	796.4	595.9
15°	2712.5	2645.3	2578.1	2410.0	2238.2	2142.3	2033.5	1806.8	1452.2	1179.6	887.4
17.5°	3282.7	3244.9	3175.8	2929.5	2713.1	2563.4	2450.3	2153.8	1789.0	1477.9	1147.2
20°	3939.2	3845.7	3722.2	3423.3	3127.5	2939.9	2781.0	2419.8	1998.0	1640.4	1284.7
22.5°	4491.7	4425.1	4247.9	3853.7	3418.5	3258.3	3064.0	2629.4	2132.5	1709.5	1300.7
25°	4983.2	4878.6	4656.2	4187.3	3741.8	3469.2	3230.9	2743.1	2182.0	1714.4	1274.3
27.5°	5271.1	5134.7	4873.1	4362.1	3853.7	3552.3	3288.3	2762.6	2150.8	1649.6	1178.4
30°	5466.0	5194.6	4905.5	4364.0	3818.2	3510.1	3236.3	2664.2	2021.3	1501.7	1017.0
32.5°	5144.5	4987.4	4711.1	4190.4	3625.1	3324.3	3052.4	2450.9	1818.9	1282.3	707.8
35°	4740.5	4613.4	4373.1	3856.0	3335.3	3051.8	2763.3	2177.1	1555.5	881.4	323.9
37.5°	4271.1	4171.5	3912.9	3440.4	2982.1	2704.6	2415.5	1855.7	1095.2	437.0	196.8
40°	3635.5	3551.1	3339.0	2959.4	2537.1	2273.0	2006.5	1388.1	594.7	243.8	128.3
42.5°	2988.2	2917.2	2724.1	2395.9	2024.9	1807.3	1572.6	845.9	295.8	153.4	71.5
45°	1945.4	1856.8	1752.9	1602.6	1419.2	1285.3	1008.5	408.3	175.4	85.5	41.0
47.5°	1115.4	1056.7	886.2	699.2	567.8	518.3	377.1	190.1	96.5	49.5	25.0
50°	501.1	463.3	388.8	316.6	229.2	179.1	152.2	95.3	47.7	26.9	17.1
52.5°	123.5	125.9	119.2	104.5	92.9	78.8	68.4	44.6	25.0	16.5	11.0
55°	41.0	41.6	37.9	36.0	33.0	30.6	28.1	20.2	15.2	14.7	5.5
57.5°	14.7	14.7	15.2	14.1	13.5	12.9	12.2	10.4	9.2	5.5	3.1
60°	5.5	5.5	5.5	6.1	6.1	6.1	6.7	6.1	4.3	3.1	2.5
62.5°	2.5	2.5	2.5	2.5	3.1	3.1	3.7	3.1	2.5	2.5	1.9
65°	1.2	1.2	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
67.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.9	1.9
70°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.9	1.9
72.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.9	1.9
75°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.9
77.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2	1.2	1.2	1.9
80°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2	1.2	1.2	1.9
82.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2	1.2	1.2	1.9
85°	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2	1.2	1.9
87.5°	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
2.5°	171.8	168.1	160.8	155.2	151.0	150.4	146.7	140.6	138.1	133.8	130.2
5°	211.5	202.4	190.7	179.7	171.8	167.5	154.6	143.1	136.3	129.6	123.5
7.5°	254.2	233.4	213.3	195.6	184.5	177.9	162.6	143.6	131.4	121.7	113.7
10°	308.1	265.2	230.5	203.0	188.3	179.1	160.8	138.1	122.9	111.3	103.3
12.5°	430.9	314.1	246.3	206.6	188.3	175.4	153.4	130.8	113.7	99.6	91.1
15°	641.1	438.9	292.1	208.4	182.2	167.5	142.4	118.6	101.5	86.8	78.8
17.5°	839.2	577.6	364.9	221.3	178.5	155.8	127.7	104.5	86.8	72.8	66.0
20°	941.9	646.7	405.2	231.1	172.4	141.2	110.6	89.2	72.2	59.9	54.4
22.5°	944.3	640.5	385.7	208.4	149.8	121.0	94.7	73.4	58.7	48.3	44.1
25°	886.2	566.6	317.2	162.6	121.0	101.5	78.8	59.9	45.8	38.5	35.4
27.5°	776.9	458.4	234.1	117.3	94.7	80.7	61.8	45.8	34.8	30.0	28.1
30°	600.8	283.6	129.6	86.8	71.5	60.5	44.6	30.6	26.2	23.3	22.0
32.5°	298.3	138.7	91.7	61.8	48.9	38.5	28.1	22.6	20.2	18.3	17.7
35°	162.0	99.6	57.4	37.3	29.3	24.5	18.9	15.9	14.7	14.1	14.1
37.5°	113.1	59.3	34.8	22.6	18.3	16.5	13.5	11.6	11.0	11.0	11.0
40°	62.4	35.4	21.4	14.7	12.2	11.0	9.2	8.5	8.5	8.5	9.2
42.5°	36.0	22.0	14.7	10.4	8.5	7.9	6.7	6.1	6.7	6.7	7.3
45°	23.3	16.5	9.8	7.3	6.1	5.5	4.9	4.9	5.5	5.5	6.1
47.5°	16.5	11.6	6.7	4.9	3.7	3.7	3.7	3.7	4.3	4.9	5.5
50°	9.8	6.1	3.7	3.1	2.5	2.5	2.5	3.1	3.7	3.7	4.3
52.5°	5.5	3.7	2.5	2.5	1.9	1.9	2.5	2.5	3.1	3.7	4.3
55°	3.1	2.5	1.9	1.9	1.9	1.9	1.9	2.5	2.5	3.1	3.7
57.5°	2.5	1.9	1.9	1.9	1.9	1.9	1.9	2.5	2.5	3.1	3.1
60°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.5	2.5	3.1	3.1
62.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.5	2.5	2.5	2.5	3.1
65°	1.9	1.9	1.9	2.5	1.9	2.5	2.5	2.5	2.5	2.5	3.1
67.5°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.1
70°	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.1
72.5°	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.1
75°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
80°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	1.9	1.9	1.9	1.9	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
2.5°	129.0	124.6	121.7	120.4	118.0	118.6	116.7	115.5	111.9	111.9	109.4
5°	119.2	113.7	110.0	108.2	105.7	105.1	103.3	101.5	97.8	97.2	95.3
7.5°	108.8	103.3	99.0	97.2	94.7	94.1	91.7	90.5	87.4	86.8	84.9
10°	97.8	91.7	88.0	86.2	83.8	83.8	81.9	80.7	78.2	78.2	77.0
12.5°	86.2	80.7	78.2	75.8	74.5	74.5	73.4	72.2	70.3	70.9	70.3
15°	74.0	69.7	67.2	66.0	65.4	65.4	64.7	64.2	63.0	64.2	63.0
17.5°	62.4	59.3	57.4	56.8	56.2	56.2	56.2	56.8	56.2	57.4	57.4
20°	51.4	48.9	47.7	47.7	47.0	48.3	48.3	49.5	49.5	51.4	52.0
22.5°	42.2	40.3	39.7	39.7	39.7	41.0	41.6	42.8	43.4	45.2	46.4
25°	33.7	33.0	33.0	33.0	33.7	34.8	36.0	37.3	37.9	40.3	41.0
27.5°	27.5	26.9	27.5	27.5	28.1	30.0	31.2	32.4	33.7	35.4	36.6
30°	22.0	22.0	22.6	23.3	23.9	25.0	26.9	28.1	29.3	31.2	32.4
32.5°	17.7	18.3	18.9	19.6	19.6	21.4	22.6	24.5	25.0	26.9	28.1
35°	14.7	15.2	15.9	16.5	16.5	18.3	19.6	20.8	22.0	23.3	24.5
37.5°	11.6	12.2	13.5	14.1	14.1	15.9	16.5	17.7	18.9	20.2	21.4
40°	9.8	10.4	11.6	11.6	12.2	13.5	14.1	15.2	16.5	17.7	18.9
42.5°	7.9	8.5	9.8	10.4	10.4	11.6	12.2	13.5	14.1	15.2	15.9
45°	7.3	7.3	8.5	8.5	9.2	9.8	11.0	11.6	12.2	13.5	14.1
47.5°	6.1	6.7	7.3	7.9	7.9	8.5	9.2	9.8	10.4	11.6	12.2
50°	4.9	5.5	6.7	6.7	6.7	7.9	8.5	9.2	9.2	9.8	10.4
52.5°	4.9	4.9	5.5	6.1	6.1	6.7	7.3	7.9	7.9	8.5	9.2
55°	4.3	4.3	4.9	5.5	5.5	6.1	6.7	6.7	7.3	7.3	7.9
57.5°	3.7	4.3	4.9	4.9	4.9	5.5	6.1	6.1	6.7	6.7	7.3
60°	3.7	4.3	4.3	4.9	4.9	5.5	5.5	5.5	6.1	6.1	6.1
62.5°	3.7	3.7	4.3	4.3	4.3	4.9	4.9	5.5	5.5	5.5	5.5
65°	3.7	3.7	4.3	4.3	4.3	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	3.1	3.7	3.7	3.7	4.3	4.3	4.3	4.3	4.3	4.3	4.3
70°	3.1	3.1	3.7	3.7	3.7	4.3	4.3	4.3	4.3	4.3	4.3
72.5°	3.1	3.1	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
75°	3.1	3.1	3.1	3.1	3.1	3.7	3.7	3.7	3.7	3.1	3.1
77.5°	2.5	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.5
80°	2.5	2.5	3.1	2.5	3.1	3.1	3.1	3.1	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.9	1.9
85°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.9	1.9	1.9	1.2
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	1.9	1.9	1.9	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219463

CATALOG NUMBER: LDSQA4A15927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
2.5°	108.2	109.4	108.2	109.4	106.3	107.6	108.8	105.7
5°	94.1	92.9	93.6	94.7	92.3	92.9	93.6	91.1
7.5°	84.3	84.9	83.8	84.9	83.2	83.8	84.3	82.5
10°	76.4	77.0	76.4	77.0	75.1	76.4	77.0	75.1
12.5°	69.1	70.3	69.7	70.9	69.1	70.3	71.5	69.1
15°	63.6	64.7	64.2	65.4	64.2	65.4	66.6	64.7
17.5°	58.1	59.3	59.3	60.5	59.9	61.1	62.4	60.5
20°	52.6	54.4	54.4	55.6	55.6	56.2	58.1	56.2
22.5°	47.7	49.5	49.5	50.7	50.7	52.0	53.2	52.0
25°	42.2	44.6	45.2	46.4	46.4	47.7	49.5	48.3
27.5°	38.5	40.3	41.0	42.2	42.8	44.1	45.2	44.1
30°	33.7	36.0	36.6	37.9	38.5	40.3	41.0	40.3
32.5°	30.0	31.8	32.4	33.7	34.8	36.0	37.3	36.6
35°	26.2	28.1	28.7	30.0	30.6	32.4	33.7	33.0
37.5°	23.3	25.0	25.6	26.2	26.9	28.7	30.0	29.3
40°	20.2	21.4	22.0	23.3	23.9	25.0	26.2	26.2
42.5°	17.7	18.9	19.6	20.2	20.8	22.0	23.3	22.6
45°	15.2	16.5	17.1	17.7	18.3	18.9	20.2	19.6
47.5°	12.9	14.1	14.7	15.2	15.9	16.5	17.7	17.1
50°	11.0	12.2	12.2	12.9	13.5	14.1	15.2	14.7
52.5°	9.8	10.4	11.0	11.0	11.6	12.2	13.5	12.9
55°	8.5	9.2	9.2	9.8	9.8	10.4	11.0	11.0
57.5°	7.3	7.9	7.9	8.5	8.5	9.2	9.8	9.8
60°	6.7	6.7	7.3	7.3	7.3	7.9	7.9	7.9
62.5°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
65°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	4.3	4.3	4.3	4.3	4.3	3.7	3.7	3.7
70°	3.7	3.7	3.7	3.7	3.7	3.1	3.1	3.1
72.5°	3.7	3.7	3.1	3.1	3.1	3.1	3.1	2.5
75°	3.1	3.1	3.1	3.1	2.5	2.5	2.5	2.5
77.5°	2.5	2.5	2.5	2.5	1.9	1.9	1.9	1.9
80°	2.5	1.9	1.9	1.9	1.9	1.9	1.9	1.2
82.5°	1.9	1.9	1.9	1.2	1.2	1.2	1.2	1.2
85°	1.2	1.2	1.2	1.2	0.6	0.6	0.6	0.6
87.5°	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)