

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219481

Luminaire Tested: **LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1403.4 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15859	15859	15859
5°	41718	15112	9870
10°	163550	13083	8214
15°	301109	10310	7281
20°	378360	7289	6629
25°	452562	4799	5900
30°	475917	3009	5168
35°	479758	1821	4482
40°	441466	1214	3819
45°	314092	877	3178
50°	129793	678	2607
55°	7499	659	2280
60°	872	620	1860
65°	298	734	1307
70°	368	736	906
75°	487	973	973
80°	0	1450	1060
85°	0	2890	1445



TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	1.8
10°-20°	205.6	14.7
20°-30°	425.3	30.3
30°-40°	463.0	33.0
40°-50°	253.9	18.1
50°-60°	22.0	1.6
60°-70°	3.6	0.3
70°-80°	2.6	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	656.7	46.8
0°-40°	1119.8	79.8
0°-60°	1395.6	99.4
0°-90°	1403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1403.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	164	164	164	164	164	
5°	429	293	155	107	102	78
15°	3002	1262	103	69	73	838
25°	4234	1679	45	42	55	1912
35°	4057	459	15	24	38	2490
45°	2293	47	6	14	23	1750
55°	44	5	4	8	14	151
65°	1	2	3	5	6	2
75°	1	2	3	4	3	1
85°	0	1	3	2	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7
2.5°	257.5	248.5	247.2	248.5	242.2	241.5	242.7	237.6	233.1	228.6	224.7
5°	429.0	410.4	404.6	396.9	377.6	371.2	369.9	349.4	329.5	310.9	293.4
7.5°	833.6	796.4	776.5	737.8	678.8	652.5	638.4	570.9	508.0	450.8	398.8
10°	1662.6	1565.0	1517.5	1444.9	1315.8	1252.3	1206.0	1036.5	869.5	708.9	567.7
12.5°	2426.2	2372.2	2302.2	2263.7	2054.3	1974.1	1897.6	1662.6	1408.4	1148.9	891.4
15°	3002.3	2923.3	2848.7	2830.8	2666.4	2572.6	2487.9	2244.4	1942.0	1611.9	1262.0
17.5°	3340.7	3284.1	3213.5	3179.5	2986.8	2911.1	2814.8	2579.0	2284.9	1956.1	1549.6
20°	3670.1	3586.7	3487.1	3435.7	3222.5	3135.2	3026.0	2778.1	2466.7	2117.3	1710.8
22.5°	3971.3	3863.5	3722.1	3642.5	3403.0	3306.6	3184.6	2916.2	2579.0	2179.6	1724.3
25°	4233.9	4136.3	3948.2	3808.8	3526.3	3412.6	3270.7	2990.0	2619.5	2174.4	1678.6
27.5°	4284.0	4218.6	4049.7	3888.5	3569.3	3442.8	3295.7	3005.4	2591.2	2103.2	1556.0
30°	4254.5	4183.8	4048.4	3884.0	3551.3	3423.5	3270.7	2940.0	2480.7	1936.8	1331.3
32.5°	4183.2	4122.3	3960.4	3787.0	3462.7	3329.8	3168.6	2786.5	2291.4	1672.3	979.3
35°	4056.7	3964.9	3769.6	3627.1	3322.0	3185.2	2988.1	2581.6	2008.1	1202.2	459.2
37.5°	3799.2	3709.9	3569.3	3437.7	3140.3	2979.1	2771.1	2296.5	1488.6	655.7	283.8
40°	3490.9	3413.9	3291.3	3163.4	2857.1	2671.5	2442.2	1795.0	876.0	369.3	174.6
42.5°	3155.7	3076.1	2937.4	2788.4	2454.5	2258.6	2010.7	1161.8	461.7	217.7	95.0
45°	2292.6	2221.4	2120.5	2013.3	1820.0	1678.6	1352.4	610.0	255.6	115.6	46.9
47.5°	1568.9	1484.1	1297.9	1072.5	869.5	743.7	559.4	264.6	131.0	57.8	27.6
50°	861.2	771.3	676.3	526.6	352.5	289.7	225.4	127.8	59.1	28.9	15.4
52.5°	211.3	186.9	170.8	157.3	124.5	112.4	95.0	53.3	26.9	16.0	10.9
55°	44.4	41.1	39.2	38.5	35.3	34.1	29.5	20.6	14.8	10.3	5.1
57.5°	12.9	12.2	12.9	12.9	12.9	12.2	12.2	9.0	8.3	5.1	3.2
60°	4.5	4.5	4.5	5.1	5.1	5.1	5.7	5.7	4.5	3.2	2.6
62.5°	1.9	1.9	1.9	2.6	2.6	3.2	3.2	3.2	2.6	2.6	1.9
65°	1.3	1.3	1.3	1.3	1.9	1.9	1.9	1.9	1.9	1.9	1.9
67.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.9
70°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.9
72.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.9
75°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.9
77.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.3	1.3	1.3	1.9
80°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	1.3	1.3	1.3
85°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	1.3	1.3	1.3
87.5°	0.0	0.0	0.0	0.6	0.6	0.6	0.6	0.6	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7
2.5°	213.8	207.4	199.7	191.4	190.1	185.6	179.2	170.2	167.0	160.6	154.7
5°	268.4	251.1	233.1	217.1	212.0	204.8	193.3	177.2	167.0	155.4	145.8
7.5°	341.6	301.9	265.2	236.3	227.3	215.8	197.8	177.2	161.9	145.8	133.0
10°	439.3	358.4	295.4	248.5	233.7	218.4	194.5	169.6	151.6	133.0	119.5
12.5°	627.5	441.1	323.6	254.9	234.4	214.5	184.3	157.3	136.8	118.2	104.6
15°	892.0	598.6	380.9	259.5	228.0	203.5	168.3	140.7	120.1	102.8	89.9
17.5°	1115.5	747.5	457.3	272.2	223.4	189.5	149.6	121.4	101.5	86.0	75.7
20°	1224.6	814.3	491.9	274.2	210.7	168.3	127.8	100.8	83.5	70.7	61.7
22.5°	1211.9	791.8	459.9	240.2	177.9	142.0	105.9	81.6	66.8	56.5	50.1
25°	1125.7	694.2	375.0	183.6	138.7	114.9	82.9	63.6	52.0	44.9	39.8
27.5°	981.3	557.5	273.5	129.7	105.3	87.3	61.7	48.8	39.8	34.6	31.5
30°	755.9	356.4	157.3	93.2	76.4	62.3	46.2	35.3	30.2	26.9	24.4
32.5°	389.8	173.3	104.6	66.8	54.0	44.9	32.1	25.6	22.5	20.6	19.3
35°	213.8	123.3	72.6	43.1	34.6	28.9	21.9	18.0	16.7	15.4	15.4
37.5°	147.0	76.4	40.5	25.6	21.2	18.0	14.8	12.9	12.2	12.2	12.2
40°	84.7	40.5	23.2	16.0	13.5	12.2	10.3	9.6	9.6	9.6	10.3
42.5°	43.7	23.8	15.4	10.9	9.6	8.3	7.0	7.0	7.0	7.7	8.3
45°	25.6	16.0	10.3	7.0	6.4	5.7	5.1	5.1	5.7	6.4	7.0
47.5°	16.0	10.9	6.4	4.5	3.9	3.9	3.9	3.9	4.5	5.1	5.7
50°	10.9	5.7	3.9	2.6	2.6	2.6	2.6	3.2	3.9	4.5	5.1
52.5°	5.7	3.2	2.6	1.9	1.9	1.9	2.6	2.6	3.2	3.9	4.5
55°	3.2	2.6	1.9	1.9	1.9	1.9	1.9	2.6	3.2	3.9	4.5
57.5°	2.6	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	3.2	3.9
60°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	3.2	3.9
62.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	3.2	3.2
65°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	3.2	3.2
67.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	3.2
70°	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	3.2
72.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6
75°	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6	3.2
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6
80°	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6
82.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6
85°	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6	2.6
87.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.6	2.6	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7
2.5°	151.6	146.4	141.3	141.3	138.7	134.8	133.6	129.7	127.1	125.8	124.5
5°	138.7	131.0	123.9	123.3	120.1	115.6	113.7	109.8	107.2	105.9	105.3
7.5°	123.9	116.2	109.2	107.9	105.3	102.1	100.2	97.0	95.7	94.4	93.8
10°	109.8	102.1	97.0	95.7	93.8	91.2	89.3	87.3	86.0	85.4	85.4
12.5°	95.7	89.9	85.4	84.2	82.9	80.9	79.6	78.3	77.7	77.7	77.7
15°	82.9	77.7	73.9	73.9	72.6	71.3	71.3	70.0	69.4	70.0	70.7
17.5°	70.0	66.1	63.0	63.0	62.3	61.7	61.7	61.7	62.3	63.0	64.3
20°	57.8	54.5	53.3	53.3	52.7	53.3	53.3	54.0	54.5	56.5	58.4
22.5°	46.9	44.9	43.7	44.4	44.4	44.9	45.6	46.9	48.2	50.1	52.0
25°	37.9	36.6	35.9	36.6	37.2	37.9	39.2	40.5	42.4	44.4	46.9
27.5°	30.2	29.5	29.5	30.2	30.8	32.1	34.1	35.3	37.2	39.2	41.8
30°	24.4	23.8	24.4	25.6	26.3	27.6	28.9	30.8	32.8	34.6	37.2
32.5°	19.3	19.9	20.6	21.2	21.9	23.8	25.0	26.3	28.2	30.2	32.8
35°	16.0	16.7	17.3	18.0	18.6	19.9	21.2	22.5	24.4	26.3	28.9
37.5°	12.9	13.5	14.2	15.4	16.0	16.7	18.6	19.3	21.2	22.5	25.0
40°	10.9	11.6	12.2	12.9	13.5	14.8	16.0	16.7	18.0	19.9	21.9
42.5°	9.0	9.6	10.3	10.9	11.6	12.9	13.5	14.8	16.0	17.3	18.6
45°	7.7	8.3	9.0	9.6	10.3	10.9	11.6	12.9	13.5	14.8	16.0
47.5°	6.4	7.0	8.3	8.3	9.0	9.6	10.3	10.9	12.2	12.9	14.2
50°	5.7	6.4	7.0	7.7	7.7	8.3	9.0	9.6	10.3	10.9	12.2
52.5°	5.1	5.7	6.4	6.4	7.0	7.7	8.3	8.3	9.0	9.6	10.3
55°	4.5	5.1	5.7	5.7	6.4	7.0	7.0	7.7	8.3	8.3	9.0
57.5°	4.5	4.5	5.1	5.1	5.7	5.7	6.4	7.0	7.0	7.7	8.3
60°	3.9	4.5	4.5	5.1	5.1	5.7	5.7	6.4	6.4	7.0	7.0
62.5°	3.9	3.9	4.5	4.5	5.1	5.1	5.7	5.7	5.7	6.4	6.4
65°	3.9	3.9	4.5	4.5	4.5	5.1	5.1	5.1	5.1	5.7	5.7
67.5°	3.2	3.9	3.9	4.5	4.5	4.5	4.5	4.5	5.1	5.1	5.1
70°	3.2	3.9	3.9	3.9	3.9	4.5	4.5	4.5	4.5	4.5	4.5
72.5°	3.2	3.2	3.2	3.2	3.9	3.9	3.9	3.9	3.9	3.9	3.9
75°	3.2	3.2	3.2	3.2	3.2	3.9	3.9	3.9	3.9	3.9	3.9
77.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
80°	2.6	2.6	2.6	2.6	2.6	3.2	2.6	2.6	2.6	2.6	2.6
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	1.9	1.9
85°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	1.9	1.9	1.9	1.9
87.5°	2.6	2.6	2.6	1.9	1.9	1.9	1.9	1.9	1.9	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219481

CATALOG NUMBER: LDSQA4A15930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	163.7	163.7	163.7	163.7	163.7	163.7	163.7	163.7
2.5°	122.7	121.4	122.7	121.4	121.4	118.8	120.8	119.5
5°	103.4	102.1	103.4	102.8	101.5	100.8	102.1	101.5
7.5°	92.5	91.2	92.5	92.5	91.2	90.6	91.9	91.2
10°	84.2	83.5	84.2	84.2	83.5	82.9	84.2	83.5
12.5°	77.0	76.4	77.7	77.7	77.0	77.0	78.3	77.0
15°	70.7	70.7	72.0	72.0	72.0	72.0	73.2	72.6
17.5°	64.3	65.5	66.8	67.4	67.4	67.4	68.7	68.7
20°	59.1	60.4	61.7	62.3	63.0	63.0	64.3	64.3
22.5°	53.3	54.5	56.5	57.1	57.8	58.4	59.7	59.7
25°	48.2	49.4	51.4	52.0	53.3	54.0	55.2	55.2
27.5°	43.1	44.9	46.2	47.5	48.2	49.4	50.7	50.7
30°	38.5	40.5	41.8	43.1	43.7	44.9	46.2	46.2
32.5°	34.1	35.9	37.2	38.5	39.8	40.5	42.4	42.4
35°	30.2	31.5	33.4	34.1	35.3	36.6	37.9	37.9
37.5°	26.3	27.6	28.9	30.2	31.5	32.1	33.4	34.1
40°	23.2	24.4	25.6	26.3	27.6	28.9	29.5	30.2
42.5°	19.9	21.2	22.5	23.2	24.4	25.0	26.3	26.3
45°	17.3	18.6	19.3	19.9	21.2	21.9	23.2	23.2
47.5°	14.8	16.0	16.7	17.3	18.0	18.6	19.9	19.9
50°	12.9	13.5	14.2	14.8	15.4	16.7	17.3	17.3
52.5°	10.9	12.2	12.2	12.9	13.5	14.2	14.8	15.4
55°	9.6	10.3	10.9	10.9	11.6	12.2	12.9	13.5
57.5°	8.3	9.0	9.6	9.6	10.3	10.3	10.9	11.6
60°	7.7	7.7	8.3	8.3	8.3	9.0	9.0	9.6
62.5°	6.4	6.4	7.0	7.0	7.0	7.0	7.0	7.0
65°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
67.5°	5.1	5.1	5.1	5.1	4.5	4.5	4.5	4.5
70°	4.5	4.5	4.5	4.5	3.9	3.9	3.9	3.2
72.5°	3.9	3.9	3.9	3.9	3.2	3.2	2.6	2.6
75°	3.2	3.2	3.2	3.2	3.2	2.6	2.6	2.6
77.5°	3.2	2.6	2.6	2.6	2.6	2.6	2.6	1.9
80°	2.6	2.6	1.9	1.9	1.9	1.9	1.9	1.9
82.5°	1.9	1.9	1.9	1.9	1.3	1.3	1.3	1.3
85°	1.9	1.3	1.3	1.3	1.3	1.3	1.3	1.3
87.5°	1.3	0.6	0.6	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)