

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219493

Luminaire Tested: **LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1291.8 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	13940	13940	13940
5°	31226	13118	9394
10°	122421	11480	7397
15°	265766	9307	6449
20°	396494	6887	5814
25°	515703	4853	5056
30°	576906	3266	4430
35°	519187	1916	3761
40°	423711	1315	3275
45°	243289	891	2672
50°	71151	693	2246
55°	8208	557	1858
60°	1763	639	1511
65°	596	596	1054
70°	566	736	736
75°	487	973	749
80°	0	1450	725
85°	0	2890	778



TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.6	1.6
10°-20°	176.8	13.7
20°-30°	421.8	32.7
30°-40°	445.2	34.5
40°-50°	201.9	15.6
50°-60°	17.7	1.4
60°-70°	3.7	0.3
70°-80°	2.5	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.3	47.9
0°-40°	1064.5	82.4
0°-60°	1284.1	99.4
0°-90°	1291.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	144	144	144	144	144	
5°	321	235	135	104	97	58
15°	2650	932	93	64	64	771
25°	4825	1283	45	39	47	2192
35°	4390	354	16	22	32	2711
45°	1776	50	6	12	20	1408
55°	49	8	3	7	11	97
65°	3	3	3	5	5	3
75°	1	1	3	3	2	1
85°	0	1	3	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
2.5°	214.0	215.3	209.5	210.2	204.3	206.9	204.9	199.8	195.8	189.4	186.8
5°	321.1	322.9	310.0	306.1	292.5	292.5	286.7	273.0	260.8	245.8	235.4
7.5°	587.0	594.7	555.8	526.6	483.8	473.4	453.3	406.6	368.4	329.5	300.3
10°	1244.5	1230.3	1149.9	1083.8	973.5	932.6	878.1	743.9	620.6	498.1	402.1
12.5°	1962.5	2008.5	1853.6	1799.7	1625.3	1588.3	1472.2	1253.0	1044.8	828.2	636.3
15°	2649.9	2663.6	2528.1	2440.4	2227.8	2179.8	2037.1	1779.6	1499.5	1197.2	932.0
17.5°	3201.9	3256.4	3057.2	2963.3	2687.0	2609.7	2441.8	2128.5	1816.6	1486.5	1172.0
20°	3846.0	3860.2	3624.1	3443.1	3081.9	2964.6	2763.5	2375.0	2003.4	1626.6	1301.7
22.5°	4431.5	4428.3	4124.7	3869.2	3412.0	3272.0	3023.6	2563.1	2131.2	1688.8	1313.9
25°	4824.6	4835.0	4510.0	4207.8	3646.8	3457.4	3177.2	2661.0	2174.6	1686.9	1282.8
27.5°	5034.1	5023.7	4675.4	4352.4	3733.1	3520.9	3216.8	2664.3	2135.0	1620.7	1189.5
30°	5157.3	5018.5	4646.9	4311.5	3674.7	3456.8	3147.4	2561.8	2003.4	1472.8	1022.8
32.5°	4827.8	4774.0	4450.3	4094.3	3473.6	3257.7	2952.2	2343.8	1794.6	1246.5	732.9
35°	4390.1	4391.9	4076.1	3743.4	3158.4	2970.4	2655.2	2078.6	1539.6	866.4	354.1
37.5°	3930.9	3937.3	3637.1	3327.7	2806.9	2609.1	2314.0	1776.4	1107.7	441.0	213.3
40°	3350.5	3364.0	3105.2	2856.8	2376.3	2185.6	1922.3	1344.4	619.3	246.4	144.6
42.5°	2737.5	2754.4	2524.8	2304.3	1895.8	1738.7	1505.3	832.8	307.4	159.6	84.9
45°	1775.8	1824.4	1653.8	1561.0	1324.3	1231.0	982.6	424.8	185.5	93.4	49.9
47.5°	1016.2	1016.9	873.0	699.1	573.3	498.8	389.8	193.2	108.3	52.6	30.5
50°	472.1	483.8	383.3	319.1	228.3	193.2	158.9	104.4	57.0	30.5	18.8
52.5°	137.5	145.2	131.7	119.3	101.2	90.2	77.2	51.3	29.8	18.1	11.7
55°	48.6	51.9	48.6	45.4	40.9	36.9	33.1	24.7	16.8	11.0	7.8
57.5°	20.1	20.8	20.1	19.5	18.1	18.1	16.2	13.7	10.4	7.1	5.1
60°	9.1	9.7	9.1	9.7	9.1	9.1	9.1	9.7	6.5	4.6	3.9
62.5°	3.9	4.6	4.6	4.6	4.6	5.1	5.1	4.6	3.9	3.3	2.6
65°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
67.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
70°	2.0	2.0	2.0	2.0	2.0	2.0	1.3	1.3	2.0	2.0	2.0
72.5°	2.0	2.0	2.0	2.0	1.3	1.3	1.3	1.3	1.3	2.0	2.0
75°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
77.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.3	1.3	1.3
80°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.3	1.3	1.3
85°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.3	1.3	1.3
87.5°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
2.5°	183.5	177.7	168.6	162.8	160.2	156.3	153.7	147.2	144.6	139.4	137.5
5°	225.7	214.0	200.4	189.4	182.3	174.4	162.8	149.8	143.4	134.9	130.4
7.5°	273.7	248.4	224.4	204.9	195.8	185.5	170.6	150.5	138.1	127.1	120.6
10°	334.6	282.7	245.1	214.0	200.4	186.8	168.6	145.2	129.7	116.7	109.6
12.5°	477.4	341.2	263.9	219.2	201.7	184.8	162.2	138.1	120.0	105.0	97.3
15°	686.9	476.7	314.5	223.7	197.2	176.4	150.5	126.4	107.6	92.8	84.9
17.5°	872.3	607.7	384.6	240.6	195.8	166.7	136.2	111.6	93.4	79.1	72.7
20°	973.5	676.5	431.2	251.0	190.0	151.8	120.0	96.6	79.1	66.8	61.0
22.5°	975.4	672.5	414.4	228.3	167.3	131.7	103.8	81.7	66.1	55.1	50.6
25°	917.0	599.9	345.7	179.7	136.8	111.6	86.9	68.1	53.9	45.4	41.5
27.5°	808.1	487.7	254.2	129.7	107.0	90.2	70.1	54.4	42.2	36.9	33.8
30°	635.6	317.8	148.5	96.6	83.1	69.4	53.2	38.3	33.1	29.2	26.6
32.5°	341.2	154.3	103.8	71.4	59.0	48.6	35.0	27.9	24.0	21.4	20.8
35°	178.4	112.9	69.4	45.4	37.6	31.8	24.0	19.5	17.5	16.2	16.2
37.5°	127.8	70.7	44.1	29.2	24.7	20.1	16.8	14.3	13.0	13.0	13.0
40°	75.8	43.5	26.6	18.8	16.2	14.3	12.3	10.4	10.4	10.4	10.4
42.5°	46.0	27.2	18.8	13.0	11.7	10.4	9.1	8.4	7.8	7.8	8.4
45°	28.5	18.8	12.3	9.7	9.1	7.8	7.1	6.5	6.5	6.5	7.1
47.5°	18.1	13.7	9.1	6.5	5.8	5.1	4.6	4.6	5.1	5.1	5.8
50°	13.7	8.4	5.8	4.6	3.9	3.9	3.3	3.9	3.9	4.6	5.1
52.5°	7.8	5.1	3.9	3.3	3.3	2.6	2.6	3.3	3.3	3.9	4.6
55°	5.1	3.9	3.3	2.6	2.6	2.6	2.6	2.6	3.3	3.3	3.9
57.5°	3.9	3.3	2.6	2.6	2.6	2.0	2.6	2.6	2.6	3.3	3.9
60°	3.3	2.6	2.6	2.6	2.6	2.0	2.0	2.6	2.6	3.3	3.3
62.5°	2.6	2.6	2.6	2.6	2.6	2.0	2.6	2.6	2.6	2.6	3.3
65°	2.0	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	3.3
67.5°	2.0	2.0	2.6	2.6	2.6	2.0	2.6	2.6	2.6	2.6	3.3
70°	2.0	2.0	2.0	2.6	2.6	2.0	2.6	2.6	2.6	2.6	2.6
72.5°	2.0	2.0	2.0	2.6	2.6	2.0	2.6	2.6	2.6	2.6	2.6
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.6	2.6	2.6
77.5°	2.0	2.0	2.0	2.0	2.6	2.0	2.6	2.6	2.6	2.6	2.6
80°	2.0	2.0	2.0	2.0	2.0	2.0	2.6	2.6	2.6	2.6	2.6
82.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.6	2.6	2.6	2.6
85°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.6	2.6	2.6	2.6
87.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
2.5°	132.3	130.4	126.4	125.8	125.1	122.6	120.6	118.7	118.7	116.7	115.4
5°	122.6	119.3	114.8	112.9	112.2	109.0	106.3	104.4	103.8	101.9	99.9
7.5°	112.2	108.3	103.2	101.2	100.5	97.3	94.6	92.8	91.5	89.5	88.2
10°	101.2	96.6	92.1	90.2	89.5	86.2	84.3	82.4	81.1	79.8	78.5
12.5°	89.5	85.6	81.1	79.1	78.5	75.8	74.0	72.7	72.0	70.7	70.1
15°	77.8	74.0	70.1	68.7	68.1	66.1	64.8	64.3	63.6	63.6	62.9
17.5°	66.1	62.9	59.7	59.0	58.4	57.0	56.4	55.7	56.4	56.4	57.0
20°	55.1	52.6	49.9	49.9	49.3	48.6	48.6	48.6	49.9	50.6	51.9
22.5°	45.4	43.5	41.5	41.5	41.5	41.5	41.5	42.8	44.1	45.4	46.0
25°	37.6	35.6	35.0	35.0	35.0	35.6	36.3	37.6	38.9	40.2	41.5
27.5°	30.5	29.2	29.2	29.2	29.8	30.5	31.1	32.5	34.4	35.6	36.9
30°	24.7	24.0	24.0	24.7	25.2	25.9	27.2	28.5	29.8	31.1	32.5
32.5°	19.5	20.1	20.1	20.8	21.4	22.1	23.4	24.7	25.9	27.2	27.9
35°	16.2	16.2	16.8	17.5	18.1	18.8	20.1	21.4	22.1	23.4	24.7
37.5°	13.0	13.7	14.3	14.9	15.5	16.2	16.8	18.1	18.8	20.1	21.4
40°	11.0	11.7	12.3	13.0	13.0	14.3	14.3	15.5	16.2	17.5	18.8
42.5°	9.1	9.7	10.4	11.0	11.0	11.7	12.3	13.0	14.3	14.9	16.2
45°	7.1	7.8	8.4	9.1	9.7	10.4	10.4	11.7	12.3	13.0	14.3
47.5°	6.5	7.1	7.8	7.8	8.4	9.1	9.1	10.4	11.0	11.7	12.3
50°	5.1	5.8	6.5	7.1	7.1	7.8	8.4	9.1	9.7	10.4	10.4
52.5°	4.6	5.1	5.8	5.8	6.5	7.1	7.1	7.8	8.4	8.4	9.1
55°	4.6	5.1	5.1	5.8	5.8	6.5	6.5	7.1	7.1	7.8	7.8
57.5°	3.9	4.6	4.6	5.1	5.1	5.8	5.8	6.5	6.5	6.5	7.1
60°	3.9	3.9	4.6	4.6	5.1	5.1	5.1	5.8	5.8	5.8	6.5
62.5°	3.3	3.9	3.9	4.6	4.6	4.6	5.1	5.1	5.1	5.8	5.8
65°	3.3	3.9	3.9	4.6	4.6	4.6	4.6	4.6	5.1	5.1	5.1
67.5°	3.3	3.3	3.9	3.9	3.9	3.9	4.6	4.6	4.6	4.6	4.6
70°	3.3	3.3	3.3	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9
72.5°	2.6	3.3	3.3	3.3	3.3	3.9	3.9	3.9	3.9	3.9	3.3
75°	2.6	2.6	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3
77.5°	2.6	2.6	2.6	3.3	3.3	3.3	3.3	3.3	3.3	2.6	2.6
80°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.0
82.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.0	2.0	2.0
85°	2.6	2.0	2.6	2.6	2.6	2.0	2.0	2.0	2.0	2.0	1.3
87.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219493

CATALOG NUMBER: LDSQA4A15935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
2.5°	114.1	112.9	113.5	113.5	112.2	111.6	111.6	112.2
5°	98.6	97.3	97.9	97.9	96.6	96.0	96.0	96.6
7.5°	86.9	85.6	86.2	86.2	84.9	84.9	84.9	84.9
10°	77.8	77.2	77.2	77.2	75.8	76.5	75.8	75.2
12.5°	69.4	69.4	69.4	69.4	68.7	69.4	68.7	68.7
15°	62.9	62.9	63.6	63.6	63.6	64.3	64.3	64.3
17.5°	57.7	58.4	59.0	59.7	59.7	60.3	60.3	60.3
20°	52.6	53.9	54.4	55.1	55.1	56.4	55.7	56.4
22.5°	47.3	48.6	49.3	49.9	50.6	51.3	51.3	51.9
25°	42.8	44.1	44.7	45.4	46.0	47.3	47.3	47.3
27.5°	38.3	39.6	40.2	41.5	42.2	43.5	43.5	43.5
30°	33.8	35.0	35.6	36.3	37.6	38.9	38.9	39.6
32.5°	29.2	31.1	31.8	32.5	33.8	35.0	35.6	35.6
35°	25.9	27.2	27.9	29.2	29.8	31.8	31.8	31.8
37.5°	22.7	24.0	25.2	25.9	26.6	27.9	28.5	29.2
40°	20.1	21.4	22.1	22.7	24.0	25.2	25.9	25.9
42.5°	17.5	18.8	19.5	20.1	20.8	22.1	22.1	22.1
45°	15.5	16.2	16.8	17.5	18.1	18.8	19.5	19.5
47.5°	13.0	14.3	14.3	14.9	15.5	16.8	16.8	17.5
50°	11.0	12.3	12.3	13.0	13.7	14.3	14.9	14.9
52.5°	9.7	10.4	11.0	11.0	11.7	12.3	13.0	13.0
55°	8.4	9.1	9.1	9.7	9.7	10.4	11.0	11.0
57.5°	7.1	7.8	8.4	8.4	8.4	9.1	9.1	9.7
60°	6.5	7.1	7.1	7.1	7.1	7.8	7.8	7.8
62.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
65°	5.1	5.1	5.1	5.1	4.6	4.6	4.6	4.6
67.5°	4.6	4.6	4.6	4.6	3.9	3.9	3.9	3.9
70°	3.9	3.9	3.9	3.9	3.3	3.3	3.3	2.6
72.5°	3.3	3.3	3.3	3.3	3.3	2.6	2.6	2.6
75°	3.3	2.6	2.6	2.6	2.6	2.6	2.0	2.0
77.5°	2.6	2.6	2.6	2.0	2.0	2.0	2.0	2.0
80°	2.0	2.0	2.0	2.0	2.0	1.3	1.3	1.3
82.5°	2.0	1.3	1.3	1.3	1.3	1.3	1.3	1.3
85°	1.3	1.3	1.3	1.3	0.7	0.7	0.7	0.7
87.5°	1.3	0.7	0.7	0.7	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)