

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219511

Luminaire Tested: **LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1421.3 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	106	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	71	90	82	76	71		80	74	70			78	73	69			76
5	86	76	69	64	84	75	68	64		73	67	63			71	66	62			70
6	80	70	62	57	79	69	62	57		67	61	57			66	60	56			64
7	75	64	57	52	74	63	56	51		62	56	51			60	55	51			59
8	70	59	52	47	69	58	51	46		57	51	46			56	50	46			55
9	66	54	47	42	64	54	47	42		53	46	42			52	46	42			51
10	62	50	43	38	60	50	43	38		49	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17021	17021	17021
5°	39900	16065	11232
10°	157657	14126	9365
15°	291772	11313	8214
20°	374113	8227	7433
25°	447624	5836	6584
30°	475962	3848	5794
35°	487800	2318	5050
40°	446524	1505	4350
45°	322203	1055	3548
50°	140674	844	2954
55°	9695	709	2500
60°	1763	678	2034
65°	642	642	1444
70°	595	793	991
75°	524	1048	1048
80°	0	1562	1172
85°	0	3112	778

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	1.8
10°-20°	201.2	14.2
20°-30°	421.2	29.6
30°-40°	468.8	33.0
40°-50°	269.1	18.9
50°-60°	26.9	1.9
60°-70°	4.2	0.3
70°-80°	2.7	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	648.0	45.6
0°-40°	1116.8	78.6
0°-60°	1412.8	99.4
0°-90°	1421.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1421.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	176	176	176	176	176	
5°	410	283	165	120	116	75
15°	2909	1162	113	79	82	822
25°	4188	1598	55	48	62	1896
35°	4125	488	20	28	43	2519
45°	2352	59	8	15	26	1796
55°	57	8	4	9	15	171
65°	3	2	3	6	6	4
75°	1	1	3	4	3	1
85°	0	1	3	2	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7
2.5°	262.5	257.0	251.4	247.9	244.3	249.3	245.7	244.3	234.5	229.7	225.4
5°	410.3	399.8	384.4	371.7	359.2	361.9	352.1	340.3	315.8	298.3	282.8
7.5°	791.9	766.0	718.3	672.2	626.0	617.6	586.8	533.5	464.9	413.1	368.3
10°	1602.7	1524.3	1436.8	1342.2	1231.6	1200.8	1124.4	980.2	822.7	642.7	512.5
12.5°	2365.9	2330.2	2227.2	2104.7	1985.0	1911.5	1832.4	1594.3	1344.3	1054.4	812.2
15°	2909.2	2887.5	2797.1	2685.9	2557.0	2509.5	2412.8	2175.4	1859.6	1513.0	1161.6
17.5°	3311.8	3274.7	3180.2	3059.0	2906.4	2865.8	2750.2	2514.3	2186.6	1838.6	1448.7
20°	3628.9	3605.9	3483.3	3337.7	3154.9	3105.9	2970.8	2725.1	2368.7	1999.0	1602.0
22.5°	3914.0	3874.8	3724.2	3550.5	3341.9	3289.4	3138.9	2869.3	2486.3	2074.6	1629.3
25°	4187.7	4128.2	3945.4	3717.9	3472.8	3401.4	3236.2	2950.5	2529.7	2080.9	1598.5
27.5°	4267.5	4237.4	4068.7	3804.0	3520.4	3440.0	3267.7	2968.7	2513.6	2023.5	1487.9
30°	4254.9	4229.7	4089.0	3812.4	3512.0	3427.3	3252.2	2912.7	2419.8	1873.7	1292.5
32.5°	4215.0	4205.2	4035.0	3739.6	3433.6	3341.2	3152.2	2773.4	2244.0	1645.4	944.6
35°	4124.7	4086.2	3874.1	3596.1	3302.0	3200.5	2986.9	2573.8	2012.3	1198.0	488.0
37.5°	3860.0	3829.9	3662.6	3419.0	3132.6	3002.4	2776.9	2316.2	1557.9	681.2	292.0
40°	3530.9	3516.3	3384.6	3166.9	2860.9	2713.9	2468.8	1895.4	950.8	387.2	192.6
42.5°	3193.4	3189.3	3048.5	2821.0	2489.1	2320.4	2066.2	1278.5	505.5	233.8	111.4
45°	2351.8	2377.1	2279.1	2142.6	1889.0	1766.6	1436.8	658.8	291.3	129.5	58.8
47.5°	1649.6	1621.6	1448.0	1209.2	977.4	827.6	626.0	311.6	155.4	67.9	33.6
50°	933.4	938.2	781.4	632.2	414.5	328.4	249.3	156.8	74.9	35.7	20.3
52.5°	243.6	254.8	219.9	189.1	161.1	131.0	105.7	67.9	35.7	21.0	13.3
55°	57.4	59.5	55.3	51.8	49.0	43.4	38.5	29.4	19.6	13.3	8.4
57.5°	20.3	21.0	20.3	20.3	19.6	18.9	17.5	15.4	11.9	8.4	5.6
60°	9.1	9.8	9.1	9.8	9.8	9.8	9.8	9.8	7.0	5.0	3.5
62.5°	4.2	4.2	4.2	4.2	5.0	5.0	5.6	5.6	4.2	3.5	2.8
65°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.1
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
70°	2.1	2.1	2.1	1.4	1.4	1.4	1.4	1.4	1.4	1.4	2.1
72.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
75°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
77.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.4	1.4	1.4	1.4
80°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.4	1.4	1.4
82.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.4	1.4	1.4
85°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.4	1.4	1.4
87.5°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7
2.5°	217.8	217.0	209.4	203.7	201.0	196.7	191.9	184.8	177.1	170.2	167.3
5°	264.6	255.5	239.5	226.1	219.9	213.5	202.4	189.8	177.8	165.2	158.9
7.5°	325.6	299.0	267.5	242.9	232.5	222.0	205.8	188.3	172.3	155.4	146.3
10°	408.9	347.3	292.6	253.4	238.1	224.0	201.0	179.3	161.8	143.6	131.7
12.5°	584.6	432.0	319.3	258.4	238.1	219.9	191.9	166.6	147.0	128.1	116.9
15°	842.3	583.2	377.4	263.2	233.1	210.1	177.8	150.6	129.5	112.8	102.3
17.5°	1050.3	722.6	449.5	275.9	226.8	196.7	159.7	131.0	111.4	95.9	87.5
20°	1155.2	781.4	482.4	278.0	211.5	175.7	137.9	110.6	93.2	79.8	72.9
22.5°	1153.2	762.5	453.0	243.6	185.5	152.0	116.2	91.0	77.0	66.5	60.9
25°	1080.4	675.0	378.1	194.6	149.8	126.0	94.5	73.6	62.3	54.6	49.7
27.5°	943.9	548.3	282.2	144.2	116.9	99.4	73.6	58.8	49.7	44.2	40.6
30°	740.8	366.9	177.8	107.1	88.9	74.9	56.7	45.5	39.2	34.4	32.2
32.5°	408.2	191.2	119.7	78.4	65.1	54.6	42.0	32.9	28.7	25.2	24.6
35°	225.4	135.1	85.4	52.5	43.4	37.1	28.7	23.8	21.0	19.6	19.6
37.5°	159.7	86.8	51.1	32.9	28.0	24.6	19.6	16.8	16.1	15.4	15.4
40°	95.9	51.1	30.8	21.7	18.9	16.8	14.8	12.6	12.6	11.9	12.6
42.5°	52.5	30.8	21.0	15.4	13.3	12.6	10.5	9.8	9.8	9.8	10.5
45°	31.5	20.3	14.8	11.2	9.8	8.4	7.7	7.0	7.7	7.7	8.4
47.5°	20.3	14.8	9.8	7.0	6.3	5.6	5.0	5.6	5.6	6.3	7.0
50°	14.0	9.1	6.3	4.2	4.2	3.5	4.2	4.2	5.0	5.6	6.3
52.5°	9.1	6.3	4.2	3.5	2.8	2.8	2.8	3.5	4.2	5.0	5.6
55°	5.6	4.2	3.5	2.8	2.8	2.8	2.8	2.8	3.5	4.2	5.0
57.5°	4.2	3.5	2.8	2.1	2.1	2.1	2.8	2.8	3.5	3.5	4.2
60°	2.8	2.8	2.1	2.1	2.1	2.1	2.1	2.8	2.8	3.5	4.2
62.5°	2.8	2.8	2.1	2.1	2.1	2.1	2.8	2.8	2.8	3.5	3.5
65°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	3.5
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	3.5
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	3.5
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	2.8
77.5°	1.4	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	2.8
80°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	2.8
82.5°	1.4	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	2.8
85°	1.4	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8	2.8
87.5°	1.4	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7
2.5°	163.8	158.9	154.7	156.1	153.4	148.4	147.0	143.6	139.3	138.6	138.6
5°	152.0	144.2	137.9	137.2	134.4	128.8	127.4	123.9	120.4	119.7	119.0
7.5°	137.2	128.8	123.3	121.9	119.7	114.8	114.1	110.6	108.5	107.1	107.1
10°	122.6	114.8	109.9	109.2	107.8	103.7	103.0	100.1	98.0	97.3	96.6
12.5°	108.5	102.3	98.0	97.3	95.9	92.5	91.7	89.6	88.2	87.5	87.5
15°	95.2	89.6	86.1	85.4	84.7	81.2	81.2	79.8	79.1	79.1	79.8
17.5°	81.9	77.0	74.2	73.6	73.6	70.7	71.4	70.7	70.7	70.7	72.1
20°	68.6	64.4	62.3	63.1	61.6	60.9	61.6	61.6	61.6	63.1	65.1
22.5°	57.4	54.0	51.8	52.5	52.5	51.8	52.5	53.3	54.6	56.7	58.8
25°	46.9	44.2	43.4	44.2	44.2	44.2	45.5	46.9	48.3	50.4	52.5
27.5°	37.8	35.7	35.7	36.4	37.1	37.1	39.2	40.6	42.7	44.8	46.9
30°	30.1	29.4	29.4	30.8	30.8	31.5	34.4	35.7	37.1	39.2	41.3
32.5°	23.8	23.8	24.6	25.9	25.9	27.3	29.4	30.8	32.2	34.4	36.4
35°	19.6	20.3	21.0	21.7	22.4	23.1	25.2	26.6	28.0	30.1	31.5
37.5°	16.1	16.8	17.5	18.9	18.9	19.6	21.7	23.1	23.8	25.9	28.0
40°	13.3	14.0	14.8	16.1	16.1	16.8	18.9	19.6	20.3	22.4	24.6
42.5°	11.2	11.9	12.6	13.3	14.0	14.8	16.1	16.8	18.2	19.6	21.0
45°	9.1	9.8	10.5	11.2	11.9	12.6	13.3	14.8	15.4	16.8	18.2
47.5°	7.7	8.4	9.1	9.8	10.5	10.5	11.9	12.6	13.3	14.8	16.1
50°	7.0	7.7	8.4	8.4	9.1	9.8	10.5	11.2	11.9	12.6	14.0
52.5°	5.6	6.3	7.0	7.7	7.7	8.4	9.1	9.8	10.5	11.2	11.9
55°	5.6	5.6	6.3	7.0	7.0	7.7	8.4	9.1	9.1	9.8	10.5
57.5°	5.0	5.6	5.6	6.3	6.3	7.0	7.7	7.7	8.4	8.4	9.1
60°	4.2	5.0	5.6	5.6	5.6	6.3	6.3	7.0	7.0	7.7	7.7
62.5°	4.2	5.0	5.0	5.6	5.6	5.6	6.3	6.3	6.3	7.0	7.0
65°	4.2	4.2	5.0	5.0	5.0	5.0	5.6	5.6	5.6	6.3	6.3
67.5°	3.5	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.6	5.6
70°	3.5	3.5	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.0	5.0
72.5°	3.5	3.5	3.5	3.5	4.2	4.2	4.2	4.2	4.2	4.2	4.2
75°	2.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
77.5°	2.8	2.8	2.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
80°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.1	2.1
85°	2.8	2.8	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
87.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219511

CATALOG NUMBER: LDSQA4A15940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	175.7	175.7	175.7	175.7	175.7	175.7	175.7	175.7
2.5°	135.8	134.4	133.7	135.8	133.1	134.4	133.7	134.4
5°	116.9	115.5	114.8	116.9	114.1	115.5	114.1	115.5
7.5°	105.0	104.3	103.7	105.0	103.0	104.3	103.7	104.3
10°	95.2	94.5	93.9	95.9	93.9	95.2	94.5	95.2
12.5°	86.8	86.8	86.1	87.5	86.1	87.5	86.8	87.5
15°	79.1	79.8	79.1	80.5	79.8	81.2	80.5	81.9
17.5°	72.9	73.6	73.6	75.6	74.9	77.0	76.3	77.0
20°	66.5	67.2	67.9	69.3	69.3	71.4	70.7	72.1
22.5°	60.2	61.6	61.6	63.8	63.8	65.8	65.8	66.5
25°	54.0	56.0	56.7	58.1	58.8	60.9	60.9	61.6
27.5°	49.0	50.4	51.1	53.3	54.0	56.0	56.0	57.4
30°	43.4	45.5	46.2	47.6	48.3	50.4	50.4	51.8
32.5°	38.5	39.9	41.3	42.7	43.4	45.5	45.5	46.9
35°	33.6	35.7	36.4	37.8	39.2	41.3	41.3	42.7
37.5°	29.4	31.5	32.2	33.6	35.0	37.1	37.1	38.5
40°	25.9	28.0	28.7	30.1	30.8	33.6	33.6	34.4
42.5°	23.1	24.6	25.2	26.6	27.3	28.7	28.7	30.1
45°	19.6	21.0	21.7	22.4	23.8	25.2	25.2	25.9
47.5°	16.8	18.2	18.9	19.6	20.3	21.7	21.7	23.1
50°	14.8	15.4	16.1	16.8	17.5	18.9	18.9	19.6
52.5°	12.6	13.3	14.0	14.8	15.4	16.1	16.8	17.5
55°	11.2	11.9	11.9	12.6	13.3	14.0	14.0	14.8
57.5°	9.8	10.5	10.5	10.5	11.2	11.9	11.9	12.6
60°	8.4	9.1	9.1	9.1	9.8	9.8	9.8	10.5
62.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
65°	6.3	6.3	6.3	6.3	6.3	6.3	5.6	6.3
67.5°	5.6	5.6	5.6	5.0	5.0	5.0	5.0	5.0
70°	5.0	5.0	5.0	4.2	4.2	4.2	3.5	3.5
72.5°	4.2	4.2	4.2	3.5	3.5	3.5	2.8	2.8
75°	3.5	3.5	3.5	3.5	2.8	2.8	2.8	2.8
77.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.1	2.1
80°	2.8	2.1	2.1	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	1.4	1.4	1.4	1.4
85°	1.4	1.4	1.4	1.4	1.4	1.4	0.7	0.7
87.5°	1.4	0.7	0.7	0.7	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)