

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219513

Luminaire Tested: **LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1322.4 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	83	79		85	81	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	86	76	69	64	85	75	69	64	73	68	63		72	67	63		70
6	81	70	63	58	79	69	62	57	67	61	57		66	61	57		64
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	13824	13824	13824
5°	26490	13177	10687
10°	86605	11677	9099
15°	212099	9648	8033
20°	399639	7351	7206
25°	668972	5216	6307
30°	847456	3580	5369
35°	772187	2330	4565
40°	508541	1657	3870
45°	220286	1096	3192
50°	39079	784	2637
55°	6266	608	2213
60°	1550	562	1686
65°	504	665	1330
70°	425	821	1020
75°	561	823	823
80°	0	1227	837
85°	0	2445	778



TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.3	1.4
10°-20°	147.1	11.1
20°-30°	443.1	33.5
30°-40°	504.3	38.1
40°-50°	186.5	14.1
50°-60°	14.8	1.1
60°-70°	4.0	0.3
70°-80°	2.8	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.5	46.0
0°-40°	1112.7	84.1
0°-60°	1314.0	99.4
0°-90°	1322.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1322.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	143	143	143	143	143	
5°	272	200	136	114	110	44
15°	2115	714	96	76	80	663
25°	6258	1044	49	47	59	2857
35°	6529	366	20	27	39	3882
45°	1608	43	8	15	23	1361
55°	37	8	4	9	13	61
65°	2	2	3	6	6	3
75°	2	2	2	4	2	1
85°	0	2	2	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7
2.5°	183.5	185.0	183.5	180.5	180.5	177.0	175.6	174.0	170.4	168.3	165.4
5°	272.4	268.0	264.4	255.6	252.6	244.7	238.9	230.9	220.0	210.5	200.3
7.5°	466.1	459.5	445.7	419.4	403.4	383.8	368.5	343.0	310.2	283.2	256.4
10°	880.4	852.0	819.2	760.2	717.3	671.4	635.0	566.6	484.3	416.6	351.0
12.5°	1418.6	1420.8	1359.6	1259.9	1180.4	1099.6	1037.0	910.3	764.7	637.2	511.2
15°	2114.8	2074.7	2011.5	1858.5	1699.7	1582.5	1482.7	1290.4	1084.4	897.9	714.5
17.5°	2848.1	2864.9	2717.1	2467.2	2216.0	2040.6	1889.8	1598.5	1353.9	1123.0	898.7
20°	3876.5	3761.4	3550.1	3145.3	2754.9	2500.8	2277.2	1899.4	1557.7	1264.2	1012.3
22.5°	5062.0	4876.2	4446.6	3876.5	3285.9	2934.0	2622.4	2102.5	1687.3	1336.3	1050.8
25°	6258.5	6116.6	5431.9	4579.8	3733.7	3277.9	2874.4	2240.1	1749.2	1353.1	1044.4
27.5°	7181.8	6950.3	6170.4	5059.9	4000.9	3462.8	2991.6	2282.3	1736.1	1312.4	982.5
30°	7575.9	7283.2	6418.8	5169.1	4003.2	3432.2	2933.3	2198.6	1642.9	1208.9	865.9
32.5°	7332.7	6994.8	6123.0	4866.8	3729.3	3193.3	2708.4	2017.2	1488.4	1046.4	650.3
35°	6529.4	6193.0	5385.3	4270.3	3292.3	2824.1	2402.5	1780.6	1267.9	775.6	365.6
37.5°	5346.7	5059.9	4482.4	3579.3	2774.6	2394.4	2043.5	1500.1	944.5	445.0	183.5
40°	4021.3	3819.6	3473.0	2838.7	2245.9	1956.8	1674.2	1149.1	573.9	223.5	104.1
42.5°	2787.7	2656.6	2482.6	2100.3	1732.5	1533.7	1307.2	767.5	294.9	123.0	64.9
45°	1607.9	1525.7	1477.5	1314.5	1170.9	1074.2	873.9	413.6	149.3	73.5	43.0
47.5°	710.0	655.4	632.1	563.7	524.4	498.2	395.5	176.3	80.1	47.3	35.8
50°	259.3	259.3	260.0	228.7	187.2	168.3	131.8	77.9	45.2	37.1	26.2
52.5°	91.7	90.3	93.9	88.8	77.9	69.9	58.2	39.3	27.7	23.3	14.6
55°	37.1	35.8	37.1	35.0	32.8	30.6	26.9	21.1	17.5	14.6	8.0
57.5°	16.7	16.7	17.5	16.7	16.7	15.4	13.8	16.0	12.4	8.0	5.2
60°	8.0	8.0	8.7	8.7	8.7	8.0	8.0	8.7	7.3	5.2	3.6
62.5°	3.6	3.6	4.4	4.4	4.4	4.4	4.4	5.2	3.6	2.9	2.2
65°	2.2	1.5	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
67.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.2	2.2
70°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.2
72.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.2
75°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	2.2
77.5°	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.5	1.5	2.2
80°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.5	1.5	1.5
82.5°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	1.5	1.5	1.5
85°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.7	0.7	0.7	0.7	0.7	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7
2.5°	162.3	160.2	155.9	153.6	150.7	148.6	147.2	144.1	141.2	139.0	137.7
5°	190.7	182.7	173.3	166.1	160.2	156.6	150.7	145.7	139.8	135.5	131.8
7.5°	232.2	212.6	191.5	177.0	169.0	161.6	151.4	142.7	134.8	128.9	123.8
10°	297.1	254.9	217.8	189.4	175.6	165.4	149.3	137.0	126.8	118.7	113.6
12.5°	405.0	318.2	252.6	204.7	183.5	168.3	145.7	128.9	116.6	108.5	101.9
15°	552.7	411.4	300.8	222.8	192.9	171.1	139.8	119.4	105.7	96.2	90.3
17.5°	691.8	509.1	355.4	244.7	202.4	172.5	131.8	107.1	92.5	83.7	77.9
20°	779.2	572.3	391.8	257.1	205.4	168.3	120.8	93.9	79.4	71.3	65.6
22.5°	799.6	579.7	388.9	245.4	192.9	155.2	105.7	80.8	67.0	59.7	54.6
25°	769.7	538.9	348.1	211.8	164.6	130.3	88.1	65.6	55.4	48.8	45.2
27.5°	694.8	458.7	275.3	159.5	123.0	96.2	67.0	51.0	44.4	39.3	37.1
30°	560.0	322.6	172.5	99.0	78.6	63.3	48.0	39.3	34.2	32.0	29.8
32.5°	339.4	166.1	91.0	59.0	49.5	43.0	35.0	29.1	26.2	24.8	24.0
35°	161.6	87.5	56.2	40.0	35.0	30.6	25.6	21.8	20.4	19.7	19.7
37.5°	91.7	56.8	37.9	26.9	24.0	21.1	18.9	16.7	16.0	16.0	16.0
40°	58.2	36.4	24.8	19.7	17.5	16.0	14.6	13.1	13.1	13.1	13.1
42.5°	37.9	26.2	18.9	14.6	13.1	12.4	10.9	10.2	10.2	10.2	10.9
45°	29.8	21.8	15.4	11.6	10.2	9.5	8.7	8.0	8.0	8.0	8.7
47.5°	25.6	15.4	10.2	8.0	6.6	6.6	5.8	5.8	5.8	6.6	7.3
50°	15.4	9.5	6.6	5.2	4.4	4.4	4.4	4.4	4.4	5.2	5.8
52.5°	8.7	5.8	4.4	3.6	2.9	2.9	2.9	2.9	3.6	4.4	4.4
55°	5.8	4.4	2.9	2.9	2.2	2.2	2.2	2.9	2.9	3.6	4.4
57.5°	3.6	2.9	2.2	2.2	2.2	2.2	2.2	2.2	2.9	3.6	3.6
60°	2.9	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.9	2.9	3.6
62.5°	2.2	2.2	2.9	2.2	2.2	2.2	2.2	2.2	2.9	2.9	3.6
65°	2.2	2.2	2.9	2.9	2.2	2.2	2.2	2.2	2.2	2.9	3.6
67.5°	2.2	2.2	2.9	2.9	2.9	2.9	2.2	2.2	2.2	2.9	2.9
70°	2.2	2.9	2.9	2.9	2.9	2.9	2.9	2.2	2.2	2.9	2.9
72.5°	2.2	2.9	2.9	2.9	2.9	2.9	2.9	2.2	2.2	2.9	2.9
75°	2.2	2.2	2.9	2.9	2.9	2.9	2.9	2.2	2.2	2.2	2.9
77.5°	2.2	2.2	2.9	2.9	2.9	2.9	2.9	2.2	2.2	2.2	2.9
80°	2.2	2.2	2.2	2.9	2.2	2.9	2.2	2.2	2.2	2.2	2.2
82.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
85°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
87.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7
2.5°	135.5	134.0	131.8	131.0	131.8	131.0	127.5	126.8	125.3	125.3	125.3
5°	128.2	126.0	123.0	121.6	121.6	120.1	116.6	115.9	113.6	113.6	112.8
7.5°	119.4	116.6	112.8	111.4	111.4	109.9	106.4	104.9	103.4	103.4	102.6
10°	109.2	105.7	101.9	101.2	100.5	98.3	96.2	95.5	93.2	93.9	93.2
12.5°	97.7	94.6	91.7	90.3	90.3	88.1	86.7	86.0	85.3	85.3	85.3
15°	86.7	83.0	80.1	79.4	79.4	78.6	77.2	77.2	75.8	77.2	77.2
17.5°	74.3	71.3	70.6	69.2	69.9	69.2	67.7	68.4	68.4	69.2	69.9
20°	62.6	60.4	59.7	59.0	59.7	59.7	59.0	59.7	60.4	62.6	64.1
22.5°	52.4	51.0	51.0	50.2	51.0	51.7	51.0	52.4	53.9	55.4	57.5
25°	43.7	43.0	43.0	43.0	43.7	44.4	45.2	46.6	47.3	49.5	51.0
27.5°	35.8	35.8	35.8	36.4	37.1	37.9	38.6	40.8	41.5	43.7	45.2
30°	29.8	29.1	29.8	30.6	31.3	32.8	33.5	35.0	35.8	37.9	39.3
32.5°	24.0	24.8	25.6	26.2	26.9	27.7	28.4	29.8	31.3	32.8	34.2
35°	20.4	20.4	21.1	21.8	22.6	24.0	24.8	25.6	26.9	28.4	29.1
37.5°	16.7	17.5	18.2	18.9	19.7	20.4	21.1	21.8	22.6	24.0	25.6
40°	13.8	14.6	15.4	16.0	16.0	17.5	17.5	18.9	19.7	21.1	22.6
42.5°	11.6	12.4	13.1	13.8	13.8	14.6	15.4	16.0	16.7	18.2	19.7
45°	9.5	10.2	10.9	11.6	11.6	12.4	13.1	13.8	14.6	16.0	16.7
47.5°	8.0	8.7	9.5	10.2	10.2	10.9	11.6	12.4	12.4	13.8	14.6
50°	6.6	7.3	8.0	8.7	8.7	9.5	10.2	10.9	10.9	11.6	12.4
52.5°	5.2	5.8	7.3	7.3	8.0	8.7	8.7	9.5	9.5	10.2	10.9
55°	5.2	5.8	6.6	6.6	7.3	8.0	8.0	8.7	8.7	8.7	9.5
57.5°	4.4	5.2	5.8	6.6	6.6	7.3	7.3	7.3	7.3	8.0	8.0
60°	4.4	5.2	5.2	5.8	5.8	6.6	6.6	6.6	6.6	7.3	7.3
62.5°	4.4	4.4	5.2	5.2	5.8	5.8	5.8	6.6	6.6	6.6	6.6
65°	3.6	4.4	5.2	5.2	5.2	5.8	5.8	5.8	5.8	5.8	5.8
67.5°	3.6	4.4	4.4	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
70°	3.6	3.6	4.4	4.4	4.4	5.2	5.2	5.2	4.4	5.2	4.4
72.5°	2.9	3.6	3.6	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
75°	2.9	3.6	3.6	3.6	3.6	4.4	4.4	3.6	3.6	3.6	3.6
77.5°	2.9	2.9	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.9
80°	2.9	2.9	2.9	2.9	3.6	3.6	2.9	2.9	2.9	2.9	2.9
82.5°	2.2	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.2	2.2	2.2
85°	2.2	2.2	2.9	2.9	2.9	2.9	2.2	2.2	2.2	2.2	1.5
87.5°	2.2	2.2	2.2	2.9	2.2	2.2	2.2	2.2	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219513

CATALOG NUMBER: LDSQA4A15950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	142.7	142.7	142.7	142.7	142.7	142.7	142.7	142.7
2.5°	123.0	122.3	123.0	122.3	122.3	123.0	120.8	122.3
5°	111.4	109.9	110.7	109.9	109.2	109.9	108.5	109.9
7.5°	101.2	100.5	100.5	100.5	99.7	100.5	99.0	100.5
10°	92.5	91.7	91.7	91.7	91.7	92.5	91.0	92.5
12.5°	83.7	83.7	84.4	83.7	84.4	85.3	83.7	85.3
15°	76.5	77.2	77.9	77.9	78.6	79.4	78.6	80.1
17.5°	70.6	71.3	72.8	72.8	73.5	75.1	74.3	75.8
20°	64.9	65.6	67.0	67.0	67.7	69.2	68.4	69.9
22.5°	58.2	59.7	60.4	61.2	61.9	63.3	62.6	64.1
25°	51.7	53.9	54.6	55.4	56.2	57.5	57.5	59.0
27.5°	46.6	48.0	48.8	49.5	51.0	52.4	52.4	53.1
30°	40.8	42.2	43.7	44.4	45.2	46.6	46.6	48.0
32.5°	35.8	37.1	37.9	38.6	40.0	41.5	42.2	43.0
35°	30.6	32.8	33.5	35.0	35.8	37.9	37.9	38.6
37.5°	26.9	28.4	29.8	30.6	32.0	33.5	33.5	35.0
40°	24.0	25.6	26.2	26.9	28.4	29.8	29.8	30.6
42.5°	20.4	22.6	23.3	24.0	24.8	26.2	26.9	27.7
45°	18.2	18.9	19.7	20.4	21.1	22.6	22.6	23.3
47.5°	15.4	16.0	16.7	17.5	18.2	18.9	19.7	20.4
50°	13.1	13.8	14.6	14.6	15.4	16.7	16.7	17.5
52.5°	10.9	11.6	12.4	12.4	13.1	14.6	14.6	15.4
55°	9.5	10.2	10.9	10.9	11.6	12.4	12.4	13.1
57.5°	8.7	8.7	9.5	9.5	10.2	10.2	10.9	10.9
60°	7.3	8.0	8.0	8.0	8.7	8.7	8.7	8.7
62.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.3
65°	5.8	5.8	5.8	5.8	5.8	5.8	5.2	5.8
67.5°	5.2	5.2	5.2	5.2	4.4	4.4	4.4	4.4
70°	4.4	4.4	4.4	4.4	4.4	3.6	3.6	3.6
72.5°	3.6	3.6	3.6	3.6	3.6	2.9	2.9	2.9
75°	3.6	3.6	2.9	2.9	2.9	2.9	2.9	2.2
77.5°	2.9	2.9	2.9	2.9	2.2	2.2	2.2	2.2
80°	2.2	2.2	2.2	2.2	2.2	2.2	1.5	1.5
82.5°	2.2	1.5	1.5	1.5	1.5	1.5	1.5	1.5
85°	1.5	1.5	1.5	1.5	0.7	0.7	0.7	0.7
87.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)