

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212194

Luminaire Tested: **LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1803.1 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	18242	18242	18242
5°	40376	17251	12127
10°	161612	14992	10132
15°	372528	11925	8896
20°	556103	8464	7938
25°	729387	5633	7076
30°	837266	3557	6175
35°	767693	2271	5357
40°	629553	1492	4553
45°	364975	1028	3672
50°	103433	754	3029
55°	9475	709	2533
60°	1453	814	2112
65°	390	779	1513
70°	482	963	1190
75°	636	1273	1273
80°	0	1897	948
85°	0	3779	889



TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.7	1.5
10°-20°	239.8	13.3
20°-30°	584.2	32.4
30°-40°	633.2	35.1
40°-50°	286.9	15.9
50°-60°	22.2	1.2
60°-70°	4.6	0.3
70°-80°	3.4	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.8	47.2
0°-40°	1483.9	82.3
0°-60°	1793.0	99.4
0°-90°	1803.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1803.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	188	188	188	188	188	
5°	415	306	177	134	125	75
15°	3714	1215	119	86	89	1079
25°	6824	1745	53	52	66	3110
35°	6491	444	19	30	45	3993
45°	2664	56	8	17	27	2103
55°	56	8	4	10	15	128
65°	2	2	3	7	7	3
75°	2	2	3	5	3	1
85°	0	2	3	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3
2.5°	282.1	277.0	279.5	272.9	268.6	265.3	267.0	265.3	254.4	251.9	243.6
5°	415.2	407.6	407.6	393.4	378.3	369.1	369.1	358.2	334.8	323.8	306.2
7.5°	744.0	729.0	716.5	672.1	614.3	581.7	573.4	527.3	467.9	430.2	385.8
10°	1642.9	1580.2	1535.8	1420.3	1265.4	1169.2	1128.2	969.2	780.0	637.8	508.9
12.5°	2762.7	2677.4	2599.6	2410.4	2187.8	2036.3	1955.1	1720.8	1353.4	1090.6	816.0
15°	3714.4	3622.3	3530.2	3300.2	3064.9	2933.5	2784.5	2474.1	1988.6	1615.4	1215.2
17.5°	4495.3	4443.4	4348.8	4011.5	3715.2	3510.2	3355.4	2949.4	2449.8	2023.8	1570.9
20°	5394.2	5266.1	5097.0	4687.7	4282.6	4025.8	3808.1	3313.4	2736.0	2246.4	1759.3
22.5°	6150.8	6059.4	5816.8	5277.0	4681.0	4461.8	4195.7	3600.6	2920.1	2341.0	1781.0
25°	6823.7	6680.6	6375.8	5733.9	5123.8	4750.5	4424.1	3756.2	2987.9	2347.6	1745.0
27.5°	7217.8	7031.2	6673.0	5973.4	5277.0	4864.4	4502.8	3783.0	2945.2	2258.9	1613.7
30°	7484.8	7113.2	6717.4	5975.8	5228.4	4806.6	4431.7	3648.2	2767.8	2056.4	1392.6
32.5°	7044.6	6829.4	6451.2	5738.1	4963.9	4552.2	4179.8	3356.2	2490.8	1755.9	969.2
35°	6491.4	6317.3	5988.3	5280.3	4567.3	4179.0	3783.8	2981.1	2130.0	1206.9	443.5
37.5°	5848.6	5712.2	5358.2	4711.2	4083.4	3703.5	3307.6	2541.0	1499.8	598.4	269.4
40°	4978.2	4862.6	4572.2	4052.5	3474.2	3112.6	2747.7	1900.7	814.3	333.9	175.8
42.5°	4091.8	3994.7	3730.2	3280.9	2772.9	2474.9	2153.4	1158.3	405.1	210.1	98.0
45°	2664.0	2542.7	2400.3	2194.5	1943.4	1760.1	1381.0	559.1	240.2	117.2	56.1
47.5°	1527.4	1447.0	1213.6	957.4	777.5	709.7	516.3	260.3	132.3	67.8	34.3
50°	686.3	634.4	532.2	433.6	313.8	245.2	208.4	130.6	65.3	36.8	23.4
52.5°	169.1	172.4	163.2	143.1	127.2	107.9	93.7	61.0	34.3	22.6	15.0
55°	56.1	56.9	51.9	49.4	45.3	41.8	38.5	27.7	20.9	20.1	7.5
57.5°	20.1	20.1	20.9	19.2	18.4	17.6	16.7	14.2	12.6	7.5	4.2
60°	7.5	7.5	7.5	8.3	8.3	8.3	9.3	8.3	5.8	4.2	3.4
62.5°	3.4	3.4	3.4	3.4	4.2	4.2	5.0	4.2	3.4	3.4	2.5
65°	1.7	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
67.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5	2.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5	2.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5
80°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	2.5
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3
2.5°	235.1	230.2	220.2	212.6	206.7	205.9	200.8	192.5	189.2	183.3	178.2
5°	289.5	277.0	261.1	246.1	235.1	229.4	211.8	195.8	186.7	177.4	169.1
7.5°	348.2	319.7	292.2	267.8	252.7	243.6	222.6	196.6	179.9	166.5	155.7
10°	421.8	363.3	315.5	277.9	257.8	245.2	220.2	189.2	168.2	152.4	141.4
12.5°	590.1	430.2	337.3	282.9	257.8	240.2	210.1	179.1	155.7	136.5	124.7
15°	878.0	600.9	400.1	285.4	249.4	229.4	195.0	162.3	139.0	118.9	107.9
17.5°	1149.1	790.9	499.6	303.0	244.4	213.4	175.0	143.1	118.9	99.6	90.4
20°	1289.7	885.4	555.0	316.4	236.0	193.4	151.5	122.2	98.8	82.1	74.5
22.5°	1293.1	877.1	528.1	285.4	205.1	165.7	129.7	100.5	80.4	66.2	60.2
25°	1213.6	775.8	434.4	222.6	165.7	139.0	107.9	82.1	62.8	52.7	48.6
27.5°	1063.7	627.8	320.6	160.6	129.7	110.5	84.6	62.8	47.8	41.0	38.5
30°	822.7	388.3	177.4	118.9	98.0	82.9	61.0	41.8	36.0	31.8	30.2
32.5°	408.4	190.0	125.5	84.6	67.0	52.7	38.5	31.0	27.7	25.0	24.2
35°	221.8	136.5	78.6	51.0	40.2	33.5	25.9	21.8	20.1	19.2	19.2
37.5°	154.9	81.2	47.8	31.0	25.0	22.6	18.4	15.9	15.0	15.0	15.0
40°	85.4	48.6	29.4	20.1	16.7	15.0	12.6	11.8	11.8	11.8	12.6
42.5°	49.4	30.2	20.1	14.2	11.8	10.9	9.3	8.3	9.3	9.3	10.1
45°	31.8	22.6	13.4	10.1	8.3	7.5	6.6	6.6	7.5	7.5	8.3
47.5°	22.6	15.9	9.3	6.6	5.0	5.0	5.0	5.0	5.8	6.6	7.5
50°	13.4	8.3	5.0	4.2	3.4	3.4	3.4	4.2	5.0	5.0	5.8
52.5°	7.5	5.0	3.4	3.4	2.5	2.5	3.4	3.4	4.2	5.0	5.8
55°	4.2	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.0
57.5°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
60°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
62.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	4.2
65°	2.5	2.5	2.5	3.4	2.5	3.4	3.4	3.4	3.4	3.4	4.2
67.5°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.2
70°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.2
72.5°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.2
75°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
77.5°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
80°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
85°	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3
2.5°	176.6	170.8	166.5	164.8	161.5	162.3	159.8	158.2	153.2	153.2	149.8
5°	163.2	155.7	150.7	148.1	144.8	143.9	141.4	139.0	133.9	133.1	130.6
7.5°	149.0	141.4	135.6	133.1	129.7	128.9	125.5	123.8	119.7	118.9	116.4
10°	133.9	125.5	120.6	118.1	114.7	114.7	112.1	110.5	107.1	107.1	105.4
12.5°	118.1	110.5	107.1	103.8	102.2	102.2	100.5	98.8	96.2	97.1	96.2
15°	101.3	95.4	92.0	90.4	89.5	89.5	88.7	87.8	86.2	87.8	86.2
17.5°	85.4	81.2	78.6	77.8	77.0	77.0	77.0	77.8	77.0	78.6	78.6
20°	70.3	67.0	65.3	65.3	64.5	66.2	66.2	67.8	67.8	70.3	71.1
22.5°	57.8	55.2	54.4	54.4	54.4	56.1	56.9	58.6	59.4	62.0	63.7
25°	46.1	45.3	45.3	45.3	46.1	47.8	49.4	51.0	51.9	55.2	56.1
27.5°	37.7	36.8	37.7	37.7	38.5	41.0	42.6	44.4	46.1	48.6	50.2
30°	30.2	30.2	31.0	31.8	32.6	34.3	36.8	38.5	40.2	42.6	44.4
32.5°	24.2	25.0	25.9	26.8	26.8	29.4	31.0	33.5	34.3	36.8	38.5
35°	20.1	20.9	21.8	22.6	22.6	25.0	26.8	28.5	30.2	31.8	33.5
37.5°	15.9	16.7	18.4	19.2	19.2	21.8	22.6	24.2	25.9	27.7	29.4
40°	13.4	14.2	15.9	15.9	16.7	18.4	19.2	20.9	22.6	24.2	25.9
42.5°	10.9	11.8	13.4	14.2	14.2	15.9	16.7	18.4	19.2	20.9	21.8
45°	10.1	10.1	11.8	11.8	12.6	13.4	15.0	15.9	16.7	18.4	19.2
47.5°	8.3	9.3	10.1	10.9	10.9	11.8	12.6	13.4	14.2	15.9	16.7
50°	6.6	7.5	9.3	9.3	9.3	10.9	11.8	12.6	12.6	13.4	14.2
52.5°	6.6	6.6	7.5	8.3	8.3	9.3	10.1	10.9	10.9	11.8	12.6
55°	5.8	5.8	6.6	7.5	7.5	8.3	9.3	9.3	10.1	10.1	10.9
57.5°	5.0	5.8	6.6	6.6	6.6	7.5	8.3	8.3	9.3	9.3	10.1
60°	5.0	5.8	5.8	6.6	6.6	7.5	7.5	7.5	8.3	8.3	8.3
62.5°	5.0	5.0	5.8	5.8	5.8	6.6	6.6	7.5	7.5	7.5	7.5
65°	5.0	5.0	5.8	5.8	5.8	6.6	6.6	6.6	6.6	6.6	6.6
67.5°	4.2	5.0	5.0	5.0	5.8	5.8	5.8	5.8	5.8	5.8	5.8
70°	4.2	4.2	5.0	5.0	5.0	5.8	5.8	5.8	5.8	5.8	5.8
72.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
75°	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.0	5.0	4.2	4.2
77.5°	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.4
80°	3.4	3.4	4.2	3.4	4.2	4.2	4.2	4.2	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	1.7
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212194

CATALOG NUMBER: LDSQA4A20930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	188.3	188.3	188.3	188.3	188.3	188.3	188.3	188.3
2.5°	148.1	149.8	148.1	149.8	145.6	147.3	149.0	144.8
5°	128.9	127.2	128.0	129.7	126.4	127.2	128.0	124.7
7.5°	115.5	116.4	114.7	116.4	113.8	114.7	115.5	113.0
10°	104.6	105.4	104.6	105.4	103.0	104.6	105.4	103.0
12.5°	94.6	96.2	95.4	97.1	94.6	96.2	98.0	94.6
15°	87.0	88.7	87.8	89.5	87.8	89.5	91.2	88.7
17.5°	79.5	81.2	81.2	82.9	82.1	83.7	85.4	82.9
20°	72.0	74.5	74.5	76.2	76.2	77.0	79.5	77.0
22.5°	65.3	67.8	67.8	69.4	69.4	71.1	72.8	71.1
25°	57.8	61.0	62.0	63.7	63.7	65.3	67.8	66.2
27.5°	52.7	55.2	56.1	57.8	58.6	60.2	62.0	60.2
30°	46.1	49.4	50.2	51.9	52.7	55.2	56.1	55.2
32.5°	41.0	43.4	44.4	46.1	47.8	49.4	51.0	50.2
35°	36.0	38.5	39.3	41.0	41.8	44.4	46.1	45.3
37.5°	31.8	34.3	35.1	36.0	36.8	39.3	41.0	40.2
40°	27.7	29.4	30.2	31.8	32.6	34.3	36.0	36.0
42.5°	24.2	25.9	26.8	27.7	28.5	30.2	31.8	31.0
45°	20.9	22.6	23.4	24.2	25.0	25.9	27.7	26.8
47.5°	17.6	19.2	20.1	20.9	21.8	22.6	24.2	23.4
50°	15.0	16.7	16.7	17.6	18.4	19.2	20.9	20.1
52.5°	13.4	14.2	15.0	15.0	15.9	16.7	18.4	17.6
55°	11.8	12.6	12.6	13.4	13.4	14.2	15.0	15.0
57.5°	10.1	10.9	10.9	11.8	11.8	12.6	13.4	13.4
60°	9.3	9.3	10.1	10.1	10.1	10.9	10.9	10.9
62.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3
65°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
67.5°	5.8	5.8	5.8	5.8	5.8	5.0	5.0	5.0
70°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	4.2
72.5°	5.0	5.0	4.2	4.2	4.2	4.2	4.2	3.4
75°	4.2	4.2	4.2	4.2	3.4	3.4	3.4	3.4
77.5°	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
80°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	1.7
82.5°	2.5	2.5	2.5	1.7	1.7	1.7	1.7	1.7
85°	1.7	1.7	1.7	1.7	0.8	0.8	0.8	0.8
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)