

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212202

Luminaire Tested: **LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1541.1 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	84
3	99	91	85	81	97	90	84	80		87	83	79		85	81	77		82	79	76
4	92	83	77	72	90	82	76	71		80	75	70		78	73	70		76	72	69
5	86	76	69	64	85	75	69	64		73	68	63		72	67	63		70	66	62
6	81	70	63	58	79	69	62	57		67	61	57		66	61	57		64	60	56
7	75	64	57	52	74	63	57	52		62	56	51		61	55	51		59	55	51
8	70	59	52	47	69	58	51	47		57	51	46		56	50	46		55	50	46
9	66	54	47	42	65	54	47	42		53	46	42		52	46	42		51	46	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	16120	16120	16120
5°	30866	15345	12467
10°	100947	13605	10604
15°	247202	11233	9367
20°	465773	8577	8392
25°	779689	6082	7343
30°	987709	4184	6275
35°	899994	2708	5322
40°	592714	1935	4515
45°	256756	1288	3713
50°	45545	889	3075
55°	7313	709	2584
60°	1821	659	1976
65°	573	779	1559
70°	482	963	1190
75°	636	936	936
80°	0	1395	948
85°	0	2779	889



TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	1.4
10°-20°	171.4	11.1
20°-30°	516.4	33.5
30°-40°	587.7	38.1
40°-50°	217.3	14.1
50°-60°	17.3	1.1
60°-70°	4.6	0.3
70°-80°	3.2	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.2	46.0
0°-40°	1296.9	84.2
0°-60°	1531.4	99.4
0°-90°	1541.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	166	166	166	166	166	
5°	317	233	158	132	128	51
15°	2465	833	112	88	93	773
25°	7294	1217	57	55	69	3330
35°	7610	426	23	31	45	4524
45°	1874	50	9	17	27	1587
55°	43	9	4	10	15	71
65°	2	2	3	7	7	3
75°	2	2	2	4	2	1
85°	0	2	2	2	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4
2.5°	213.9	215.6	213.9	210.5	210.5	206.2	204.6	202.9	198.6	196.0	192.7
5°	317.4	312.3	308.2	297.9	294.6	285.2	278.4	269.0	256.3	245.4	233.4
7.5°	543.2	535.6	519.5	488.9	470.2	447.3	429.5	399.8	361.6	330.2	298.8
10°	1026.2	993.1	954.8	886.1	836.1	782.6	740.2	660.3	564.4	485.4	409.1
12.5°	1653.4	1656.0	1584.6	1468.4	1375.8	1281.6	1208.7	1061.0	891.2	742.6	595.8
15°	2464.8	2418.1	2344.2	2166.0	1981.0	1844.3	1728.1	1504.1	1263.8	1046.6	832.6
17.5°	3319.6	3339.0	3166.8	2875.6	2582.9	2378.2	2202.5	1863.0	1577.9	1308.8	1047.4
20°	4518.0	4383.9	4137.8	3665.8	3210.9	2914.7	2654.1	2213.5	1815.5	1473.4	1179.8
22.5°	5899.8	5683.4	5182.6	4518.0	3829.6	3419.8	3056.5	2450.3	1966.6	1557.5	1224.8
25°	7294.3	7128.8	6331.0	5337.9	4351.7	3820.3	3350.1	2610.8	2038.7	1577.0	1217.1
27.5°	8370.6	8100.6	7191.6	5897.2	4663.1	4035.9	3486.7	2660.0	2023.4	1529.5	1145.0
30°	8829.7	8488.5	7481.0	6024.5	4665.7	4000.2	3418.8	2562.5	1914.9	1409.0	1009.2
32.5°	8546.2	8152.5	7136.5	5672.2	4346.6	3721.8	3156.6	2351.1	1735.0	1219.7	757.9
35°	7610.1	7217.9	6276.6	4977.1	3837.3	3291.5	2800.1	2075.2	1477.8	904.0	426.1
37.5°	6231.7	5897.2	5224.2	4171.7	3233.8	2790.7	2381.6	1748.5	1100.8	518.6	213.9
40°	4686.9	4451.8	4047.8	3308.5	2617.6	2280.6	1951.4	1339.3	668.8	260.6	121.4
42.5°	3249.0	3096.3	2893.5	2447.8	2019.3	1787.5	1523.5	894.6	343.7	143.4	75.5
45°	1874.1	1778.2	1722.2	1532.0	1364.8	1251.9	1018.5	482.2	174.0	85.7	50.2
47.5°	827.5	763.8	736.7	657.0	611.1	580.6	461.0	205.4	93.4	55.1	41.6
50°	302.2	302.2	303.0	266.6	218.1	196.0	153.6	90.8	52.6	43.3	30.6
52.5°	106.9	105.3	109.5	103.6	90.8	81.4	67.9	45.8	32.2	27.1	17.0
55°	43.3	41.6	43.3	40.8	38.2	35.7	31.4	24.6	20.4	17.0	9.4
57.5°	19.5	19.5	20.4	19.5	19.5	17.8	16.2	18.7	14.5	9.4	5.9
60°	9.4	9.4	10.2	10.2	10.2	9.4	9.4	10.2	8.6	5.9	4.2
62.5°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.9	4.2	3.4	2.5
65°	2.5	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
67.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5	2.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	2.5
80°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4
2.5°	189.3	186.7	181.7	179.1	175.7	173.1	171.5	168.1	164.6	162.2	160.4
5°	222.3	213.0	202.0	193.5	186.7	182.6	175.7	169.8	163.0	157.8	153.6
7.5°	270.7	247.8	223.2	206.2	196.9	188.5	176.6	166.4	157.0	150.2	144.2
10°	346.3	297.0	253.8	220.7	204.6	192.7	174.0	159.5	147.7	138.3	132.4
12.5°	471.9	370.9	294.6	238.5	213.9	196.0	169.8	150.2	135.8	126.5	118.9
15°	644.2	479.5	350.6	259.7	225.0	199.4	163.0	139.1	123.0	112.0	105.3
17.5°	806.3	593.3	414.2	285.2	236.0	201.1	153.6	124.8	107.8	97.7	90.8
20°	908.2	667.2	456.6	299.6	239.3	196.0	141.0	109.5	92.6	83.2	76.5
22.5°	931.9	675.6	453.2	286.0	225.0	180.7	123.0	94.2	78.1	69.6	63.7
25°	897.1	628.1	405.7	247.0	191.8	151.9	102.7	76.5	64.5	56.9	52.6
27.5°	809.8	534.8	320.8	185.8	143.4	112.0	78.1	59.4	51.8	45.8	43.3
30°	652.7	376.0	201.1	115.4	91.6	73.8	56.1	45.8	39.9	37.4	34.9
32.5°	395.5	193.5	106.1	68.7	57.8	50.2	40.8	33.9	30.6	28.8	28.0
35°	188.5	101.8	65.3	46.7	40.8	35.7	29.8	25.4	23.8	22.9	22.9
37.5°	106.9	66.2	44.1	31.4	28.0	24.6	22.1	19.5	18.7	18.7	18.7
40°	67.9	42.4	28.8	22.9	20.4	18.7	17.0	15.3	15.3	15.3	15.3
42.5°	44.1	30.6	22.1	17.0	15.3	14.5	12.7	11.8	11.8	11.8	12.7
45°	34.9	25.4	17.8	13.6	11.8	11.0	10.2	9.4	9.4	9.4	10.2
47.5°	29.8	17.8	11.8	9.4	7.6	7.6	6.8	6.8	6.8	7.6	8.6
50°	17.8	11.0	7.6	5.9	5.1	5.1	5.1	5.1	5.1	5.9	6.8
52.5°	10.2	6.8	5.1	4.2	3.4	3.4	3.4	3.4	4.2	5.1	5.1
55°	6.8	5.1	3.4	3.4	2.5	2.5	2.5	3.4	3.4	4.2	5.1
57.5°	4.2	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4	4.2	4.2
60°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
62.5°	2.5	2.5	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
65°	2.5	2.5	3.4	3.4	2.5	2.5	2.5	2.5	2.5	3.4	4.2
67.5°	2.5	2.5	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4	3.4
70°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	3.4	3.4
72.5°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	3.4	3.4
75°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4
77.5°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4
80°	2.5	2.5	2.5	3.4	2.5	3.4	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4
2.5°	157.8	156.2	153.6	152.8	153.6	152.8	148.5	147.7	146.0	146.0	146.0
5°	149.4	146.9	143.4	141.8	141.8	140.1	135.8	135.0	132.4	132.4	131.6
7.5°	139.1	135.8	131.6	129.9	129.9	128.2	124.0	122.2	120.6	120.6	119.7
10°	127.3	123.0	118.9	117.9	117.1	114.6	112.0	111.2	108.6	109.5	108.6
12.5°	113.8	110.3	106.9	105.3	105.3	102.7	101.0	100.2	99.4	99.4	99.4
15°	101.0	96.7	93.4	92.6	92.6	91.6	89.9	89.9	88.3	89.9	89.9
17.5°	86.6	83.2	82.4	80.6	81.4	80.6	79.0	79.8	79.8	80.6	81.4
20°	73.0	70.4	69.6	68.7	69.6	69.6	68.7	69.6	70.4	73.0	74.6
22.5°	61.1	59.4	59.4	58.6	59.4	60.2	59.4	61.1	62.8	64.5	67.1
25°	51.0	50.2	50.2	50.2	51.0	51.8	52.6	54.3	55.1	57.8	59.4
27.5°	41.6	41.6	41.6	42.4	43.3	44.1	45.0	47.5	48.3	51.0	52.6
30°	34.9	33.9	34.9	35.7	36.5	38.2	39.0	40.8	41.6	44.1	45.8
32.5°	28.0	28.8	29.8	30.6	31.4	32.2	33.0	34.9	36.5	38.2	39.9
35°	23.8	23.8	24.6	25.4	26.3	28.0	28.8	29.8	31.4	33.0	33.9
37.5°	19.5	20.4	21.2	22.1	22.9	23.8	24.6	25.4	26.3	28.0	29.8
40°	16.2	17.0	17.8	18.7	18.7	20.4	20.4	22.1	22.9	24.6	26.3
42.5°	13.6	14.5	15.3	16.2	16.2	17.0	17.8	18.7	19.5	21.2	22.9
45°	11.0	11.8	12.7	13.6	13.6	14.5	15.3	16.2	17.0	18.7	19.5
47.5°	9.4	10.2	11.0	11.8	11.8	12.7	13.6	14.5	14.5	16.2	17.0
50°	7.6	8.6	9.4	10.2	10.2	11.0	11.8	12.7	12.7	13.6	14.5
52.5°	5.9	6.8	8.6	8.6	9.4	10.2	10.2	11.0	11.0	11.8	12.7
55°	5.9	6.8	7.6	7.6	8.6	9.4	9.4	10.2	10.2	10.2	11.0
57.5°	5.1	5.9	6.8	7.6	7.6	8.6	8.6	8.6	8.6	9.4	9.4
60°	5.1	5.9	5.9	6.8	6.8	7.6	7.6	7.6	7.6	8.6	8.6
62.5°	5.1	5.1	5.9	5.9	6.8	6.8	6.8	7.6	7.6	7.6	7.6
65°	4.2	5.1	5.9	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8
67.5°	4.2	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
70°	4.2	4.2	5.1	5.1	5.1	5.9	5.9	5.9	5.1	5.9	5.1
72.5°	3.4	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
75°	3.4	4.2	4.2	4.2	4.2	5.1	5.1	4.2	4.2	4.2	4.2
77.5°	3.4	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.4
80°	3.4	3.4	3.4	3.4	4.2	4.2	3.4	3.4	3.4	3.4	3.4
82.5°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5
85°	2.5	2.5	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5	1.7
87.5°	2.5	2.5	2.5	3.4	2.5	2.5	2.5	2.5	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212202

CATALOG NUMBER: LDSQA4A20935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	166.4	166.4	166.4	166.4	166.4	166.4	166.4	166.4
2.5°	143.4	142.6	143.4	142.6	142.6	143.4	141.0	142.6
5°	129.9	128.2	129.0	128.2	127.3	128.2	126.5	128.2
7.5°	117.9	117.1	117.1	117.1	116.2	117.1	115.4	117.1
10°	107.8	106.9	106.9	106.9	106.9	107.8	106.1	107.8
12.5°	97.7	97.7	98.5	97.7	98.5	99.4	97.7	99.4
15°	89.1	89.9	90.8	90.8	91.6	92.6	91.6	93.4
17.5°	82.4	83.2	84.9	84.9	85.7	87.4	86.6	88.3
20°	75.5	76.5	78.1	78.1	79.0	80.6	79.8	81.4
22.5°	67.9	69.6	70.4	71.4	72.2	73.8	73.0	74.6
25°	60.2	62.8	63.7	64.5	65.3	67.1	67.1	68.7
27.5°	54.3	56.1	56.9	57.8	59.4	61.1	61.1	62.0
30°	47.5	49.2	51.0	51.8	52.6	54.3	54.3	56.1
32.5°	41.6	43.3	44.1	45.0	46.7	48.3	49.2	50.2
35°	35.7	38.2	39.0	40.8	41.6	44.1	44.1	45.0
37.5°	31.4	33.0	34.9	35.7	37.4	39.0	39.0	40.8
40°	28.0	29.8	30.6	31.4	33.0	34.9	34.9	35.7
42.5°	23.8	26.3	27.1	28.0	28.8	30.6	31.4	32.2
45°	21.2	22.1	22.9	23.8	24.6	26.3	26.3	27.1
47.5°	17.8	18.7	19.5	20.4	21.2	22.1	22.9	23.8
50°	15.3	16.2	17.0	17.0	17.8	19.5	19.5	20.4
52.5°	12.7	13.6	14.5	14.5	15.3	17.0	17.0	17.8
55°	11.0	11.8	12.7	12.7	13.6	14.5	14.5	15.3
57.5°	10.2	10.2	11.0	11.0	11.8	11.8	12.7	12.7
60°	8.6	9.4	9.4	9.4	10.2	10.2	10.2	10.2
62.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.6
65°	6.8	6.8	6.8	6.8	6.8	6.8	5.9	6.8
67.5°	5.9	5.9	5.9	5.9	5.1	5.1	5.1	5.1
70°	5.1	5.1	5.1	5.1	5.1	4.2	4.2	4.2
72.5°	4.2	4.2	4.2	4.2	4.2	3.4	3.4	3.4
75°	4.2	4.2	3.4	3.4	3.4	3.4	3.4	2.5
77.5°	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
80°	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7
82.5°	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	1.7	1.7	1.7	0.8	0.8	0.8	0.8
87.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)