

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212174

Luminaire Tested: **LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1459.0 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	83	79		85	81	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	86	76	69	64	85	75	69	64	73	68	63		72	67	63		70
6	81	70	63	58	79	69	62	57	67	61	57		66	61	57		64
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15248	15248	15248
5°	29232	14528	11806
10°	95557	12886	10034
15°	234023	10641	8866
20°	440938	8113	7959
25°	738109	5751	6959
30°	935044	3960	5929
35°	852003	2578	5038
40°	561111	1834	4262
45°	243070	1206	3521
50°	43103	844	2894
55°	6925	692	2449
60°	1705	620	1879
65°	550	734	1490
70°	453	906	1161
75°	599	898	898
80°	0	1339	893
85°	0	2668	889



TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.2	1.4
10°-20°	162.3	11.1
20°-30°	488.8	33.5
30°-40°	556.4	38.1
40°-50°	205.7	14.1
50°-60°	16.3	1.1
60°-70°	4.4	0.3
70°-80°	3.1	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.3	46.0
0°-40°	1227.7	84.1
0°-60°	1449.8	99.4
0°-90°	1459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1459.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	157	157	157	157	157	
5°	301	221	149	125	121	49
15°	2333	788	106	84	88	732
25°	6905	1152	54	52	65	3152
35°	7204	403	22	30	43	4283
45°	1774	47	9	16	26	1502
55°	41	9	4	10	14	67
65°	2	2	3	6	6	3
75°	2	2	2	4	2	1
85°	0	2	2	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4
2.5°	202.5	204.1	202.5	199.3	199.3	195.2	193.7	192.1	188.0	185.6	182.4
5°	300.6	295.7	291.8	282.1	278.8	270.0	263.5	254.7	242.6	232.2	221.0
7.5°	514.2	507.0	491.7	462.8	445.1	423.5	406.6	378.5	342.2	312.6	282.9
10°	971.4	940.1	904.0	838.9	791.4	740.8	700.6	625.1	534.3	459.6	387.3
12.5°	1565.2	1567.6	1500.1	1390.1	1302.5	1213.3	1144.2	1004.4	843.7	703.0	564.1
15°	2333.4	2289.1	2219.3	2050.6	1875.4	1746.1	1635.9	1423.8	1196.4	990.7	788.2
17.5°	3142.5	3161.0	2997.9	2722.3	2445.0	2251.4	2085.1	1763.8	1493.8	1239.0	991.5
20°	4277.1	4150.2	3917.0	3470.4	3039.7	2759.2	2512.6	2095.5	1718.7	1394.9	1116.9
22.5°	5585.2	5380.2	4906.2	4277.1	3625.4	3237.3	2893.4	2319.7	1861.7	1474.4	1159.5
25°	6905.3	6748.6	5993.3	5053.3	4119.5	3616.6	3171.5	2471.6	1930.0	1493.0	1152.2
27.5°	7924.2	7668.6	6808.2	5582.7	4414.5	3820.6	3300.7	2518.2	1915.6	1447.9	1083.9
30°	8358.9	8035.8	7082.1	5703.3	4416.9	3787.0	3236.5	2425.8	1812.7	1333.8	955.4
32.5°	8090.5	7717.6	6755.8	5369.8	4114.7	3523.4	2988.2	2225.7	1642.4	1154.6	717.5
35°	7204.3	6833.0	5941.9	4711.8	3632.6	3116.1	2650.7	1964.6	1398.9	855.7	403.3
37.5°	5899.3	5582.7	4945.6	3949.2	3061.4	2641.9	2254.6	1655.3	1042.2	491.0	202.5
40°	4437.0	4214.4	3831.8	3132.1	2478.0	2159.0	1847.3	1268.0	633.1	246.7	114.9
42.5°	3075.8	2931.2	2739.1	2317.4	1911.5	1692.2	1442.2	846.9	325.4	135.8	71.5
45°	1774.2	1683.4	1630.3	1450.2	1292.0	1185.2	964.2	456.3	164.7	81.1	47.4
47.5°	783.4	723.1	697.4	621.9	578.6	549.7	436.3	194.5	88.4	52.2	39.4
50°	286.0	286.0	286.8	252.3	206.6	185.6	145.4	86.0	49.8	41.0	28.9
52.5°	101.2	99.6	103.7	98.1	86.0	77.2	64.2	43.4	30.6	25.7	16.2
55°	41.0	39.4	41.0	38.6	36.2	33.7	29.8	23.3	19.2	16.2	8.8
57.5°	18.5	18.5	19.2	18.5	18.5	16.9	15.3	17.7	13.6	8.8	5.6
60°	8.8	8.8	9.7	9.7	9.7	8.8	8.8	9.7	8.0	5.6	4.1
62.5°	4.1	4.1	4.8	4.8	4.8	4.8	4.8	5.6	4.1	3.2	2.4
65°	2.4	1.6	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
67.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.4	2.4
70°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.4
72.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.4
75°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.4
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.6	1.6	2.4
80°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.6	1.6	1.6
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.6	1.6
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4
2.5°	179.2	176.8	171.9	169.5	166.3	163.9	162.3	159.1	155.9	153.5	151.8
5°	210.5	201.7	191.3	183.3	176.8	172.7	166.3	160.6	154.2	149.4	145.4
7.5°	256.3	234.6	211.4	195.2	186.4	178.4	167.1	157.4	148.6	142.2	136.6
10°	327.8	281.2	240.2	209.0	193.7	182.4	164.7	151.0	139.8	131.0	125.3
12.5°	446.8	351.1	278.8	225.8	202.5	185.6	160.6	142.2	128.6	119.7	112.6
15°	609.8	453.9	331.8	245.8	212.9	188.9	154.2	131.8	116.5	106.1	99.6
17.5°	763.4	561.6	392.1	270.0	223.4	190.4	145.4	118.2	102.0	92.3	86.0
20°	859.8	631.6	432.3	283.6	226.6	185.6	133.4	103.7	87.6	78.7	72.3
22.5°	882.2	639.6	429.1	270.8	212.9	171.2	116.5	89.2	73.9	65.9	60.2
25°	849.3	594.6	384.1	233.8	181.6	143.8	97.3	72.3	61.0	53.8	49.8
27.5°	766.6	506.2	303.7	176.0	135.8	106.1	73.9	56.2	49.0	43.4	41.0
30°	617.8	356.0	190.4	109.3	86.7	69.9	53.0	43.4	37.8	35.4	33.0
32.5°	374.4	183.3	100.5	65.1	54.6	47.4	38.6	32.2	28.9	27.4	26.6
35°	178.4	96.4	61.9	44.2	38.6	33.7	28.1	24.2	22.5	21.8	21.8
37.5°	101.2	62.7	41.8	29.8	26.6	23.3	20.9	18.5	17.7	17.7	17.7
40°	64.2	40.2	27.4	21.8	19.2	17.7	16.2	14.5	14.5	14.5	14.5
42.5°	41.8	28.9	20.9	16.2	14.5	13.6	12.1	11.2	11.2	11.2	12.1
45°	33.0	24.2	16.9	12.9	11.2	10.4	9.7	8.8	8.8	8.8	9.7
47.5°	28.1	16.9	11.2	8.8	7.3	7.3	6.5	6.5	6.5	7.3	8.0
50°	16.9	10.4	7.3	5.6	4.8	4.8	4.8	4.8	4.8	5.6	6.5
52.5°	9.7	6.5	4.8	4.1	3.2	3.2	3.2	3.2	4.1	4.8	4.8
55°	6.5	4.8	3.2	3.2	2.4	2.4	2.4	3.2	3.2	4.1	4.8
57.5°	4.1	3.2	2.4	2.4	2.4	2.4	2.4	2.4	3.2	4.1	4.1
60°	3.2	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	4.1
62.5°	2.4	2.4	3.2	2.4	2.4	2.4	2.4	2.4	3.2	3.2	4.1
65°	2.4	2.4	3.2	3.2	2.4	2.4	2.4	2.4	2.4	3.2	4.1
67.5°	2.4	2.4	3.2	3.2	3.2	3.2	2.4	2.4	2.4	3.2	3.2
70°	2.4	3.2	3.2	3.2	3.2	3.2	3.2	2.4	2.4	3.2	3.2
72.5°	2.4	3.2	3.2	3.2	3.2	3.2	3.2	2.4	2.4	3.2	3.2
75°	2.4	2.4	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4	3.2
77.5°	2.4	2.4	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4	3.2
80°	2.4	2.4	2.4	3.2	2.4	3.2	2.4	2.4	2.4	2.4	2.4
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
85°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
87.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4
2.5°	149.4	147.9	145.4	144.6	145.4	144.6	140.6	139.8	138.2	138.2	138.2
5°	141.4	139.0	135.8	134.2	134.2	132.6	128.6	127.7	125.3	125.3	124.6
7.5°	131.8	128.6	124.6	123.0	123.0	121.4	117.3	115.8	114.1	114.1	113.3
10°	120.6	116.5	112.6	111.7	110.9	108.5	106.1	105.3	102.9	103.7	102.9
12.5°	107.7	104.4	101.2	99.6	99.6	97.3	95.6	94.9	94.0	94.0	94.0
15°	95.6	91.6	88.4	87.6	87.6	86.7	85.2	85.2	83.6	85.2	85.2
17.5°	81.9	78.7	77.9	76.3	77.2	76.3	74.8	75.5	75.5	76.3	77.2
20°	69.0	66.6	65.9	65.1	65.9	65.9	65.1	65.9	66.6	69.0	70.7
22.5°	57.8	56.2	56.2	55.4	56.2	57.1	56.2	57.8	59.5	61.0	63.4
25°	48.2	47.4	47.4	47.4	48.2	49.0	49.8	51.4	52.2	54.6	56.2
27.5°	39.4	39.4	39.4	40.2	41.0	41.8	42.6	45.0	45.8	48.2	49.8
30°	33.0	32.2	33.0	33.7	34.6	36.2	37.0	38.6	39.4	41.8	43.4
32.5°	26.6	27.4	28.1	28.9	29.8	30.6	31.3	33.0	34.6	36.2	37.8
35°	22.5	22.5	23.3	24.2	25.0	26.6	27.4	28.1	29.8	31.3	32.2
37.5°	18.5	19.2	20.1	20.9	21.8	22.5	23.3	24.2	25.0	26.6	28.1
40°	15.3	16.2	16.9	17.7	17.7	19.2	19.2	20.9	21.8	23.3	25.0
42.5°	12.9	13.6	14.5	15.3	15.3	16.2	16.9	17.7	18.5	20.1	21.8
45°	10.4	11.2	12.1	12.9	12.9	13.6	14.5	15.3	16.2	17.7	18.5
47.5°	8.8	9.7	10.4	11.2	11.2	12.1	12.9	13.6	13.6	15.3	16.2
50°	7.3	8.0	8.8	9.7	9.7	10.4	11.2	12.1	12.1	12.9	13.6
52.5°	5.6	6.5	8.0	8.0	8.8	9.7	9.7	10.4	10.4	11.2	12.1
55°	5.6	6.5	7.3	7.3	8.0	8.8	8.8	9.7	9.7	9.7	10.4
57.5°	4.8	5.6	6.5	7.3	7.3	8.0	8.0	8.0	8.0	8.8	8.8
60°	4.8	5.6	5.6	6.5	6.5	7.3	7.3	7.3	7.3	8.0	8.0
62.5°	4.8	4.8	5.6	5.6	6.5	6.5	6.5	7.3	7.3	7.3	7.3
65°	4.1	4.8	5.6	5.6	5.6	6.5	6.5	6.5	6.5	6.5	6.5
67.5°	4.1	4.8	4.8	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
70°	4.1	4.1	4.8	4.8	4.8	5.6	5.6	5.6	4.8	5.6	4.8
72.5°	3.2	4.1	4.1	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
75°	3.2	4.1	4.1	4.1	4.1	4.8	4.8	4.1	4.1	4.1	4.1
77.5°	3.2	3.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	3.2
80°	3.2	3.2	3.2	3.2	4.1	4.1	3.2	3.2	3.2	3.2	3.2
82.5°	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4
85°	2.4	2.4	3.2	3.2	3.2	3.2	2.4	2.4	2.4	2.4	1.6
87.5°	2.4	2.4	2.4	3.2	2.4	2.4	2.4	2.4	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212174

CATALOG NUMBER: LDSQA4A20927D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	157.4	157.4	157.4	157.4	157.4	157.4	157.4	157.4
2.5°	135.8	135.0	135.8	135.0	135.0	135.8	133.4	135.0
5°	123.0	121.4	122.1	121.4	120.6	121.4	119.7	121.4
7.5°	111.7	110.9	110.9	110.9	110.0	110.9	109.3	110.9
10°	102.0	101.2	101.2	101.2	101.2	102.0	100.5	102.0
12.5°	92.3	92.3	93.2	92.3	93.2	94.0	92.3	94.0
15°	84.3	85.2	86.0	86.0	86.7	87.6	86.7	88.4
17.5°	77.9	78.7	80.4	80.4	81.1	82.8	81.9	83.6
20°	71.5	72.3	73.9	73.9	74.8	76.3	75.5	77.2
22.5°	64.2	65.9	66.6	67.5	68.3	69.9	69.0	70.7
25°	57.1	59.5	60.2	61.0	61.9	63.4	63.4	65.1
27.5°	51.4	53.0	53.8	54.6	56.2	57.8	57.8	58.6
30°	45.0	46.6	48.2	49.0	49.8	51.4	51.4	53.0
32.5°	39.4	41.0	41.8	42.6	44.2	45.8	46.6	47.4
35°	33.7	36.2	37.0	38.6	39.4	41.8	41.8	42.6
37.5°	29.8	31.3	33.0	33.7	35.4	37.0	37.0	38.6
40°	26.6	28.1	28.9	29.8	31.3	33.0	33.0	33.7
42.5°	22.5	25.0	25.7	26.6	27.4	28.9	29.8	30.6
45°	20.1	20.9	21.8	22.5	23.3	25.0	25.0	25.7
47.5°	16.9	17.7	18.5	19.2	20.1	20.9	21.8	22.5
50°	14.5	15.3	16.2	16.2	16.9	18.5	18.5	19.2
52.5°	12.1	12.9	13.6	13.6	14.5	16.2	16.2	16.9
55°	10.4	11.2	12.1	12.1	12.9	13.6	13.6	14.5
57.5°	9.7	9.7	10.4	10.4	11.2	11.2	12.1	12.1
60°	8.0	8.8	8.8	8.8	9.7	9.7	9.7	9.7
62.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.0
65°	6.5	6.5	6.5	6.5	6.5	6.5	5.6	6.5
67.5°	5.6	5.6	5.6	5.6	4.8	4.8	4.8	4.8
70°	4.8	4.8	4.8	4.8	4.8	4.1	4.1	4.1
72.5°	4.1	4.1	4.1	4.1	4.1	3.2	3.2	3.2
75°	4.1	4.1	3.2	3.2	3.2	3.2	3.2	2.4
77.5°	3.2	3.2	3.2	3.2	2.4	2.4	2.4	2.4
80°	2.4	2.4	2.4	2.4	2.4	2.4	1.6	1.6
82.5°	2.4	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	1.6	1.6	1.6	0.8	0.8	0.8	0.8
87.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)