

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212182

Luminaire Tested: **LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1600.4 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	106	104	110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	85
3	99	91	86	81	97	90	85	80		87	83	79		85	81	78		82	79	76
4	93	84	77	72	91	83	76	72		80	75	71		78	74	70		76	72	69
5	87	77	70	65	85	76	69	64		74	68	64		72	67	63		70	66	63
6	81	70	63	58	79	69	63	58		68	62	57		66	61	57		65	60	57
7	76	65	57	52	74	64	57	52		62	56	52		61	56	52		60	55	51
8	71	59	52	47	69	59	52	47		58	51	47		57	51	47		55	50	47
9	66	55	48	43	65	54	48	43		53	47	43		52	47	43		51	46	42
10	62	51	44	39	61	50	44	39		49	43	39		48	43	39		48	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	17273	17273	17273
5°	38684	16250	11640
10°	151686	14224	9168
15°	329291	11524	7973
20°	491237	8536	7206
25°	638936	6007	6264
30°	714765	4049	5481
35°	643245	2377	4660
40°	524943	1631	4072
45°	301433	1096	3315
50°	88166	844	2788
55°	10168	692	2297
60°	2170	794	1879
65°	734	734	1284
70°	680	906	906
75°	599	1198	898
80°	0	1785	893
85°	0	3557	889



TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	1.6
10°-20°	219.1	13.7
20°-30°	522.6	32.7
30°-40°	551.6	34.5
40°-50°	250.1	15.6
50°-60°	21.9	1.4
60°-70°	4.6	0.3
70°-80°	3.0	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	767.3	47.9
0°-40°	1318.9	82.4
0°-60°	1591.0	99.4
0°-90°	1600.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1600.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	178	178	178	178	178	
5°	398	292	167	129	120	71
15°	3283	1155	115	79	80	955
25°	5978	1589	56	48	59	2715
35°	5439	439	20	27	39	3359
45°	2200	62	8	15	24	1744
55°	60	10	4	9	14	120
65°	3	3	3	6	6	4
75°	2	2	3	4	2	1
85°	0	2	3	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3
2.5°	265.2	266.7	259.6	260.3	253.1	256.3	254.0	247.5	242.6	234.6	231.4
5°	397.8	400.2	384.1	379.3	362.4	362.4	355.2	338.3	323.0	304.5	291.8
7.5°	727.2	736.8	688.6	652.5	599.4	586.6	561.7	503.8	456.5	408.2	372.0
10°	1542.0	1524.3	1424.7	1342.7	1206.1	1155.4	1087.9	921.7	769.0	617.1	498.2
12.5°	2431.5	2488.5	2296.6	2229.8	2013.7	1967.9	1824.1	1552.4	1294.5	1026.1	788.2
15°	3283.3	3300.2	3132.2	3023.7	2760.2	2700.6	2523.8	2204.9	1857.8	1483.4	1154.7
17.5°	3967.0	4034.6	3787.9	3671.3	3329.0	3233.4	3025.3	2637.2	2250.6	1841.8	1451.9
20°	4765.0	4782.6	4490.2	4266.0	3818.4	3673.0	3423.9	2942.6	2482.2	2015.3	1612.7
22.5°	5490.6	5486.6	5110.5	4793.9	4227.4	4053.8	3746.1	3175.5	2640.5	2092.4	1627.9
25°	5977.5	5990.3	5587.8	5213.3	4518.2	4283.7	3936.5	3296.9	2694.2	2090.0	1589.4
27.5°	6237.0	6224.2	5792.7	5392.5	4625.2	4362.4	3985.5	3301.0	2645.3	2008.0	1473.7
30°	6389.7	6217.8	5757.4	5341.8	4552.8	4282.8	3899.6	3174.0	2482.2	1824.8	1267.1
32.5°	5981.6	5914.8	5513.8	5072.7	4303.8	4036.2	3657.7	2904.0	2223.4	1544.4	908.0
35°	5439.1	5441.5	5050.2	4638.0	3913.2	3680.2	3289.6	2575.4	1907.6	1073.5	438.8
37.5°	4870.2	4878.2	4506.2	4123.0	3477.7	3232.6	2867.0	2200.9	1372.5	546.4	264.4
40°	4151.0	4167.9	3847.3	3539.5	2944.2	2707.9	2381.7	1665.8	767.4	305.4	179.2
42.5°	3391.8	3412.6	3128.1	2855.0	2348.7	2154.2	1865.0	1031.8	380.9	197.7	105.3
45°	2200.2	2260.3	2049.0	1934.1	1640.8	1525.0	1217.3	526.3	229.8	115.8	61.9
47.5°	1259.1	1260.0	1081.6	866.2	710.3	618.0	483.0	239.4	134.2	65.1	37.8
50°	585.0	599.4	474.9	395.3	282.9	239.4	196.9	129.4	70.7	37.8	23.3
52.5°	170.3	180.0	163.0	147.9	125.3	111.7	95.6	63.4	37.0	22.5	14.5
55°	60.2	64.2	60.2	56.2	50.6	45.8	41.0	30.6	20.9	13.6	9.7
57.5°	25.0	25.7	25.0	24.2	22.5	22.5	20.1	16.9	12.9	8.8	6.5
60°	11.2	12.1	11.2	12.1	11.2	11.2	11.2	12.1	8.0	5.6	4.8
62.5°	4.8	5.6	5.6	5.6	5.6	6.5	6.5	5.6	4.8	4.1	3.2
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
67.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
70°	2.4	2.4	2.4	2.4	2.4	2.4	1.6	1.6	2.4	2.4	2.4
72.5°	2.4	2.4	2.4	2.4	1.6	1.6	1.6	1.6	1.6	2.4	2.4
75°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.6	1.6	1.6
80°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.6	1.6	1.6
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.6	1.6	1.6
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3
2.5°	227.4	220.2	209.0	201.7	198.4	193.7	190.4	182.4	179.2	172.7	170.3
5°	279.7	265.2	248.2	234.6	225.8	216.1	201.7	185.6	177.6	167.1	161.5
7.5°	339.0	307.8	278.0	254.0	242.6	229.8	211.4	186.4	171.2	157.4	149.4
10°	414.6	350.4	303.8	265.2	248.2	231.4	209.0	180.0	160.6	144.6	135.8
12.5°	591.4	422.6	327.0	271.5	249.9	229.0	201.0	171.2	148.6	130.2	120.6
15°	851.0	590.6	389.7	277.3	244.3	218.6	186.4	156.7	133.4	114.9	105.3
17.5°	1080.8	753.0	476.6	298.1	242.6	206.6	168.8	138.2	115.8	98.1	89.9
20°	1206.1	838.2	534.3	311.0	235.4	188.0	148.6	119.7	98.1	82.8	75.5
22.5°	1208.5	833.3	513.4	282.9	207.3	163.0	128.6	101.3	81.9	68.3	62.7
25°	1136.2	743.3	428.2	222.6	169.5	138.2	107.7	84.3	66.6	56.2	51.4
27.5°	1001.2	604.2	315.0	160.6	132.6	111.7	86.7	67.5	52.2	45.8	41.8
30°	787.5	393.8	184.0	119.7	102.9	86.0	65.9	47.4	41.0	36.2	33.0
32.5°	422.6	191.3	128.6	88.4	73.1	60.2	43.4	34.6	29.8	26.6	25.7
35°	221.0	139.8	86.0	56.2	46.6	39.4	29.8	24.2	21.8	20.1	20.1
37.5°	158.3	87.6	54.6	36.2	30.6	25.0	20.9	17.7	16.2	16.2	16.2
40°	94.0	53.8	33.0	23.3	20.1	17.7	15.3	12.9	12.9	12.9	12.9
42.5°	57.1	33.8	23.3	16.2	14.5	12.9	11.2	10.4	9.7	9.7	10.4
45°	35.4	23.3	15.3	12.1	11.2	9.7	8.8	8.0	8.0	8.0	8.8
47.5°	22.5	16.9	11.2	8.0	7.3	6.5	5.6	5.6	6.5	6.5	7.3
50°	16.9	10.4	7.3	5.6	4.8	4.8	4.1	4.8	4.8	5.6	6.5
52.5°	9.7	6.5	4.8	4.1	4.1	3.2	3.2	4.1	4.1	4.8	5.6
55°	6.5	4.8	4.1	3.2	3.2	3.2	3.2	3.2	4.1	4.1	4.8
57.5°	4.8	4.1	3.2	3.2	3.2	2.4	3.2	3.2	3.2	4.1	4.8
60°	4.1	3.2	3.2	3.2	3.2	2.4	2.4	3.2	3.2	4.1	4.1
62.5°	3.2	3.2	3.2	3.2	3.2	2.4	3.2	3.2	3.2	3.2	4.1
65°	2.4	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.1
67.5°	2.4	2.4	3.2	3.2	3.2	2.4	3.2	3.2	3.2	3.2	4.1
70°	2.4	2.4	2.4	3.2	3.2	2.4	3.2	3.2	3.2	3.2	3.2
72.5°	2.4	2.4	2.4	3.2	3.2	2.4	3.2	3.2	3.2	3.2	3.2
75°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	3.2
77.5°	2.4	2.4	2.4	2.4	3.2	2.4	3.2	3.2	3.2	3.2	3.2
80°	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	3.2	3.2	3.2
82.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	3.2	3.2
85°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	3.2	3.2
87.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3
2.5°	163.9	161.5	156.7	155.9	155.0	151.8	149.4	147.0	147.0	144.6	143.0
5°	151.8	147.9	142.2	139.8	139.0	135.0	131.8	129.4	128.6	126.2	123.8
7.5°	139.0	134.2	127.7	125.3	124.6	120.6	117.3	114.9	113.3	110.9	109.3
10°	125.3	119.7	114.1	111.7	110.9	106.9	104.4	102.0	100.5	98.8	97.3
12.5°	110.9	106.1	100.5	98.1	97.3	94.0	91.6	89.9	89.2	87.6	86.7
15°	96.4	91.6	86.7	85.2	84.3	81.9	80.4	79.5	78.7	78.7	77.9
17.5°	81.9	77.9	73.9	73.1	72.3	70.7	69.9	69.0	69.9	69.9	70.7
20°	68.3	65.1	61.9	61.9	61.0	60.2	60.2	60.2	61.9	62.7	64.2
22.5°	56.2	53.8	51.4	51.4	51.4	51.4	51.4	53.0	54.6	56.2	57.1
25°	46.6	44.2	43.4	43.4	43.4	44.2	45.0	46.6	48.2	49.8	51.4
27.5°	37.8	36.2	36.2	36.2	37.0	37.8	38.6	40.2	42.6	44.2	45.8
30°	30.6	29.8	29.8	30.6	31.3	32.2	33.8	35.4	37.0	38.6	40.2
32.5°	24.2	25.0	25.0	25.7	26.6	27.4	28.9	30.6	32.2	33.8	34.6
35°	20.1	20.1	20.9	21.8	22.5	23.3	25.0	26.6	27.4	28.9	30.6
37.5°	16.2	16.9	17.7	18.5	19.2	20.1	20.9	22.5	23.3	25.0	26.6
40°	13.6	14.5	15.3	16.2	16.2	17.7	17.7	19.2	20.1	21.8	23.3
42.5°	11.2	12.1	12.9	13.6	13.6	14.5	15.3	16.2	17.7	18.5	20.1
45°	8.8	9.7	10.4	11.2	12.1	12.9	12.9	14.5	15.3	16.2	17.7
47.5°	8.0	8.8	9.7	9.7	10.4	11.2	11.2	12.9	13.6	14.5	15.3
50°	6.5	7.3	8.0	8.8	8.8	9.7	10.4	11.2	12.1	12.9	12.9
52.5°	5.6	6.5	7.3	7.3	8.0	8.8	8.8	9.7	10.4	10.4	11.2
55°	5.6	6.5	6.5	7.3	7.3	8.0	8.0	8.8	8.8	9.7	9.7
57.5°	4.8	5.6	5.6	6.5	6.5	7.3	7.3	8.0	8.0	8.0	8.8
60°	4.8	4.8	5.6	5.6	6.5	6.5	6.5	7.3	7.3	7.3	8.0
62.5°	4.1	4.8	4.8	5.6	5.6	5.6	6.5	6.5	6.5	7.3	7.3
65°	4.1	4.8	4.8	5.6	5.6	5.6	5.6	5.6	6.5	6.5	6.5
67.5°	4.1	4.1	4.8	4.8	4.8	4.8	5.6	5.6	5.6	5.6	5.6
70°	4.1	4.1	4.1	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
72.5°	3.2	4.1	4.1	4.1	4.1	4.8	4.8	4.8	4.8	4.8	4.1
75°	3.2	3.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
77.5°	3.2	3.2	3.2	4.1	4.1	4.1	4.1	4.1	4.1	3.2	3.2
80°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.4
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.4	2.4	2.4
85°	3.2	2.4	3.2	3.2	3.2	2.4	2.4	2.4	2.4	2.4	1.6
87.5°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212182

CATALOG NUMBER: LDSQA4A20927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	178.3	178.3	178.3	178.3	178.3	178.3	178.3	178.3
2.5°	141.4	139.8	140.6	140.6	139.0	138.2	138.2	139.0
5°	122.1	120.6	121.4	121.4	119.7	118.9	118.9	119.7
7.5°	107.7	106.1	106.9	106.9	105.3	105.3	105.3	105.3
10°	96.4	95.6	95.6	95.6	94.0	94.9	94.0	93.2
12.5°	86.0	86.0	86.0	86.0	85.2	86.0	85.2	85.2
15°	77.9	77.9	78.7	78.7	78.7	79.5	79.5	79.5
17.5°	71.5	72.3	73.1	73.9	73.9	74.8	74.8	74.8
20°	65.1	66.6	67.5	68.3	68.3	69.9	69.0	69.9
22.5°	58.6	60.2	61.0	61.9	62.7	63.4	63.4	64.2
25°	53.0	54.6	55.4	56.2	57.1	58.6	58.6	58.6
27.5°	47.4	49.0	49.8	51.4	52.2	53.8	53.8	53.8
30°	41.8	43.4	44.2	45.0	46.6	48.2	48.2	49.0
32.5°	36.2	38.6	39.4	40.2	41.8	43.4	44.2	44.2
35°	32.2	33.8	34.6	36.2	37.0	39.4	39.4	39.4
37.5°	28.1	29.8	31.3	32.2	33.0	34.6	35.4	36.2
40°	25.0	26.6	27.4	28.1	29.8	31.3	32.2	32.2
42.5°	21.8	23.3	24.2	25.0	25.7	27.4	27.4	27.4
45°	19.2	20.1	20.9	21.8	22.5	23.3	24.2	24.2
47.5°	16.2	17.7	17.7	18.5	19.2	20.9	20.9	21.8
50°	13.6	15.3	15.3	16.2	16.9	17.7	18.5	18.5
52.5°	12.1	12.9	13.6	13.6	14.5	15.3	16.2	16.2
55°	10.4	11.2	11.2	12.1	12.1	12.9	13.6	13.6
57.5°	8.8	9.7	10.4	10.4	10.4	11.2	11.2	12.1
60°	8.0	8.8	8.8	8.8	8.8	9.7	9.7	9.7
62.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
65°	6.5	6.5	6.5	6.5	5.6	5.6	5.6	5.6
67.5°	5.6	5.6	5.6	5.6	4.8	4.8	4.8	4.8
70°	4.8	4.8	4.8	4.8	4.1	4.1	4.1	3.2
72.5°	4.1	4.1	4.1	4.1	4.1	3.2	3.2	3.2
75°	4.1	3.2	3.2	3.2	3.2	3.2	2.4	2.4
77.5°	3.2	3.2	3.2	2.4	2.4	2.4	2.4	2.4
80°	2.4	2.4	2.4	2.4	2.4	1.6	1.6	1.6
82.5°	2.4	1.6	1.6	1.6	1.6	1.6	1.6	1.6
85°	1.6	1.6	1.6	1.6	0.8	0.8	0.8	0.8
87.5°	1.6	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)