

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212214

Luminaire Tested: **LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1722.7 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20634	20634	20634
5°	48370	19478	13614
10°	191093	17116	11352
15°	353663	13700	9969
20°	453484	9969	9010
25°	542575	7076	7974
30°	576918	4653	7025
35°	591280	2803	6126
40°	541244	1834	5261
45°	390553	1288	4302
50°	170500	1025	3572
55°	11755	861	3006
60°	2131	814	2461
65°	779	779	1742
70°	708	963	1190
75°	636	1273	1273
80°	0	1897	1395
85°	0	3779	889



TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	1.8
10°-20°	243.9	14.2
20°-30°	510.5	29.6
30°-40°	568.3	33.0
40°-50°	326.2	18.9
50°-60°	32.6	1.9
60°-70°	5.1	0.3
70°-80°	3.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.4	45.6
0°-40°	1353.7	78.6
0°-60°	1712.5	99.4
0°-90°	1722.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1722.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	213	213	213	213	213	
5°	497	343	200	146	140	91
15°	3526	1408	137	96	99	997
25°	5076	1938	66	59	75	2299
35°	5000	592	24	34	52	3053
45°	2851	71	9	19	31	2177
55°	70	10	5	11	18	208
65°	3	2	3	7	8	4
75°	2	2	3	4	3	1
85°	0	2	3	2	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0
2.5°	318.2	311.5	304.7	300.5	296.2	302.2	297.8	296.2	284.3	278.4	273.3
5°	497.4	484.6	465.9	450.6	435.4	438.8	426.9	412.5	382.7	361.5	342.9
7.5°	959.9	928.5	870.8	814.7	758.7	748.6	711.3	646.6	563.6	500.8	446.4
10°	1942.6	1847.6	1741.4	1627.0	1492.8	1455.5	1363.0	1188.2	997.3	779.0	621.2
12.5°	2867.7	2824.4	2699.8	2551.1	2406.1	2316.9	2221.0	1932.4	1629.4	1278.2	984.5
15°	3526.3	3500.0	3390.5	3255.6	3099.4	3041.7	2924.6	2637.0	2254.1	1834.1	1407.9
17.5°	4014.3	3969.4	3854.7	3707.9	3522.9	3473.7	3333.6	3047.6	2650.4	2228.6	1755.9
20°	4398.8	4370.8	4222.3	4045.7	3824.2	3764.8	3601.0	3303.1	2871.1	2423.0	1941.8
22.5°	4744.2	4696.6	4514.2	4303.8	4050.8	3987.1	3804.7	3478.0	3013.7	2514.7	1974.9
25°	5076.0	5003.8	4782.3	4506.6	4209.5	4123.0	3922.6	3576.3	3066.3	2522.3	1937.5
27.5°	5172.7	5136.2	4931.8	4611.0	4267.2	4169.7	3960.8	3598.5	3046.8	2452.7	1803.4
30°	5157.4	5127.0	4956.3	4621.1	4257.0	4154.4	3942.2	3530.6	2933.1	2271.1	1566.6
32.5°	5109.1	5097.3	4891.0	4532.8	4162.0	4050.0	3820.9	3361.7	2720.0	1994.4	1145.0
35°	4999.7	4953.0	4695.8	4358.9	4002.4	3879.4	3620.6	3119.8	2439.1	1452.2	591.5
37.5°	4678.9	4642.3	4439.5	4144.2	3797.0	3639.2	3365.9	2807.5	1888.3	825.8	353.9
40°	4279.9	4262.2	4102.6	3838.6	3467.8	3289.5	2992.5	2297.4	1152.6	469.4	233.4
42.5°	3870.9	3865.8	3695.2	3419.4	3017.1	2812.6	2504.6	1549.7	612.8	283.5	135.0
45°	2850.7	2881.3	2762.5	2597.0	2289.8	2141.3	1741.4	798.6	353.1	157.0	71.2
47.5°	1999.5	1965.6	1755.1	1465.7	1184.8	1003.2	758.7	377.6	188.5	82.4	40.8
50°	1131.3	1137.3	947.1	766.4	502.4	398.0	302.2	190.1	90.8	43.3	24.6
52.5°	295.4	308.9	266.5	229.1	195.2	158.7	128.2	82.4	43.3	25.4	16.2
55°	69.6	72.2	67.1	62.8	59.4	52.6	46.7	35.7	23.7	16.2	10.2
57.5°	24.6	25.4	24.6	24.6	23.7	22.9	21.2	18.7	14.5	10.2	6.8
60°	11.0	11.8	11.0	11.8	11.8	11.8	11.8	11.8	8.6	5.9	4.2
62.5°	5.1	5.1	5.1	5.1	5.9	5.9	6.8	6.8	5.1	4.2	3.4
65°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
70°	2.5	2.5	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7
80°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0
2.5°	263.9	263.1	253.8	247.0	243.6	238.5	232.6	224.0	214.7	206.2	202.8
5°	320.8	309.8	290.2	274.2	266.5	258.9	245.2	229.9	215.6	200.3	192.6
7.5°	394.7	362.4	324.2	294.6	281.8	269.0	249.5	228.3	208.7	188.5	177.4
10°	495.7	421.0	354.7	307.2	288.6	271.5	243.6	217.3	196.0	174.0	159.5
12.5°	708.6	523.7	387.0	313.1	288.6	266.5	232.6	202.0	178.2	155.3	141.8
15°	1021.0	707.0	457.5	319.0	282.6	254.6	215.6	182.6	157.0	136.6	123.8
17.5°	1273.0	875.9	544.9	334.4	275.0	238.5	193.5	158.7	135.0	116.2	106.1
20°	1400.3	947.1	584.8	337.0	256.2	213.0	167.2	134.1	112.8	96.7	88.3
22.5°	1397.8	924.2	549.1	295.4	225.0	184.2	141.0	110.3	93.4	80.6	73.8
25°	1309.6	818.2	458.3	236.0	181.6	152.8	114.6	89.1	75.5	66.2	60.2
27.5°	1144.0	664.6	342.1	174.8	141.8	120.6	89.1	71.2	60.2	53.4	49.2
30°	897.9	444.7	215.6	129.9	107.8	90.8	68.7	55.1	47.5	41.6	39.0
32.5°	494.8	231.7	145.1	95.0	79.0	66.2	51.0	39.9	34.9	30.6	29.8
35°	273.3	163.8	103.6	63.7	52.6	45.0	34.9	28.8	25.4	23.7	23.7
37.5°	193.5	105.3	62.0	39.9	33.9	29.8	23.7	20.4	19.5	18.7	18.7
40°	116.2	62.0	37.4	26.3	22.9	20.4	17.8	15.3	15.3	14.5	15.3
42.5°	63.7	37.4	25.4	18.7	16.2	15.3	12.7	11.8	11.8	11.8	12.7
45°	38.2	24.6	17.8	13.6	11.8	10.2	9.4	8.6	9.4	9.4	10.2
47.5°	24.6	17.8	11.8	8.6	7.6	6.8	5.9	6.8	6.8	7.6	8.6
50°	17.0	11.0	7.6	5.1	5.1	4.2	5.1	5.1	5.9	6.8	7.6
52.5°	11.0	7.6	5.1	4.2	3.4	3.4	3.4	4.2	5.1	5.9	6.8
55°	6.8	5.1	4.2	3.4	3.4	3.4	3.4	3.4	4.2	5.1	5.9
57.5°	5.1	4.2	3.4	2.5	2.5	2.5	3.4	3.4	4.2	4.2	5.1
60°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.1
62.5°	3.4	3.4	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2	4.2
65°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
77.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
82.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
85°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
87.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0
2.5°	198.6	192.6	187.5	189.3	185.8	179.9	178.2	174.0	168.9	168.1	168.1
5°	184.2	174.8	167.2	166.3	163.0	156.2	154.4	150.2	146.0	145.1	144.2
7.5°	166.3	156.2	149.4	147.7	145.1	139.1	138.3	134.1	131.6	129.9	129.9
10°	148.5	139.1	133.2	132.4	130.7	125.6	124.8	121.4	118.8	117.9	117.1
12.5°	131.6	123.8	118.8	117.9	116.2	112.0	111.2	108.6	106.9	106.1	106.1
15°	115.4	108.6	104.4	103.6	102.6	98.5	98.5	96.7	95.9	95.9	96.7
17.5°	99.4	93.4	89.9	89.1	89.1	85.7	86.6	85.7	85.7	85.7	87.4
20°	83.2	78.1	75.5	76.3	74.6	73.8	74.6	74.6	74.6	76.3	79.0
22.5°	69.6	65.3	62.8	63.7	63.7	62.8	63.7	64.5	66.2	68.7	71.2
25°	56.9	53.4	52.6	53.4	53.4	53.4	55.1	56.9	58.6	61.1	63.7
27.5°	45.8	43.3	43.3	44.1	45.0	45.0	47.5	49.2	51.8	54.3	56.9
30°	36.5	35.7	35.7	37.4	37.4	38.2	41.6	43.3	45.0	47.5	50.0
32.5°	28.8	28.8	29.8	31.4	31.4	33.0	35.7	37.4	39.0	41.6	44.1
35°	23.7	24.6	25.4	26.3	27.1	28.0	30.6	32.2	33.9	36.5	38.2
37.5°	19.5	20.4	21.2	22.9	22.9	23.7	26.3	28.0	28.8	31.4	33.9
40°	16.2	17.0	17.8	19.5	19.5	20.4	22.9	23.7	24.6	27.1	29.8
42.5°	13.6	14.5	15.3	16.2	17.0	17.8	19.5	20.4	22.1	23.7	25.4
45°	11.0	11.8	12.7	13.6	14.5	15.3	16.2	17.8	18.7	20.4	22.1
47.5°	9.4	10.2	11.0	11.8	12.7	12.7	14.5	15.3	16.2	17.8	19.5
50°	8.6	9.4	10.2	10.2	11.0	11.8	12.7	13.6	14.5	15.3	17.0
52.5°	6.8	7.6	8.6	9.4	9.4	10.2	11.0	11.8	12.7	13.6	14.5
55°	6.8	6.8	7.6	8.6	8.6	9.4	10.2	11.0	11.0	11.8	12.7
57.5°	5.9	6.8	6.8	7.6	7.6	8.6	9.4	9.4	10.2	10.2	11.0
60°	5.1	5.9	6.8	6.8	6.8	7.6	7.6	8.6	8.6	9.4	9.4
62.5°	5.1	5.9	5.9	6.8	6.8	6.8	7.6	7.6	7.6	8.6	8.6
65°	5.1	5.1	5.9	5.9	5.9	5.9	6.8	6.8	6.8	7.6	7.6
67.5°	4.2	5.1	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8
70°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.9	5.9	5.9	5.9
72.5°	4.2	4.2	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1
75°	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
77.5°	3.4	3.4	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
85°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212214

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	213.0	213.0	213.0	213.0	213.0	213.0	213.0	213.0
2.5°	164.6	163.0	162.2	164.6	161.2	163.0	162.2	163.0
5°	141.8	140.0	139.1	141.8	138.3	140.0	138.3	140.0
7.5°	127.3	126.5	125.6	127.3	124.8	126.5	125.6	126.5
10°	115.4	114.6	113.8	116.2	113.8	115.4	114.6	115.4
12.5°	105.3	105.3	104.4	106.1	104.4	106.1	105.3	106.1
15°	95.9	96.7	95.9	97.5	96.7	98.5	97.5	99.4
17.5°	88.3	89.1	89.1	91.6	90.8	93.4	92.5	93.4
20°	80.6	81.4	82.4	84.0	84.0	86.6	85.7	87.4
22.5°	73.0	74.6	74.6	77.3	77.3	79.8	79.8	80.6
25°	65.3	67.9	68.7	70.4	71.2	73.8	73.8	74.6
27.5°	59.4	61.1	62.0	64.5	65.3	67.9	67.9	69.6
30°	52.6	55.1	56.1	57.8	58.6	61.1	61.1	62.8
32.5°	46.7	48.3	50.0	51.8	52.6	55.1	55.1	56.9
35°	40.8	43.3	44.1	45.8	47.5	50.0	50.0	51.8
37.5°	35.7	38.2	39.0	40.8	42.4	45.0	45.0	46.7
40°	31.4	33.9	34.9	36.5	37.4	40.8	40.8	41.6
42.5°	28.0	29.8	30.6	32.2	33.0	34.9	34.9	36.5
45°	23.7	25.4	26.3	27.1	28.8	30.6	30.6	31.4
47.5°	20.4	22.1	22.9	23.7	24.6	26.3	26.3	28.0
50°	17.8	18.7	19.5	20.4	21.2	22.9	22.9	23.7
52.5°	15.3	16.2	17.0	17.8	18.7	19.5	20.4	21.2
55°	13.6	14.5	14.5	15.3	16.2	17.0	17.0	17.8
57.5°	11.8	12.7	12.7	12.7	13.6	14.5	14.5	15.3
60°	10.2	11.0	11.0	11.0	11.8	11.8	11.8	12.7
62.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
65°	7.6	7.6	7.6	7.6	7.6	7.6	6.8	7.6
67.5°	6.8	6.8	6.8	5.9	5.9	5.9	5.9	5.9
70°	5.9	5.9	5.9	5.1	5.1	5.1	4.2	4.2
72.5°	5.1	5.1	5.1	4.2	4.2	4.2	3.4	3.4
75°	4.2	4.2	4.2	4.2	3.4	3.4	3.4	3.4
77.5°	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
80°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	1.7	1.7	1.7	1.7
85°	1.7	1.7	1.7	1.7	1.7	1.7	0.8	0.8
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)