

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212226

Luminaire Tested: **LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2002.2 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	22630	22630	22630
5°	59524	21569	14081
10°	233333	18661	11706
15°	429574	14703	10380
20°	539793	10392	9443
25°	645660	6862	8423
30°	678981	4307	7372
35°	684459	2590	6398
40°	629843	1745	5438
45°	448108	1247	4521
50°	185164	980	3723
55°	10674	929	3243
60°	1259	891	2674
65°	413	1054	1880
70°	510	1048	1303
75°	674	1385	1385
80°	0	2064	1506
85°	0	4113	2001

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	1.8
10°-20°	293.4	14.7
20°-30°	606.8	30.3
30°-40°	660.6	33.0
40°-50°	362.2	18.1
50°-60°	31.4	1.6
60°-70°	5.1	0.3
70°-80°	3.7	0.2
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.9	46.8
0°-40°	1597.5	79.8
0°-60°	1991.1	99.4
0°-90°	2002.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2002.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	234	234	234	234	234	
5°	612	419	222	153	145	112
15°	4283	1800	147	99	104	1196
25°	6040	2395	64	60	79	2728
35°	5788	655	22	35	54	3552
45°	3271	67	9	19	33	2496
55°	63	7	6	12	19	216
65°	2	3	5	7	8	3
75°	2	3	4	6	4	1
85°	0	2	4	3	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6
2.5°	367.4	354.6	352.8	354.6	345.4	344.5	346.3	339.0	332.6	326.2	320.6
5°	612.1	585.4	577.2	566.2	538.7	529.6	527.7	498.4	470.0	443.4	418.7
7.5°	1189.3	1136.1	1107.7	1052.7	968.5	930.8	910.7	814.6	724.6	643.1	569.0
10°	2372.0	2232.8	2165.0	2061.4	1877.3	1786.6	1720.6	1478.8	1240.5	1011.5	809.9
12.5°	3461.4	3384.4	3284.6	3229.6	2931.0	2816.3	2707.4	2372.0	2009.2	1639.0	1271.7
15°	4283.2	4170.5	4064.2	4038.6	3804.0	3670.2	3549.3	3202.1	2770.6	2299.7	1800.3
17.5°	4766.0	4685.4	4584.6	4536.1	4261.2	4153.1	4015.7	3679.4	3259.8	2790.7	2210.7
20°	5236.0	5116.9	4975.0	4901.6	4597.4	4472.8	4317.0	3963.4	3519.0	3020.6	2440.8
22.5°	5665.7	5511.8	5310.2	5196.6	4855.0	4717.4	4543.4	4160.4	3679.4	3109.6	2460.0
25°	6040.4	5901.2	5632.7	5433.9	5030.8	4868.6	4666.2	4265.8	3737.1	3102.2	2394.9
27.5°	6111.8	6018.5	5777.5	5547.6	5092.2	4911.7	4701.9	4287.8	3696.8	3000.5	2219.8
30°	6069.8	5969.0	5775.7	5541.1	5066.6	4884.2	4666.2	4194.3	3539.2	2763.3	1899.3
32.5°	5968.0	5881.0	5650.1	5402.8	4940.1	4750.4	4520.5	3975.4	3269.0	2385.8	1397.3
35°	5787.6	5656.6	5378.1	5174.6	4739.5	4544.3	4263.0	3683.0	2864.9	1715.0	655.1
37.5°	5420.2	5292.9	5092.2	4904.3	4480.2	4250.2	3953.4	3276.3	2123.7	935.5	405.0
40°	4980.5	4870.4	4695.5	4513.2	4076.2	3811.4	3484.3	2560.8	1249.7	526.7	249.2
42.5°	4502.2	4388.6	4190.7	3978.1	3501.7	3222.2	2868.6	1657.4	658.7	310.6	135.6
45°	3270.8	3169.1	3025.3	2872.2	2596.5	2394.9	1929.5	870.4	364.6	165.0	66.9
47.5°	2238.3	2117.4	1851.6	1530.1	1240.5	1060.9	798.0	377.5	186.9	82.5	39.4
50°	1228.6	1100.3	964.7	751.3	503.0	413.2	321.6	182.3	84.2	41.2	21.9
52.5°	301.4	266.6	243.7	224.4	177.8	160.4	135.6	76.0	38.5	22.9	15.6
55°	63.2	58.6	55.8	55.0	50.4	48.6	42.1	29.4	21.1	14.6	7.3
57.5°	18.3	17.4	18.3	18.3	18.3	17.4	17.4	12.8	12.0	7.3	4.6
60°	6.5	6.5	6.5	7.3	7.3	7.3	8.2	8.2	6.5	4.6	3.7
62.5°	2.7	2.7	2.7	3.7	3.7	4.6	4.6	4.6	3.7	3.7	2.7
65°	1.8	1.8	1.8	1.8	2.7	2.7	2.7	2.7	2.7	2.7	2.7
67.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7
70°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7
72.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7
75°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	2.7
77.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.8	1.8	1.8	2.7
80°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.8	1.8	1.8	1.8
82.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.8	1.8	1.8
85°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.8	1.8	1.8
87.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.8	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6
2.5°	305.1	295.8	285.0	273.0	271.2	264.8	255.6	242.9	238.2	229.0	220.8
5°	383.0	358.2	332.6	309.7	302.3	292.2	275.8	252.8	238.2	221.8	208.0
7.5°	487.4	430.6	378.3	337.2	324.4	307.8	282.2	252.8	230.9	208.0	189.7
10°	626.7	511.3	421.4	354.6	333.5	311.5	277.6	241.9	216.2	189.7	170.5
12.5°	895.1	629.4	461.8	363.7	334.4	306.0	262.9	224.4	195.1	168.6	149.4
15°	1272.6	853.8	543.3	370.2	325.2	290.5	240.0	200.6	171.3	146.6	128.2
17.5°	1591.4	1066.4	652.3	388.5	318.9	270.3	213.5	173.1	144.8	122.7	108.2
20°	1747.2	1161.7	701.8	391.3	300.6	240.0	182.3	143.8	119.0	100.8	88.0
22.5°	1728.9	1129.7	656.0	342.7	253.8	202.5	151.2	116.4	95.3	80.6	71.4
25°	1606.1	990.4	535.0	262.1	197.9	164.0	118.2	90.7	74.2	64.2	56.8
27.5°	1399.9	795.3	390.3	185.1	150.2	124.6	88.0	69.7	56.8	49.5	45.0
30°	1078.4	508.5	224.4	132.8	109.0	89.0	65.9	50.4	43.0	38.5	34.9
32.5°	556.1	247.4	149.4	95.3	77.0	64.2	45.8	36.6	32.0	29.4	27.4
35°	305.1	175.8	103.5	61.4	49.5	41.2	31.2	25.7	23.8	21.9	21.9
37.5°	209.8	109.0	57.8	36.6	30.2	25.7	21.1	18.3	17.4	17.4	17.4
40°	121.0	57.8	33.0	22.9	19.2	17.4	14.6	13.8	13.8	13.8	14.6
42.5°	62.3	33.9	21.9	15.6	13.8	12.0	10.1	10.1	10.1	11.0	12.0
45°	36.6	22.9	14.6	10.1	9.1	8.2	7.3	7.3	8.2	9.1	10.1
47.5°	22.9	15.6	9.1	6.5	5.5	5.5	5.5	5.5	6.5	7.3	8.2
50°	15.6	8.2	5.5	3.7	3.7	3.7	3.7	4.6	5.5	6.5	7.3
52.5°	8.2	4.6	3.7	2.7	2.7	2.7	3.7	3.7	4.6	5.5	6.5
55°	4.6	3.7	2.7	2.7	2.7	2.7	2.7	3.7	4.6	5.5	6.5
57.5°	3.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.6	5.5
60°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.6	5.5
62.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.6	4.6
65°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	4.6	4.6
67.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	4.6
70°	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	4.6
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7
75°	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7	4.6
77.5°	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7
80°	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7
82.5°	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7
85°	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	2.7	2.7	2.7	2.7	2.7	2.7	3.7	3.7	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6
2.5°	216.2	209.0	201.5	201.5	197.9	192.4	190.6	185.1	181.4	179.6	177.8
5°	197.9	186.9	176.8	175.8	171.3	165.0	162.2	156.6	153.0	151.2	150.2
7.5°	176.8	165.9	155.8	153.9	150.2	145.7	142.9	138.3	136.6	134.7	133.8
10°	156.6	145.7	138.3	136.6	133.8	130.1	127.4	124.6	122.7	121.9	121.9
12.5°	136.6	128.2	121.9	120.0	118.2	115.4	113.6	111.8	110.9	110.9	110.9
15°	118.2	110.9	105.4	105.4	103.5	101.7	101.7	99.8	98.9	99.8	100.8
17.5°	99.8	94.3	89.8	89.8	89.0	88.0	88.0	88.0	89.0	89.8	91.6
20°	82.5	77.9	76.0	76.0	75.1	76.0	76.0	77.0	77.9	80.6	83.4
22.5°	66.9	64.2	62.3	63.2	63.2	64.2	65.0	66.9	68.7	71.4	74.2
25°	54.1	52.2	51.3	52.2	53.1	54.1	55.8	57.8	60.4	63.2	66.9
27.5°	43.0	42.1	42.1	43.0	44.0	45.8	48.6	50.4	53.1	55.8	59.6
30°	34.9	33.9	34.9	36.6	37.5	39.4	41.2	44.0	46.7	49.5	53.1
32.5°	27.4	28.4	29.4	30.2	31.2	33.9	35.8	37.5	40.3	43.0	46.7
35°	22.9	23.8	24.7	25.7	26.6	28.4	30.2	32.0	34.9	37.5	41.2
37.5°	18.3	19.2	20.2	21.9	22.9	23.8	26.6	27.4	30.2	32.0	35.8
40°	15.6	16.6	17.4	18.3	19.2	21.1	22.9	23.8	25.7	28.4	31.2
42.5°	12.8	13.8	14.6	15.6	16.6	18.3	19.2	21.1	22.9	24.7	26.6
45°	11.0	12.0	12.8	13.8	14.6	15.6	16.6	18.3	19.2	21.1	22.9
47.5°	9.1	10.1	12.0	12.0	12.8	13.8	14.6	15.6	17.4	18.3	20.2
50°	8.2	9.1	10.1	11.0	11.0	12.0	12.8	13.8	14.6	15.6	17.4
52.5°	7.3	8.2	9.1	9.1	10.1	11.0	12.0	12.0	12.8	13.8	14.6
55°	6.5	7.3	8.2	8.2	9.1	10.1	10.1	11.0	12.0	12.0	12.8
57.5°	6.5	6.5	7.3	7.3	8.2	8.2	9.1	10.1	10.1	11.0	12.0
60°	5.5	6.5	6.5	7.3	7.3	8.2	8.2	9.1	9.1	10.1	10.1
62.5°	5.5	5.5	6.5	6.5	7.3	7.3	8.2	8.2	8.2	9.1	9.1
65°	5.5	5.5	6.5	6.5	6.5	7.3	7.3	7.3	7.3	8.2	8.2
67.5°	4.6	5.5	5.5	6.5	6.5	6.5	6.5	6.5	7.3	7.3	7.3
70°	4.6	5.5	5.5	5.5	5.5	6.5	6.5	6.5	6.5	6.5	6.5
72.5°	4.6	4.6	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5	5.5
75°	4.6	4.6	4.6	4.6	4.6	5.5	5.5	5.5	5.5	5.5	5.5
77.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6
80°	3.7	3.7	3.7	3.7	3.7	4.6	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	2.7	2.7
85°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	2.7	2.7	2.7	2.7
87.5°	3.7	3.7	3.7	2.7	2.7	2.7	2.7	2.7	2.7	1.8	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212226

CATALOG NUMBER: LDSQA4A20940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	233.6	233.6	233.6	233.6	233.6	233.6	233.6	233.6
2.5°	175.0	173.1	175.0	173.1	173.1	169.5	172.2	170.5
5°	147.4	145.7	147.4	146.6	144.8	143.8	145.7	144.8
7.5°	132.0	130.1	132.0	132.0	130.1	129.2	131.0	130.1
10°	120.0	119.0	120.0	120.0	119.0	118.2	120.0	119.0
12.5°	109.9	109.0	110.9	110.9	109.9	109.9	111.8	109.9
15°	100.8	100.8	102.6	102.6	102.6	102.6	104.4	103.5
17.5°	91.6	93.5	95.3	96.2	96.2	96.2	98.1	98.1
20°	84.2	86.1	88.0	89.0	89.8	89.8	91.6	91.6
22.5°	76.0	77.9	80.6	81.5	82.5	83.4	85.2	85.2
25°	68.7	70.5	73.3	74.2	76.0	77.0	78.8	78.8
27.5°	61.4	64.2	65.9	67.8	68.7	70.5	72.4	72.4
30°	55.0	57.8	59.6	61.4	62.3	64.2	65.9	65.9
32.5°	48.6	51.3	53.1	55.0	56.8	57.8	60.4	60.4
35°	43.0	45.0	47.6	48.6	50.4	52.2	54.1	54.1
37.5°	37.5	39.4	41.2	43.0	45.0	45.8	47.6	48.6
40°	33.0	34.9	36.6	37.5	39.4	41.2	42.1	43.0
42.5°	28.4	30.2	32.0	33.0	34.9	35.8	37.5	37.5
45°	24.7	26.6	27.4	28.4	30.2	31.2	33.0	33.0
47.5°	21.1	22.9	23.8	24.7	25.7	26.6	28.4	28.4
50°	18.3	19.2	20.2	21.1	21.9	23.8	24.7	24.7
52.5°	15.6	17.4	17.4	18.3	19.2	20.2	21.1	21.9
55°	13.8	14.6	15.6	15.6	16.6	17.4	18.3	19.2
57.5°	12.0	12.8	13.8	13.8	14.6	14.6	15.6	16.6
60°	11.0	11.0	12.0	12.0	12.0	12.8	12.8	13.8
62.5°	9.1	9.1	10.1	10.1	10.1	10.1	10.1	10.1
65°	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
67.5°	7.3	7.3	7.3	7.3	6.5	6.5	6.5	6.5
70°	6.5	6.5	6.5	6.5	5.5	5.5	5.5	4.6
72.5°	5.5	5.5	5.5	5.5	4.6	4.6	3.7	3.7
75°	4.6	4.6	4.6	4.6	4.6	3.7	3.7	3.7
77.5°	4.6	3.7	3.7	3.7	3.7	3.7	3.7	2.7
80°	3.7	3.7	2.7	2.7	2.7	2.7	2.7	2.7
82.5°	2.7	2.7	2.7	2.7	1.8	1.8	1.8	1.8
85°	2.7	1.8	1.8	1.8	1.8	1.8	1.8	1.8
87.5°	1.8	1.0	1.0	1.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)