

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212188

Luminaire Tested: **LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1526.6 lumens
Efficiency: N/A
Efficacy: 53.0 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	57	64	60	56	54		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	15955	15955	15955
5°	30574	15209	12350
10°	99983	13477	10506
15°	244855	11133	9277
20°	461340	8495	8320
25°	772282	6029	7290
30°	978324	4139	6208
35°	891431	2673	5263
40°	587074	1922	4477
45°	254318	1274	3699
50°	45108	889	3044
55°	7246	709	2567
60°	1802	659	1957
65°	573	779	1559
70°	482	963	1190
75°	636	936	936
80°	0	1395	948
85°	0	2779	889



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.1	1.4
10°-20°	169.8	11.1
20°-30°	511.5	33.5
30°-40°	582.1	38.1
40°-50°	215.2	14.1
50°-60°	17.1	1.1
60°-70°	4.6	0.3
70°-80°	3.2	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.4	46.0
0°-40°	1284.6	84.1
0°-60°	1516.9	99.4
0°-90°	1526.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1526.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	165	165	165	165	165	
5°	314	231	156	131	127	51
15°	2441	825	111	87	92	766
25°	7225	1206	56	55	68	3298
35°	7538	422	23	31	44	4481
45°	1856	50	9	17	27	1572
55°	43	9	4	10	15	70
65°	2	2	3	7	7	3
75°	2	2	2	4	2	1
85°	0	2	2	2	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7
2.5°	211.8	213.5	211.8	208.6	208.6	204.2	202.6	201.0	196.8	194.2	190.9
5°	314.4	309.4	305.1	295.0	291.8	282.5	275.7	266.6	253.8	243.0	231.2
7.5°	538.1	530.5	514.5	484.2	465.7	443.0	425.4	395.9	358.2	327.0	295.8
10°	1016.4	983.6	945.8	877.7	828.1	775.1	733.1	654.1	559.1	480.9	405.2
12.5°	1637.7	1640.2	1569.6	1454.4	1362.8	1269.4	1197.1	1050.9	882.7	735.6	590.2
15°	2441.4	2395.1	2322.0	2145.5	1962.2	1826.9	1711.6	1489.7	1251.8	1036.6	824.7
17.5°	3288.0	3307.3	3136.6	2848.2	2558.3	2355.6	2181.6	1845.4	1562.9	1296.3	1037.4
20°	4475.0	4342.2	4098.4	3631.0	3180.4	2887.0	2628.9	2192.6	1798.2	1459.4	1168.6
22.5°	5843.8	5629.3	5133.4	4475.0	3793.3	3387.2	3027.4	2427.1	1947.9	1542.7	1213.1
25°	7225.0	7061.1	6270.8	5287.1	4310.2	3784.0	3318.2	2586.0	2019.4	1562.0	1205.6
27.5°	8291.0	8023.7	7123.3	5841.1	4618.9	3997.5	3453.6	2634.7	2004.2	1515.0	1134.1
30°	8745.8	8407.8	7409.9	5967.3	4621.4	3962.2	3386.3	2538.1	1896.6	1395.6	999.5
32.5°	8465.0	8075.0	7068.6	5618.4	4305.2	3686.5	3126.6	2328.8	1718.4	1208.1	750.8
35°	7537.7	7149.4	6217.0	4929.9	3800.8	3260.2	2773.4	2055.6	1463.7	895.4	422.0
37.5°	6172.4	5841.1	5174.6	4132.0	3203.1	2764.2	2359.0	1731.8	1090.4	513.7	211.8
40°	4642.3	4409.5	4009.3	3277.0	2592.7	2259.0	1932.7	1326.6	662.5	258.2	120.2
42.5°	3218.2	3066.9	2865.9	2424.6	2000.0	1770.5	1509.0	886.1	340.5	142.1	74.8
45°	1856.3	1761.3	1705.8	1517.4	1351.9	1240.0	1008.8	477.6	172.3	84.9	49.6
47.5°	819.8	756.6	729.8	650.7	605.3	575.0	456.5	203.4	92.5	54.6	41.2
50°	299.3	299.3	300.2	263.9	216.1	194.2	152.2	89.9	52.1	42.9	30.2
52.5°	106.0	104.2	108.5	102.6	89.9	80.7	67.3	45.4	31.9	27.0	16.9
55°	42.9	41.2	42.9	40.3	37.8	35.4	31.1	24.3	20.2	16.9	9.3
57.5°	19.4	19.4	20.2	19.4	19.4	17.7	16.0	18.5	14.2	9.3	5.9
60°	9.3	9.3	10.1	10.1	10.1	9.3	9.3	10.1	8.4	5.9	4.2
62.5°	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.9	4.2	3.4	2.5
65°	2.5	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
67.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5	2.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	2.5
80°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7
2.5°	187.5	184.9	179.9	177.4	174.0	171.5	169.8	166.5	163.0	160.6	158.9
5°	220.2	211.0	200.1	191.7	184.9	180.7	174.0	168.2	161.4	156.4	152.2
7.5°	268.2	245.4	221.1	204.2	195.0	186.7	174.8	164.7	155.5	148.8	142.9
10°	343.0	294.2	251.4	218.6	202.6	190.9	172.3	158.1	146.3	137.0	131.1
12.5°	467.5	367.4	291.8	236.3	211.8	194.2	168.2	148.8	134.5	125.2	117.8
15°	638.2	475.0	347.3	257.3	222.8	197.6	161.4	137.9	121.9	111.0	104.2
17.5°	798.6	587.6	410.2	282.5	233.7	199.3	152.2	123.5	106.8	96.7	89.9
20°	899.6	660.8	452.3	296.8	237.1	194.2	139.6	108.5	91.6	82.4	75.7
22.5°	923.1	669.3	449.0	283.3	222.8	179.1	121.9	93.3	77.4	69.0	63.0
25°	888.6	622.2	401.8	244.6	190.0	150.5	101.7	75.7	63.8	56.4	52.1
27.5°	802.1	529.7	317.8	184.1	142.1	111.0	77.4	58.9	51.3	45.4	42.9
30°	646.5	372.4	199.3	114.3	90.8	73.1	55.5	45.4	39.5	37.0	34.4
32.5°	391.8	191.7	105.0	68.2	57.2	49.6	40.3	33.6	30.2	28.6	27.8
35°	186.7	100.9	64.7	46.2	40.3	35.4	29.4	25.3	23.5	22.6	22.6
37.5°	106.0	65.6	43.7	31.1	27.8	24.3	21.8	19.4	18.5	18.5	18.5
40°	67.3	42.0	28.6	22.6	20.2	18.5	16.9	15.2	15.2	15.2	15.2
42.5°	43.7	30.2	21.8	16.9	15.2	14.2	12.6	11.8	11.8	11.8	12.6
45°	34.4	25.3	17.7	13.4	11.8	10.9	10.1	9.3	9.3	9.3	10.1
47.5°	29.4	17.7	11.8	9.3	7.6	7.6	6.8	6.8	6.8	7.6	8.4
50°	17.7	10.9	7.6	5.9	5.1	5.1	5.1	5.1	5.1	5.9	6.8
52.5°	10.1	6.8	5.1	4.2	3.4	3.4	3.4	3.4	4.2	5.1	5.1
55°	6.8	5.1	3.4	3.4	2.5	2.5	2.5	3.4	3.4	4.2	5.1
57.5°	4.2	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4	4.2	4.2
60°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
62.5°	2.5	2.5	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
65°	2.5	2.5	3.4	3.4	2.5	2.5	2.5	2.5	2.5	3.4	4.2
67.5°	2.5	2.5	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4	3.4
70°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	3.4	3.4
72.5°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	3.4	3.4
75°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4
77.5°	2.5	2.5	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	3.4
80°	2.5	2.5	2.5	3.4	2.5	3.4	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7
2.5°	156.4	154.6	152.2	151.4	152.2	151.4	147.2	146.3	144.6	144.6	144.6
5°	148.0	145.4	142.1	140.4	140.4	138.7	134.5	133.6	131.1	131.1	130.3
7.5°	137.9	134.5	130.3	128.6	128.6	127.0	122.7	121.0	119.4	119.4	118.6
10°	126.2	121.9	117.8	116.9	116.1	113.4	111.0	110.2	107.7	108.5	107.7
12.5°	112.6	109.3	106.0	104.2	104.2	101.7	100.1	99.2	98.4	98.4	98.4
15°	100.1	95.9	92.5	91.6	91.6	90.8	89.1	89.1	87.4	89.1	89.1
17.5°	85.8	82.4	81.5	79.8	80.7	79.8	78.2	79.0	79.0	79.8	80.7
20°	72.3	69.8	69.0	68.2	69.0	69.0	68.2	69.0	69.8	72.3	73.9
22.5°	60.6	58.9	58.9	58.0	58.9	59.7	58.9	60.6	62.2	63.8	66.5
25°	50.4	49.6	49.6	49.6	50.4	51.3	52.1	53.8	54.6	57.2	58.9
27.5°	41.2	41.2	41.2	42.0	42.9	43.7	44.5	47.1	47.9	50.4	52.1
30°	34.4	33.6	34.4	35.4	36.2	37.8	38.7	40.3	41.2	43.7	45.4
32.5°	27.8	28.6	29.4	30.2	31.1	31.9	32.8	34.4	36.2	37.8	39.5
35°	23.5	23.5	24.3	25.3	26.1	27.8	28.6	29.4	31.1	32.8	33.6
37.5°	19.4	20.2	21.0	21.8	22.6	23.5	24.3	25.3	26.1	27.8	29.4
40°	16.0	16.9	17.7	18.5	18.5	20.2	20.2	21.8	22.6	24.3	26.1
42.5°	13.4	14.2	15.2	16.0	16.0	16.9	17.7	18.5	19.4	21.0	22.6
45°	10.9	11.8	12.6	13.4	13.4	14.2	15.2	16.0	16.9	18.5	19.4
47.5°	9.3	10.1	10.9	11.8	11.8	12.6	13.4	14.2	14.2	16.0	16.9
50°	7.6	8.4	9.3	10.1	10.1	10.9	11.8	12.6	12.6	13.4	14.2
52.5°	5.9	6.8	8.4	8.4	9.3	10.1	10.1	10.9	10.9	11.8	12.6
55°	5.9	6.8	7.6	7.6	8.4	9.3	9.3	10.1	10.1	10.1	10.9
57.5°	5.1	5.9	6.8	7.6	7.6	8.4	8.4	8.4	8.4	9.3	9.3
60°	5.1	5.9	5.9	6.8	6.8	7.6	7.6	7.6	7.6	8.4	8.4
62.5°	5.1	5.1	5.9	5.9	6.8	6.8	6.8	7.6	7.6	7.6	7.6
65°	4.2	5.1	5.9	5.9	5.9	6.8	6.8	6.8	6.8	6.8	6.8
67.5°	4.2	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
70°	4.2	4.2	5.1	5.1	5.1	5.9	5.9	5.9	5.1	5.9	5.1
72.5°	3.4	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
75°	3.4	4.2	4.2	4.2	4.2	5.1	5.1	4.2	4.2	4.2	4.2
77.5°	3.4	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.4
80°	3.4	3.4	3.4	3.4	4.2	4.2	3.4	3.4	3.4	3.4	3.4
82.5°	2.5	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5
85°	2.5	2.5	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5	1.7
87.5°	2.5	2.5	2.5	3.4	2.5	2.5	2.5	2.5	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212188

CATALOG NUMBER: LDSQA4A20930D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	164.7	164.7	164.7	164.7	164.7	164.7	164.7	164.7
2.5°	142.1	141.2	142.1	141.2	141.2	142.1	139.6	141.2
5°	128.6	127.0	127.8	127.0	126.2	127.0	125.2	127.0
7.5°	116.9	116.1	116.1	116.1	115.1	116.1	114.3	116.1
10°	106.8	106.0	106.0	106.0	106.0	106.8	105.0	106.8
12.5°	96.7	96.7	97.5	96.7	97.5	98.4	96.7	98.4
15°	88.3	89.1	89.9	89.9	90.8	91.6	90.8	92.5
17.5°	81.5	82.4	84.0	84.0	84.9	86.6	85.8	87.4
20°	74.8	75.7	77.4	77.4	78.2	79.8	79.0	80.7
22.5°	67.3	69.0	69.8	70.6	71.4	73.1	72.3	73.9
25°	59.7	62.2	63.0	63.8	64.7	66.5	66.5	68.2
27.5°	53.8	55.5	56.4	57.2	58.9	60.6	60.6	61.4
30°	47.1	48.8	50.4	51.3	52.1	53.8	53.8	55.5
32.5°	41.2	42.9	43.7	44.5	46.2	47.9	48.8	49.6
35°	35.4	37.8	38.7	40.3	41.2	43.7	43.7	44.5
37.5°	31.1	32.8	34.4	35.4	37.0	38.7	38.7	40.3
40°	27.8	29.4	30.2	31.1	32.8	34.4	34.4	35.4
42.5°	23.5	26.1	27.0	27.8	28.6	30.2	31.1	31.9
45°	21.0	21.8	22.6	23.5	24.3	26.1	26.1	27.0
47.5°	17.7	18.5	19.4	20.2	21.0	21.8	22.6	23.5
50°	15.2	16.0	16.9	16.9	17.7	19.4	19.4	20.2
52.5°	12.6	13.4	14.2	14.2	15.2	16.9	16.9	17.7
55°	10.9	11.8	12.6	12.6	13.4	14.2	14.2	15.2
57.5°	10.1	10.1	10.9	10.9	11.8	11.8	12.6	12.6
60°	8.4	9.3	9.3	9.3	10.1	10.1	10.1	10.1
62.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	8.4
65°	6.8	6.8	6.8	6.8	6.8	6.8	5.9	6.8
67.5°	5.9	5.9	5.9	5.9	5.1	5.1	5.1	5.1
70°	5.1	5.1	5.1	5.1	5.1	4.2	4.2	4.2
72.5°	4.2	4.2	4.2	4.2	4.2	3.4	3.4	3.4
75°	4.2	4.2	3.4	3.4	3.4	3.4	3.4	2.5
77.5°	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
80°	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7
82.5°	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7
85°	1.7	1.7	1.7	1.7	0.8	0.8	0.8	0.8
87.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)