

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212200

Luminaire Tested: **LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1706.4 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20441	20441	20441
5°	47903	19294	13488
10°	189283	16949	11244
15°	350303	13570	9869
20°	449175	9876	8928
25°	537423	7001	7899
30°	571448	4609	6958
35°	585662	2779	6067
40°	536110	1796	5210
45°	386854	1274	4261
50°	168887	1025	3542
55°	11654	844	2989
60°	2112	814	2441
65°	779	779	1742
70°	708	963	1190
75°	636	1273	1273
80°	0	1897	1395
85°	0	3779	889

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.7	1.8
10°-20°	241.5	14.2
20°-30°	505.7	29.6
30°-40°	562.9	33.0
40°-50°	323.1	18.9
50°-60°	32.3	1.9
60°-70°	5.1	0.3
70°-80°	3.2	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.9	45.6
0°-40°	1340.8	78.6
0°-60°	1696.2	99.4
0°-90°	1706.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1706.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	211	211	211	211	211	
5°	493	340	198	145	139	90
15°	3493	1395	135	95	98	987
25°	5028	1919	66	58	74	2277
35°	4952	586	24	34	51	3024
45°	2824	71	9	18	31	2156
55°	69	10	5	11	18	206
65°	3	2	3	7	8	4
75°	2	2	3	4	3	1
85°	0	2	3	2	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0
2.5°	315.2	308.5	301.8	297.5	293.4	299.3	295.0	293.4	281.6	275.7	270.7
5°	492.6	480.0	461.5	446.4	431.3	434.6	422.9	408.5	379.0	358.1	339.7
7.5°	950.8	919.7	862.5	807.0	751.5	741.4	704.5	640.6	558.2	496.0	442.2
10°	1924.2	1830.1	1725.0	1611.5	1478.6	1441.7	1350.0	1176.9	987.7	771.7	615.4
12.5°	2840.5	2797.6	2674.1	2526.9	2383.2	2294.9	2199.9	1914.1	1614.0	1266.0	975.1
15°	3492.8	3466.7	3358.2	3224.6	3070.0	3012.8	2896.8	2611.8	2232.6	1816.6	1394.6
17.5°	3976.2	3931.6	3818.2	3672.6	3489.4	3440.7	3302.0	3018.7	2625.3	2207.5	1739.3
20°	4357.0	4329.2	4182.2	4007.2	3787.9	3729.0	3566.8	3271.8	2843.8	2400.0	1923.4
22.5°	4699.1	4652.0	4471.3	4262.9	4012.3	3949.3	3768.6	3444.9	2985.1	2490.8	1956.2
25°	5027.8	4956.3	4736.9	4463.7	4169.4	4083.8	3885.4	3542.5	3037.2	2498.4	1919.1
27.5°	5123.7	5087.4	4884.9	4567.2	4226.6	4130.1	3923.2	3564.3	3017.8	2429.4	1786.3
30°	5108.5	5078.2	4909.2	4577.3	4216.6	4114.9	3904.6	3497.0	2905.3	2249.5	1551.8
32.5°	5060.6	5048.8	4844.6	4489.8	4122.5	4011.5	3784.5	3329.8	2694.2	1975.5	1134.0
35°	4952.2	4905.9	4651.2	4317.4	3964.4	3842.5	3586.2	3090.2	2415.9	1438.3	585.9
37.5°	4634.3	4598.2	4397.4	4104.8	3761.0	3604.6	3333.9	2780.7	1870.4	817.9	350.6
40°	4239.3	4221.7	4063.6	3802.2	3434.8	3258.3	2964.0	2275.6	1141.6	464.9	231.2
42.5°	3834.1	3829.0	3660.1	3386.9	2988.5	2785.8	2480.7	1535.0	607.0	280.8	133.6
45°	2823.7	2854.0	2736.2	2572.3	2268.0	2120.9	1725.0	791.0	349.8	155.5	70.6
47.5°	1980.5	1946.9	1738.5	1451.8	1173.5	993.6	751.5	374.1	186.6	81.5	40.3
50°	1120.6	1126.4	938.2	759.1	497.7	394.2	299.3	188.3	89.9	42.9	24.3
52.5°	292.6	306.0	263.9	227.0	193.4	157.3	127.0	81.5	42.9	25.2	16.0
55°	69.0	71.4	66.5	62.2	58.9	52.1	46.2	35.3	23.5	16.0	10.1
57.5°	24.3	25.2	24.3	24.3	23.5	22.6	21.0	18.5	14.2	10.1	6.8
60°	10.9	11.8	10.9	11.8	11.8	11.8	11.8	11.8	8.4	5.9	4.2
62.5°	5.0	5.0	5.0	5.0	5.9	5.9	6.8	6.8	5.0	4.2	3.4
65°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
70°	2.5	2.5	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7
80°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0
2.5°	261.4	260.6	251.4	244.6	241.3	236.2	230.4	221.9	212.6	204.2	201.0
5°	317.8	306.8	287.4	271.5	263.9	256.3	243.0	227.8	213.5	198.4	190.9
7.5°	391.0	358.9	321.1	291.8	279.1	266.5	247.1	226.1	206.7	186.6	175.7
10°	490.9	417.0	351.4	304.3	285.8	269.0	241.3	215.2	194.2	172.3	158.1
12.5°	701.9	518.6	383.4	310.2	285.8	263.9	230.4	200.1	176.5	153.8	140.4
15°	1011.3	700.2	453.1	316.1	280.0	252.2	213.5	180.7	155.5	135.3	122.7
17.5°	1260.9	867.6	539.7	331.2	272.4	236.2	191.7	157.3	133.6	115.1	105.0
20°	1387.0	938.2	579.2	333.8	253.8	211.0	165.6	132.8	111.8	95.8	87.4
22.5°	1384.6	915.4	543.9	292.6	222.8	182.4	139.6	109.3	92.5	79.8	73.1
25°	1297.1	810.4	453.9	233.7	179.9	151.4	113.4	88.3	74.8	65.5	59.7
27.5°	1133.2	658.2	338.7	173.1	140.4	119.4	88.3	70.6	59.7	53.0	48.8
30°	889.4	440.5	213.5	128.6	106.8	89.9	68.2	54.6	47.1	41.2	38.7
32.5°	490.1	229.5	143.8	94.1	78.2	65.5	50.4	39.5	34.4	30.2	29.4
35°	270.7	162.2	102.6	63.0	52.1	44.5	34.4	28.6	25.2	23.5	23.5
37.5°	191.7	104.2	61.4	39.5	33.6	29.4	23.5	20.2	19.4	18.5	18.5
40°	115.1	61.4	37.0	26.1	22.6	20.2	17.7	15.0	15.0	14.2	15.0
42.5°	63.0	37.0	25.2	18.5	16.0	15.0	12.6	11.8	11.8	11.8	12.6
45°	37.8	24.3	17.7	13.4	11.8	10.1	9.3	8.4	9.3	9.3	10.1
47.5°	24.3	17.7	11.8	8.4	7.6	6.8	5.9	6.8	6.8	7.6	8.4
50°	16.9	10.9	7.6	5.0	5.0	4.2	5.0	5.0	5.9	6.8	7.6
52.5°	10.9	7.6	5.0	4.2	3.4	3.4	3.4	4.2	5.0	5.9	6.8
55°	6.8	5.0	4.2	3.4	3.4	3.4	3.4	3.4	4.2	5.0	5.9
57.5°	5.0	4.2	3.4	2.5	2.5	2.5	3.4	3.4	4.2	4.2	5.0
60°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.0
62.5°	3.4	3.4	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2	4.2
65°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
77.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
80°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
82.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
85°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
87.5°	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0
2.5°	196.6	190.9	185.8	187.4	184.1	178.2	176.5	172.3	167.4	166.4	166.4
5°	182.4	173.1	165.6	164.7	161.4	154.6	153.0	148.8	144.6	143.8	142.9
7.5°	164.7	154.6	148.0	146.2	143.8	137.9	137.0	132.8	130.3	128.6	128.6
10°	147.2	137.9	132.0	131.1	129.4	124.4	123.5	120.2	117.8	116.9	116.0
12.5°	130.3	122.7	117.8	116.9	115.1	111.0	110.2	107.7	105.8	105.0	105.0
15°	114.3	107.7	103.4	102.6	101.7	97.5	97.5	95.8	95.0	95.0	95.8
17.5°	98.4	92.5	89.1	88.3	88.3	84.9	85.7	84.9	84.9	84.9	86.6
20°	82.4	77.4	74.8	75.6	73.9	73.1	73.9	73.9	73.9	75.6	78.2
22.5°	69.0	64.7	62.2	63.0	63.0	62.2	63.0	63.8	65.5	68.2	70.6
25°	56.4	53.0	52.1	53.0	53.0	53.0	54.6	56.4	58.0	60.6	63.0
27.5°	45.4	42.9	42.9	43.7	44.5	44.5	47.1	48.8	51.3	53.8	56.4
30°	36.2	35.3	35.3	37.0	37.0	37.8	41.2	42.9	44.5	47.1	49.6
32.5°	28.6	28.6	29.4	31.1	31.1	32.8	35.3	37.0	38.7	41.2	43.7
35°	23.5	24.3	25.2	26.1	27.0	27.8	30.2	31.9	33.6	36.2	37.8
37.5°	19.4	20.2	21.0	22.6	22.6	23.5	26.1	27.8	28.6	31.1	33.6
40°	16.0	16.9	17.7	19.4	19.4	20.2	22.6	23.5	24.3	27.0	29.4
42.5°	13.4	14.2	15.0	16.0	16.9	17.7	19.4	20.2	21.8	23.5	25.2
45°	10.9	11.8	12.6	13.4	14.2	15.0	16.0	17.7	18.5	20.2	21.8
47.5°	9.3	10.1	10.9	11.8	12.6	12.6	14.2	15.0	16.0	17.7	19.4
50°	8.4	9.3	10.1	10.1	10.9	11.8	12.6	13.4	14.2	15.0	16.9
52.5°	6.8	7.6	8.4	9.3	9.3	10.1	10.9	11.8	12.6	13.4	14.2
55°	6.8	6.8	7.6	8.4	8.4	9.3	10.1	10.9	10.9	11.8	12.6
57.5°	5.9	6.8	6.8	7.6	7.6	8.4	9.3	9.3	10.1	10.1	10.9
60°	5.0	5.9	6.8	6.8	6.8	7.6	7.6	8.4	8.4	9.3	9.3
62.5°	5.0	5.9	5.9	6.8	6.8	6.8	7.6	7.6	7.6	8.4	8.4
65°	5.0	5.0	5.9	5.9	5.9	5.9	6.8	6.8	6.8	7.6	7.6
67.5°	4.2	5.0	5.0	5.0	5.9	5.9	5.9	5.9	5.9	6.8	6.8
70°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
72.5°	4.2	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0
75°	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
77.5°	3.4	3.4	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
85°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212200

CATALOG NUMBER: LDSQA4A20930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	211.0	211.0	211.0	211.0	211.0	211.0	211.0	211.0
2.5°	163.0	161.4	160.6	163.0	159.8	161.4	160.6	161.4
5°	140.4	138.7	137.9	140.4	137.0	138.7	137.0	138.7
7.5°	126.1	125.2	124.4	126.1	123.5	125.2	124.4	125.2
10°	114.3	113.4	112.6	115.1	112.6	114.3	113.4	114.3
12.5°	104.2	104.2	103.4	105.0	103.4	105.0	104.2	105.0
15°	95.0	95.8	95.0	96.7	95.8	97.5	96.7	98.4
17.5°	87.4	88.3	88.3	90.8	89.9	92.5	91.6	92.5
20°	79.8	80.7	81.5	83.2	83.2	85.7	84.9	86.6
22.5°	72.3	73.9	73.9	76.6	76.6	79.0	79.0	79.8
25°	64.7	67.3	68.2	69.8	70.6	73.1	73.1	73.9
27.5°	58.9	60.6	61.4	63.8	64.7	67.3	67.3	69.0
30°	52.1	54.6	55.4	57.2	58.0	60.6	60.6	62.2
32.5°	46.2	47.9	49.6	51.3	52.1	54.6	54.6	56.4
35°	40.3	42.9	43.7	45.4	47.1	49.6	49.6	51.3
37.5°	35.3	37.8	38.7	40.3	42.0	44.5	44.5	46.2
40°	31.1	33.6	34.4	36.2	37.0	40.3	40.3	41.2
42.5°	27.8	29.4	30.2	31.9	32.8	34.4	34.4	36.2
45°	23.5	25.2	26.1	27.0	28.6	30.2	30.2	31.1
47.5°	20.2	21.8	22.6	23.5	24.3	26.1	26.1	27.8
50°	17.7	18.5	19.4	20.2	21.0	22.6	22.6	23.5
52.5°	15.0	16.0	16.9	17.7	18.5	19.4	20.2	21.0
55°	13.4	14.2	14.2	15.0	16.0	16.9	16.9	17.7
57.5°	11.8	12.6	12.6	12.6	13.4	14.2	14.2	15.0
60°	10.1	10.9	10.9	10.9	11.8	11.8	11.8	12.6
62.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
65°	7.6	7.6	7.6	7.6	7.6	7.6	6.8	7.6
67.5°	6.8	6.8	6.8	5.9	5.9	5.9	5.9	5.9
70°	5.9	5.9	5.9	5.0	5.0	5.0	4.2	4.2
72.5°	5.0	5.0	5.0	4.2	4.2	4.2	3.4	3.4
75°	4.2	4.2	4.2	4.2	3.4	3.4	3.4	3.4
77.5°	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
80°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	1.7	1.7	1.7	1.7
85°	1.7	1.7	1.7	1.7	1.7	1.7	0.8	0.8
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)