

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219537

Luminaire Tested: **LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2082.2 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23531	23531	23531
5°	61906	22435	14645
10°	242669	19408	12178
15°	446754	15295	10792
20°	561381	10804	9825
25°	671484	7140	8765
30°	706141	4474	7663
35°	711837	2696	6658
40°	655035	1821	5653
45°	466028	1302	4699
50°	192564	1025	3873
55°	11097	963	3378
60°	1318	930	2790
65°	436	1100	1948
70°	538	1076	1360
75°	711	1422	1422
80°	0	2120	1562
85°	0	4224	2112

TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.2	1.8
10°-20°	305.1	14.7
20°-30°	631.1	30.3
30°-40°	687.0	33.0
40°-50°	376.7	18.1
50°-60°	32.6	1.6
60°-70°	5.3	0.3
70°-80°	3.8	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	974.4	46.8
0°-40°	1661.4	79.8
0°-60°	2070.7	99.4
0°-90°	2082.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2082.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	243	243	243	243	243	
5°	637	435	231	159	151	116
15°	4454	1872	152	103	108	1244
25°	6282	2491	67	63	82	2837
35°	6019	681	23	36	56	3694
45°	3402	70	10	20	34	2596
55°	66	8	6	12	20	225
65°	2	3	5	8	8	3
75°	2	3	4	6	4	1
85°	0	2	4	3	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9
2.5°	382.1	368.8	366.9	368.8	359.2	358.3	360.2	352.6	345.9	339.2	333.4
5°	636.6	608.8	600.3	588.8	560.2	550.8	548.8	518.3	488.8	461.1	435.4
7.5°	1236.9	1181.5	1152.0	1094.8	1007.2	968.0	947.1	847.2	753.6	668.8	591.8
10°	2466.9	2322.1	2251.6	2143.9	1952.4	1858.1	1789.4	1538.0	1290.1	1052.0	842.3
12.5°	3599.9	3519.8	3416.0	3358.8	3048.2	2929.0	2815.7	2466.9	2089.6	1704.6	1322.6
15°	4454.5	4337.3	4226.8	4200.1	3956.2	3817.0	3691.3	3330.2	2881.4	2391.7	1872.3
17.5°	4956.6	4872.8	4768.0	4717.5	4431.6	4319.2	4176.3	3826.6	3390.2	2902.3	2299.1
20°	5445.4	5321.6	5174.0	5097.7	4781.3	4651.7	4489.7	4121.9	3659.8	3141.4	2538.4
22.5°	5892.3	5732.3	5522.6	5404.5	5049.2	4906.1	4725.1	4326.8	3826.6	3234.0	2558.4
25°	6282.0	6137.2	5858.0	5651.3	5232.0	5063.3	4852.8	4436.4	3886.6	3226.3	2490.7
27.5°	6356.3	6259.2	6008.6	5769.5	5295.9	5108.2	4890.0	4459.3	3844.7	3120.5	2308.6
30°	6312.6	6207.8	6006.7	5762.7	5269.3	5079.6	4852.8	4362.1	3680.8	2873.8	1975.3
32.5°	6206.7	6116.2	5876.1	5618.9	5137.7	4940.4	4701.3	4134.4	3399.8	2481.2	1453.2
35°	6019.1	5882.9	5593.2	5381.6	4929.1	4726.1	4433.5	3830.3	2979.5	1783.6	681.3
37.5°	5637.0	5504.6	5295.9	5100.5	4659.4	4420.2	4111.5	3407.4	2208.6	972.9	421.2
40°	5179.7	5065.2	4883.3	4693.7	4239.2	3963.9	3623.7	2663.2	1299.7	547.8	259.2
42.5°	4682.3	4564.1	4358.3	4137.2	3641.8	3351.1	2983.3	1723.7	685.0	323.0	141.0
45°	3401.6	3295.9	3146.3	2987.1	2700.4	2490.7	2006.7	905.2	379.2	171.6	69.6
47.5°	2327.8	2202.1	1925.7	1591.3	1290.1	1103.3	829.9	392.6	194.4	85.8	41.0
50°	1277.7	1144.3	1003.3	781.4	523.1	429.7	334.5	189.6	87.6	42.8	22.8
52.5°	313.5	277.3	253.4	233.4	184.9	166.8	141.0	79.0	40.0	23.8	16.2
55°	65.7	60.9	58.0	57.2	52.4	50.5	43.8	30.6	21.9	15.2	7.6
57.5°	19.0	18.1	19.0	19.0	19.0	18.1	18.1	13.3	12.5	7.6	4.8
60°	6.8	6.8	6.8	7.6	7.6	7.6	8.5	8.5	6.8	4.8	3.8
62.5°	2.8	2.8	2.8	3.8	3.8	4.8	4.8	4.8	3.8	3.8	2.8
65°	1.9	1.9	1.9	1.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8
67.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8
70°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8
72.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8
77.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.8
80°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	1.9
82.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
85°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
87.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9
2.5°	317.3	307.6	296.4	283.9	282.0	275.4	265.8	252.6	247.7	238.2	229.6
5°	398.3	372.5	345.9	322.1	314.4	303.9	286.8	262.9	247.7	230.7	216.3
7.5°	506.9	447.8	393.4	350.7	337.4	320.1	293.5	262.9	240.1	216.3	197.3
10°	651.8	531.8	438.3	368.8	346.8	324.0	288.7	251.6	224.8	197.3	177.3
12.5°	930.9	654.6	480.3	378.2	347.8	318.2	273.4	233.4	202.9	175.3	155.4
15°	1323.5	888.0	565.0	385.0	338.2	302.1	249.6	208.6	178.2	152.5	133.3
17.5°	1655.1	1109.1	678.4	404.0	331.7	281.1	222.0	180.0	150.6	127.6	112.5
20°	1817.1	1208.2	729.9	407.0	312.6	249.6	189.6	149.6	123.8	104.8	91.5
22.5°	1798.1	1174.9	682.2	356.4	264.0	210.6	157.2	121.1	99.1	83.8	74.3
25°	1670.3	1030.0	556.4	272.6	205.8	170.6	122.9	94.3	77.2	66.8	59.1
27.5°	1455.9	827.1	405.9	192.5	156.2	129.6	91.5	72.5	59.1	51.5	46.8
30°	1121.5	528.8	233.4	138.1	113.4	92.6	68.5	52.4	44.7	40.0	36.3
32.5°	578.3	257.3	155.4	99.1	80.1	66.8	47.6	38.1	33.3	30.6	28.5
35°	317.3	182.8	107.6	63.9	51.5	42.8	32.4	26.7	24.8	22.8	22.8
37.5°	218.2	113.4	60.1	38.1	31.4	26.7	21.9	19.0	18.1	18.1	18.1
40°	125.8	60.1	34.3	23.8	20.0	18.1	15.2	14.4	14.4	14.4	15.2
42.5°	64.8	35.3	22.8	16.2	14.4	12.5	10.5	10.5	10.5	11.4	12.5
45°	38.1	23.8	15.2	10.5	9.5	8.5	7.6	7.6	8.5	9.5	10.5
47.5°	23.8	16.2	9.5	6.8	5.7	5.7	5.7	5.7	6.8	7.6	8.5
50°	16.2	8.5	5.7	3.8	3.8	3.8	3.8	4.8	5.7	6.8	7.6
52.5°	8.5	4.8	3.8	2.8	2.8	2.8	3.8	3.8	4.8	5.7	6.8
55°	4.8	3.8	2.8	2.8	2.8	2.8	2.8	3.8	4.8	5.7	6.8
57.5°	3.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	5.7
60°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	5.7
62.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	4.8
65°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	4.8
67.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	4.8
70°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	4.8
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8
75°	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	4.8
77.5°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8
80°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8
82.5°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8
85°	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9
2.5°	224.8	217.4	209.6	209.6	205.8	200.1	198.2	192.5	188.7	186.8	184.9
5°	205.8	194.4	183.9	182.8	178.2	171.6	168.7	162.9	159.1	157.2	156.2
7.5°	183.9	172.5	162.0	160.1	156.2	151.5	148.6	143.8	142.1	140.1	139.2
10°	162.9	151.5	143.8	142.1	139.2	135.3	132.5	129.6	127.6	126.8	126.8
12.5°	142.1	133.3	126.8	124.8	122.9	120.0	118.1	116.3	115.3	115.3	115.3
15°	122.9	115.3	109.6	109.6	107.6	105.8	105.8	103.8	102.9	103.8	104.8
17.5°	103.8	98.1	93.4	93.4	92.6	91.5	91.5	91.5	92.6	93.4	95.3
20°	85.8	81.0	79.0	79.0	78.1	79.0	79.0	80.1	81.0	83.8	86.7
22.5°	69.6	66.8	64.8	65.7	65.7	66.8	67.6	69.6	71.4	74.3	77.2
25°	56.3	54.3	53.4	54.3	55.2	56.3	58.0	60.1	62.8	65.7	69.6
27.5°	44.7	43.8	43.8	44.7	45.8	47.6	50.5	52.4	55.2	58.0	62.0
30°	36.3	35.3	36.3	38.1	39.0	41.0	42.8	45.8	48.6	51.5	55.2
32.5°	28.5	29.5	30.6	31.4	32.4	35.3	37.2	39.0	41.9	44.7	48.6
35°	23.8	24.8	25.7	26.7	27.7	29.5	31.4	33.3	36.3	39.0	42.8
37.5°	19.0	20.0	21.0	22.8	23.8	24.8	27.7	28.5	31.4	33.3	37.2
40°	16.2	17.3	18.1	19.0	20.0	21.9	23.8	24.8	26.7	29.5	32.4
42.5°	13.3	14.4	15.2	16.2	17.3	19.0	20.0	21.9	23.8	25.7	27.7
45°	11.4	12.5	13.3	14.4	15.2	16.2	17.3	19.0	20.0	21.9	23.8
47.5°	9.5	10.5	12.5	12.5	13.3	14.4	15.2	16.2	18.1	19.0	21.0
50°	8.5	9.5	10.5	11.4	11.4	12.5	13.3	14.4	15.2	16.2	18.1
52.5°	7.6	8.5	9.5	9.5	10.5	11.4	12.5	12.5	13.3	14.4	15.2
55°	6.8	7.6	8.5	8.5	9.5	10.5	10.5	11.4	12.5	12.5	13.3
57.5°	6.8	6.8	7.6	7.6	8.5	8.5	9.5	10.5	10.5	11.4	12.5
60°	5.7	6.8	6.8	7.6	7.6	8.5	8.5	9.5	9.5	10.5	10.5
62.5°	5.7	5.7	6.8	6.8	7.6	7.6	8.5	8.5	8.5	9.5	9.5
65°	5.7	5.7	6.8	6.8	6.8	7.6	7.6	7.6	7.6	8.5	8.5
67.5°	4.8	5.7	5.7	6.8	6.8	6.8	6.8	6.8	7.6	7.6	7.6
70°	4.8	5.7	5.7	5.7	5.7	6.8	6.8	6.8	6.8	6.8	6.8
72.5°	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7
75°	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7
77.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
80°	3.8	3.8	3.8	3.8	3.8	4.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8	2.8	2.8
87.5°	3.8	3.8	3.8	2.8	2.8	2.8	2.8	2.8	2.8	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219537

CATALOG NUMBER: LDSQA4A20950D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	242.9	242.9	242.9	242.9	242.9	242.9	242.9	242.9
2.5°	182.0	180.0	182.0	180.0	180.0	176.3	179.1	177.3
5°	153.3	151.5	153.3	152.5	150.6	149.6	151.5	150.6
7.5°	137.3	135.3	137.3	137.3	135.3	134.4	136.2	135.3
10°	124.8	123.8	124.8	124.8	123.8	122.9	124.8	123.8
12.5°	114.3	113.4	115.3	115.3	114.3	114.3	116.3	114.3
15°	104.8	104.8	106.7	106.7	106.7	106.7	108.6	107.6
17.5°	95.3	97.2	99.1	100.0	100.0	100.0	102.0	102.0
20°	87.6	89.5	91.5	92.6	93.4	93.4	95.3	95.3
22.5°	79.0	81.0	83.8	84.8	85.8	86.7	88.6	88.6
25°	71.4	73.3	76.2	77.2	79.0	80.1	82.0	82.0
27.5°	63.9	66.8	68.5	70.5	71.4	73.3	75.3	75.3
30°	57.2	60.1	62.0	63.9	64.8	66.8	68.5	68.5
32.5°	50.5	53.4	55.2	57.2	59.1	60.1	62.8	62.8
35°	44.7	46.8	49.5	50.5	52.4	54.3	56.3	56.3
37.5°	39.0	41.0	42.8	44.7	46.8	47.6	49.5	50.5
40°	34.3	36.3	38.1	39.0	41.0	42.8	43.8	44.7
42.5°	29.5	31.4	33.3	34.3	36.3	37.2	39.0	39.0
45°	25.7	27.7	28.5	29.5	31.4	32.4	34.3	34.3
47.5°	21.9	23.8	24.8	25.7	26.7	27.7	29.5	29.5
50°	19.0	20.0	21.0	21.9	22.8	24.8	25.7	25.7
52.5°	16.2	18.1	18.1	19.0	20.0	21.0	21.9	22.8
55°	14.4	15.2	16.2	16.2	17.3	18.1	19.0	20.0
57.5°	12.5	13.3	14.4	14.4	15.2	15.2	16.2	17.3
60°	11.4	11.4	12.5	12.5	12.5	13.3	13.3	14.4
62.5°	9.5	9.5	10.5	10.5	10.5	10.5	10.5	10.5
65°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
67.5°	7.6	7.6	7.6	7.6	6.8	6.8	6.8	6.8
70°	6.8	6.8	6.8	6.8	5.7	5.7	5.7	4.8
72.5°	5.7	5.7	5.7	5.7	4.8	4.8	3.8	3.8
75°	4.8	4.8	4.8	4.8	4.8	3.8	3.8	3.8
77.5°	4.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8
80°	3.8	3.8	2.8	2.8	2.8	2.8	2.8	2.8
82.5°	2.8	2.8	2.8	2.8	1.9	1.9	1.9	1.9
85°	2.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9
87.5°	1.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)