

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212212

Luminaire Tested: **LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1854.3 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20964	20964	20964
5°	55119	19964	13041
10°	216109	17284	10850
15°	397862	13610	9618
20°	499938	9619	8753
25°	597997	6349	7803
30°	628844	3993	6824
35°	633914	2413	5913
40°	583331	1606	5033
45°	415022	1178	4192
50°	171479	889	3451
55°	9897	861	3006
60°	1143	814	2461
65°	390	963	1742
70°	482	963	1190
75°	636	1273	1273
80°	0	1897	1395
85°	0	3779	1890

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	1.8
10°-20°	271.7	14.7
20°-30°	562.0	30.3
30°-40°	611.8	33.0
40°-50°	335.5	18.1
50°-60°	29.0	1.6
60°-70°	4.7	0.3
70°-80°	3.4	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	867.7	46.8
0°-40°	1479.6	79.8
0°-60°	1844.1	99.4
0°-90°	1854.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1854.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	216	216	216	216	216	
5°	567	388	205	142	134	103
15°	3967	1667	136	92	96	1108
25°	5594	2218	59	56	73	2526
35°	5360	607	20	32	50	3290
45°	3029	62	9	18	31	2312
55°	59	7	5	11	18	200
65°	2	2	4	7	8	2
75°	2	2	3	5	3	1
85°	0	2	3	2	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4
2.5°	340.3	328.4	326.6	328.4	319.9	319.0	320.7	314.0	308.1	302.2	297.0
5°	566.8	542.2	534.6	524.4	499.0	490.5	488.8	461.7	435.4	410.7	387.8
7.5°	1101.4	1052.2	1025.8	975.0	896.9	862.2	843.4	754.3	671.2	595.7	527.0
10°	2196.9	2067.9	2005.1	1909.2	1738.6	1654.6	1593.6	1369.6	1148.9	936.8	750.2
12.5°	3205.8	3134.6	3042.0	2991.1	2714.5	2608.4	2507.4	2196.9	1860.9	1518.1	1177.8
15°	3967.0	3862.6	3764.2	3740.3	3523.1	3399.2	3287.2	2965.7	2566.0	2129.8	1667.4
17.5°	4414.1	4339.4	4246.1	4201.1	3946.6	3846.4	3719.1	3407.8	3019.1	2584.6	2047.5
20°	4849.4	4739.0	4607.6	4539.7	4258.0	4142.6	3998.2	3670.8	3259.3	2797.6	2260.6
22.5°	5247.4	5104.8	4918.2	4812.9	4496.5	4369.1	4207.9	3853.2	3407.8	2880.0	2278.3
25°	5594.5	5465.4	5216.9	5032.6	4659.3	4509.1	4321.6	3950.9	3461.2	2873.2	2218.1
27.5°	5660.6	5574.1	5350.9	5137.9	4716.2	4549.0	4354.7	3971.1	3423.9	2779.0	2056.0
30°	5621.6	5528.2	5349.3	5132.0	4692.5	4523.6	4321.6	3884.6	3277.8	2559.2	1759.0
32.5°	5527.4	5446.8	5233.0	5003.8	4575.4	4399.8	4186.7	3681.8	3027.5	2209.6	1294.1
35°	5360.2	5238.9	4981.0	4792.6	4389.5	4208.8	3948.2	3411.1	2653.4	1588.5	606.7
37.5°	5020.0	4902.1	4716.2	4542.2	4149.4	3936.4	3661.4	3034.4	1967.0	866.3	375.0
40°	4612.7	4510.8	4348.8	4179.8	3775.2	3530.0	3227.0	2371.7	1157.4	487.8	230.8
42.5°	4169.8	4064.6	3881.2	3684.4	3243.1	2984.3	2656.8	1535.0	610.1	287.7	125.6
45°	3029.3	2935.1	2801.8	2660.2	2404.8	2218.1	1787.0	806.1	337.7	152.8	62.0
47.5°	2073.0	1961.0	1714.9	1417.1	1148.9	982.6	739.1	349.7	173.0	76.3	36.5
50°	1137.8	1019.1	893.4	695.8	465.8	382.7	297.8	168.9	78.1	38.2	20.4
52.5°	279.1	246.9	225.7	207.9	164.6	148.5	125.6	70.4	35.7	21.2	14.5
55°	58.6	54.3	51.8	51.0	46.7	45.0	39.0	27.1	19.5	13.6	6.8
57.5°	17.0	16.2	17.0	17.0	17.0	16.2	16.2	11.8	11.0	6.8	4.2
60°	5.9	5.9	5.9	6.8	6.8	6.8	7.6	7.6	5.9	4.2	3.4
62.5°	2.5	2.5	2.5	3.4	3.4	4.2	4.2	4.2	3.4	3.4	2.5
65°	1.7	1.7	1.7	1.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5
67.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
70°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.5
77.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.5
80°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	1.7	1.7	1.7	1.7
82.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
85°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
87.5°	0.0	0.0	0.0	0.8	0.8	0.8	0.8	0.8	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4
2.5°	282.6	274.1	263.8	252.8	251.2	245.2	236.7	224.9	220.6	212.2	204.5
5°	354.6	331.8	308.1	286.8	280.0	270.7	255.4	234.2	220.6	205.3	192.6
7.5°	451.4	398.9	350.5	312.3	300.3	285.0	261.4	234.2	213.8	192.6	175.7
10°	580.4	473.5	390.3	328.4	308.9	288.5	257.1	224.0	200.3	175.7	157.8
12.5°	829.0	582.9	427.7	336.9	309.7	283.4	243.6	207.9	180.7	156.1	138.3
15°	1178.6	790.8	503.1	342.8	301.2	269.0	222.3	185.8	158.7	135.7	118.8
17.5°	1473.9	987.7	604.2	359.8	295.3	250.3	197.7	160.4	134.1	113.7	100.2
20°	1618.2	1076.0	650.0	362.3	278.3	222.3	168.9	133.2	110.3	93.3	81.4
22.5°	1601.2	1046.2	607.6	317.3	235.0	187.5	140.0	107.8	88.3	74.6	66.2
25°	1487.5	917.3	495.5	242.6	183.3	151.8	109.5	84.0	68.7	59.4	52.6
27.5°	1296.6	736.6	361.5	171.4	139.1	115.4	81.4	64.5	52.6	45.8	41.6
30°	998.7	470.9	207.9	123.0	101.0	82.2	61.0	46.7	39.8	35.7	32.2
32.5°	515.1	229.1	138.3	88.3	71.2	59.4	42.4	33.9	29.8	27.1	25.4
35°	282.6	163.0	95.9	56.9	45.8	38.2	28.8	23.7	22.1	20.4	20.4
37.5°	194.2	101.0	53.4	33.9	28.0	23.7	19.5	17.0	16.2	16.2	16.2
40°	112.0	53.4	30.6	21.2	17.8	16.2	13.6	12.7	12.7	12.7	13.6
42.5°	57.8	31.4	20.4	14.5	12.7	11.0	9.4	9.4	9.4	10.2	11.0
45°	33.9	21.2	13.6	9.4	8.6	7.6	6.8	6.8	7.6	8.6	9.4
47.5°	21.2	14.5	8.6	5.9	5.1	5.1	5.1	5.1	5.9	6.8	7.6
50°	14.5	7.6	5.1	3.4	3.4	3.4	3.4	4.2	5.1	5.9	6.8
52.5°	7.6	4.2	3.4	2.5	2.5	2.5	3.4	3.4	4.2	5.1	5.9
55°	4.2	3.4	2.5	2.5	2.5	2.5	2.5	3.4	4.2	5.1	5.9
57.5°	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.1
60°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	5.1
62.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
65°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	4.2	4.2
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	4.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	4.2
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4
75°	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	4.2
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
80°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
82.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
85°	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.4	3.4	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4
2.5°	200.3	193.4	186.7	186.7	183.3	178.2	176.5	171.4	168.0	166.3	164.6
5°	183.3	173.0	163.8	163.0	158.7	152.8	150.2	145.1	141.8	140.0	139.1
7.5°	163.8	153.6	144.2	142.6	139.1	134.9	132.4	128.2	126.5	124.7	123.8
10°	145.1	134.9	128.2	126.5	123.8	120.6	117.9	115.4	113.7	112.8	112.8
12.5°	126.5	118.8	112.8	111.2	109.5	106.9	105.3	103.5	102.6	102.6	102.6
15°	109.5	102.6	97.5	97.5	95.9	94.2	94.2	92.5	91.6	92.5	93.3
17.5°	92.5	87.4	83.2	83.2	82.2	81.4	81.4	81.4	82.2	83.2	84.9
20°	76.3	72.2	70.4	70.4	69.6	70.4	70.4	71.2	72.2	74.6	77.2
22.5°	62.0	59.4	57.8	58.6	58.6	59.4	60.2	62.0	63.7	66.2	68.7
25°	50.0	48.3	47.5	48.3	49.2	50.0	51.8	53.4	55.9	58.6	62.0
27.5°	39.8	39.0	39.0	39.8	40.8	42.4	45.0	46.7	49.2	51.8	55.1
30°	32.2	31.4	32.2	33.9	34.9	36.5	38.2	40.8	43.3	45.8	49.2
32.5°	25.4	26.3	27.1	28.0	28.8	31.4	33.0	34.9	37.4	39.8	43.3
35°	21.2	22.1	22.9	23.7	24.6	26.3	28.0	29.8	32.2	34.9	38.2
37.5°	17.0	17.8	18.6	20.4	21.2	22.1	24.6	25.4	28.0	29.8	33.0
40°	14.5	15.3	16.2	17.0	17.8	19.5	21.2	22.1	23.7	26.3	28.8
42.5°	11.8	12.7	13.6	14.5	15.3	17.0	17.8	19.5	21.2	22.9	24.6
45°	10.2	11.0	11.8	12.7	13.6	14.5	15.3	17.0	17.8	19.5	21.2
47.5°	8.6	9.4	11.0	11.0	11.8	12.7	13.6	14.5	16.2	17.0	18.6
50°	7.6	8.6	9.4	10.2	10.2	11.0	11.8	12.7	13.6	14.5	16.2
52.5°	6.8	7.6	8.6	8.6	9.4	10.2	11.0	11.0	11.8	12.7	13.6
55°	5.9	6.8	7.6	7.6	8.6	9.4	9.4	10.2	11.0	11.0	11.8
57.5°	5.9	5.9	6.8	6.8	7.6	7.6	8.6	9.4	9.4	10.2	11.0
60°	5.1	5.9	5.9	6.8	6.8	7.6	7.6	8.6	8.6	9.4	9.4
62.5°	5.1	5.1	5.9	5.9	6.8	6.8	7.6	7.6	7.6	8.6	8.6
65°	5.1	5.1	5.9	5.9	5.9	6.8	6.8	6.8	6.8	7.6	7.6
67.5°	4.2	5.1	5.1	5.9	5.9	5.9	5.9	5.9	6.8	6.8	6.8
70°	4.2	5.1	5.1	5.1	5.1	5.9	5.9	5.9	5.9	5.9	5.9
72.5°	4.2	4.2	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1	5.1
75°	4.2	4.2	4.2	4.2	4.2	5.1	5.1	5.1	5.1	5.1	5.1
77.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	3.4	3.4	3.4	3.4	3.4	4.2	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	2.5	2.5	2.5	2.5
87.5°	3.4	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212212

CATALOG NUMBER: LDSQA4A20935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	216.4	216.4	216.4	216.4	216.4	216.4	216.4	216.4
2.5°	162.0	160.4	162.0	160.4	160.4	157.0	159.5	157.8
5°	136.6	134.9	136.6	135.7	134.1	133.2	134.9	134.1
7.5°	122.2	120.6	122.2	122.2	120.6	119.6	121.4	120.6
10°	111.2	110.3	111.2	111.2	110.3	109.5	111.2	110.3
12.5°	101.8	101.0	102.6	102.6	101.8	101.8	103.5	101.8
15°	93.3	93.3	95.0	95.0	95.0	95.0	96.7	95.9
17.5°	84.9	86.6	88.3	89.1	89.1	89.1	90.8	90.8
20°	78.1	79.8	81.4	82.2	83.2	83.2	84.9	84.9
22.5°	70.4	72.2	74.6	75.5	76.3	77.2	79.0	79.0
25°	63.7	65.3	67.9	68.7	70.4	71.2	73.0	73.0
27.5°	56.9	59.4	61.0	62.8	63.7	65.3	67.1	67.1
30°	51.0	53.4	55.1	56.9	57.8	59.4	61.0	61.0
32.5°	45.0	47.5	49.2	51.0	52.6	53.4	55.9	55.9
35°	39.8	41.6	44.1	45.0	46.7	48.3	50.0	50.0
37.5°	34.9	36.5	38.2	39.8	41.6	42.4	44.1	45.0
40°	30.6	32.2	33.9	34.9	36.5	38.2	39.0	39.8
42.5°	26.3	28.0	29.8	30.6	32.2	33.0	34.9	34.9
45°	22.9	24.6	25.4	26.3	28.0	28.8	30.6	30.6
47.5°	19.5	21.2	22.1	22.9	23.7	24.6	26.3	26.3
50°	17.0	17.8	18.6	19.5	20.4	22.1	22.9	22.9
52.5°	14.5	16.2	16.2	17.0	17.8	18.6	19.5	20.4
55°	12.7	13.6	14.5	14.5	15.3	16.2	17.0	17.8
57.5°	11.0	11.8	12.7	12.7	13.6	13.6	14.5	15.3
60°	10.2	10.2	11.0	11.0	11.0	11.8	11.8	12.7
62.5°	8.6	8.6	9.4	9.4	9.4	9.4	9.4	9.4
65°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
67.5°	6.8	6.8	6.8	6.8	5.9	5.9	5.9	5.9
70°	5.9	5.9	5.9	5.9	5.1	5.1	5.1	4.2
72.5°	5.1	5.1	5.1	5.1	4.2	4.2	3.4	3.4
75°	4.2	4.2	4.2	4.2	4.2	3.4	3.4	3.4
77.5°	4.2	3.4	3.4	3.4	3.4	3.4	3.4	2.5
80°	3.4	3.4	2.5	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	1.7	1.7	1.7	1.7
85°	2.5	1.7	1.7	1.7	1.7	1.7	1.7	1.7
87.5°	1.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)