

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212238

Luminaire Tested: **LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2004.4 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	21642	21642	21642
5°	48438	20353	14577
10°	189972	17825	11490
15°	412394	14432	9999
20°	615216	10691	9031
25°	800201	7536	7856
30°	895165	5067	6868
35°	805596	2980	5830
40°	657450	2036	5096
45°	377497	1384	4137
50°	110411	1055	3481
55°	12752	844	2888
60°	2732	969	2344
65°	917	917	1605
70°	878	1133	1133
75°	749	1497	1160
80°	0	2232	1116
85°	0	4446	1223

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.0	1.6
10°-20°	274.4	13.7
20°-30°	654.5	32.7
30°-40°	690.8	34.5
40°-50°	313.3	15.6
50°-60°	27.5	1.4
60°-70°	5.7	0.3
70°-80°	3.8	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.9	47.9
0°-40°	1651.7	82.4
0°-60°	1992.5	99.4
0°-90°	2004.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2004.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	223	223	223	223	223	
5°	498	365	209	161	150	89
15°	4112	1446	144	99	100	1196
25°	7486	1991	70	60	74	3401
35°	6812	550	25	34	49	4207
45°	2755	78	10	19	30	2184
55°	76	12	5	11	17	151
65°	4	4	4	8	7	5
75°	2	2	4	5	3	2
85°	0	2	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4
2.5°	332.0	334.0	325.0	326.1	317.0	321.0	318.0	309.9	303.9	293.9	289.9
5°	498.1	501.1	481.0	475.0	453.9	453.9	444.7	423.6	404.5	381.5	365.3
7.5°	910.7	922.8	862.4	817.2	750.8	734.6	703.4	631.0	571.6	511.2	466.0
10°	1931.2	1909.0	1784.3	1681.5	1510.5	1447.2	1362.6	1154.3	963.0	772.8	623.9
12.5°	3045.3	3116.6	2876.2	2792.6	2521.9	2464.5	2284.4	1944.2	1621.2	1285.1	987.2
15°	4111.9	4133.0	3922.6	3786.9	3456.8	3382.3	3160.9	2761.4	2326.7	1857.7	1446.1
17.5°	4968.3	5052.9	4743.9	4598.0	4169.2	4049.5	3788.9	3302.9	2818.7	2306.5	1818.4
20°	5967.6	5989.8	5623.5	5342.6	4782.1	4600.0	4288.0	3685.2	3108.5	2524.0	2019.7
22.5°	6876.3	6871.3	6400.3	6003.9	5294.3	5076.9	4691.5	3977.0	3306.8	2620.5	2038.8
25°	7486.2	7502.2	6998.1	6529.1	5658.7	5364.8	4930.0	4129.1	3374.2	2617.5	1990.6
27.5°	7811.2	7795.1	7254.7	6753.5	5792.5	5463.4	4991.4	4134.1	3312.8	2514.9	1845.6
30°	8002.4	7787.1	7210.4	6690.1	5701.9	5363.7	4883.8	3975.0	3108.5	2285.4	1587.0
32.5°	7491.2	7407.6	6905.5	6353.0	5390.0	5054.8	4580.8	3636.9	2784.6	1934.1	1137.1
35°	6811.9	6814.9	6324.9	5808.6	4900.9	4609.0	4120.0	3225.4	2389.1	1344.5	549.5
37.5°	6099.4	6109.5	5643.5	5163.6	4355.4	4048.5	3590.6	2756.3	1718.9	684.3	331.1
40°	5198.8	5219.9	4818.4	4432.9	3687.2	3391.4	2982.8	2086.1	961.0	382.4	224.4
42.5°	4247.8	4274.0	3917.6	3575.5	2941.6	2698.1	2335.7	1292.1	477.0	247.5	131.8
45°	2755.4	2830.8	2566.1	2422.3	2054.9	1910.0	1524.6	659.2	287.9	144.9	77.5
47.5°	1576.9	1577.9	1354.6	1084.9	889.6	773.9	604.8	299.9	168.0	81.5	47.3
50°	732.6	750.8	594.7	495.1	354.2	299.9	246.6	162.0	88.5	47.3	29.2
52.5°	213.3	225.4	204.3	185.2	157.0	139.9	119.7	79.5	46.3	28.2	18.1
55°	75.5	80.6	75.5	70.5	63.4	57.3	51.3	38.3	26.2	17.1	12.1
57.5°	31.2	32.2	31.2	30.2	28.2	28.2	25.2	21.1	16.1	11.0	8.1
60°	14.1	15.1	14.1	15.1	14.1	14.1	14.1	15.1	10.1	7.0	6.0
62.5°	6.0	7.0	7.0	7.0	7.0	8.1	8.1	7.0	6.0	5.0	4.0
65°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	3.1	3.1	3.1	3.1	3.1	3.1	2.0	2.0	3.1	3.1	3.1
72.5°	3.1	3.1	3.1	3.1	2.0	2.0	2.0	2.0	2.0	3.1	3.1
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.0	2.0	2.0
80°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.0	2.0	2.0
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4
2.5°	284.8	275.8	261.6	252.5	248.6	242.5	238.5	228.4	224.4	216.4	213.3
5°	350.2	332.0	311.0	293.9	282.8	270.8	252.5	232.5	222.4	209.3	202.3
7.5°	424.7	385.4	348.2	318.0	303.9	287.9	264.6	233.4	214.4	197.2	187.1
10°	519.3	438.8	380.4	332.0	311.0	289.9	261.6	225.4	201.2	181.2	170.0
12.5°	740.7	529.3	409.6	340.1	313.0	286.8	251.6	214.4	186.2	163.0	150.9
15°	1065.7	739.7	488.1	347.2	305.9	273.7	233.4	196.3	167.1	143.9	131.8
17.5°	1353.5	942.9	596.7	373.4	303.9	258.7	211.3	173.1	144.9	122.8	112.7
20°	1510.5	1049.7	669.2	389.4	294.9	235.4	186.2	149.9	122.8	103.7	94.6
22.5°	1513.5	1043.5	643.0	354.2	259.6	204.3	161.0	126.8	102.6	85.6	78.4
25°	1423.0	930.9	536.3	278.7	212.4	173.1	134.8	105.7	83.5	70.5	64.4
27.5°	1253.9	756.8	394.5	201.2	166.0	139.9	108.7	84.5	65.4	57.3	52.3
30°	986.2	493.1	230.4	149.9	128.8	107.7	82.5	59.3	51.3	45.3	41.3
32.5°	529.3	239.5	161.0	110.7	91.6	75.5	54.3	43.3	37.3	33.2	32.2
35°	276.7	175.1	107.7	70.5	58.4	49.3	37.3	30.2	27.2	25.2	25.2
37.5°	198.3	109.6	68.5	45.3	38.3	31.2	26.2	22.2	20.2	20.2	20.2
40°	117.8	67.4	41.3	29.2	25.2	22.2	19.1	16.1	16.1	16.1	16.1
42.5°	71.4	42.3	29.2	20.2	18.1	16.1	14.1	13.2	12.1	12.1	13.2
45°	44.3	29.2	19.1	15.1	14.1	12.1	11.0	10.1	10.1	10.1	11.0
47.5°	28.2	21.1	14.1	10.1	9.0	8.1	7.0	7.0	8.1	8.1	9.0
50°	21.1	13.2	9.0	7.0	6.0	6.0	5.0	6.0	6.0	7.0	8.1
52.5°	12.1	8.1	6.0	5.0	5.0	4.0	4.0	5.0	5.0	6.0	7.0
55°	8.1	6.0	5.0	4.0	4.0	4.0	4.0	4.0	5.0	5.0	6.0
57.5°	6.0	5.0	4.0	4.0	4.0	3.1	4.0	4.0	4.0	5.0	6.0
60°	5.0	4.0	4.0	4.0	4.0	3.1	3.1	4.0	4.0	5.0	5.0
62.5°	4.0	4.0	4.0	4.0	4.0	3.1	4.0	4.0	4.0	4.0	5.0
65°	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.0
67.5°	3.1	3.1	4.0	4.0	4.0	3.1	4.0	4.0	4.0	4.0	5.0
70°	3.1	3.1	3.1	4.0	4.0	3.1	4.0	4.0	4.0	4.0	4.0
72.5°	3.1	3.1	3.1	4.0	4.0	3.1	4.0	4.0	4.0	4.0	4.0
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0
77.5°	3.1	3.1	3.1	3.1	4.0	3.1	4.0	4.0	4.0	4.0	4.0
80°	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0
82.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
85°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4
2.5°	205.3	202.3	196.3	195.2	194.2	190.2	187.1	184.2	184.2	181.2	179.2
5°	190.2	185.2	178.1	175.1	174.1	169.1	165.1	162.0	161.0	157.9	155.0
7.5°	174.1	168.0	160.0	157.0	155.9	150.9	146.9	143.9	141.9	138.9	136.9
10°	157.0	149.9	142.9	139.9	138.9	133.8	130.8	127.8	125.8	123.8	121.7
12.5°	138.9	132.8	125.8	122.8	121.7	117.8	114.7	112.7	111.8	109.6	108.7
15°	120.8	114.7	108.7	106.7	105.7	102.6	100.6	99.7	98.6	98.6	97.6
17.5°	102.6	97.6	92.6	91.6	90.5	88.5	87.6	86.5	87.6	87.6	88.5
20°	85.6	81.5	77.5	77.5	76.4	75.5	75.5	75.5	77.5	78.4	80.6
22.5°	70.5	67.4	64.4	64.4	64.4	64.4	64.4	66.4	68.5	70.5	71.4
25°	58.4	55.3	54.3	54.3	54.3	55.3	56.4	58.4	60.4	62.3	64.4
27.5°	47.3	45.3	45.3	45.3	46.3	47.3	48.3	50.3	53.3	55.3	57.3
30°	38.3	37.3	37.3	38.3	39.3	40.3	42.3	44.3	46.3	48.3	50.3
32.5°	30.2	31.2	31.2	32.2	33.2	34.2	36.3	38.3	40.3	42.3	43.3
35°	25.2	25.2	26.2	27.2	28.2	29.2	31.2	33.2	34.2	36.3	38.3
37.5°	20.2	21.1	22.2	23.1	24.2	25.2	26.2	28.2	29.2	31.2	33.2
40°	17.1	18.1	19.1	20.2	20.2	22.2	22.2	24.2	25.2	27.2	29.2
42.5°	14.1	15.1	16.1	17.1	17.1	18.1	19.1	20.2	22.2	23.1	25.2
45°	11.0	12.1	13.2	14.1	15.1	16.1	16.1	18.1	19.1	20.2	22.2
47.5°	10.1	11.0	12.1	12.1	13.2	14.1	14.1	16.1	17.1	18.1	19.1
50°	8.1	9.0	10.1	11.0	11.0	12.1	13.2	14.1	15.1	16.1	16.1
52.5°	7.0	8.1	9.0	9.0	10.1	11.0	11.0	12.1	13.2	13.2	14.1
55°	7.0	8.1	8.1	9.0	9.0	10.1	10.1	11.0	11.0	12.1	12.1
57.5°	6.0	7.0	7.0	8.1	8.1	9.0	9.0	10.1	10.1	10.1	11.0
60°	6.0	6.0	7.0	7.0	8.1	8.1	8.1	9.0	9.0	9.0	10.1
62.5°	5.0	6.0	6.0	7.0	7.0	7.0	8.1	8.1	8.1	9.0	9.0
65°	5.0	6.0	6.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1
67.5°	5.0	5.0	6.0	6.0	6.0	6.0	7.0	7.0	7.0	7.0	7.0
70°	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
72.5°	4.0	5.0	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	5.0
75°	4.0	4.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
77.5°	4.0	4.0	4.0	5.0	5.0	5.0	5.0	5.0	5.0	4.0	4.0
80°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1
82.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1	3.1
85°	4.0	3.1	4.0	4.0	4.0	3.1	3.1	3.1	3.1	3.1	2.0
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212238

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	223.4	223.4	223.4	223.4	223.4	223.4	223.4	223.4
2.5°	177.2	175.1	176.1	176.1	174.1	173.1	173.1	174.1
5°	153.0	150.9	151.9	151.9	149.9	148.9	148.9	149.9
7.5°	134.8	132.8	133.8	133.8	131.8	131.8	131.8	131.8
10°	120.8	119.7	119.7	119.7	117.8	118.8	117.8	116.8
12.5°	107.7	107.7	107.7	107.7	106.7	107.7	106.7	106.7
15°	97.6	97.6	98.6	98.6	98.6	99.7	99.7	99.7
17.5°	89.6	90.5	91.6	92.6	92.6	93.6	93.6	93.6
20°	81.5	83.5	84.5	85.6	85.6	87.6	86.5	87.6
22.5°	73.5	75.5	76.4	77.5	78.4	79.5	79.5	80.6
25°	66.4	68.5	69.4	70.5	71.4	73.5	73.5	73.5
27.5°	59.3	61.4	62.3	64.4	65.4	67.4	67.4	67.4
30°	52.3	54.3	55.3	56.4	58.4	60.4	60.4	61.4
32.5°	45.3	48.3	49.3	50.3	52.3	54.3	55.3	55.3
35°	40.3	42.3	43.3	45.3	46.3	49.3	49.3	49.3
37.5°	35.2	37.3	39.3	40.3	41.3	43.3	44.3	45.3
40°	31.2	33.2	34.2	35.2	37.3	39.3	40.3	40.3
42.5°	27.2	29.2	30.2	31.2	32.2	34.2	34.2	34.2
45°	24.2	25.2	26.2	27.2	28.2	29.2	30.2	30.2
47.5°	20.2	22.2	22.2	23.1	24.2	26.2	26.2	27.2
50°	17.1	19.1	19.1	20.2	21.1	22.2	23.1	23.1
52.5°	15.1	16.1	17.1	17.1	18.1	19.1	20.2	20.2
55°	13.2	14.1	14.1	15.1	15.1	16.1	17.1	17.1
57.5°	11.0	12.1	13.2	13.2	13.2	14.1	14.1	15.1
60°	10.1	11.0	11.0	11.0	11.0	12.1	12.1	12.1
62.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
65°	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0
67.5°	7.0	7.0	7.0	7.0	6.0	6.0	6.0	6.0
70°	6.0	6.0	6.0	6.0	5.0	5.0	5.0	4.0
72.5°	5.0	5.0	5.0	5.0	5.0	4.0	4.0	4.0
75°	5.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1
77.5°	4.0	4.0	4.0	3.1	3.1	3.1	3.1	3.1
80°	3.1	3.1	3.1	3.1	3.1	2.0	2.0	2.0
82.5°	3.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0
85°	2.0	2.0	2.0	2.0	1.1	1.1	1.1	1.1
87.5°	2.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)