

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212250

Luminaire Tested: **LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2258.1 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	22843	22843	22843
5°	50558	21608	15190
10°	202406	18769	12680
15°	466552	14924	11133
20°	696443	10588	9948
25°	913473	7055	8851
30°	1048584	4452	7730
35°	961455	2862	6694
40°	788439	1859	5691
45°	457095	1288	4590
50°	129536	949	3798
55°	11873	878	3175
60°	1821	1008	2635
65°	481	963	1926
70°	595	1190	1473
75°	786	1572	1572
80°	0	2343	1172
85°	0	4668	1223

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	1.5
10°-20°	300.3	13.3
20°-30°	731.7	32.4
30°-40°	793.0	35.1
40°-50°	359.3	15.9
50°-60°	27.8	1.2
60°-70°	5.7	0.3
70°-80°	4.2	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1065.5	47.2
0°-40°	1858.5	82.3
0°-60°	2245.5	99.4
0°-90°	2258.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2258.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	236	236	236	236	236	
5°	520	384	222	168	156	94
15°	4652	1522	149	108	111	1352
25°	8546	2186	66	65	83	3895
35°	8130	556	24	38	57	5001
45°	3336	70	9	21	34	2634
55°	70	9	5	13	19	161
65°	2	3	4	8	8	3
75°	2	3	4	6	4	1
85°	0	3	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
2.5°	353.3	346.9	350.1	341.7	336.5	332.3	334.3	332.3	318.7	315.5	305.1
5°	519.9	510.4	510.4	492.7	473.8	462.2	462.2	448.7	419.3	405.7	383.6
7.5°	931.9	913.0	897.3	841.7	769.4	728.5	718.0	660.4	585.9	538.8	483.2
10°	2057.6	1978.9	1923.4	1778.8	1584.9	1464.2	1412.9	1213.8	976.9	798.7	637.4
12.5°	3460.0	3353.1	3255.7	3018.8	2740.0	2550.3	2448.6	2155.0	1694.9	1365.7	1022.0
15°	4651.9	4536.5	4421.3	4133.0	3838.4	3673.9	3487.3	3098.5	2490.4	2022.9	1522.0
17.5°	5629.8	5564.8	5446.4	5023.9	4652.9	4396.0	4202.1	3693.8	3068.1	2534.5	1967.4
20°	6755.5	6595.2	6383.4	5870.9	5363.6	5041.8	4769.2	4149.8	3426.6	2813.3	2203.3
22.5°	7703.1	7588.9	7284.8	6608.8	5862.5	5587.9	5254.5	4509.3	3657.2	2931.8	2230.5
25°	8545.9	8366.6	7985.0	7181.1	6417.0	5949.5	5540.7	4704.3	3742.0	2940.2	2185.5
27.5°	9039.5	8805.8	8357.1	7480.9	6608.8	6092.1	5639.2	4737.8	3688.5	2829.1	2020.9
30°	9373.9	8908.5	8412.8	7484.0	6548.0	6019.7	5550.1	4569.1	3466.3	2575.4	1744.2
32.5°	8822.5	8553.3	8079.4	7186.3	6216.9	5701.1	5234.6	4203.2	3119.4	2199.1	1213.8
35°	8129.8	7911.7	7499.8	6613.0	5720.0	5233.6	4738.9	3733.6	2667.6	1511.4	555.6
37.5°	7324.7	7153.9	6710.5	5900.3	5114.1	4638.3	4142.4	3182.3	1878.3	749.5	337.5
40°	6234.6	6090.0	5726.2	5075.3	4351.0	3898.3	3441.2	2380.4	1019.9	418.2	220.1
42.5°	5124.5	5002.9	4671.7	4108.9	3472.7	3099.5	2697.0	1450.7	507.4	263.1	122.7
45°	3336.4	3184.3	3006.2	2748.3	2433.9	2204.3	1729.5	700.2	300.8	146.7	70.3
47.5°	1912.9	1812.3	1519.9	1199.1	973.8	888.9	646.7	326.0	165.7	84.9	43.0
50°	859.5	794.5	666.6	543.0	393.0	307.2	261.0	163.6	81.8	46.1	29.4
52.5°	211.8	215.9	204.3	179.3	159.3	135.2	117.5	76.6	43.0	28.3	18.8
55°	70.3	71.4	64.9	61.8	56.6	52.4	48.2	34.6	26.2	25.2	9.4
57.5°	25.2	25.2	26.2	24.2	23.0	22.0	20.9	17.8	15.7	9.4	5.2
60°	9.4	9.4	9.4	10.4	10.4	10.4	11.5	10.4	7.3	5.2	4.2
62.5°	4.2	4.2	4.2	4.2	5.2	5.2	6.3	5.2	4.2	4.2	3.1
65°	2.1	2.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	3.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
2.5°	294.5	288.2	275.7	266.3	259.0	257.9	251.5	241.1	236.9	229.6	223.3
5°	362.7	346.9	327.0	308.2	294.5	287.2	265.2	245.2	233.7	222.2	211.8
7.5°	436.0	400.5	365.9	335.4	316.6	305.1	278.8	246.3	225.4	208.6	195.0
10°	528.2	455.0	395.1	347.9	322.8	307.2	275.7	236.9	210.7	190.8	177.2
12.5°	739.0	538.8	422.4	354.4	322.8	300.8	263.1	224.3	195.0	170.9	156.2
15°	1099.6	752.6	501.1	357.4	312.4	287.2	244.2	203.3	174.0	148.8	135.2
17.5°	1439.2	990.5	625.7	379.5	306.1	267.3	219.1	179.3	148.8	124.8	113.2
20°	1615.3	1109.0	695.0	396.3	295.6	242.1	189.7	153.0	123.7	102.7	93.3
22.5°	1619.5	1098.5	661.4	357.4	256.8	207.5	162.4	125.8	100.6	82.8	75.5
25°	1519.9	971.7	544.0	278.8	207.5	174.0	135.2	102.7	78.6	66.0	60.8
27.5°	1332.3	786.1	401.5	201.2	162.4	138.4	105.8	78.6	59.7	51.3	48.2
30°	1030.4	486.3	222.2	148.8	122.7	103.7	76.6	52.4	45.0	39.8	37.8
32.5°	511.5	238.0	157.2	105.8	83.9	66.0	48.2	38.8	34.6	31.5	30.5
35°	277.8	170.9	98.5	63.9	50.3	42.0	32.5	27.3	25.2	24.2	24.2
37.5°	193.9	101.7	59.7	38.8	31.5	28.3	23.0	19.9	18.8	18.8	18.8
40°	106.9	60.8	36.7	25.2	20.9	18.8	15.7	14.7	14.7	14.7	15.7
42.5°	61.8	37.8	25.2	17.8	14.7	13.6	11.5	10.4	11.5	11.5	12.6
45°	39.8	28.3	16.7	12.6	10.4	9.4	8.4	8.4	9.4	9.4	10.4
47.5°	28.3	19.9	11.5	8.4	6.3	6.3	6.3	6.3	7.3	8.4	9.4
50°	16.7	10.4	6.3	5.2	4.2	4.2	4.2	5.2	6.3	6.3	7.3
52.5°	9.4	6.3	4.2	4.2	3.1	3.1	4.2	4.2	5.2	6.3	7.3
55°	5.2	4.2	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	6.3
57.5°	4.2	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	5.2
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	5.2	5.2
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	5.2
65°	3.1	3.1	3.1	4.2	3.1	4.2	4.2	4.2	4.2	4.2	5.2
67.5°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.2
70°	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.2
72.5°	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.2
75°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
77.5°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
80°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
82.5°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
85°	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
87.5°	3.1	3.1	3.1	3.1	4.2	4.2	4.2	4.2	4.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
2.5°	221.2	213.9	208.6	206.4	202.3	203.3	200.2	198.1	191.8	191.8	187.6
5°	204.3	195.0	188.7	185.5	181.3	180.3	177.2	174.0	167.7	166.7	163.6
7.5°	186.5	177.2	169.8	166.7	162.4	161.4	157.2	155.1	149.9	148.8	145.7
10°	167.7	157.2	150.9	147.8	143.6	143.6	140.4	138.4	134.2	134.2	132.1
12.5°	147.8	138.4	134.2	130.0	127.9	127.9	125.8	123.7	120.5	121.6	120.5
15°	126.8	119.5	115.3	113.2	112.1	112.1	111.0	110.0	108.0	110.0	108.0
17.5°	106.9	101.7	98.5	97.5	96.5	96.5	96.5	97.5	96.5	98.5	98.5
20°	88.1	83.9	81.8	81.8	80.7	82.8	82.8	84.9	84.9	88.1	89.1
22.5°	72.4	69.1	68.1	68.1	68.1	70.3	71.4	73.4	74.4	77.6	79.7
25°	57.6	56.6	56.6	56.6	57.6	59.7	61.8	63.9	64.9	69.1	70.3
27.5°	47.2	46.1	47.2	47.2	48.2	51.3	53.4	55.6	57.6	60.8	62.8
30°	37.8	37.8	38.8	39.8	40.9	43.0	46.1	48.2	50.3	53.4	55.6
32.5°	30.5	31.5	32.5	33.5	33.5	36.7	38.8	42.0	43.0	46.1	48.2
35°	25.2	26.2	27.3	28.3	28.3	31.5	33.5	35.7	37.8	39.8	42.0
37.5°	19.9	20.9	23.0	24.2	24.2	27.3	28.3	30.5	32.5	34.6	36.7
40°	16.7	17.8	19.9	19.9	20.9	23.0	24.2	26.2	28.3	30.5	32.5
42.5°	13.6	14.7	16.7	17.8	17.8	19.9	20.9	23.0	24.2	26.2	27.3
45°	12.6	12.6	14.7	14.7	15.7	16.7	18.8	19.9	20.9	23.0	24.2
47.5°	10.4	11.5	12.6	13.6	13.6	14.7	15.7	16.7	17.8	19.9	20.9
50°	8.4	9.4	11.5	11.5	11.5	13.6	14.7	15.7	15.7	16.7	17.8
52.5°	8.4	8.4	9.4	10.4	10.4	11.5	12.6	13.6	13.6	14.7	15.7
55°	7.3	7.3	8.4	9.4	9.4	10.4	11.5	11.5	12.6	12.6	13.6
57.5°	6.3	7.3	8.4	8.4	8.4	9.4	10.4	10.4	11.5	11.5	12.6
60°	6.3	7.3	7.3	8.4	8.4	9.4	9.4	9.4	10.4	10.4	10.4
62.5°	6.3	6.3	7.3	7.3	7.3	8.4	8.4	9.4	9.4	9.4	9.4
65°	6.3	6.3	7.3	7.3	7.3	8.4	8.4	8.4	8.4	8.4	8.4
67.5°	5.2	6.3	6.3	6.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
70°	5.2	5.2	6.3	6.3	6.3	7.3	7.3	7.3	7.3	7.3	7.3
72.5°	5.2	5.2	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
75°	5.2	5.2	5.2	5.2	5.2	6.3	6.3	6.3	6.3	5.2	5.2
77.5°	4.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.2
80°	4.2	4.2	5.2	4.2	5.2	5.2	5.2	5.2	4.2	4.2	4.2
82.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.1	3.1
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	3.1	3.1	3.1	2.1
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	3.1	3.1	3.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212250

CATALOG NUMBER: LDSQA4A25930D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
2.5°	185.5	187.6	185.5	187.6	182.4	184.5	186.5	181.3
5°	161.4	159.3	160.3	162.4	158.2	159.3	160.3	156.2
7.5°	144.6	145.7	143.6	145.7	142.6	143.6	144.6	141.5
10°	131.1	132.1	131.1	132.1	128.9	131.1	132.1	128.9
12.5°	118.5	120.5	119.5	121.6	118.5	120.5	122.7	118.5
15°	109.0	111.0	110.0	112.1	110.0	112.1	114.2	111.0
17.5°	99.6	101.7	101.7	103.7	102.7	104.8	106.9	103.7
20°	90.2	93.3	93.3	95.4	95.4	96.5	99.6	96.5
22.5°	81.8	84.9	84.9	87.0	87.0	89.1	91.2	89.1
25°	72.4	76.6	77.6	79.7	79.7	81.8	84.9	82.8
27.5°	66.0	69.1	70.3	72.4	73.4	75.5	77.6	75.5
30°	57.6	61.8	62.8	64.9	66.0	69.1	70.3	69.1
32.5°	51.3	54.5	55.6	57.6	59.7	61.8	63.9	62.8
35°	45.0	48.2	49.3	51.3	52.4	55.6	57.6	56.6
37.5°	39.8	43.0	44.0	45.0	46.1	49.3	51.3	50.3
40°	34.6	36.7	37.8	39.8	40.9	43.0	45.0	45.0
42.5°	30.5	32.5	33.5	34.6	35.7	37.8	39.8	38.8
45°	26.2	28.3	29.4	30.5	31.5	32.5	34.6	33.5
47.5°	22.0	24.2	25.2	26.2	27.3	28.3	30.5	29.4
50°	18.8	20.9	20.9	22.0	23.0	24.2	26.2	25.2
52.5°	16.7	17.8	18.8	18.8	19.9	20.9	23.0	22.0
55°	14.7	15.7	15.7	16.7	16.7	17.8	18.8	18.8
57.5°	12.6	13.6	13.6	14.7	14.7	15.7	16.7	16.7
60°	11.5	11.5	12.6	12.6	12.6	13.6	13.6	13.6
62.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
65°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
67.5°	7.3	7.3	7.3	7.3	7.3	6.3	6.3	6.3
70°	6.3	6.3	6.3	6.3	6.3	5.2	5.2	5.2
72.5°	6.3	6.3	5.2	5.2	5.2	5.2	5.2	4.2
75°	5.2	5.2	5.2	5.2	4.2	4.2	4.2	4.2
77.5°	4.2	4.2	4.2	4.2	3.1	3.1	3.1	3.1
80°	4.2	3.1	3.1	3.1	3.1	3.1	3.1	2.1
82.5°	3.1	3.1	3.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)